

XLERATOReco[®] HAND DRYER



ENHANCED STANDARD FEATURES



Adjustable Speed and
Sound Control



Multi-Voltage Options:
110-120V Or 208-277V



500 Watts
No Heat



Externally Visible
Service LED

10

SECONDS¹
dry time

95%

COST SAVINGS
versus paper towels

1.7

WATT HOURS
energy use



XLERATOR^{eco}® HAND DRYER



MODELS: **XL - BW W GR C SB SI SP - ECO -H** (HEPA Filter) OPTIONS: **-1.1N** (Noise Reduction Nozzle) **-VOLTAGE** (See Chart)



XL-BW-ECO

White Thermoset Resin (BMC)

TESTED TO **PCR** DRY TIME: 10 SECONDS¹ ENERGY PER USE: 1.7 Wh¹
GUIDELINES



UL Environment published the first global Product Category Rules (PCR) for hand dryers which outlined industry consensus testing procedures to quantify environmental impact and performance. Third-party testing to these guidelines documents a product's environmental impact over its lifecycle. This impact is detailed in certified, internationally-recognized Environmental Product Declarations (EPDs). EPDs enable specifiers and buyers to make true apples-to-apples comparisons and more informed product selections. Excel Dryer received the industry's first certified EPDs.

FEATURES & BENEFITS

- ✓ 50% Longer Life
- ✓ Industry Leading 7-Year Limited Warranty
- ✓ 95% Cost Savings Vs. Paper Towels
- ✓ Helps Qualify For The Most LEED® Credits
- ✓ No Heat Technology
- ✓ Made In USA Certified®
- ✓ A Hygienic Hand Drying Solution
- ✓ Washable Pre-Filter

OPTIONS

- ✓ **Electrostatic HEPA (eHEPA®) Filtration System:** Removes 99.999% of viruses and 99.97% of potentially present bacteria at 0.3 microns from the airstream².
- ✓ **1.1" Noise Reduction Nozzle:** Reduces the sound level by 9 decibels by significantly decreasing air deflection noise while only increasing dry time by approximately 3 seconds.



XL-W-ECO

White Epoxy Painted



XL-GR-ECO-H

Graphite Textured Painted



XL-SP-ECO-H³

Custom Special Paint



XL-SI-ECO-H⁴

Custom Special Image



XL-C-ECO

Chrome Plated



XL-SB-ECO

Brushed Stainless Steel

PERFORMANCE

ADJUSTABLE SOUND LEVEL: 65-75 dB **ADJUSTABLE VELOCITY:** 13,000-20,000 LFM

FLOW RATE: 43-65 CFM

DIMENSIONS

Width 11 3/4" (298 mm) **Height** 12 11/16" (322 mm) **Depth** 6 11/16" (170 mm)

ELECTRICAL

VOLTS	AMPS	WATTS	HERTZ	
110-120V	4.3-4.5A	460-530W	50/60 Hz	UL US
208-277V	2-2.2A	425-500W	50/60 Hz	UL US
230V	2.2A	500W	50 Hz	CE

NOTE: Drawing 4.5 Amps or less allows for the installation of multiple XLERATOReco units on one circuit, significantly reducing installation costs and creating a return on investment of less than one year.

CERTIFICATIONS



WEIGHT

XL-BW-ECO: 15 lbs. (6.8 kgs.)

XL-SB-ECO: 16 lbs. (7.26 kgs.)

XL-W-ECO, XL-GR-ECO, XL-C-ECO, XL-SI-ECO, XL-SP-ECO: 17 lbs. (7.71 kgs.)

ACTIVATION

Automatic Sensor Operated

MOUNTING

Surface Mounted

SUGGESTED MOUNTING HEIGHTS

Men 45" (114 cm)

Women 43" (109 cm)

Accessible 37" (94 cm)

Note: Heights measured from floor to bottom of dryer.

ACCESSORIES

- ✓ Antimicrobial Wall Guards (#89B, #89W, #89S)
- ✓ XChanger® Paper Towel Dispenser Retrofit Kit (#40575, #40550)
- ✓ ADA-Compliant Recess Kit (#40502)

#40502



¹Dry time and energy use testing performed by SGS International on standard XLERATOR Hand Dryer with 0.8" nozzle to 0.25g or less of residual moisture, pursuant to the UL Environment Global Product Category Rules (PCR) for Hand Dryers. ²Based on testing performed by LMS Technologies, 2023. ³Special Paint powder-coated covers are available in many colors and textures. ⁴Exclusive digital image technology allows for the addition of company, school or team logos with any color, design or a "green message".



TIME TO THROW IN THE TOWEL®

EXCEL DRYER INC • 1.800.255.9235 • EXCELDRYER.COM

MAY 2024

24ECS1298