

CATALOGUE OF PRODUCTS

ROOF PANEL · FACADE · WALL · COLD STORAGE · ARCHITECTONIC
FACADE · COMPOSITE SLAB · PROFILED SHEETING · SELFSUPPORTING
TRAY · LIGHTING PANEL · ROOF



Hiansa

Grupo Hiemesa



HIANSA PRESENTATION

Hiansa is one of the leading manufacturers and suppliers of lacquered steel for roofs and façades, an essential application in industrial construction.

The advantages of shaped lacquered steel are its light weight, its mechanical strength, its ease of transportation and handling, its speed of assembly and the multiple aesthetic possibilities, which, in the case of Hiansa, include a variety of finishes and coverings: galvanised, lacquered (range of colours), aluzinc, etc.


At Hiansa, the most innovative designers will find a wide range of products and a suitable response to the technical, functional and aesthetic requirements of façade and roof closures for modern architecture.

Meanwhile, with the unstoppable technical progress of light metal closures, Hiansa has developed a comprehensive range of profiles guaranteeing the majority of solutions designed.

All our products are recognised for their competitive quality. This range does not just include profiles, but a wide range of finishes and special parts to finish the project: curved, drilled profiles, sandwich panels with rigid polyurethane and polyisocyanurate foam insulation, refrigeration panels, self-supporting trays and complementary natural lighting (translucid integrated modules), ventilation and insulation systems, composite slab sheeting, DECK coverings, finishes, etc.

PANEL CUB 2GR/3GR

ROOF PANEL WITH FLASHING



EXTERIOR FACE:
Pre-painted steel


INSULATION:
Polyurethane (PUR) and Polyisocyanurate (PIR)

INTERIOR FACE:
Pre-painted steel, centesimal aluminium, bitumen. cardboard

THICKNESS (mm):
30/40/50/60/80/100/120


USEFUL WIDTH 1000 mm

USE:
Sloping roof surfaces



PANEL AGRO 3GR

ROOF PANEL WITH FLASHING FOR AGRICULTURAL USE



EXTERIOR FACE:
Pre-painted steel


INSULATION:
Polyurethane (PUR)

INTERIOR FACE:
Polyester

THICKNESS (mm):
30/40/50


USEFUL WIDTH 1000 mm

USE:
Sloping roof surfaces



EASY CUB 3GR/5GR

ROOF PANEL WITHOUT FLASHING



EXTERIOR FACE:
Pre-painted steel


INTERIOR FACE:
Pre-painted steel

USEFUL WIDTH 1000 mm

INSULATION:
Polyurethane (PUR) and
Polyisocyanurate (PIR)


THICKNESS (mm):
30/40/50/60

USE:
Sloping roof surfaces



EASY AGRO 3GR/5GR

ROOF PANEL WITH UT FLASHING FOR AGRICULTURAL USE



EXTERIOR FACE:
Pre-painted steel


INTERIOR FACE:
Polyester

USEFUL WIDTH 1000 mm

INSULATION:
Polyurethane (PUR)


THICKNESS (mm):
10/30/50

USE:
Sloping roof surfaces



EASY ALU 3GR/5GR

ROOF PANEL WITHOUT FLASHING



EXTERIOR FACE:
Pre-painted steel


INTERIOR FACE:
Centesimal aluminium

USEFUL WIDTH 1000 mm

INSULATION:
Polyurethane (PUR) and
Polyisocyanurate (PIR)

THICKNESS (mm):
10/30

USE:
Sloping roof surfaces



EASY BOARD 3GR/5GR

ROOF PANEL WITHOUT FLASHING



EXTERIOR FACE:
Pre-painted steel


INTERIOR FACE:
Bituminous cardboard


USEFUL WIDTH 1000 mm

INSULATION:
Polyurethane (PUR) and
Polyisocyanurate (PIR)

THICKNESS (mm):
10/30

USE:
Sloping roof surfaces and DECK





EXTERIOR FACE:
Pre-painted steel

INTERIOR FACE:
Pre-painted steel

EXTERIOR COLOUR FINISH:
Aged Albero
Red teja
Slate

USEFUL WIDTH 1000 mm

INTERIOR COLOUR FINISH:
Standard colours
Wood finish

INSULATION:
Polyurethane (PUR) and
Polyisocyanurate (PIR)


THICKNESS (mm):
20/30/40

USE:
Sloping roof surfaces


EXTERIOR / INTERIOR FINISHES




RED TEJA
RAL 8004 MATT






AGED ALBERO



SLATE
RAL 7022



INTERIOR WOOD FINISH
ALSO AVAILABLE IN INTERIOR WHITE



DIE-CUT RIDGE TILE




SILHOU




DIE-CUT OVER WALL CLOSURE



FLAT RIDGE TILE




GUTTER



DIE-CUT ON-WALL CLOSURE



TYPE "A" SIDE CLOSURE



GUTTER COVER



TYPE "C" SIDE CLOSURE




TYPE "B" SIDE CLOSURE



FACADE PANEL MPF/PRF/SML/LIS

FACADE PANEL



EXTERIOR / INTERIOR FACE:
Pre-painted steel

INSULATION:
Polyurethane (PUR) and
Polyisocyanurate (PIR)

USEFUL WIDTH 1100 mm


THICKNESS (mm):
35/40/50/60/80/100

USE:
Facades



MURO

WALL PANEL



EXTERIOR / INTERIOR FACE:
Pre-painted steel

INSULATION:
Polyurethane (PUR) and
Polyisocyanurate (PIR)

USEFUL WIDTH 1000 mm


THICKNESS (mm):
30/40/50

USE:
Facades, prefabricated huts,
false ceilings, refrigeration
chambers and subdivisions



FRIGO

REFRIGERATION PANEL



EXTERIOR / INTERIOR FACE:
Pre-painted steel

INSULATION:
Polyurethane (PUR) and
Polyisocyanurate (PIR)

USEFUL WIDTH 1100 mm


THICKNESS (mm):
60/80/100/120/140/160
180/200

USE:
Cold rooms or
internal divisions



HEXAGONA

LIGHTING PANEL WITH FLASHING




COMPOSITION:
Honeycomb polycarbonate

USEFUL WIDTH 1000 mm

THICKNESS (mm):


30

USE:
Roofs



HIANSAPLUS

LIGHTING PANEL WITH FLASHING



COMPOSITION:
Honeycomb polycarbonate

USEFUL WIDTH 1000 mm

THICKNESS (mm):


30

USE:
Roofs



POLIMER

LIGHTING PANEL WITHOUT FLASHING




COMPOSITION:
Honeycomb polycarbonate

USEFUL WIDTH 1000 mm

THICKNESS (mm):


30

USE:
Roofs



POLICLADD

LIGHTING PANEL WITHOUT FLASHING




COMPOSITION:
Honeycomb polycarbonate

USEFUL WIDTH 1000 mm

THICKNESS (mm):

35

USE:
Facades



The next generation of Sandwich Panels




PANELS WITH HIGH PERFORMANCE INSULATION TECHNOLOGY

Ultra is an innovated range of Sandwich Panels, featuring outstanding characteristics of Sustainability, Insulation and Fire safety.

Developed in collaboration with DOW and its V PLUS PERFORM™ panel insulation technology, Ultra helps create future-ready buildings by placing sustainability, energy-efficiency, and people at the heart of design.


ROOF PANEL CUB 3GR y EASY CUB 5GR ULTRA




ROOF PANEL TEJA ULTRA



FACADE PANEL MPRF / PERF / SMLS / LISO ULTRA




REFRIGERATION PANEL FRIGO ULTRA



MO -18 MINIONDA

MINIONDA PROFILED SHEET



FINISH:
Pre-painted/Galvanised

THICKNESS (mm):
Up to 1,2


USEFUL WIDTH 1064 mm

USE:
Facades
Roofs



MT-32 / MT-32 F

PROFILED SHEETS




FINISH:
Pre-painted/Galvanised

THICKNESS (mm):
Up to 1,2


USEFUL WIDTH 1000 mm

USE:
Facades
Roofs



MT - 42

PROFILED SHEETS



FINISH:
Pre-painted/Galvanised

THICKNESS (mm):
Up to 1,2


USEFUL WIDTH 1000 mm

USE:
Facades, Roofs and



MT - 52

PROFILED SHEETS



FINISH:
Pre-painted/Galvanised

THICKNESS (mm):
Up to 1,2


USEFUL WIDTH 895 mm

USE:
Facades, Roofs and
Deck Roofs



MT - 44 IBIZA

ARCHITECTURAL FACADES



FINISH:
Pre-painted

USEFUL WIDTH 1010 mm


THICKNESS (mm):
Up to 1,2

USE:
Facades



MT - 53 MALLORCA

ARCHITECTURAL FACADES



FINISH:
Pre-painted

USEFUL WIDTH
804/868/990mm


THICKNESS (mm):
Up to 0,8

USE:
Facades / Dropped ceiling



MT - 30 MENORCA

ARCHITECTURAL FACADES



FINISH:
Pre-painted

USEFUL WIDTH 325 mm


THICKNESS (mm):
Up to 1,0

USE:
Facades / Dropped ceiling



MT - 35 FORMENTERA

ARCHITECTURAL FACADES



FINISH:
Pre-painted

USEFUL WIDTH 314 mm


THICKNESS (mm):
Up to 0,8

USE:
Facades / Dropped ceiling



BANDEJA BAN 130.600

SELF-SUPPORTING TRAY




FINISH:
Pre-painted/Galvanised

THICKNESS (mm):
From 0,7 up to 1,2

USEFUL WIDTH 600 mm

USE:
Facades
Roofs



BANDEJA BAN 90.380

SELF-SUPPORTING TRAY



FINISH:
Pre-painted/Galvanised

THICKNESS (mm):
From 0,7 up to 1,2

USEFUL WIDTH 380 mm

USE:
Facades
Roofs



MT - 56 DECK

DECK ROOFS



FINISH:
Pre-painted/Galvanised

THICKNESS (mm):
From 0,7 up to 1,2

USEFUL WIDTH 952 mm

USE:
Deck roofs



MT - 68 DECK

DECK ROOFS



FINISH:
Pre-painted/Galvanised

THICKNESS (mm):
From 0,7 up to 1,2


USEFUL WIDTH 880 mm

USE:
Deck roofs



FORJADO MT - 60

COMPOSITE SLAB



FINISH:
Galvanised

USEFUL WIDTH 820 mm


THICKNESS (mm):
Up to 1,2

USE:
Composite slab



FORJADO MT - 76

COMPOSITE SLAB



FINISH:
Galvanised

USEFUL WIDTH 880 mm


THICKNESS (mm):
Up to 1,2

USE:
Composite slab



FORJADO MT - 100

COMPOSITE SLAB




FINISH:
Galvanised

USEFUL WIDTH 675 mm


THICKNESS (mm):
Up to 1,2

USE:
Composite slab



MT - 60 SE

PROFILED SHEETS



FINISH:
Pre-painted/Galvanised

THICKNESS (mm):
From 0.60 up to 1,2


USEFUL WIDTH 820 mm

USE:
Roofs and permanent formwork



MT - 76 SE

PROFILED SHEETS



FINISH:
Pre-painted/Galvanised

THICKNESS (mm):
From 0.70 up to 1,2

USEFUL WIDTH 880 mm


USE:
Roofs and permanent formwork

NON-OVERLAPPING
PROFILE
TRANSVERSELY



MT - 100 SE

PROFILED SHEETS



FINISH:
Pre-painted/Galvanised

THICKNESS (mm):
From 0.70 up to 1,2

USEFUL WIDTH 675 mm


USE:
Roofs and permanent formwork

NON-OVERLAPPING
PROFILE
TRANSVERSELY



COMPACT POLYCARBONATE

SKYLIGHT



COMPOSITION:
Compact polycarbonate

THICKNESS (mm):
1,0

AVAILABLE FOR:
MO-18, MT-32, MT-42 y MT-52


Other thicknesses to consult

USE:
Facades
Roofs



STANDARD ORGANIC COATINGS

There are 19 tones available in the range of colours with standard organic coatings on polyester, comprised of 17 solid colours and 2 different shades of metallic grey. The same range of colours is applied to other organic coatings, based on the environmental conditions and the building surroundings.



1000 Blanco ostra*




2000 Arena




2005 Tabaco*



3001 Verde claro*



9005 Negro Intenso



1006 Blanco pirineo



2002 Crema Bidasoa



3000 Verde Navarro



4000 Azul lago



4001 Azul cielo*



4009 Azul Baracaldo*



5001 Gris perla



7001 Rojo teja




7004 Rojo coral*



4002 Azul marino*



Ral 5008 Azul ardoise*



Ral 9006 Silver metallic



7002 Rojo Baztán



Ral 9007 Hiansa metallic

*These colours are always on request.

Contact our sales department for colours that are not in the standard range. After applying the most advanced printing techniques to print this catalogue, we cannot guarantee the absolute accuracy with reality due to the difference in media and printing system.



DISTRIBUTED BY:

Polígono Industrial Dehesa de las Cigüeñas
parcela A1
14420 VILAFRANCA DE CÓRDOBA (ESPAÑA)
Tel. +34 957 198 900
Fax +34 957 198 910

