

SEAMLESS SYSTEMS.

Increase control and efficiency with a complete LiftMaster® access solution.



HIGH-TRAFFIC PERFORMANCE

Continuous-duty motors in our **gate operators** are designed to meet the demands of commercial/industrial use.

ENTRANCE MANAGEMENT

Grant access to specified individuals with **credentialed receivers**.



24/7 REMOTE ACCESS

LiftMaster Cloud™-powered management and reporting.



TRAFFIC CONTROL

Customize a complete **Motorized Traffic Control System**, fully integrating an operator, barrier arm and traffic spikes.



CUSTOM-BUILT SOLUTIONS.

Find our recommended products below, with additional options for specific applications. Our dealers can help you find a system tailored to your exact needs.



Gate Operators	Safety Entrapment Protection	Access Control	Credential Controls	Traffic System
 <p>SL595UL Heavy-Duty AC Industrial Slide Gate Operator</p>	 <p>LMTBUL Monitored Through-Beam Photo Eyes</p>	 <p>CAPXL Connected Access Portal, High Capacity</p>	 <p>PPWR Credential Access Receiver</p>	 <p>12360 Manual Heavy-Duty Surface-Mount Traffic Spikes</p>
 <p>CSL24UL High-Traffic DC Commercial Slide Gate Operator with Battery Backup</p>	 <p>LMWEKITU Monitored Wireless Edge Kit</p>	 <p>CAP2D Connected Access Portal, 2-Door Controller</p>	 <p>PPLK1PH 1-Button Passport Lite Mini Keychain Proximity Remote Control</p>	 <p>LOOPDETLM Plug-In Loop Detector</p>
<p>LiftMaster Cloud™ Cloud-Hosted 24/7 Access Management</p>				
<p>ADDITIONAL OPTIONS</p> <ul style="list-style-type: none"> • SL585UL Industrial AC Slide Gate Operator • SL3000UL High-Traffic AC Commercial Slide Gate Operator • CSW24UL High-Traffic DC Commercial Swing Gate Operator with Battery Backup • MTS/MTF Fully Integrated Barrier Gate Traffic Spike Solution 	<ul style="list-style-type: none"> • WS5/WR5 Monitored Resistive Wraparound Edge (Square/Round) • L50 + L50E + L50CHAL Monitored Resistive Standard Edge Components • LMRRUL Monitored Retro-Reflective Photo Eye • CPSUN4G Commercial Protector System® Monitored Through-Beam Photo Eyes 	<ul style="list-style-type: none"> • LMMC-MINI ProxPoint® Plus Card Reader • CAPCELL Cellular 4G/LTE Modem with Wi-Fi® • PED42 Gooseneck Pedestal 	<ul style="list-style-type: none"> • LMPC2-ST ProxCard II® 	<ul style="list-style-type: none"> • RGL24LY Red/Green Traffic Light • MALED12 12 ft. LED Barrier Arm

AC gate operators feature **heavy-duty wormgear** motor design. DC operators feature **smooth start/stop** operation.

AC gate operators SL585UL and SL595UL include a built-in **Lockout/Tagout** feature, which restricts turning on the power to the operator while it's being serviced. This prevents accidents and meets **OSHA** requirements.

NONSTOP SERVICE.

Complete access solutions for safe and efficient operations.



LEARN MORE.

- Contact Your LiftMaster® Dealer
- Find a Dealer at LiftMaster.com
- 800.323.2276

© 2018 LiftMaster All Rights Reserved
300 Windsor Drive, Oak Brook, IL 60523
LiftMaster.com
UL® and the UL logo are trademarks of UL LLC © 2018 All Rights Reserved.
Wi-Fi® is a registered trademark of Wi-Fi Alliance
LMPAENBRTPAS 5/18



PRODUCT BROCHURE
COMMERCIAL AND INDUSTRIAL
TOTAL PERIMETER ACCESS SOLUTIONS



COMPREHENSIVE SOLUTIONS. RELIABLE PERFORMANCE.

LiftMaster® access solutions deliver industry-leading performance, safety and reliability. From commercial/industrial-grade operators to safety accessories and access management reports, our products offer best-in-class features that keep your facility operating smoothly.



CUSTOM SOLUTIONS
Our extensive line of operators and accessories can be configured for almost any application.


SYSTEMATIC SAFETY.

Beginning August 1, 2018, for a LiftMaster Slide Gate Operator to function and meet UL® 325 requirements, the operator will require a minimum of 2 independent monitored safety entrapment protection devices for each entrapment zone: 2 in the open direction and 2 in the close direction (inherent reversing system counts as 1 device).*

*Every installation is unique. It is the responsibility of the installer to ensure that all entrapment zones are protected with a minimum of 2 entrapment protection devices.




ULTRA-RELIABLE PERFORMANCE
Dependable products are engineered for uninterrupted operation.



SEAMLESS INTEGRATION
Products utilize advanced technology to work together as a comprehensive access system.



COMPREHENSIVE SERVICE
LiftMaster® Authorized Dealers are expertly trained to service and maintain your perimeter solution.



The above example is one of many installation possibilities and is for illustrative purposes only. For more information, visit DASMA.com.

A



Monitored Retro-Reflective Photo Eye (LMRRUL)

B



Monitored Wireless Edge Kit (LMWEKITU)

C



Wraparound Square Profile (WS5)

D



Monitored Small Profile Resistive Edge (S505AL)

THE BOTTOM LINE:

	VALUE
Fully integrated system: LiftMaster's full line of access solutions is tested to work together as a complete system.	SAVES NUISANCE EXPENSES DUE TO COMPATIBILITY ISSUES
Technologically advanced products: Utilize wireless technology available in our keypads, radios, remotes, dual-gate operators, loop detectors and safety edges.	SIMPLIFIES INSTALLATION, SAVING TIME AND MONEY
Unrivalled product experience: Intuitive access management solutions and user-friendly products are simple and easy to use.	KEEPS YOUR FACILITY MOVING EFFICIENTLY
Ultra-reliable performance: Our operators offer best-in-class features designed to extend gate and hardware life.	LASTING, WORRY-FREE OPERATION



CERTIFIED COMPLIANCE.

Just like you, we want your facility to be as safe as possible for your personnel and property. That's why we design our operators to meet UL 325 requirements.



LiftMaster