

# Automatic sliding door system

## ASSA ABLOY Hermetic

**ASSA ABLOY**  
Entrance Systems

The global leader in  
door opening solutions



The ASSA ABLOY Hermetic sliding door is especially designed for use in clean room environments where clean, hygienic, well-sealing doors are required

### **Sealed – Silent – Reliable**

ASSA ABLOY hermetically sealing sliding door system ASSA ABLOY Hermetic is especially designed for use in clean room environments, such as operating theatres, pharmaceutical production facilities, food preparation facilities, laboratories and other areas where clean, hygienic, well-sealing doors are required.

The ASSA ABLOY Hermetic system consists of operator, door and door frames. It is easy to install for both new construction and retrofit applications. Although the operator is small and slim in appearance, it is entirely suitable for the heaviest duty applications. During the installation the operator is programmed to comply with the customer's specific requirements.

### **Technical specifications**

Power supply	120 V AC -10% to 240 V AC +10%; 50/60 Hz
Power consumption	max. 250 W
Recommended max. door weight	200 kg
Clear opening	800 – 2500 mm
Opening and closing speed	variable up to 0.7 m/s
Hold open time	0 – 60 s
Ambient temperature	-20°C to +50°C
Relative humidity (non-condensing)	5% to 85%


### **No compromise on safety**

To permit safe passage between closing doors, the doors immediately reverse if an obstruction is detected, then resume their interrupted movement at low speed to check whether the obstruction has disappeared or not. If an obstruction is detected between opening doors and surrounding walls or interior fittings, the door immediately stops and then closes after a time delay.


The safety can be further improved by using a ASSA ABLOY presence detection system. People or objects in the doorway are detected and the door is then prevented from closing until it is safe to do so. A convenience battery is available as an accessory. This is a standby supply, which gives continued operation during a short power failure.

### **Self-monitoring**

The microprocessor has an integral self-monitoring device which detects any interference or faulty signals in door operation and takes necessary measures to ensure a safe operation. The electronics are grouped in plug-in units. Each unit is subjected to a programme of stringent quality tests before delivery.



### ASSA ABLOY Hermetic-L Left opening shown, right opening mirror image



DW = Door leaf width    COW = Clear opening width  
CL = Cover length    COH = Clear opening height

### Design

The operator cover is designed to prevent collection of dust and is easy to clean. The ASSA ABLOY Hermetic is tailored to different customer requirements. The motor, control unit and transmission are all assembled on the door sliding track. The movement is transmitted to the door leaf by means of a tooth belt. A linear actuator is used to lift the door leaf from closed position onto the sliding track.

The door leaf consists either of a core faced with plastic laminate to both sides or stainless steel on both sides. The door is hung on two plastic wheels, which together with the sliding track give exceptionally smooth and silent operation. The sealing against the wall is made by a rubber seal. A flat rubber gasket is fitted to the underside of the door to seal against the floor. This will give full ASSA ABLOY Hermetic seal. The doors can be delivered with lead for radiation protection. Window, mechanical lock and earthing kit are other options. The door can also be manually opened by means of handles on both sides of the door. To make the manual opening easier, a push & go function will automatically control the opening and closing of the door.

### Models

**ASSA ABLOY Hermetic-R** Single slide, right hand  
**ASSA ABLOY Hermetic-L** Single slide, left hand

### Standard equipment

- Electronic control unit with plug-in connections and power supply
- Door leaf faced with plastic laminate to both sides, including sliding track and handles for manual opening

### Accessories and Options

- Cover:
- clear anodized aluminium (other anodizing optional)
  - paint finished in colour according to RAL chart
- Programme selectors
- Convenience battery
- ASSA ABLOY approach and presence sensors
- Electromechanical locking device
- Manual open/close impulse
- Full (bed) and partial (nurse) opening
- Interlocking between operators
- Key switch
- Limit switch for indication of closed door
- ASSA ABLOY Automatic Door systems:
- Door leaf in optional laminates and in stainless steel
  - Reveal plate system consisting of a lining, faced with laminate in optional colours or stainless steel designed to cloak the door opening on both sides
  - Window in the door leaf
  - Mechanical cylinder lock
  - Earthing of door leaf and frame
  - Handle on one side only - outside or inside

This equipment should be installed, regularly inspected, maintained and serviced by trained and authorized personnel. Preventive maintenance plans are highly recommended for a proper and safe operation. Talk to your ASSA ABLOY Entrance Systems representative to learn more about our service offering!