


Chevron Maple



Porcelain Pavers


With a delicate gray grain with contrasting shades of gray, Chevron Maple porcelain pavers feature an elegant and classic herringbone design, a high-tech alternative to reclaimed natural wood. It replicates the appearance of natural wood but without the disadvantages of fading, twisting, warping, and poor fire resistance inherent in real wood.

Tile Tech® hardscape systems provide architects and design professionals with a complete solution to transform any roof deck, walkway, driveway, courtyard, or patio into beautiful, useful spaces. Embracing USGBC LEED standards, our paving products boast a composition that includes 35% pre-consumer recycled materials. With no traces of Volatile Organic Compounds (VOC) and a Solar Reflectance Index (SRI) of ≥ 32 , porcelain pavers emerge as an eco-friendly choice that goes beyond conventional paving solutions.




Specifications

Available Sizes (Rectified)



15-1/2" x 47-1/2"
394 x 1207 mm

Color and Shade Variation



V3
Moderate variation



LEED Opportunities

- Recycled Content:
MR Credit 4.1 and 4.2 (2 LEED pts.)
- Regional Materials (500 mi)
EQ Credit 4.2 (1 LEED pt.)
- Low Emmitting Materials
EQ Credit 4.2 (1 LEED pt.)
- Innovation in Design
ID Credit 1.1 - 1.4 (1-4 LEED pts.)
- Heat Island Effect (Non-roof)
SS Credit 7.1 (1 LEED pt.)

Shipping Details

- Packaging (24" x 24")
72 pcs. | 279 Sq.Ft. | 2,700 lbs./pallet
- Packaging (24" x 48")
32 pcs. | 256 Sq.Ft. | 2,350 lbs./pallet

Thickness:	3/4" 19 mm	
Weight:	9 lbs./Sq.Ft.	
Water Absorption:	Max. 0.05%	ISO10543-3
Static Load (Center)	≥1,840 lbf.	ASTM N/A, EN 12825
Bending Strength	3,300 lbs.	ASTM C-648, ISO 10545-4
Distribution Load	2,500 lbs.	ASTM N/A, EN 12825
Slip Resistant	R11	DIN51130
COF (Wet, Dry)	>0.60	ASTM C-1028-7, ISO N/A
Abrasion Resistant	Yes (Class 5)	ASTM C-1027, ISO 10545-6
Stain Resistant	Yes (Class 5)	ASTM C-1378, ISO 10545-14
Frost Resistant	Yes	ASTM C-1026, ISO 10545-12
Chemical Resistance	Yes	ASTM C-650, ISO 10545-13
Solar Reflectance (SRI)	50	
Rectified	Yes	

Full test reports and specification details available on our website.

