

Rhythm.

RT acoustic

Wellness by design.

T 02-318-3960-1
E contact@rtacoustic.com
W rtacoustic.com

Recycled PET Grid Baffles

Introducing Rhythm by Baffles the perfect acoustic solution for those looking for a decorative and functional addition to their space. These floating panels create a cloud-like effect that transforms any room. The minimalist design, featuring geometric shapes and clean lines, makes

Rhythm a statement piece that is sure to impress. Crafted from 100% polyester fiber, these panels are lightweight yet powerful sound absorbers. They are easy to install on ceilings, using minimal hardware. You can adjust the hanging height to target specific frequencies, or simply clip them to the wall for removable sound control.

Experience the beauty of design and acoustics with Rhythm by Baffles.



02 Rhythm



Classic

Recycled PET Grid Baffles

Introducing a modular suspended ceiling system with premium NRC performance

- Acoustic ceiling system
- 16 acoustic baffles panel
- Made from PET with up to 60% post - consumer recycled content
- Sound absorbing breathable surface
- Low VOC emissions



Recycled
PET Fiber



Sound
Absorption



Low VOC
(Low Phenol &
Formaldehyde)



High Resistance
to Fire



Breathable
Panel

Product Specification

Material	100% PET Felt
Recycled Content	60% min
Thickness	12 mm
Dimension (WxLxD)	1000 x 1000 x 200 mm
Flammability	EN 13501-1 : Class B - s1 , d0
Color Fastness to light	ISO 105 - B02 : Rating 6-7
Emission Data	TVOC Emission Rate : 0.021 mg/m ³ Formaldehyde Emission Rate : : 2 Qg/m ³
Attachment Method	Coatea wire rope 1.5 mm and Hardware
Accessibility	Yes , quick release cables
Installation	Yes , have installation manual

03 Rhythm



Pop

Recycled PET Grid Baffles

Introducing a modular suspended ceiling system with premium NRC performance

- Acoustic ceiling system
- 16 acoustic baffles panel
- Made from PET with up to 60% post - consumer recycled content
- Sound absorbing breathable surface
- Low VOC emissions



Recycled
PET Fiber



Sound
Absorption



Low VOC
(Low Phenol &
Formaldehyde)



High Resistance
to Fire



Breathable
Panel

Product Specification

Material	100% PET Felt
Recycled Content	60% min
Thickness	12 mm
Dimension (WxLxD)	1000 x 1000 x 200 mm
Flammability	EN 13501-1 : Class B - s1 , d0
Color Fastness to light	ISO 105 - B02 : Rating 6-7
Emission Data	TVOC Emission Rate : 0.021 mg/m ³ Formaldehyde Emission Rate : : 2 Qg/m ³
Attachment Method	Coatea wire rope 1.5 mm and Hardware
Accessibility	Yes , quick release cables
Installation	Yes , have installation manual

04 Rhythm



Jazz

Recycled PET Grid Baffles

Introducing a modular suspended ceiling system with premium NRC performance

- Acoustic ceiling system
- 16 acoustic baffles panel
- Made from PET with up to 60% post - consumer recycled content
- Sound absorbing breathable surface
- Low VOC emissions



Recycled
PET Fiber



Sound
Absorption



Low VOC
(Low Phenol &
Formaldehyde)



High Resistance
to Fire



Breathable
Panel

Product Specification

Material	100% PET Felt
Recycled Content	60% min
Thickness	12 mm
Dimension (WxLxD)	1000 x 1000 x 200 mm
Flammability	EN 13501-1 : Class B - s1 , d0
Color Fastness to light	ISO 105 - B02 : Rating 6-7
Emission Data	TVOC Emission Rate : 0.021 mg/m ³ Formaldehyde Emission Rate : : 2 Qg/m ³
Attachment Method	Coatea wire rope 1.5 mm and Hardware
Accessibility	Yes , quick release cables
Installation	Yes , have installation manual



Hiphop

Recycled PET Grid Baffles

Introducing a modular suspended ceiling system with premium NRC performance

- Acoustic ceiling system
- 16 acoustic baffles panel
- Made from PET with up to 60% post - consumer recycled content
- Sound absorbing breathable surface
- Low VOC emissions



Recycled PET Fiber



Sound Absorption



Low VOC (Low Phenol & Formaldehyde)



High Resistance to Fire



Breathable Panel

Product Specification

Material	100% PET Felt
Recycled Content	60% min
Thickness	12 mm
Dimension (WxLxD)	1000 x 1000 x 200 mm
Flammability	EN 13501-1 : Class B - s1 , d0
Color Fastness to light	ISO 105 - B02 : Rating 6-7
Emission Data	TVOC Emission Rate : 0.021 mg/m ³ Formaldehyde Emission Rate : : 2 Qg/m ³
Attachment Method	Coatea wire rope 1.5 mm and Hardware
Accessibility	Yes , quick release cables
Installation	Yes , have installation manual

Available colour




Stone
LRV : 45.83



Mist
LRV : 34.15



Graphite
LRV : 20.64



Rock
LRV : 15.97



Eggshell
LRV : 39.25



Sand
LRV : 31.79



Citron
LRV : 44.03



Teal
LRV : 10.88



Cobalt
LRV : 7.97



Amber
LRV : 41.39



Sunrise
LRV : 24.15



Rose
LRV : 9.34



Ruby
LRV : 8.97



Black
LRV : 2.21

** Please note that the colour of the actual product may differ from those shown in the illustrations.