



Simon 270

Make it better, simplify.

simon



Simon 270. Make it better, simplify.

The beauty of simplicity goes far beyond appearance.

The things that make our lives better are simple.

By simplifying, we eliminate excess to highlight what's essential.

Because to be simple is to be honest, intimate, and practical.

Sure, simplicity makes things easier, but it isn't easy to achieve.

At Simon, we've been chasing it for more than 100 years.

And today, we can tell you:

Make it better, simplify.

Simon 270.

Index

SPIRIT

Design - Usability	8
CLEAN schuko	12
Simplified connectivity	14
Product collection	16
Finishes	18

CONNECTIVITY

Feel the space	26
Simon iO architecture	28
iO devices	34
Simon iO app	42
Voice assistants	44

CHARGING SOLUTIONS


USB charging	48
Monoblocks	49

INSTALLATION

Simplified installation	51
Multiple frame-holder	54
Surface-mount installation	55
Element configuration	56
Sustainable packaging	58

COMPOSITIONS

Frames	62
Features	64
Article Numbers	66



SPIRIT

For better integration,
simplify the design.



For a better appearance,
simplify the concept.

ICON DESIGN



8

Simon 270 presents Icon, a reinvented design. With a neutral and unobtrusive design, it blends into any space, so it seems like it's been there all along.

Icon's design is authentically timeless, even the connected version.

MINIMA DESIGN



9



The best designs are the least designed. That's Minima. It has a smooth rocker and a CLEAN schuko that's level with the wall, for minimal intrusion and maximum functionality while resisting dirt.

One smooth and continuous surface where the joints are almost imperceptible. The maximum expression of minimalism.

For better use, simplify the mechanism.

Simplification means getting rid of the extras. That's why we've removed all unnecessary elements, reducing the frame thickness by up to 35% and removing all types of ridges. That way, the frame seamlessly integrates into the wall,

along with the mechanisms, socket outlets and even the other frames. The finishes and materials have been standardised, for a light but heavy-duty design on both the frames and the rockers.



100% TOUCH

Practicality and appearance aren't at odds. In this collection, the different control mechanisms have the same usability and **progressive touch functionality**. The entire rocker surface is used and has a very pleasant, **uniform feel** with a

short and precise stroke. Plus, their **100% touch** mechanism means the rockers return to their **original positions**, so they're always in **perfect order** and harmony.

For a better socket,
simplify its spirit.



CLEAN SCHUKO

The key to the elegance of the new Simon 270 CLEAN schuko is its simplicity. Its design goes beyond appearance to improve people's quality of life. CLEAN has reinvented the conventional socket format to incorporate a **flat surface** that's flush with the wall for total integration that keeps it **cleaner**.

MAGNETIC AUTO-COVER SYSTEM

The cleaning process for Simon 270 is as minimal as its design. Thanks to the **patented magnetic auto-cover system**, the cover automatically moves when visible plugs aren't in use. This prevents dirt from accumulating inside, **making it easier to clean and improving durability**.

SIMPLIFIED CONNECTIVITY


For better comfort,
simplify connectivity.

Connectivity for well-being. Simon 270 works perfectly with **Amazon Alexa, Hey Google**, and, of course, you **even without a HUB**. That way, you can talk to all the **Simon 270 electronic devices**,

as long as they're connected to your Wi-Fi, without needing an additional installation. But, if you prefer, you can also control them through the Simon iO smartphone app.



Available in:






Simon 270 is the result of more than a century of simplification. Its 100% touch mechanism is available in two minimalist designs.

Connected versions are also available, which are installed the same way as a conventional mechanism and are synchronized with your mobile phone through the Simon iO app or a voice assistant.







For a better appearance,
simplify the finishes.




WHITE




ALUMINIUM



TITANIUM




MATT BLACK




CHAMPAGNE



BRONZE



GOLD



COPPER


The 270 collection offers a range of colours and finishes intended to fit with any style. They blend in perfectly with any kind of materials, furniture or

décor. They're more than just part of your space, they help create your environment.




CONNECTIVITY

For better control,
simplify accessibility.



A space is only as alive as the people who live in it. Make **it connected, even without a HUB**. Simon 270 lets you create the right atmosphere for every moment, **controlling the natural or**





artificial lighting. Use standard wiring without buses or complex domotics boxes. For comfort, security and savings.





Connect to the Simon iO app and control your space. You don't even need a HUB. Just a router with a Wi-Fi connection is enough to create the atmosphere you need.



For better interaction,
simplify the connections.

- 1 iO Dimmer switch 
- 2 iO Socket 
- 3 iO Blinds 
- 4 iO Blinds 

- 5 iO Switch 
- 6 Blinds master (Central blinds control) 
- 7 Voice assistant 




Simplified connectivity without a HUB.

All the Simon 270 electronic devices are connected.

That makes them ideal for basic installations in your home, because they radically simplify connectivity. Just connect them to your Wi-Fi.

30



BENEFITS:

- All you need is iO devices with an integrated Wi-Fi connection, no HUB required*
- Interaction via the device, voice assistants and the Simon iO app
- Works with Hey Google and Amazon Alexa

* Up to 10 devices. Complete the connectivity with more features by adding a HUB.

FEATURES:

- Remote control of devices and presence simulation
- Blinds control
- Central blinds control
- Light dimming
- Control of plugged-in devices
- Additional features for your devices: power consumption control, switching-on ramps, pilot light signalling and timing


31

Discover much more at:



Better connectivity with HUB.

Complete your home's connectivity with more features by adding a HUB.



Besides all the features available without a HUB, you have:

BENEFITS:

- Complete experience customization
- Time scheduling
- Improved experience synchronization and speed
- Unlimited iO devices
- Keypads to launch experiences (p. 40)

* According to router availability.


FEATURES:

- **Experiences: Welcome - Everything off - Good morning - Sweet dreams...**
- **Time scheduling**
- **Remote control of devices and presence simulation**
- **Blinds control**
- **Central blinds control**
- **Lighting control**
- **2-way light switching**
- **Socket control**
- **Additional features for your devices: power consumption control, switching-on ramps, pilot light signalling and timing**

Discover much more at:



iO DEVICES - iO DIMMER SWITCH



USE

- Centre push - ON-OFF.
- Upper/lower push - gradually raise or lower the brightness.
- Held press - continuously raise or lower.
- 8 brightness levels - 4 lit signals with 2 brightness levels each.

MORE FEATURES

- Switching-on ramp configuration.
- Soft dimming.
- Minimum and maximum brightness customization.

COMPATIBILITY

The switch lets you manually dim the light brightness. A very practical feature that also helps reduce energy consumption. It also incorporates iO technology so you can activate it through the Simon iO App and voice assistants. It's compatible with any type of luminaire or technology.




Light bulb



LED Strip



Downlight



Modular luminaire

TRAILING & LEADING

3-wire phase cut

PWM

1-10V

DALI


iO DEVICES - iO BLINDS SWITCH

And then there was light. Just one switch can centralize the control of various blinds, shades, awnings, and curtains. But you can also control them individually from different switches.



Through the Simon iO app and voice assistants, you can set time schedules* or remotely simulate people's presence in your home.

* Function only available with HUB or Voice assistants.





The Simon 270 iO switch lets you control the load of a motor, light, or anything else you want. Using the Simon iO App and voice assistants,

you can **schedule turning-on times** to avoid unnecessary light use, or delay turning on and off.



Simon 270 is available for various **socket outlets** and socket shapes. The Icon design has connected versions that incorporate iO technology. With the Simon iO App, you can analyse **light consumption**.


And with voice assistants or the Simon iO HUB, you can schedule on and off times or associate them with customized experiences*.



* Function only available with HUB or Voice assistants.



iO MASTER DIMMER SWITCH
Dim the light in your rooms from more than one place.



iO MASTER BLINDS SWITCH
Centralise and switch all the blinds in your home.



iO MASTER SWITCH
Send simultaneous orders to other iO mechanisms.

All under your command. These mechanisms give you central control, even for different devices, just by pressing a rocker.

That way, you can, for example, dim lights or control blinds from different parts of your house... or all in one place.



For a better experience,
simplify command.



KEYPAD FOR FOUR EXPERIENCES




KEYPAD FOR TWO EXPERIENCES

Presenting the Master Experience Keypad.* Superior control to launch several actions at once, just by pressing a single rocker.


Configure it and enjoy a customized experience, with modes like Good Morning, Sweet Dreams, Presence simulation, Timed Experiences, and more.




*Only available with Simon iO HUB.



For better intuition,
simplify usability.




SIMON iO APP



43

Available in:



The Simon iO App is the definition of intelligence. It's an application that recognises all the iO devices in your home: blinds, switches, and thermostats.

It intuitively controls things like temperature and lighting, from your smartphone, no matter where you are.

VOICE ASSISTANTS

For better performance,
simplify communication.

To change your home's environment at will, all you have to do is ask. Your voice controls all the connected Simon iO devices.

Create routines and specific commands. Anything is possible. iO technology installation. **Works with Hey Google and Amazon Alexa.**



Available in:






CHARGING
SOLUTIONS

For better integration,
simplify the design.



USB CHARGING



USB A+C
3.1A



USB A+A
2.1A

Don't run out of battery. Always have a USB charging point nearby, for your smartphone, tablet and other devices, with a range of modular and monoblock versions combined with other features.


 **QUICKCHARGE**

Charging technology that recognizes the device type and allows fast charging for connected devices up to 18W, with type-A or type-C ports.

 **SMARTCHARGE**

USB charger that charges at the required amperage, in the safest, fastest, and most efficient way possible.

MONOBLOCKS



2-WAY SWITCH + USB A
2.1A



SOCKET + 2 USB

All for one and one for all. Monoblock modules are preconfigured kits that combine various features in a single block.

They're installed as a unit and don't require additional frames. The fusion of features allows a clean appearance with optimised dimensions.



INSTALLATION

For a better installation,
simplify the process.



SIMPLIFIED INSTALLATION


The simplification of Simon 270 includes the installation process, too. The electrical connections and mechanical fasteners have been improved, and they include an easy-to-place metal frame-holder.



MECHANISM

1. Ergonomic connection levers to facilitate installation and maintenance.
2. Electrical connections are fast, secure and reliable.
3. Double-entry terminals for bridging multiple mechanisms.

4. Outdoor installation diagram.
5. User-friendly coloured levers in the mechanisms.
6. All mechanisms include a rocker.



SOCKET OUTLET


1. Single-side wire input.
2. Fast terminal connection using screws.
3. Supplied with loosened screws.
4. Walls separating terminals.
5. Outdoor installation diagram.
6. All mechanisms include a pre-clipped cover.

SIMPLIFIED INSTALLATION



MULTIPLE FRAME-HOLDER

For better results,
simplify alignment.



The **metal** multiple frame-holders ensure a **perfectly aligned** installation that guarantees safety and **robustness**. With precise snap-fit and **easy installation**, as well as rigid support for a perfect finish on the wall.

SURFACE MOUNTING

No walls are off limits. Simon 270 has **surface-mount boxes, which are flatter and more compact**, perfect for walls that don't allow recessed mounting or spaces where an industrial appearance is desirable.







MECHANISM



FRAME + ROCKER
OR FRAME-HOLDER



FRAME-HOLDER



The whole collection is made up of three main elements: the mechanisms, the frames and the frame-holders.

Both the frames and frame-holders are modular, so they can be configured with the desired features.

For a better planet, simplify the packaging.

Simplification also means minimising environmental impact. That's why we've removed the plastic from all the packaging in the collection. For the first time, they're printed with less ink, with only small

details in blue, avoiding single colour printing. Plus, they're made with 100% recycled materials. A new concept that's simpler, more honest, and more environmentally friendly.





COMPOSITIONS


For better versatility,
simplify customization.



The Simon 270 collection offers infinite possibilities. Customize the modules however you want. You can combine features using the available frames.

Create the composition that works best for your space's needs.


Minima Design Frames



62

You can exchange the switches for other features in the collection: socket outlets, USB, master switches, dimmable, blinds or iO switches...

Icon Design Frames



63

Mechanisms

MINIMA



Switch / 2-way switch
Intermediate Switch /
Push-button switch

iO switch

Light symbol

Bell symbol

Indicators

ICON




Switch / 2-way switch
Intermediate Switch /
Push-button switch

iO switch

Light symbol

Bell symbol

Indicators




Pull-cord
switch

Card reader

Buzzer

Socket outlets

SOCKET OUTLETS



CLEAN schuko

Socket outlet

Two-pole socket outlet

iO socket

USB CHARGING



Monoblock 2-way switch
+ USB

Monoblock CLEAN schuko
+ 2 USB

USB Type C + USB Type A

USB Type A + USB Type A

Lighting control and comfort

MINIMA



iO dimmer switch

iO blinds switch

Blinds switch

1-10V PWM DALI

ICON




iO dimmer switch

iO blinds switch

Blinds switch

Rotary dimmer

Master switches and keypads



iO Master Switch


iO Dimmer Switch

iO Master blinds switch

Two-Experience
iO Keypad

Four-Experience
iO Keypad

Multimedia



HDMI

USB

HDMI + USB

TV+ SAT



VGA + mini jack

RJ45

Fibre optics

Frames

FRAMES

FRAME SIZES	MINIMA DESIGN	MINIMA DESIGN, VERTICAL	ICON DESIGN
1 element 85x85 mm			
2 elements 156x85 mm			
3 elements 227x85 mm			
4 elements 298x85 mm			

MINIMA DESIGN

ART. NO.	FRAME	COLOURS	DESCRIPTION
27101610	-090 -091 -093 -094 -095 -096 -097 -098		Minima design frame, 1 element
27101620	-090 -091 -093 -094 -095 -096 -097 -098		Minima design frame, 2 elements
27101630	-090 -091 -093 -094 -095 -096 -097 -098		Minima design frame, 3 elements

ART. NO.	FRAME	COLOURS	DESCRIPTION
27110610	-090 -091 -093 -094 -095 -096 -097 -098		Minima design frame for CLEAN German socket outlet, 1 element
27110620	-090 -091 -093 -094 -095 -096 -097 -098		Minima design frame for CLEAN German socket outlet, 2 elements
27110630	-090 -091 -093 -094 -095 -096 -097 -098		Minima design frame for CLEAN German socket outlet, 3 elements
27110640	-090 -091 -093 -094 -095 -096 -097 -098		Minima design frame for CLEAN German socket outlet, 4 elements

ART. NO.	FRAME	COLOURS	DESCRIPTION
27191620	-090 -091 -093 -094 -095 -096 -097 -098		Minima design frame, 2 elements: 1 narrow module + 1 CLEAN German socket outlet
27191630	-090 -091 -093 -094 -095 -096 -097 -098		Minima design frame, 3 elements: 2 narrow modules + 1 CLEAN German socket outlet

ART. NO.	FRAME	COLOURS	DESCRIPTION
27190620	-090 -091 -093 -094 -095 -096 -097 -098		Frame for 2 elements: 1 CLEAN German socket outlet + 1 module
27190630	-090 -091 -093 -094 -095 -096 -097 -098		Frame for 3 elements: 1 CLEAN German socket outlet + 2 modules
27193630	-090 -091 -093 -094 -095 -096 -097 -098		Frame for 3 elements: 2 CLEAN German socket outlets + 1 module
27190640	-090 -091 -093 -094 -095 -096 -097 -098		Frame for 4 elements: 2 CLEAN German socket outlets + 2 modules

MINIMA DESIGN, VERTICAL

ART. NO.	FRAME	COLOURS	DESCRIPTION
27111620	-090 -091 -093 -094 -095 -096 -097 -098		Minima design frame, vertical, 2 elements
27111630	-090 -091 -093 -094 -095 -096 -097 -098		Minima design frame, vertical, 3 elements

ART. NO.	FRAME	COLOURS	DESCRIPTION
27192620	-090 -091 -093 -094 -095 -096 -097 -098		Minima design frame, vertical, 2 elements: 1 narrow module + 1 CLEAN German socket outlet
27192630	-090 -091 -093 -094 -095 -096 -097 -098		Minima design frame, vertical, 3 elements: 2 narrow modules + 1 CLEAN German socket outlet


ICON DESIGN

ART. NO.	FRAME	COLOURS	DESCRIPTION
27000610	-090 -091 -093 -094 -095 -096 -097 -098		Icon design frame, 1 element
27000620	-090 -091 -093 -094 -095 -096 -097 -098		Icon design frame, 2 elements
27000630	-090 -091 -093 -094 -095 -096 -097 -098		Icon design frame, 3 elements
27000640	-090 -091 -093 -094 -095 -096 -097 -098		Icon design frame, 4 elements

ART. NO.	FRAME	COLOURS	DESCRIPTION
27192610	-090 -091 -093 -094 -095 -096 -097 -098		Icon design frame for IP44 mechanisms, 1 element

ARTICLE NUMBERS

FRAME-HOLDERS



ART. NO.	FRAMES	DESCRIPTION
20000910-039		Frame-holder 1 element
20000920-039		Frame-holder 2 elements
20000930-039		Frame-holder 3 elements
20000940-039		Frame-holder 4 elements

SURFACE-MOUNT BOXES

STANDARD	COMPACT WITH FRAME
<p>For 1 element 85x85 mm For 2 elements 156x85 mm For 3 elements 227x85 mm</p>	<p>For 2 elements 156x85 mm For 3 elements 227x85 mm</p>

STANDARD

COMPACT WITH FRAME



ART. NO.	FRAME	DESCRIPTION
20000751	-090 -098	Surface-mount box 1 element
20000752	-090 -098	Surface-mount box 2 elements
20000753	-090 -098	Surface-mount box 3 elements



ART. NO.	FRAME	DESCRIPTION
20000811	-090 -098	Compact Surface-mount Box 1 element
20000821	-090 -098	Compact Surface-mount Box 2 elements
20000831*	-090 -098	Compact Surface-mount Box 3 elements

No frame-holder required

*Next release.

ARTICLE NUMBERS

Mechanisms

NARROW MODULE SWITCHES



ART. NO.	FRAME	DESCRIPTION	Max. intensity	Power supply	Terminal connection
20001101	-090 -091 -093 -094 -095 -096 -097 -098	Push-button Switch, narrow module	10 Ax	250Vac	Fast
20001201	-090 -091 -093 -094 -095 -096 -097 -098	Push-button 2-way switch, narrow module	10 Ax	250Vac	Fast
20001251	-090 -091 -093 -094 -095 -096 -097 -098	Intermediate push-button switch, narrow module	10 Ax	250Vac	Fast
20001150	-090 -091 -093 -094 -095 -096 -097 -098	Neutral push-button switch, narrow module	10 A	250Vac	Fast



ART. NO.	FRAME	DESCRIPTION	Max. intensity	Power supply	Terminal connection
20000951	-090	Monoblock 2-way switch Kit 10AX IP44	10 Ax	250Vac	Fast
20000952	-090	Monoblock push-button switch kit 10A IP44	10A	250Vac	Fast



ART. NO.	FRAME	DESCRIPTION	Max. intensity	Power supply	Terminal connection
20001151	-090 -091 -093 -094 -095 -096 -097 -098	Push-button switch with light symbol, narrow module	10A	250Vac	Fast



ART. NO.	FRAME	DESCRIPTION	Max. intensity	Power supply	Terminal connection
20001152	-090 -091 -093 -094 -095 -096 -097 -098	Push-button switch with bell symbol, narrow module	10A	250Vac	Fast



ART. NO.	FRAME	DESCRIPTION	Max. intensity	Power supply	Terminal connection
20001204	-090 -091 -093 -094 -095 -096 -097 -098	2-way switch with light indicator, narrow module	10 Ax	250Vac	Fast
20001160	-090 -098	Neutral push-button switch with light indicator, narrow module	10A	250Vac	Fast



ART. NO.	FRAME	DESCRIPTION	Max. intensity	Power supply	Terminal connection
20001161	-090 -098	Push-button switch with light symbol and light indicator, narrow module	10A	250Vac	Fast









ART. NO.	FRAME	DESCRIPTION	Max. intensity	Power supply	Terminal connection
20001102*	-090 -098	Pilot switch, narrow module	16 Ax	250Vac	Fast
20001134*	-090 -098	Two-pole pilot switch, narrow module	16 Ax	250Vac	Screw

*Next release.

ARTICLE NUMBERS




SWITCHES

ART. NO.	COLOURS	DESCRIPTION	Max. intensity	Power supply	Terminal connection
 20000101	-090 -091 -093 -094 -095 -096 -097 -098	Touch switch	10 Ax	250Vac	Fast
20000201	-090 -091 -093 -094 -095 -096 -097 -098	Touch 2-way switch	10 Ax	250Vac	Fast
20000251	-090 -091 -093 -094 -095 -096 -097 -098	Intermediate touch switch	10 Ax	250Vac	Fast
20000150	-090 -091 -093 -094 -095 -096 -097 -098	Neutral push-button switch	10 A	250Vac	Fast
 20000151	-090 -091 -093 -094 -095 -096 -097 -098	Push-button switch with light symbol	10A	250Vac	Fast
 20000152	-090 -091 -093 -094 -095 -096 -097 -098	Push-button switch with bell symbol	10A	250Vac	Fast
 20000204	-090 -091 -093 -094 -095 -096 -097 -098	2-way switch with light indicator	10 Ax	250Vac	Fast
20000160	-090 -098	Neutral push-button switch with light indicator	10A	250Vac	Fast
 20000161	-090 -098	Push-button switch with light symbol and light indicator	10A	250Vac	Fast
 20000102*	-090 -098	Pilot switch	16 Ax	250Vac	Fast
20000134*	-090 -098	Two-pole pilot switch	16 Ax	250Vac	Screw

*Next release.

ARTICLE NUMBERS

SPECIAL MECHANISMS

ART. NO.	COLOURS	DESCRIPTION	Power supply	Terminal connection
 20000806*	-090 -098	Bell (buzzer)	230Vac	Screw
 20000526	-090 -091 -093 -094 -095 -096 -097 -098	Card Reader 1 microswitch	10(1.5 ind)A	250Vac
20000550*	-090 -091 -093 -094 -095 -096 -097 -098	Card Reader 2 microswitches	10(1.5 ind)A	250Vac
 20000153*	-090 -098	Pull-cord push-button switch	10A	250Vac

71






*Next release.




Socket outlets

SOCKET OUTLETS

ART. NO.	COLOURS	DESCRIPTION	Max. intensity	Power supply	Terminal connection
 20000434	-090 -091 -093 -094 -095 -096 -097 -098	CLEAN schuko	16A	250Vac	Screw
 20000432	-090 -093 -098	CLEAN schuko	16A	250Vac	Screw
 20000472	-090 -098	CLEAN schuko	16A	250Vac	Fast
 20000431	-090 -098	Two-pole socket outlet	16A	250Vac	Screw

CHARGING SOLUTIONS

ART. NO.	COLOURS	DESCRIPTION	Outlet voltage	Max. intensity	Power supply	Terminal connection
 27191610	-090 -091 -093 -094 -095 -096 -097 -098	Monoblock 2-way switch + USB Kit Smartcharge 	5Vdc (USB)	10Ax (2-way switch) / 2.1A (USB)	250Vac (2-way switch) / 127-230Vac (USB)	Rapid and screw
 27190610	-090 -091 -093 -094 -095 -096 -097 -098	Monoblock CLEAN schuko + 2 USB Kit	5Vdc	16A	230Vac	Screw
 20000196	-090 -091 -093 -094 -095 -096 -097 -098	Double USB Charger A+A 3.1 A Smart 	5Vdc	3.1A	127-230Vac	Screw

ART. NO.	COLOURS	DESCRIPTION	Outlet voltage	Max. intensity	Power supply	Terminal connection
 20000096	-090 -091 -093 -094 -095 -096 -097 -098	Double USB Charger A+A 2.1 A	5Vdc	2.1A	127-230Vac	Screw
 20000296	-090 -091 -093 -094 -095 -096 -097 -098	Double USB Charger A+C 3.1 A Quick 	5-12Vdc	3A (5Vdc) / 2A (9Vdc) / 1.5A (12Vdc)	127-230Vac	Screw

Multimedia

TV SOCKETS

ART. NO.	COLOURS	DESCRIPTION	Max. intensity	Power supply	Terminal connection
20000486	-090 -091 -093 -094 -095 -096 -097 -098	Single R/TV+Sat Socket	Meets Spanish Common Telecommunications Infrastructures Regulations	Compatible with TDT	Screw
20000487	-090 -091 -093 -094 -095 -096 -097 -098	Intermediate R/TV+Sat Socket	Meets Spanish Common Telecommunications Infrastructures Regulations	Compatible with TDT	Screw
20000488	-090 -091 -093 -094 -095 -096 -097 -098	End R/TV+SAT Socket	Meets Spanish Common Telecommunications Infrastructures Regulations	Compatible with TDT	Screw

ART. NO.	COLOURS	DESCRIPTION
20000053	-090 -098	Cover for R/TV+Sat Socket

VOICE AND DATA

ART. NO.	COLOURS	DESCRIPTION
20000087	-090 -093 -098	Cover for RJ45 w/o connector

ART. NO.	COLOURS	DESCRIPTION
20000088	-090 -093 -098	Cover for double RJ45 w/o connector

ART. NO.	COLOURS	DESCRIPTION
20000187	-090 -091 -093 -094 -095 -096 -097 -098	Cover for RJ45 with connector

ART. NO.	COLOURS	DESCRIPTION
20000188*	-090 -091 -093 -094 -095 -096 -097 -098	Cover for double RJ45 with connector

ART. NO.	COLOURS	DESCRIPTION
20000546	-090 -098	Double Fibre Optics Socket

ART. NO.	COLOURS	DESCRIPTION	Terminal connection
20000094	-090 -091 -093 -094 -095 -096 -097 -098	HDMI connector 2.0 4K F-F	Female-Female

ART. NO.	COLOURS	DESCRIPTION	Terminal connection
20000095	-090 -091 -093 -094 -095 -096 -097 -098	HDMI Connector 2.0 4K+ USB Type A	Female-Female and Screw

ART. NO.	COLOURS	DESCRIPTION	Terminal connection
20000090	-090 -091 -093 -094 -095 -096 -097 -098	Type A USB Data connector	Screw

ART. NO.	COLOURS	DESCRIPTION	Terminal connection
20000091	-090 -098	VGA connector + minijack	Screw

*Next release.

Features

LIGHTING CONTROL



ART. NO.	COLOURS	DESCRIPTION	Power and load type	Power supply	Terminal connection
20000313	-090 -091 -093 -094 -095 -096 -097 -098	Rotary dimmer 2-wire PC	6-120W 25-100VA 6-60W	230Vac	Screw

COMFORT



ART. NO.	COLOURS	DESCRIPTION	Max. intensity	Power supply	Terminal connection
20001333	-090 -091 -093 -094 -095 -096 -097 -098	Blinds switch 3 positions, narrow module	10 Ax	250Vac	Fast



ART. NO.	COLOURS	DESCRIPTION	Max. intensity	Power supply	Terminal connection
20000333	-090 -091 -093 -094 -095 -096 -097 -098	Blinds switch 3 pos.	10 Ax	250Vac	Fast

Various

WIRE OUTLET



ART. NO.	COLOURS	DESCRIPTION
20000801	-090 -098	Wire outlet

BLIND COVER



ART. NO.	COLOURS	DESCRIPTION
20001800	-090 -091 -093 -094 -095 -096 -097 -098	Blind cover, narrow module



ART. NO.	COLOURS	DESCRIPTION
20000800	-090 -091 -093 -094 -095 -096 -097 -098	Blind cover

SWITCHES

ART. NO.	COLOURS	DESCRIPTION	Power and load type						Power supply	Terminal connection
			Incandescent halogen 230V	Electromagnetic Halogen Transformer	Electronic Halogen Transformer	Fluorescence	LED	Engines		
21001201	-090 -091	iO Simon switch narrow rocker	2,300W	2,300W	2,300W	500W	500W	2,300W	127-230Vac	Screw
	-093 -094 -095 -096 -097 -098									
21000201	-090 -091	iO Simon switch	2,300W	2,300W	2,300W	500W	500W	2,300W	127-230Vac	Screw
	-093 -094 -095 -096 -097 -098									

SOCKET OUTLETS

ART. NO.	COLOURS	DESCRIPTION	Max. intensity	Power supply	Terminal connection
21000432	-090 -091 -093 -094 -095 -096 -097 -098	iO Simon CLEAN schuko	16A (5A LED/CFL)	230Vac	Screw

LIGHTING CONTROL

ART. NO.	COLOURS	DESCRIPTION	Power and load type				Max. intensity	Power supply	Terminal connection
			Incandescent halogen 230V	Electromagnetic Halogen Transformer	Electronic Halogen Transformer	Fluorescence			
21001314	-090 -091 -093 -094 -095 -096	Dimmer switch PWM iO Simon LED Strip, narrow rocker					120W (12Vdc) / 240W (24Vdc)	12/24Vdc	Screw
21001316	-097 -098	Dimmer switch Dali iO Simon, narrow rocker						127-230Vac	Screw
21001317		Dimmer switch 1-10 V iO Simon narrow rocker						127-230Vac	Screw
21001321		Dimmer switch 3-wire PC iO Simon narrow rocker	240W	240W	240W	240W		127-230Vac	Screw
21000321	-090 -091	3-wire PC Dimmer switch iO Simon	240W	240W	240W	240W		127-230Vac	Screw
	-093 -094 -095 -096 -097 -098								





COMFORT

ART. NO.	COLOURS	DESCRIPTION	Max. intensity	Power supply	Terminal connection
21001333	-090 -091 -093 -094 -095 -096 -097 -098	iO Simon Blinds switch, narrow rocker	50-700VA (230Vac)	127-230Vac	Screw
21000333	-090 -091 -093 -094 -095 -096 -097 -098	iO Simon blinds switch	50-700VA (230Vac)	127-230Vac	Screw

MASTER SWITCHES

ART. NO.	COLOURS	DESCRIPTION	Power supply	Terminal connection
21011036	-090 -091 -093 -094 -095 -096 -097 -098	iO Simon Master Switch, narrow rocker	127-230Vac	Screw
21010036	-090 -091 -093 -094 -095 -096 -097 -098	iO Simon Master switch	127-230Vac	Screw

ARTICLE NUMBERS


	ART. NO.	COLOURS	DESCRIPTION	Power supply	Terminal connection
	21001121	-090 -091 -093 -094 -095 -096 -097 -098	iO Simon Master dimmer switch, narrow rocker	127-230Vac	Screw
	ART. NO.	COLOURS	DESCRIPTION	Power supply	Terminal connection
	21000121	-090 -091 -093 -094 -095 -096 -097 -098	iO Simon Master Dimmer Switch	127-230Vac	Screw
	ART. NO.	COLOURS	DESCRIPTION	Power supply	Terminal connection
	21001133	-090 -091 -093 -094 -095 -096 -097 -098	iO Simon Master blinds switch, narrow rocker	127-230Vac	Screw
	ART. NO.	COLOURS	DESCRIPTION	Power supply	Terminal connection
	21000133	-090 -091 -093 -094 -095 -096 -097 -098	iO Simon Master blinds switch	127-230Vac	Screw

80

EXPERIENCES

	ART. NO.	COLOURS	DESCRIPTION	Power supply	Terminal connection
	21021035	-090 -091 -093 -094 -095 -096 -097 -098	iO Simon 2 Experience Keypad	127-230Vac	Screw
	ART. NO.	COLOURS	DESCRIPTION	Power supply	Terminal connection
	21040035	-090 -091 -093 -094 -095 -096 -097 -098	iO Simon 4 Experience Keypad	127-230Vac	Screw

IO ACCESSORIES

	ART. NO.	DESCRIPTION	Max. Intensity	Power supply	Terminal connection
	10002890-039	Everything Off (DIN) Switch for iO Lighting Available with two-pole relay to turn off all non-connected devices. You can install one switch for each circuit you want to control.	16A	100-230Vac	Screw



www.simonelectric.com



SIMON HOLDING

Diputación, 390-392
08013 Barcelona
Tel. 651 761 336

**Technical Customer
Service**

Tel. 651 761 346
E-mail: sat@simon.es

Projects Departament

Tel. 651 761 346
E-mail: proyectos@simon.es

Customer Service

Tel. 651 761 314