LEDVANCE.COM

LEDVANCE

NEW: PANEL COMFORT GEN 2
INCLUDING ALL NEW ACCESSORIES

WHATEVER YOUR PROJECT – CEILINGS LOVE OUR PANELS

POWERED THROUGH
OUR NEW PORTFOLIO

THE NEW PANEL PORTFOLIO

SOLUTIONS FOR EVERY CEILING AND APPLICATION

Our panel portfolio is designed to match different project needs. From everyday installations to demanding projects, each family offers clear advantages in performance, flexibility and installation.

PANEL COMFORT GEN 2

FOR PROJECTS THAT REQUIRE **HIGHEST PERFORMANCE**

TUNABLE WHITE/ HCL TYPES AVAILABLE LATER IN 2026



PANEL COMPACT GEN 2

MAIN PANEL RANGE **FOR STANDARD APPLICATIONS**



LUMEN/WATT PERFORMANCE	175 lm/W	140 lm/W
LIFETIME	100 kh	75 kh
LUMEN OUTPUT	5 280 lm	4 200 lm
GUARANTEE	7 years	5 years

MULTI SELECT

MULTI SELECT LUMINAIRES

Easily switch colour temperatures and/or luminous flux on-site for maximum flexibility.

MULTI COLOUR FUNCTION

Choose from up to three different colour temperatures directly on the luminaire: warm, cool, or daylight white.

MULTI COLOUR





PANEL ECO GEN 3

PANEL RANGE
FOR
ESSENTIAL
LIGHTING



	110 lm/W
	50 kh
	3 600 lm
	3 years

MULTI LUMEN FUNCTION

Adjust luminous flux (lm) and brightness on-site to suit ceiling height or lighting requirements.

THE LEDVANCE PANEL PORTFOLIO AT A GLANCE

CLEARLY STRUCTURED. APPLICATION-DRIVEN. EASY TO UPGRADE.



PANEL COMPACT GEN 2

Standard office applications & public areas

– MULTI SELECT versions available
– Best value for great performance

PANEL INDIVILED GEN 2

Performance-driven office projects

– EVERLOOP design
– High efficiency, CRI 90
– Advanced controls

PANEL COMFORT GEN 2

Demanding project applications

– Excellent performance
– Tunable White/ HCL types available later this year

PANEL PROTECT

Special offices & public areas

– IP54 protection
– Heavy-duty applications
– Sensor ready

PANEL SURFACE

Refurbishment without ceiling changes

– Oversized dimensions
– Surface-mounted solution
– MULTI SELECT

QUICKLY IDENTIFY THE RIGHT PANEL FAMILY FOR EACH APPLICATION. SEE KEY ADVANTAGES AT A GLANCE TO SIMPLIFY SELECTION AND PLANNING.



COMPLETING THE PORTFOLIO: PANEL ADD-ONS & SERVICES

ACCESSORIES

Complete solutions for every installation

– Suspension kits
– Surface mounting frames
– Installation & safety accessories

PANEL PRINT SKY

Decorative luminous panels for special projects

– Design your luminaire panel

LEDVANCE PROJECT SERVICES

Specification & customised solutions for your project

See pages 12–15

NEW

PERFOR-
MANCE
CLASS

PANEL COMFORT GEN 2

PROJECT-READY PANEL FOR MAXIMUM PERFORMANCE

EXCELLENT PERFORMANCE
– Up to 175 lm/W efficacy
– Up to 5280 lm output for higher ceilings

COMFORTABLE RELIABILITY
– Lifetime up to 100000 h[1]
– 7-year guarantee[2]

LIGHTING CONTROL
– DALI-2
– Zigbee Direct and Zigbee 3.0

PROJECT READY
Ideal for offices, hospitality, and public areas – replaces existing T8/T5 recessed grid panels

GRID CEILING SIZES

MULTI LUMEN

600 mm × 600 mm or
625 mm × 625 mm or
675 mm × 675 mm

NEW: PANEL COMFORT MIX COMING SOON

1200 mm × 300 mm

[1] t[h]: L80/B10 @ 25 °C (T_a)
[2] Refer to www.ledvance.com/guarantee for precise conditions

SMART LIGHTING MADE EASY

DIRECT EASY FOR OPEN PLAN OFFICES WITH PANEL COMFORT

DIRECT EASY is the wireless lighting control solution for fast and effortless modernisation. Set up compatible LEDVANCE devices with just a simple swipe – no gateway, no additional control wiring and no complex IT infrastructure required. Fast to commission, easy to scale and designed for energy-efficient lighting.

SOLUTION COMPONENTS
EXAMPLE PRODUCT CONFIGURATION FOR OPEN-PLAN OFFICES

LED PANEL



PANEL COMFORT 600 ZB P 33W 840 U19
4099854885228

SENSOR

SENSOR DIRECT LS-PD-7 IR CI ZB
4099854476358

KINETIC SWITCH



SWITCH KINETIC DIRECT 4B BK ZB
4099854589836

OPEN PLAN OFFICE
APPLICATION IN PRACTICE

This application demonstrates how PANEL COMFORT, DIRECT EASY, sensors and wireless switches work together to create an efficient and flexible lighting solution for open-plan offices. Eighteen PANEL COMFORT luminaires are grouped into one lighting zone. Six ceiling-mounted sensors provide occupancy detection and daylight harvesting, ensuring automatic switching and consistent lighting levels, with 500 lux at workstations. Two wireless kinetic switches at the entrance doors provide convenient manual override whenever required.



FLOORPLAN

LED Panel | Sensor | Kinetic Switch

LIGHTING FUNCTIONS

ZONE CONTROL
Group luminaires into one lighting zone

MANUAL CONTROL
Wireless switching and dimming

OCCUPANCY DETECTION
Automatic control based on presence

DAYLIGHT HARVESTING
Automatic daylight harvesting for consistent lighting levels

ENERGY SAVING
Reduce energy consumption through sensor-based control

PANEL COMPACT GEN 2

VALUE CLASS

THE SMART CHOICE FOR STANDARD APPLICATIONS

WIDE RANGE
Available in multiple versions and sizes

MULTI SELECT
Select lumen and CCT at some types for flexible installation

APPLICATION READY
Ideal for offices, corridors, and public areas – replaces standard T8/T5 panels

GRID CEILING SIZES

600 mm × 600 mm or
626 mm × 625 mm

1 200 mm × 600 mm

1 200 mm × 300 mm

MULTI COLOUR

MULTI LUMEN

PANEL INDIVILED GEN 2

HIGH PERFORMANCE PANEL WITH EVERLOOP TECHNOLOGY

EVERLOOP
Easy replacement & upgrade of light source and driver

HIGH PERFORMANCE
Up to 140 lm/W, CRI 90 – brilliant, efficient light

LIGHTING CONTROL
– DALI-2
– Zigbee 3.0
– DIRECT EASY

MULTI LUMEN
Several lumen options per size – adapt to project needs

PERFOR-MANCE CLASS

Ideal design mix of PANEL INDIVILED with LINEAR INDIVILED, which was used for desk lighting here.

GRID CEILING SIZES & COLOURS

600 mm × 600 mm or
626 mm × 625 mm
Black and white



1 200 mm × 300 mm
Black and white

MULTI LUMEN

HEAVY DUTY
IP54 protection for safety in wet or dusty areas, low-profile fitting for narrow spaces

TOUGH APPLICATIONS
For offices near production, labs, healthcare & workshops – replaces T8/T5 panels in demanding environments

SENSOR READY
Individual sensor integration possible on request

PERFOR-MANCE CLASS

PANEL PROTECT

ROBUST PANEL FOR DEMANDING ENVIRONMENTS

MULTI LUMEN

600 mm × 600 mm or
625 mm × 625 mm

PANEL SURFACE

SURFACE-MOUNTED PANEL MADE FOR REFURBISHMENT

REFURBISHMENT READY
Oversized dimensions cover existing mounting marks

COMFORTABLE LIGHT
CRI 90 & SDCM < 3 for pleasant, glare-free lighting in offices and educational spaces

ENERGY SAVING
DALI-2/ZIGBEE DIRECT/ sensor versions

EMERGENCY READY
Central/decentral emergency lighting integration

VALUE CLASS

PRODUCT SIZES

MULTI COLOUR

MULTI LUMEN



674 mm × 674 mm
(replacing 4 × 18 W T8)

1 274 mm × 374 mm
(replacing 2 × 36 W T8)

1 574 mm × 374 mm
(replacing 2 × 58 W T8)

NEW PANEL ACCESSORIES

COMPATIBILITY OF PANEL ACCESSORIES WITH PANEL FAMILIES[1]

1. SURFACE MOUNT KIT H75/H50

NEW

- Pre-assembled frame with robust construction
- Easy installation with magnetic fixation system/side slide-in mounting for 1 200 mm version
- Material: aluminium, available in white or black

2. SURFACE MOUNT KIT VALUE

- Kit for tool-free mounting with corner clips
- Material: aluminium

3. SUSPENSION KIT

NEW

- Steel suspension wires with a pendant length of 1.5 m
- Easy installation with adjustable wire length and two carabiner hooks
- Single-point ceiling mounting for a clean appearance

4. RECESSED ANGLED HOLDER

NEW

- Metal bracket for securing panels above suspended ceilings
- Adjustable distance up to 112 mm
- Enables recessed installation flush with the ceiling surface

5. RECESSED MOUNT CLIPS

- Ceiling thickness: 10 to 20 mm
- Material: steel

6. RECESSED MOUNT FRAME

- Pre-assembled and ready to install
- Seamless recessed mounting
- Ceiling thickness: 8 to 30 mm
- Material: aluminium

7. RECESSED INVERTED FRAME

NEW

- Positions the panel 70 mm above the ceiling line for a distinctive recessed lighting effect
- One-piece metal frame
- Material: aluminium

8. COVER CIRCULAR CUT OUT

NEW

- Circular cut-out cover for square panels
- Material: sheet steel

9. EMERGENCY LIGHTING KIT COMPACT

NEW



- Plug-and-play system allows easy installation
- Battery technology: LiFePO4
- Integrated battery temperature control
- Compatibility with LEDVANCE luminaires tested and certified

[1] The accessories are compatible with the Panels in the respectively matching size. For details refer to the User Instructions.



COMPATIBILITIES AT A GLANCE

	Product name	GTIN (EAN)	PANEL TW/ BIOLUX	PANEL INDIVILED	PANEL PROTECT	PANEL COMFORT	PANEL COMPACT	PANEL ECO
1	Panel 600 Surface Mount Kit H75	4058075**472914**	✓	✓	✓	✓	✓	✓
	Panel 625 Surface Mount Kit H75	4058075**472938**	✓	✓	✓	✓	✓	✓
	Panel 1200x300 Surface Mount Kit H75 WT	4099854**910616**	✓	✓		✓	✓	
	Panel 600 Surface Mount Kit H75 BK	4058075**834330**	✓	✓	✓	✓	✓	✓
	Panel 625 Surface Mount Kit H75 BK	4058075**834354**	✓	✓	✓	✓	✓	✓
	Panel 1200x300 Surface Mount Kit H75 BK	4099854**912146**	✓	✓		✓	✓	
	Panel 600 Surface Mount Kit H50	4058075**826397**	✓		✓			
	Panel 625 Surface Mount Kit H50	4058075**826403**	✓		✓			
2	Panel 600 Surface Mount Kit H70 Value	4058075**402843**	✓		✓	✓	✓	✓
	Panel 625 Surface Mount Kit H70 Value	4058075**402867**	✓		✓	✓	✓	✓
	Panel 1200x300 SF Mount Kit H70 Value	4099854**018497**	✓			✓	✓	
	Panel 1200x600 Surface Mount Kit Value	4058075**389823**					✓	
3	Panel Suspension Kit G2	4099854**910500**	✓	✓[1]	✓	✓	✓	✓
4	Panel Recessed Angled Holder 4x	4099854**921216**	✓		✓	✓	✓	✓
5	Panel Recessed Mount Clips Value 4x	4058075**409859**	✓		✓	✓	✓	✓
6	Panel 600 Recessed Mount Frame	4058075**402881**	✓	✓	✓	✓	✓	✓
	Panel 625 Recessed Mount Frame	4058075**402904**	✓	✓	✓	✓	✓	✓
	Panel 1200x300 Recessed Mount Frame	4058075**472976**	✓	✓		✓	✓	
7	Panel 600 Recessed Inverted Frame H70	4099854**910425**	✓		✓	✓	✓	✓
	Panel 625 Recessed Inverted Frame H70	4099854**910449**	✓		✓	✓	✓	✓
8	Panel 600 Cover Circular Cut Out	4099854**910463**	✓		✓	✓	✓	✓
	Panel 625 Cover Circular Cut Out	4099854**910487**	✓		✓	✓	✓	✓
9	EL KIT COMP 55V 4W LI MT AT 3H WT	4058075**860711**		✓[2]		✓[2]	✓[2]	✓[2]
	ECO CLASS Surface Mount Clips 4x	4058075**403109**			✓	✓	✓	✓
	Panel Security Kit 4x	4058075**472990**	✓[3]		included[4]	included[4]	included[4]	included[4]
	Connector Box 5P L/N/E 4X G2	4099854**910555**			pre-installed	pre-installed	✓	✓
	Connector Box 5P L/N/E/D+/D- 4X G2	4099854**910593**		pre-installed	pre-installed	pre-installed	pre-installed[5]	
	EM CON BOX 105V 3W LI AT 3H TS	4099854**455933**			✓[2]			
	Panel 1200 Cable Extension Twist Lock	4099854**018510**				✓[6]		

[1] 4058075402928 will be phased out and replaced by 4099854910500 in September 2026 | [2] Not in combination with Surface Mount Kits
[3] DALI versions only | [4] Not for 625 versions | [5] Pre-installed for DALI versions | [6] Only for 1200 Edgelit versions (GEN1)

PANEL PRINT SKY

A NEW WORLD OF LIGHT

DESIGNED LIGHT EXPERIENCE
Individually printed luminous panels creating a natural-looking sky or featuring your own logo, photo, or design

HIGH-QUALITY PRINT
Premium printing realised in France for vivid, durable visuals

LIGHT CONTROL
DALI versions available for convenient dimming

TRY NOW.
DESIGN YOUR LIGHT.
Contact your local LEDVANCE sales representative.

PRODUCT SIZES

PANEL SKY INDIVIDUAL
600 mm × 600 mm or
625 mm × 625 mm

PANEL SKY SET4
4 × 600 mm × 600 mm or
4 × 625 mm × 625 mm

PANEL SKY SET6
6 × 600 mm × 600 mm or
6 × 625 mm × 625 mm

PANEL SKY SET9
9 × 600 mm × 600 mm or
9 × 625 mm × 625 mm

SPECIFICATION SERVICES FROM LEDVANCE

LEDVANCE PROJECT SERVICES

ALL INFORMATION ON SUCCESSFUL PROJECTS CAN BE FOUND HERE:

ledvance.com/project-services

Besides LEDVANCE catalogue-standard products, we provide tailored solutions that match the complexity and specific needs of your project.

YOUR PROJECT IS OUR BUSINESS

Your competent contact person at LEDVANCE accompanies you through your whole project.

Being your single source for all lighting products and components makes working with us even more comfortable.

TESTING

We test products in our own accredited labs. This ensures that the highest quality standards are maintained even after the specification has been finalised.

IP water chamber testing

IP dust chamber testing


Electromagnetic compatibility (EMC) testing

SPECIFICATION

EASY & FAST CHANGES	Add your specific setup and project requirements to our standard offerings.
MID-LEVEL COMPLEXITY	Choose from our SPECIFY range and your customised modification.
HIGH COMPLEXITY FROM SCRATCH	Completely customised products for your specific lighting needs.

ANY QUESTIONS? TALK TO US.

Are you interested in our services for your projects? Our project business experts are happy to advise you.

You can reach us at
contact@ledvance.com
or by phone on
+49 89 780673-600

PANEL COMFORT 600 GEN 2

1

PANEL COMFORT 600
Square recessed panel luminaires, for 600 x 600 mm ceiling systems

2

PANEL COMFORT 600 MULTI SELECT
Square recessed panel luminaire with Multi Lumen function, for 600 x 600 mm ceiling systems

3

PANEL COMFORT 600 DALI
Square recessed panel luminaires with DALI-2 technology, for 600 x 600 mm ceiling systems

4

PANEL COMFORT 600 ZIGBEE
Square recessed panel luminaire with Zigbee 3.0 technology, for 600 x 600 mm ceiling systems

Product name[2]	GTIN (EAN)	W	lm	lm/W	K	L80			L × W × H [mm] Ø × H [mm]	No.
PANEL COMFORT 600										
PL CMFT 600 P 22W 830	4099854**884092**	22	3740	170	3000	100000	110		595 x 595 x 34	1
PL CMFT 600 P 22W 840	4099854**884115**	22	3850	175	4000	100000	110		595 x 595 x 34	1
PL CMFT 600 P 22W 830 U19	4099854**884139**	22	3740	170	3000	100000	90		595 x 595 x 34	1
PL CMFT 600 P 22W 840 U19	4099854**884153**	22	3850	175	4000	100000	90		595 x 595 x 34	1
PANEL COMFORT 600 MULTI SELECT										
PL CMFT 600 P 30W ML 830 U19	4099854**884672**	30 / 26 / 21	5100 / 4420 / 3570	170	3000	100000	90		595 x 595 x 34	2
PL CMFT 600 P 30W ML 840 U19	4099854**884696**	30 / 26 / 21	5250 / 4550 / 3675	175	4000	100000	90		595 x 595 x 34	2
PL CMFT 600 P 30W ML 865 U19	4099854**884719**	30 / 26 / 21	5100 / 4420 / 3570	170	6500	100000	90		595 x 595 x 34	2
PL CMFT 600 P 30W ML 940 U19	4099854**884733**	30 / 26 / 21	4800 / 4160 / 3360	160	4000	100000	90		595 x 595 x 34	2
PANEL COMFORT 600 DALI										
PL CMFT 600 DA P 24W 830	4099854**884443**	24	3840	160	3000	100000	110	DALI-2, IoT	595 x 595 x 34	3
PL CMFT 600 DA P 24W 840	4099854**884481**	24	3840	160	4000	100000	110	DALI-2, IoT	595 x 595 x 34	3
PL CMFT 600 DA P 24W 830 U19	4099854**884504**	24	3840	160	3000	100000	90	DALI-2, IoT	595 x 595 x 34	3
PL CMFT 600 DA P 24W 840 U19	4099854**884528**	24	3840	160	4000	100000	90	DALI-2, IoT	595 x 595 x 34	3
PL CMFT 600 DA P 33W 830 U19	4099854**884900**	33	5280	160	3000	100000	90	DALI-2, IoT	595 x 595 x 34	3
PL CMFT 600 DA P 33W 840 U19	4099854**885020**	33	5280	160	4000	100000	90	DALI-2, IoT	595 x 595 x 34	3
PL CMFT 600 DA P 33W 865 U19	4099854**885082**	33	5280	160	6500	100000	90	DALI-2, IoT	595 x 595 x 34	3
PL CMFT 600 DA P 33W 940 U19	4099854**885129**	33	4950	150	4000	100000	90	DALI-2, IoT	595 x 595 x 34	3
PANEL COMFORT 600 ZIGBEE										
PL CMFT 600 ZB P 33W 830 U19	4099854**885204**	33	5280	160	3000	100000	90	Zigbee Direct, IoT	595 x 595 x 34	4
PL CMFT 600 ZB P 33W 840 U19	4099854**885228**	33	5280	160	4000	100000	90	Zigbee Direct, IoT	595 x 595 x 34	4
PL CMFT 600 ZB P 33W 940 U19	4099854**885280**	33	4950	150	4000	100000	90	Zigbee Direct, IoT	595 x 595 x 34	4

SUPERIOR CLASS PERFORMANCE CLASS VALUE CLASS

[1] Refer to www.ledvance.com/guarantee for precise conditions | [2] Available from September 2026

PANEL COMFORT 625 GEN 2

1

PANEL COMFORT 625
Square recessed panel luminaires, for 625 x 625 mm ceiling systems

2

PANEL COMFORT 625 MULTI SELECT
Square recessed panel luminaire with Multi Lumen function, for 625 x 625 mm ceiling systems

3

PANEL COMFORT 625 DALI
Square recessed panel luminaires with DALI-2 technology, for 625 x 625 mm ceiling systems

4

PANEL COMFORT 625 ZIGBEE
Square recessed panel luminaire with Zigbee 3.0 technology, for 625 x 625 mm ceiling systems

Product name[2]	GTIN (EAN)	W	lm	lm/W	K	L80			L × W × H [mm] Ø × H [mm]	No.
PANEL COMFORT 625										
PL CMFT 625 P 22W 830	4099854**885440**	22	3740	170	3000	100000	110		620 x 620 x 34	1
PL CMFT 625 P 22W 840	4099854**885464**	22	3850	175	4000	100000	110		620 x 620 x 34	1
PL CMFT 625 P 22W 830 U19	4099854**885488**	22	3740	170	3000	100000	90		620 x 620 x 34	1
PL CMFT 625 P 22W 840 U19	4099854**885501**	22	3850	175	4000	100000	90		620 x 620 x 34	1
PANEL COMFORT 625 MULTI SELECT										
PL CMFT 625 P 30W ML 830 U19	4099854**885785**	30 / 26 / 21	5100 / 4420 / 3570	170	3000	100000	90		620 x 620 x 34	2
PL CMFT 625 P 30W ML 840 U19	4099854**885808**	30 / 26 / 21	5250 / 4550 / 3675	175	4000	100000	90		620 x 620 x 34	2
PL CMFT 625 P 30W ML 865 U19	4099854**885822**	30 / 26 / 21	5100 / 4420 / 3570	170	6500	100000	90		620 x 620 x 34	2
PL CMFT 625 P 30W ML 940 U19	4099854**885846**	30 / 26 / 21	4800 / 4160 / 3360	160	4000	100000	90		620 x 620 x 34	2
PANEL COMFORT 625 DALI										
PL CMFT 625 DA P 24W 830	4099854**885624**	24	3840	160	3000	100000	110	DALI-2, IoT	620 x 620 x 34	3
PL CMFT 625 DA P 24W 840	4099854**885662**	24	3840	160	4000	100000	110	DALI-2, IoT	620 x 620 x 34	3
PL CMFT 625 DA P 24W 830 U19	4099854**885686**	24	3840	160	3000	100000	90	DALI-2, IoT	620 x 620 x 34	3
PL CMFT 625 DA P 24W 840 U19	4099854**885709**	24	3840	160	4000	100000	90	DALI-2, IoT	620 x 620 x 34	3
PL CMFT 625 DA P 33W 830 U19	4099854**886485**	33	5280	160	3000	100000	90	DALI-2, IoT	620 x 620 x 34	3
PL CMFT 625 DA P 33W 840 U19	4099854**886508**	33	5280	160	4000	100000	90	DALI-2, IoT	620 x 620 x 34	3
PL CMFT 625 DA P 33W 865 U19	4099854**886539**	33	5280	160	6500	100000	90	DALI-2, IoT	620 x 620 x 34	3
PL CMFT 625 DA P 33W 940 U19	4099854**886553**	33	5280	160	4000	100000	90	DALI-2, IoT	620 x 620 x 34	3
PANEL COMFORT 625 ZIGBEE										
PL CMFT 625 ZB P 33W 830 U19	4099854**886614**	33	5280	160	3000	100000	90	Zigbee Direct, IoT	620 x 620 x 34	4
PL CMFT 625 ZB P 33W 840 U19	4099854**886645**	33	5280	160	4000	100000	90	Zigbee Direct, IoT	620 x 620 x 34	4
PL CMFT 625 ZB P 33W 940 U19	4099854**886669**	33	4950	150	4000	100000	90	Zigbee Direct, IoT	620 x 620 x 34	4

SUPERIOR CLASS PERFORMANCE CLASS VALUE CLASS

[1] Refer to www.ledvance.com/guarantee for precise conditions | [2] Available from September 2026

PANEL COMFORT 1200 GEN 2

1

PANEL COMFORT 1200
Rectangular recessed panel luminaires, for 1200 x 300 mm ceiling systems

2

PANEL COMFORT 1200 MULTI SELECT
Rectangular recessed panel luminaires with Multi Lumen function, for 1200 x 300 mm ceiling systems

3

PANEL COMFORT 1200 DALI
Rectangular recessed panel luminaires with DALI-2 technology, for 1200 x 300 mm ceiling systems

4

PANEL COMFORT 1200 ZIGBEE
Rectangular recessed panel luminaire with Zigbee 3.0 technology, for 1200 x 300 mm ceiling systems

Product name[2]	GTIN (EAN)	W	lm	lm/W	K	L80			L × W × H [mm] Ø × H [mm]	No.
PANEL COMFORT 1200										
PL CMFT 1200 P 22W 830	4099854**909306**	22	3740	170	3000	100000	110		1195 x 295 x 34	1
PL CMFT 1200 P 22W 840	4099854**909344**	22	3740	170	4000	100000	110		1195 x 295 x 34	1
PL CMFT 1200 P 22W 830 U19	4099854**909375**	22	3740	170	3000	100000	90		1195 x 295 x 34	1
PL CMFT 1200 P 22W 840 U19	4099854**909399**	22	3740	170	4000	100000	90		1195 x 295 x 34	1
PANEL COMFORT 1200 MULTI SELECT										
PL CMFT 1200 P 30W ML 830 U19	4099854**883781**	30 / 26 / 21	5100 / 4420 / 3570	170	3000	100000	90		1195 x 295 x 34	2
PL CMFT 1200 P 30W ML 840 U19	4099854**883804**	30 / 26 / 21	5100 / 4420 / 3570	170	4000	100000	90		1195 x 295 x 34	2
PL CMFT 1200 P 30W ML 940 U19	4099854**883828**	30 / 26 / 21	4650 / 4030 / 3255	155	4000	100000	90		1195 x 295 x 34	2
PANEL COMFORT 1200 DALI										
PL CMFT 1200 DA P 24W 830	4099854**909597**	24	3840	160	3000	100000	110	DALI-2, IoT	1195 x 295 x 34	3
PL CMFT 1200 DA P 24W 840	4099854**909658**	24	3840	160	4000	100000	110	DALI-2, IoT	1195 x 295 x 34	3
PL CMFT 1200 DA P 24W 830 U19	4099854**909719**	24	3840	160	3000	100000	90	DALI-2, IoT	1195 x 295 x 34	3
PL CMFT 1200 DA P 24W 840 U19	4099854**909733**	24	3840	160	4000	100000	90	DALI-2, IoT	1195 x 295 x 34	3
PL CMFT 1200 DA P 33W 830 U19	4099854**883927**	33	5115	155	3000	100000	90	DALI-2, IoT	1195 x 295 x 34	3
PL CMFT 1200 DA P 33W 840 U19	4099854**883941**	33	5115	155	4000	100000	90	DALI-2, IoT	1195 x 295 x 34	3
PL CMFT 1200 DA P 33W 940 U19	4099854**883965**	33	4950	150	4000	100000	90	DALI-2, IoT	1195 x 295 x 34	3
PANEL COMFORT 1200 ZIGBEE										
PL CMFT 1200 ZB P 33W 830 U19	4099854**884023**	33	5115	155	3000	100000	90	Zigbee Direct, IoT	1195 x 295 x 34	4
PL CMFT 1200 ZB P 33W 840 U19	4099854**884054**	33	5115	155	4000	100000	90	Zigbee Direct, IoT	1195 x 295 x 34	4
PL CMFT 1200 ZB P 33W 940 U19	4099854**884078**	33	4950	150	4000	100000	90	Zigbee Direct, IoT	1195 x 295 x 34	4

SUPERIOR CLASS PERFORMANCE CLASS VALUE CLASS

[1] Refer to www.ledvance.com/guarantee for precise conditions | [2] Available from September 2026

PANEL COMFORT 675 MULTI SELECT

PANEL COMFORT 675 MULTI SELECT

Square recessed panel luminaire with Multi Lumen function, for 675 x 675 mm ceiling systems

Product name[2]	GTIN (EAN)	W	lm	lm/W	K	L80			L × W × H [mm] Ø × H [mm]
PANEL COMFORT 675 MULTI SELECT									
PL CMFT 675 P 30W ML 840 U19	4099854**909672**	30 / 26 / 21	5250 / 4550 / 3675	175	4000	100000	90		670 x 670 x 34
PL CMFT 675 DA P 33W 840 U19	4099854**909696**	33	5280	160	4000	100000	90	DALI-2, IoT	670 x 670 x 34

SUPERIOR CLASS PERFORMANCE CLASS VALUE CLASS

[1] Refer to www.ledvance.com/guarantee for precise conditions | [2] Available from September 2026

PANEL COMFORT DRIVERS

Replacement driver



IP20

LEDVANCE 7 year guarantee[1]

Product name[2]	GTIN (EAN)	W	L × W × H [mm] Ø × H [mm]
DR DS-P- 22/220-240/550 PL CMFT	4099854**910340**	22	143 x 49 x 32
DR DS-P- 30/220-240/750 PL CMFT	4099854**910388**	30 / 26 / 21	143 x 49 x 32

SUPERIOR CLASS PERFORMANCE CLASS VALUE CLASS

[1] Refer to www.ledvance.com/guarantee for precise conditions | [2] Available from September 2026

PANEL COMPACT 600 GEN 2

1

PANEL COMPACT 600
Square recessed panel luminaires, 600 x 600 mm

2

PANEL COMPACT 600 MULTI SELECT
Square recessed panel luminaire with Multi Select function, 600 x 600 mm

3

PANEL COMPACT 600 DALI
Square recessed panel luminaire with DALI-2 IoT driver, 600 x 600 mm

4

PANEL COMPACT 600 DALI MULTI SELECT
Square recessed panel luminaire with Multi Select function and DALI-2 IoT driver, 600 x 600 mm

Product name	GTIN (EAN)	Replacement for	W	lm	lm/W	K	L80			L × W × H [mm] Ø × H [mm]	No.
PANEL COMPACT 600											
PL COMP 600 V 26W 830	4099854**734441**	4x18/4x14 FL	26	3640	140	3000	75000	110		595 x 595 x 34	1
PL COMP 600 V 26W 840	4099854**734489**	4x18/4x14 FL	26	3640	140	4000	75000	110		595 x 595 x 34	1
PL COMP 600 V 26W 830 U19	4099854**734465**	4x18/4x14 FL	26	3640	140	3000	75000	90		595 x 595 x 34	1
PL COMP 600 V 26W 840 U19	4099854**734502**	4x18/4x14 FL	26	3640	140	4000	75000	90		595 x 595 x 34	1
PANEL COMPACT 600 MULTI SELECT											
PL COMP 600 V 30W ML 83040	4099854**734526**	4x18/4x14 FL	30 / 26 / 22	4200 / 3640 / 3080	140	3000 / 4000	75000	110		595 x 595 x 34	2
PL COMP 600 V 30W ML 84065	4099854**734564**	4x18/4x14 FL	30 / 26 / 22	4200 / 3640 / 3080	140	4000 / 6500	75000	110		595 x 595 x 34	2
PL COMP 600 V 30W ML 83040 U19	4099854**734540**	4x18/4x14 FL	30 / 26 / 22	4200 / 3640 / 3080	140	3000 / 4000	75000	90		595 x 595 x 34	2
PL COMP 600 V 30W ML 84065 U19	4099854**734588**	4x18/4x14 FL	30 / 26 / 22	4200 / 3640 / 3080	140	4000 / 6500	75000	90		595 x 595 x 34	2
PL COMP 600 V 30W ML 93040 U19	4099854**734601**	4x18/4x14 FL	30 / 26 / 22	4200 / 3640 / 3080	140	3000 / 4000	75000	90		595 x 595 x 34	2
PANEL COMPACT 600 DALI											
PL COMP 600 DA V 26W 830	4099854**734762**	4x18/4x14 FL	26	3640	140	3000	75000	110	DALI-2, IoT, Push-DIM	595 x 595 x 34	3
PL COMP 600 DA V 26W 840	4099854**734847**	4x18/4x14 FL	26	3640	140	4000	75000	110	DALI-2, IoT, Push-DIM	595 x 595 x 34	3
PL COMP 600 DA V 26W 830 U19	4099854**734809**	4x18/4x14 FL	26	3640	140	3000	75000	90	DALI-2, IoT, Push-DIM	595 x 595 x 34	3
PL COMP 600 DA V 26W 840 U19	4099854**734861**	4x18/4x14 FL	26	3640	140	4000	75000	90	DALI-2, IoT, Push-DIM	595 x 595 x 34	3
PANEL COMPACT 600 DALI MULTI SELECT											
PL COMP 600 DA V 30W 83040	4099854**734885**	4x18/4x14 FL	30	4200	140	3000 / 4000	75000	110	DALI-2, IoT, Push-DIM	595 x 595 x 34	4
PL COMP 600 DA V 30W 84065	4099854**734946**	4x18/4x14 FL	30	4200	140	4000 / 6500	75000	110	DALI-2, IoT, Push-DIM	595 x 595 x 34	4
PL COMP 600 DA V 30W 83040 U19	4099854**734922**	4x18/4x14 FL	30	4200	140	3000 / 4000	75000	90	DALI-2, IoT, Push-DIM	595 x 595 x 34	4
PL COMP 600 DA V 30W 84065 U19	4099854**734960**	4x18/4x14 FL	30	4200	140	4000 / 6500	75000	90	DALI-2, IoT, Push-DIM	595 x 595 x 34	4
PL COMP 600 DA V 30W 93040 U19	4099854**734984**	4x18/4x14 FL	30	4050	135	3000 / 4000	75000	90	DALI-2, IoT, Push-DIM	595 x 595 x 34	4

SUPERIOR CLASS PERFORMANCE CLASS VALUE CLASS

[1] Refer to www.ledvance.com/guarantee for precise conditions

PANEL COMPACT 625 GEN 2

1

PANEL COMPACT 625
Square recessed panel luminaires, 625 x 625 mm

2

PANEL COMPACT 625 MULTI SELECT
Square recessed panel luminaire with Multi Select function, 625 x 625 mm

3

PANEL COMPACT 625 DALI
Square recessed panel luminaire with DALI-2 IoT driver, 625 x 625 mm

4

PANEL COMPACT 625 DALI MULTI SELECT
Square recessed panel luminaire with Multi Select function and DALI-2 IoT driver, 625 x 625 mm

Product name	GTIN (EAN)	Replacement for	W	lm	lm/W	K	L80			L × W × H [mm] Ø × H [mm]	No.
PANEL COMPACT 625											
PL COMP 625 V 26W 830	4099854**739187**	4x18/4x14 FL	26	3640	140	3000	75000	110		620 x 620 x 34	1
PL COMP 625 V 26W 840	4099854**739224**	4x18/4x14 FL	26	3640	140	4000	75000	110		620 x 620 x 34	1
PL COMP 625 V 26W 830 U19	4099854**739200**	4x18/4x14 FL	26	3640	140	3000	75000	90		620 x 620 x 34	1
PL COMP 625 V 26W 840 U19	4099854**739248**	4x18/4x14 FL	26	3640	140	4000	75000	90		620 x 620 x 34	1
PANEL COMPACT 625 MULTI SELECT											
PL COMP 625 V 30W ML 83040	4099854**739262**	4x18/4x14 FL	30 / 26 / 22	4200 / 3640 / 3080	140	3000 / 4000	75000	110		620 x 620 x 34	2
PL COMP 625 V 30W ML 83040 U19	4099854**739286**	4x18/4x14 FL	30 / 26 / 22	4200 / 3640 / 3080	140	3000 / 4000	75000	90		620 x 620 x 34	2
PL COMP 625 V 30W ML 84065 U19	4099854**739309**	4x18/4x14 FL	30 / 26 / 22	4200 / 3640 / 3080	140	4000 / 6500	75000	90		620 x 620 x 34	2
PL COMP 625 V 30W ML 93040 U19	4099854**739323**	4x18/4x14 FL	30 / 26 / 22	4200 / 3640 / 3080	135	3000 / 4000	75000	90		620 x 620 x 34	2
PANEL COMPACT 625 DALI											
PL COMP 625 DA V 26W 830	4099854**739446**	4x18/4x14 FL	26	3640	140	3000	75000	110	DALI-2, IoT, Push-DIM	620 x 620 x 34	3
PL COMP 625 DA V 26W 840	4099854**739521**	4x18/4x14 FL	26	3640	140	4000	75000	110	DALI-2, IoT, Push-DIM	620 x 620 x 34	3
PL COMP 625 DA V 26W 830 U19	4099854**739484**	4x18/4x14 FL	26	3640	140	3000	75000	90	DALI-2, IoT, Push-DIM	620 x 620 x 34	3
PL COMP 625 DA V 26W 840 U19	4099854**739545**	4x18/4x14 FL	26	3640	140	4000	75000	90	DALI-2, IoT, Push-DIM	620 x 620 x 34	3
PANEL COMPACT 625 DALI MULTI SELECT											
PL COMP 625 DA V 30W 83040	4099854**739569**	4x18/4x14 FL	30	4200	140	3000 / 4000	75000	110	DALI-2, IoT, Push-DIM	620 x 620 x 34	4
PL COMP 625 DA V 30W 83040 U19	4099854**739606**	4x18/4x14 FL	30	4200	140	3000 / 4000	75000	90	DALI-2, IoT, Push-DIM	620 x 620 x 34	4
PL COMP 625 DA V 30W 84065 U19	4099854**739644**	4x18/4x14 FL	30	4200	140	4000 / 6500	75000	90	DALI-2, IoT, Push-DIM	620 x 620 x 34	4
PL COMP 625 DA V 30W 93040 U19	4099854**739668**	4x18/4x14 FL	30	4050	135	3000 / 4000	75000	90	DALI-2, IoT, Push-DIM	620 x 620 x 34	4

SUPERIOR CLASS PERFORMANCE CLASS VALUE CLASS

[1] Refer to www.ledvance.com/guarantee for precise conditions

PANEL COMPACT 1200 GEN 2

1

PANEL COMPACT 1200
Rectangular recessed panel luminaires, 1200 x 300 mm

2

PANEL COMPACT 1200 MULTI SELECT
Rectangular recessed panel luminaire with Multi Select function, 1200 x 300 mm

3

PANEL COMPACT 1200 DALI
Rectangular recessed panel luminaire with DALI-2 IoT driver, 1200 x 300 mm

4

PANEL COMPACT 1200 DALI MULTI SELECT
Rectangular recessed panel luminaire with DALI-2 IoT driver, 1200 x 300 mm

5

PANEL COMPACT 1200 X 600
Rectangular recessed panel luminaires, 1200 x 600 mm

6

PANEL COMPACT 1200 X 600 DALI
Rectangular recessed panel luminaire with DALI-2 IoT driver, 1200 x 600 mm

Product name	GTIN (EAN)	Replacement for	W	lm	lm/W	K	L80			L × W × H [mm] Ø × H [mm]	No.
PANEL COMPACT 1200											
PL COMP 1200 V 26W 840	4099854**735165**	4x18/4x14 FL	26	3640	140	4000	75000	110		1195 x 295 x 34	1
PL COMP 1200 V 26W 840 U19	4099854**735684**	4x18/4x14 FL	26	3640	140	4000	75000	90		1195 x 295 x 34	1
PANEL COMPACT 1200 MULTI SELECT											
PL COMP 1200 V 30W ML 83040	4099854**735707**	4x18/4x14 FL	30 / 26 / 22	4200 / 3640 / 3080	140	3000 / 4000	75000	110		1195 x 295 x 34	2
PL COMP 1200 V 30W ML 83040 U19	4099854**735721**	4x18/4x14 FL	30 / 26 / 22	4200 / 3640 / 3080	140	3000 / 4000	75000	90		1195 x 295 x 34	2
PL COMP 1200 V 30W ML 84065 U19	4099854**735745**	4x18/4x14 FL	30 / 26 / 22	4200 / 3640 / 3080	140	4000 / 6500	75000	90		1195 x 295 x 34	2
PL COMP 1200 V 30W ML 93040 U19	4099854**735769**	4x18/4x14 FL	30 / 26 / 22	4200 / 3640 / 3080	140	3000 / 4000	75000	90		1195 x 295 x 34	2
PANEL COMPACT 1200 DALI											
PL COMP 1200 DA V 26W 840	4099854**735806**	4x18/4x14 FL	26	3640	140	4000	75000	110	DALI-2, IoT, Push-DIM	1195 x 295 x 34	3
PL COMP 1200 DA V 26W 840 U19	4099854**735844**	4x18/4x14 FL	26	3640	140	4000	75000	90	DALI-2, IoT, Push-DIM	1195 x 295 x 34	3
PANEL COMPACT 1200 DALI MULTI SELECT											
PL COMP 1200 DA V 30W 83040	4099854**735882**	4x18/4x14 FL	30	4200	140	3000 / 4000	75000	110	DALI-2, IoT, Push-DIM	1195 x 295 x 34	4
PL COMP 1200 DA V 30W 83040 U19	4099854**735929**	4x18/4x14 FL	30	4200	140	3000 / 4000	75000	90	DALI-2, IoT, Push-DIM	1195 x 295 x 34	4
PL COMP 1200 DA V 30W 84065 U19	4099854**735967**	4x18/4x14 FL	30	4200	140	4000 / 6500	75000	90	DALI-2, IoT, Push-DIM	1195 x 295 x 34	4
PL COMP 1200 DA V 30W 93040 U19	4099854**735981**	4x18/4x14 FL	30	4050	135	3000 / 4000	75000	90	DALI-2, IoT, Push-DIM	1195 x 295 x 34	4
PANEL COMPACT 1200 X 600											
PL COMP 1200X600 V 42W ML 83040	4099854**736865**	4x18/4x14 FL	42 / 32 / 28	5880 / 4480 / 3920	140	3000 / 4000	75000	110		1195 x 595 x 34	5
PL COMP 1200X600 V 42W ML 83040 U19	4099854**736988**	4x18/4x14 FL	42 / 32 / 28	5880 / 4480 / 3920	140	3000 / 4000	75000	90		1195 x 595 x 34	5
PANEL COMPACT 1200 X 600 DALI											
PL COMP 1200X600 DA V 42W 83040	4099854**737046**	4x18/4x14 FL	42	5880	140	3000 / 4000	75000	110	DALI-2, IoT, Push-DIM	1195 x 595 x 34	6
PL COMP 1200X600 DA V 42W 83040 U19	4099854**737183**	4x18/4x14 FL	42	5880	140	3000 / 4000	75000	90	DALI-2, IoT, Push-DIM	1195 x 595 x 34	6

SUPERIOR CLASS PERFORMANCE CLASS VALUE CLASS

[1] Refer to www.ledvance.com/guarantee for precise conditions

PANEL COMPACT DRIVERS

Sparepart drivers for PANEL COMPACT GEN 2



PRODUCT FEATURES

- Available as 26 W, 30 W and 42 W version
- Protection class: II
- Type of protection: IP20
- Supply voltage: 220…240 V
- Operating frequency: 50/60 Hz

PRODUCT BENEFITS

- Highly versatile due to selectable mA output (30 W, 42 W driver)
- Low flickering enables high light quality as well as good visual comfort
- High efficiency and reliability
- Through-wiring possible
- For cable cross sections up to 3 x 1,5 mm

AREAS OF APPLICATION

- Suitable for use with PANEL COMPACT 26 W, 30 W or 42 W

IP20

LEDVANCE 5 year guarantee[1]

Product name	GTIN (EAN)	W		L × W × H [mm] Ø × H [mm]
DR DS-V 26/220-240/700 PL COMP	4099854**748813**	26	Not dimmable	175 x 55 x 30
DR DS-V 30/220-240/800 PL COMP	4099854**748837**	30 / 26 / 22	Not dimmable	175 x 55 x 30
DR DS-V 42/220-240/1150 PL COMP1260	4099854**748851**	42 / 32 / 28	Not dimmable	175 x 55 x 30

SUPERIOR CLASS PERFORMANCE CLASS VALUE CLASS

[1] Refer to www.ledvance.com/guarantee for precise conditions

PANEL INDIVILED 600 / 625 GEN 2

1

PANEL INDIVILED 600 DALI UGR<19 GEN 2

Square recessed panel luminaires with Multi Select, DALI-2 IoT driver, EVERLOOP design and low glare, 600 x 600 mm

2

PANEL INDIVILED 600 ZIGBEE UGR<19 GEN 2

Square recessed panel luminaires with Zigbee 3.0, EVERLOOP design and low glare, 600 x 600 mm

3

PANEL INDIVILED 625 DALI UGR<19 GEN 2

Square recessed panel luminaires with Multi Select, DALI-2 IoT driver, EVERLOOP design and low glare, 625 x 625 mm

4

PANEL INDIVILED 625 ZIGBEE UGR<19 GEN 2

Square recessed panel luminaires with Zigbee 3.0, EVERLOOP design and low glare, 625 x 625 mm

Product name	GTIN (EAN)	Replacement for	W	lm	lm/W	K	L80			L x W x H [mm] Ø x H [mm]	No.
PANEL INDIVILED 600 DALI UGR<19 GEN 2											
PL INV 600 DA P 38W ML 930 U19 WT	4099854**736162**	4x18 FL	38 / 34 / 29 / 24	4900 / 4350 / 3850 / 3150	129 / 128 / 133 / 131	3000	70000	90	DALI-2, IoT	595 x 595 x 22	1
PL INV 600 DA P 38W ML 930 U19 BK	4099854**736247**	4x18 FL	38 / 34 / 29 / 24	4700 / 4250 / 3700 / 3100	124 / 125 / 128 / 129	3000	70000	90	DALI-2, IoT	595 x 595 x 22	1
PL INV 600 DA P 38W ML 940 U19 WT	4099854**736209**	4x18 FL	38 / 34 / 29 / 24	5150 / 4650 / 4000 / 3350	136 / 137 / 138 / 140	4000	70000	90	DALI-2, IoT	595 x 595 x 22	1
PL INV 600 DA P 38W ML 940 U19 BK	4099854**736285**	4x18 FL	38 / 34 / 29 / 24	4900 / 4300 / 3750 / 3150	129 / 126 / 131	4000	70000	90	DALI-2, IoT	595 x 595 x 22	1
PANEL INDIVILED 600 ZIGBEE UGR<19 GEN 2											
PL INV 600 ZB P 38W 930 U19 WT	4099854**789175**	4x18 FL	38	4900	129	3000	70000	90	Zigbee Direct, IoT	595 x 595 x 22	2
PL INV 600 ZB P 38W 930 U19 BK	4099854**789199**	4x18 FL	38	4700	124	3000	70000	90	Zigbee Direct, IoT	595 x 595 x 22	2
PL INV 600 ZB P 38W 940 U19 WT	4099854**789212**	4x18 FL	38	5150	136	4000	70000	90	Zigbee Direct, IoT	595 x 595 x 22	2
PL INV 600 ZB P 38W 940 U19 BK	4099854**789236**	4x18 FL	38	4900	129	4000	70000	90	Zigbee Direct, IoT	595 x 595 x 22	2
PANEL INDIVILED 625 DALI UGR<19 GEN 2											
PL INV 625 DA P 38W ML 930 U19 WT	4099854**736186**	4x18 FL	38 / 34 / 29 / 24	4900 / 4300 / 3850 / 3150	129 / 128 / 133 / 131	3000	70000	90	DALI-2, IoT	620 x 620 x 22	3
PL INV 625 DA P 38W ML 930 U19 BK	4099854**736261**	4x18 FL	38 / 34 / 29 / 24	4700 / 4250 / 3700 / 3100	124 / 125 / 128 / 129	3000	70000	90	DALI-2, IoT	620 x 620 x 22	3
PL INV 625 DA P 38W ML 940 U19 WT	4099854**736223**	4x18 FL	38 / 34 / 29 / 24	5150 / 4650 / 4000 / 3350	136 / 137 / 138 / 140	4000	70000	90	DALI-2, IoT	620 x 620 x 22	3
PL INV 625 DA P 38W ML 940 U19 BK	4099854**736308**	4x18 FL	38 / 34 / 29 / 24	4900 / 4300 / 3750 / 3150	129 / 126 / 131	4000	70000	90	DALI-2, IoT	620 x 620 x 22	3
PANEL INDIVILED 625 ZIGBEE UGR<19 GEN 2											
PL INV 625 ZB P 38W 930 U19 WT	4099854**789250**	4x18 FL	38	4900	129	3000	70000	90	Zigbee Direct, IoT	620 x 620 x 22	4
PL INV 625 ZB P 38W 930 U19 BK	4099854**789274**	4x18 FL	38	4700	124	3000	70000	90	Zigbee Direct, IoT	620 x 620 x 22	4
PL INV 625 ZB P 38W 940 U19 WT	4099854**789298**	4x18 FL	38	5150	136	4000	70000	90	Zigbee Direct, IoT	620 x 620 x 22	4
PL INV 625 ZB P 38W 940 U19 BK	4099854**789311**	4x18 FL	38	4900	129	4000	70000	90	Zigbee Direct, IoT	620 x 620 x 22	4

SUPERIOR CLASS PERFORMANCE CLASS VALUE CLASS

[1] Refer to www.ledvance.com/guarantee for precise conditions

PANEL INDIVILED LIGHT SOURCES DIRECT

Upgrade or replacement light source unit for symmetric light distribution



PRODUCT FEATURES

- Symmetric light distribution
- Lifetime (L80/B10): 70,000 h (at 25 °C)
- Beam angle: 90°

PRODUCT BENEFITS

- Easy upgradeability of light source and driver (EVERLOOP design)
- Easy installation, no tools required for connection
- Homogenous light distribution and reduced glare (UGR ≤ 19) thanks to IndiviLED® optics
- High performance with CRI90

AREAS OF APPLICATION

- Direct replacement for luminaires with fluorescent lamps
- Offices, education, public buildings

FURTHER PRODUCT DETAILS



LISOEV 544X29 24 19W 930 S90U19 BK

UGR < 19 | IP20 | LEDVANCE 5 year guarantee[1]

Product name	GTIN (EAN)	W	lm	lm/W	K	L80	°	L × W × H [mm] Ø × H [mm]
LISOEV 544X29 24 19W 930 S90U19 BK	4099854**793752**	19	2350	124	3000	70000	90	544 x 29 x 19
LISOEV 544X29 25 19W 930 S90U19 GY	4099854**793691**	19	2450	129	3000	70000	90	544 x 29 x 19
LISOEV 544X29 25 19W 940 S90U19 BK	4099854**793783**	19	2450	129	4000	70000	90	544 x 29 x 19
LISOEV 544X29 26 19W 940 S90U19 GY	4099854**793721**	19	2600	137	4000	70000	90	544 x 29 x 19

SAFETY ADVICE

All electrical connections must be made by a qualified person.

SUPERIOR CLASS | PERFORMANCE CLASS | VALUE CLASS

[1] Refer to www.ledvance.com/guarantee for precise conditions

PANEL INDIVILED 1200 GEN 2

1

PANEL INDIVILED 1200 DALI UGR<19 GEN 2

Rectangular recessed panel luminaires with Multi Select, DALI-2 IoT driver, EVERLOOP design and low glare, 1200 x 300 mm

2

PANEL INDIVILED 1200 ZIGBEE UGR<19 GEN 2

Rectangular recessed panel luminaires with Zigbee 3.0, EVERLOOP design and low glare, 1200 x 300 mm

Product name	GTIN (EAN)	Replacement for	W	lm	lm/W	K	L80			L × W × H [mm] Ø × H [mm]	No.
PANEL INDIVILED 1200 DALI UGR<19 GEN 2											
PL INV 1200 DA P 38W ML 930 U19 WT	4099854**736322**	4x18 FL	38 / 34 / 29 / 24	4900 / 4350 / 3850 / 3150	129 / 128 / 133 / 131	3000	70000	90	DALI-2, IoT	1195 x 295 x 22	1
PL INV 1200 DA P 38W ML 930 U19 BK	4099854**736384**	4x18 FL	38 / 34 / 29 / 24	4700 / 4250 / 3700 / 3100	124 / 125 / 128 / 129	3000	70000	90	DALI-2, IoT	1195 x 295 x 22	1
PL INV 1200 DA P 38W ML 940 U19 WT	4099854**736360**	4x18 FL	38 / 34 / 29 / 24	5150 / 4650 / 4000 / 3350	136 / 137 / 138 / 140	4000	70000	90	DALI-2, IoT	1195 x 295 x 22	1
PL INV 1200 DA P 38W ML 940 U19 BK	4099854**736407**	4x18 FL	38 / 34 / 29 / 24	4900 / 4300 / 3750 / 3150	129 / 126 / 131	4000	70000	90	DALI-2, IoT	1195 x 295 x 22	1
PANEL INDIVILED 1200 ZIGBEE UGR<19 GEN 2											
PL INV 1200 ZB P 38W 930 U19 WT	4099854**789335**	4x18 FL	38	4900	129	3000	70000	90	Zigbee Direct, IoT	1195 x 295 x 22	2
PL INV 1200 ZB P 38W 930 U19 BK	4099854**789359**	4x18 FL	38	4700	124	3000	70000	90	Zigbee Direct, IoT	1195 x 295 x 22	2
PL INV 1200 ZB P 38W 940 U19 WT	4099854**789373**	4x18 FL	38	5150	136	4000	70000	90	Zigbee Direct, IoT	1195 x 295 x 22	2
PL INV 1200 ZB P 38W 940 U19 BK	4099854**789397**	4x18 FL	38	4900	129	4000	70000	90	Zigbee Direct, IoT	1195 x 295 x 22	2

SUPERIOR CLASS PERFORMANCE CLASS VALUE CLASS

[1] Refer to www.ledvance.com/guarantee for precise conditions

LINEAR INDIVILED LIGHT SOURCES DIRECT

Upgrade or replacement light source unit for symmetric light distribution

PRODUCT FEATURES

- Symmetric light distribution
- Lifetime (L80/B10): 70,000 h (at 25 °C)
- Beam angle: 90°

PRODUCT BENEFITS

- Easy upgradeability of light source and driver (EVERLOOP design)
- Easy installation, no tools required for connection
- Homogenous light distribution and reduced glare (UGR ≤ 19) thanks to IndiviLED® optics
- High performance with CRI90

AREAS OF APPLICATION

- Direct replacement for luminaires with fluorescent lamps
- Offices, education, public buildings

FURTHER PRODUCT DETAILS



LISOEV 1074x29 46 40W 930 S90U19 BK

UGR <19 | CRI ≥90 | IP20 | LEDVANCE 5 year guarantee[1]

Product name	GTIN (EAN)	W	lm	lm/W	K	L80	∠°	L × W × H [mm] Ø × H [mm]
LISOEV 1074x29 46 40W 930 S90U19 BK	4099854**652059**	40	4650	116	3000	70000	90	1074 x 29 x 19
LISOEV 1074x29 48 40W 930 S90U19 GY	4099854**284359**	40	4800	120	3000	70000	90	1074 x 29 x 19
LISOEV 1074x29 49 40W 940 S90U19 BK	4099854**652080**	40	4900	123	4000	70000	90	1074 x 29 x 19
LISOEV 1074x29 50 40W 940 S90U19 GY	4099854**284809**	40	5050	126	4000	70000	90	1074 x 29 x 19

SAFETY ADVICE

All electrical connections must be made by a qualified person.

SUPERIOR CLASS | PERFORMANCE CLASS | VALUE CLASS

[1] Refer to www.ledvance.com/guarantee for precise conditions

PANEL PROTECT 600

1



PANEL PROTECT 600 PS

Square recessed panel luminaires with IP54 protection and Multi Lumen function, 600 x 600 mm

2

PANEL PROTECT 600 UGR<19 PS

Square recessed panel luminaires with IP54 protection, Multi Lumen function and low glare, 600 x 600 mm

3



PANEL PROTECT 600 DALI

Square recessed panel luminaires with IP54 protection, DALI-2 IoT technology, 600 x 600 mm

4



PANEL PROTECT 600 UGR<19 DALI

Square recessed panel luminaires with IP54 protection, DALI-2 IoT technology and low glare, 600 x 600 mm

5



PANEL PROTECT 600 ZIGBEE

Square recessed panel luminaires with IP54 protection, Zigbee 3.0 technology, 600 x 600 mm

6

PANEL PROTECT 600 UGR<19 ZIGBEE

Square recessed panel luminaires with IP54 protection, Zigbee 3.0 technology and low glare, 600 x 600 mm

Product name	GTIN (EAN)	Replacement for	W	lm	lm/W	K	L80			L × W × H [mm] Ø × H [mm]	No.
PANEL PROTECT 600 PS											
PL PROT 600 P 36W 830 PS	4099854**082863**	4x18 FL	36 / 31 / 26 / 22[2]	5040 / 4340 / 3640 / 3080[2]	140[2]	3000	70000	120		595 x 595 x 34	1
PL PROT 600 P 36W 840 PS	4099854**082887**	4x18 FL	36 / 31 / 26 / 22[2]	5040 / 4340 / 3640 / 3080[2]	140[2]	4000	70000	120		595 x 595 x 34	1
PANEL PROTECT 600 UGR<19 PS											
PL PROT 600 P 36W 840 U19 PS	4099854**083303**	4x18 FL	36 / 31 / 26 / 22[2]	5040 / 4340 / 3640 / 3080[2]	140[2]	4000	70000	90		595 x 595 x 34	2
PANEL PROTECT 600 DALI											
PL PROT 600 P 36W 830 DALIVR	4099854**082900**	4x18 FL	36[2]	5040[2]	140[2]	3000	70000	120	DALI-2, IoT, Push-DIM	595 x 595 x 34	3
PL PROT 600 P 36W 840 DALIVR	4099854**083105**	4x18 FL	36[2]	5040[2]	140[2]	4000	70000	120	DALI-2, IoT, Push-DIM	595 x 595 x 34	3
PANEL PROTECT 600 UGR<19 DALI											
PL PROT 600 P 36W 840 U19 DALIVR	4099854**083327**	4x18 FL	36[2]	5040[2]	140[2]	4000	70000	90	DALI-2, IoT, Push-DIM	595 x 595 x 34	4
PANEL PROTECT 600 ZIGBEE											
PL PROT 600 ZB P 36W 830	4099854**514531**	4x18 FL	36	5040	140	3000	70000	120	Zigbee Direct, IoT	595 x 595 x 34	5
PL PROT 600 ZB P 36W 840	4099854**514555**	4x18 FL	36	5040	140	4000	70000	120	Zigbee Direct, IoT	595 x 595 x 34	5
PANEL PROTECT 600 UGR<19 ZIGBEE											
PL PROT 600 ZB P 36W 840 U19	4099854**514593**	4x18 FL	36	5040	140	4000	70000	90	Zigbee Direct, IoT	595 x 595 x 34	6

SUPERIOR CLASS PERFORMANCE CLASS VALUE CLASS

[1] Refer to www.ledvance.com/guarantee for precise conditions | [2] The Panel Protect family is fulfilling the technical minimum requirements according to the German BEG subsidy program for energy efficient luminaires

PANEL PROTECT 625



1

PANEL PROTECT 625 PS

Square recessed panel luminaires with IP54 protection and Multi Lumen function, 625 x 625 mm

2

PANEL PROTECT 625 UGR<19 PS

Square recessed panel luminaires with IP54 protection, Multi Lumen function and low glare, 625 x 625 mm



3

PANEL PROTECT 625 DALI

Square recessed panel luminaires with IP54 protection, DALI-2 IoT technology, 625 x 625 mm



4

PANEL PROTECT 625 UGR<19 DALI

Square recessed panel luminaires with IP54 protection, DALI-2 IoT technology and low glare, 625 x 625 mm



5

PANEL PROTECT 625 ZIGBEE

Square recessed panel luminaires with IP54 protection, Zigbee 3.0 technology, 625 x 625 mm

6

PANEL PROTECT 625 UGR<19 ZIGBEE

Square recessed panel luminaires with IP54 protection, Zigbee 3.0 technology and low glare, 625 x 625 mm

Product name	GTIN (EAN)	Replacement for	W	lm	lm/W	K	L80			L × W × H [mm] Ø × H [mm]	No.
PANEL PROTECT 625 PS											
PL PROT 625 P 36W 830 PS	4099854**083365**	4x18 FL	36 / 31 / 26 / 22[2]	5040 / 4340 / 3640 / 3080[2]	140[2]	3000	70000	120		620 x 620 x 34	1
PL PROT 625 P 36W 840 PS	4099854**083389**	4x18 FL	36 / 31 / 26 / 22[2]	5040 / 4340 / 3640 / 3080[2]	140[2]	4000	70000	120		620 x 620 x 34	1
PANEL PROTECT 625 UGR<19 PS											
PL PROT 625 P 36W 840 U19 PS	4099854**083488**	4x18 FL	36 / 31 / 26 / 22[2]	5040 / 4340 / 3640 / 3080[2]	140[2]	4000	70000	90		620 x 620 x 34	2
PANEL PROTECT 625 DALI											
PL PROT 625 P 36W 830 DALIVR	4099854**083402**	4x18 FL	36[2]	5040[2]	140[2]	3000	70000	120	DALI-2, IoT, Push-DIM	620 x 620 x 34	3
PL PROT 625 P 36W 840 DALIVR	4099854**083440**	4x18 FL	36[2]	5040[2]	140[2]	4000	70000	120	DALI-2, IoT, Push-DIM	620 x 620 x 34	3
PANEL PROTECT 625 UGR<19 DALI											
PL PROT 625 P 36W 840 U19 DALIVR	4099854**083501**	4x18 FL	36[2]	5040[2]	140[2]	4000	70000	90	DALI-2, IoT, Push-DIM	620 x 620 x 34	4
PANEL PROTECT 625 ZIGBEE											
PL PROT 625 ZB P 36W 830	4099854**514630**	4x18 FL	36	5040	140	3000	70000	120	Zigbee Direct, IoT	620 x 620 x 34	5
PL PROT 625 ZB P 36W 840	4099854**514654**	4x18 FL	36	5040	140	4000	70000	120	Zigbee Direct, IoT	620 x 620 x 34	5
PANEL PROTECT 625 UGR<19 ZIGBEE											
PL PROT 625 ZB P 36W 840 U19	4099854**514692**	4x18 FL	36	5040	140	4000	70000	90	Zigbee Direct, IoT	620 x 620 x 34	6

SUPERIOR CLASS PERFORMANCE CLASS VALUE CLASS

[1] Refer to www.ledvance.com/guarantee for precise conditions | [2] The Panel Protect family is fulfilling the technical minimum requirements according to the German BEG subsidy program for energy efficient luminaires

PANEL SURFACE 674

1

PANEL SURFACE 674
Surface-mounted refurbishment luminaires, 674 x 674 mm

2

PANEL SURFACE DALI 674
Surface-mounted refurbishment luminaires with DALI-2 technology, 674 x 674 mm

3

PANEL SURFACE ZIGBEE 674
Surface-mounted refurbishment luminaires with Zigbee 3.0 technology, 674 x 674 mm

4

PANEL SURFACE SENSOR 674
Surface-mounted refurbishment luminaires with integrated PIR sensor, 674 x 674 mm

Product name	GTIN (EAN)	W	lm	lm/W	K	L80			L × W × H [mm] Ø × H [mm]	No.
PANEL SURFACE 674										
PL SF 674 V 32W ML 93040	4099854**729935**	32 / 27 / 21	4160 / 3645 / 2940[2]	140 / 135 / 130	3000 / 4000	75000	120		674 x 674 x 69	1
PL SF 674 V 32W ML 93040 U19	4099854**729959**	32 / 27 / 21	4160 / 3645 / 2940[2]	140 / 135 / 130	3000 / 4000	75000	90		674 x 674 x 69	1
PANEL SURFACE DALI 674										
PL SF 674 DA V 32W 93040	4099854**731563**	32	4160[3]	130	3000 / 4000	75000	120	DALI-2, IoT, Push-DIM	674 x 674 x 69	2
PL SF 674 DA V 32W 93040 U19	4099854**731587**	32	4160[3]	130	3000 / 4000	75000	90	DALI-2, IoT, Push-DIM	674 x 674 x 69	2
PANEL SURFACE ZIGBEE 674										
PL SF 674 ZB V 32W 93040	4099854**730566**	32	4160[3]	130	3000 / 4000	75000	120	Zigbee Direct, IoT	674 x 674 x 69	3
PL SF 674 ZB V 32W 93040 U19	4099854**730665**	32	4160[3]	130	3000 / 4000	75000	90	Zigbee Direct, IoT	674 x 674 x 69	3
PANEL SURFACE SENSOR 674										
PL SF 674 SNP V 32W ML 93040	4099854**731808**	32 / 27 / 21	4160 / 3645 / 2940[2]	140 / 135 / 130	3000 / 4000	75000	120		674 x 674 x 78	4
PL SF 674 SNP V 32W ML 93040 U19	4099854**731884**	32 / 27 / 21	4160 / 3645 / 2940[2]	140 / 135 / 130	3000 / 4000	75000	90		674 x 674 x 78	4

SENSOR PROPERTIES

Product name	GTIN (EAN)	Type of sensor	Sensor technology	Detection threshold of daylight sensor	Detection range of motion sensor	Sensor detection angle	Sensor controlled switching time
PL SF 674 SNP V 32W ML 93040	4099854**731808**	Motion	Passive infrared (PIR)	10…150	1…3	360	5 s…20
PL SF 674 SNP V 32W ML 93040 U19	4099854**731884**	Motion	Passive infrared (PIR)	10…150	1…3	360	5 s…20

SUPERIOR CLASS PERFORMANCE CLASS VALUE CLASS

[1] Refer to www.ledvance.com/guarantee for precise conditions | [2] 4000 lm / 3510 lm / 2835 lm @3000K | [3] 4000 lm @3000K

PANEL SURFACE 1274

1

PANEL SURFACE 1274
Surface-mounted refurbishment luminaires, 1274 x 374 mm

2

PANEL SURFACE DALI 1274
Surface-mounted refurbishment luminaires with DALI-2 technology, 1274 x 374 mm

3

PANEL SURFACE ZIGBEE 1274
Surface-mounted refurbishment luminaires with Zigbee 3.0 technology, 1274 x 374 mm

4

PANEL SURFACE SENSOR 1274
Surface-mounted refurbishment luminaires with integrated PIR sensor, 1274 x 374 mm

Product name	GTIN (EAN)	W	lm	lm/W	K	L80			L × W × H [mm] Ø × H [mm]	No.
PANEL SURFACE 1274										
PL SF 1274 V 38W ML 93040	4099854**729973**	38 / 31 / 27	5000 / 4030 / 3645[2]	135 / 130	3000 / 4000	75000	120		1274 x 373 x 69	1
PL SF 1274 V 38W ML 93040 U19	4099854**729997**	38 / 31 / 27	5000 / 4030 / 3645[2]	135 / 130	3000 / 4000	75000	90		1274 x 373 x 69	1
PANEL SURFACE DALI 1274										
PL SF 1274 DA V 38W 93040	4099854**731648**	38	5000[3]	130	3000 / 4000	75000	120	DALI-2, IoT, Push-DIM	1274 x 373 x 69	2
PL SF 1274 DA V 38W 93040 U19	4099854**731662**	38	5000[3]	130	3000 / 4000	75000	90	DALI-2, IoT, Push-DIM	1274 x 373 x 69	2
PANEL SURFACE ZIGBEE 1274										
PL SF 1274 ZB V 38W 93040	4099854**731600**	38	5000[3]	130	3000 / 4000	75000	120	Zigbee Direct, IoT	1274 x 373 x 69	3
PL SF 1274 ZB V 38W 93040 U19	4099854**731624**	38	5000[3]	130	3000 / 4000	75000	90	Zigbee Direct, IoT	1274 x 373 x 69	3
PANEL SURFACE SENSOR 1274										
PL SF 1274 SNP V 38W ML 93040	4099854**731907**	38 / 31 / 27	5000 / 4030 / 3645[2]	135 / 130	3000 / 4000	75000	120		1274 x 373 x 78	4
PL SF 1274 SNP V 38W ML 93040 U19	4099854**731921**	38 / 31 / 27	5000 / 4030 / 3645[2]	135 / 130	3000 / 4000	75000	90		1274 x 373 x 78	4

SENSOR PROPERTIES

Product name	GTIN (EAN)	Type of sensor	Sensor technology	Detection threshold of daylight sensor	Detection range of motion sensor	Sensor detection angle	Sensor controlled switching time
PL SF 1274 SNP V 38W ML 93040	4099854**731907**	Motion	Passive infrared (PIR)	10…150	1…3	360	5 s…20
PL SF 1274 SNP V 38W ML 93040 U19	4099854**731921**	Motion	Passive infrared (PIR)	10…150	1…3	360	5 s…20

SUPERIOR CLASS PERFORMANCE CLASS VALUE CLASS

[1] Refer to www.ledvance.com/guarantee for precise conditions | [2] 4750 lm / 4030 lm / 3510 lm @3000K | [3] 4750 lm @3000K

PANEL SURFACE 1574

1

PANEL SURFACE 1574
Surface-mounted refurbishment luminaires, 1574 x 374 mm

2

PANEL SURFACE DALI 1574
Surface-mounted refurbishment luminaires with DALI-2 technology, 1574 x 374 mm

3

PANEL SURFACE ZIGBEE 1574
Surface-mounted refurbishment luminaires with Zigbee 3.0 technology, 1574 x 374 mm

4

PANEL SURFACE SENSOR 1574
Surface-mounted refurbishment luminaires with integrated PIR sensor, 1574 x 374 mm

Product name	GTIN (EAN)	W	lm	lm/W	K	L80	°		L × W × H [mm] Ø × H [mm]	No.
PANEL SURFACE 1574										
PL SF 1574 V 48W ML 93040	4099854**730016**	48 / 39 / 31	6240 / 5265 / 4030[2]	140 / 135 / 130	3000 / 4000	75000	120		1574 x 373 x 69	1
PL SF 1574 V 48W ML 93040 U19	4099854**730542**	48 / 39 / 31	6240 / 5265 / 4030[2]	140 / 135 / 130	3000 / 4000	75000	90		1574 x 373 x 69	1
PANEL SURFACE DALI 1574										
PL SF 1574 DA V 48W 93040	4099854**731723**	48	6240[3]	130	3000 / 4000	75000	120	DALI-2, IoT, Push-DIM	1574 x 373 x 69	2
PL SF 1574 DA V 48W 93040 U19	4099854**731747**	48	6240[3]	130	3000 / 4000	75000	90	DALI-2, IoT, Push-DIM	1574 x 373 x 69	2
PANEL SURFACE ZIGBEE 1574										
PL SF 1574 ZB V 48W 93040	4099854**731686**	48	6240[3]	130	3000 / 4000	75000	120	Zigbee Direct, IoT	1574 x 373 x 69	3
PL SF 1574 ZB V 48W 93040 U19	4099854**731709**	48	6240[3]	130	3000 / 4000	75000	90	Zigbee Direct, IoT	1574 x 373 x 69	3
PANEL SURFACE SENSOR 1574										
PL SF 1574 SNP V 48W ML 93040	4099854**731969**	48 / 39 / 31	6240 / 5265 / 4030[2]	140 / 135 / 130	3000 / 4000	75000	120		1574 x 373 x 78	4
PL SF 1574 SNP V 48W ML 93040 U19	4099854**731983**	48 / 39 / 31	6240 / 5265 / 4030[2]	140 / 135 / 130	3000 / 4000	75000	90		1574 x 373 x 78	4

SENSOR PROPERTIES

Product name	GTIN (EAN)	Type of sensor	Sensor technology	Detection threshold of daylight sensor	Detection range of motion sensor	Sensor detection angle	Sensor controlled switching time
PL SF 1574 SNP V 48W ML 93040	4099854**731969**	Motion	Passive infrared (PIR)	10…150	1…3	360	5 s…20
PL SF 1574 SNP V 48W ML 93040 U19	4099854**731983**	Motion	Passive infrared (PIR)	10…150	1…3	360	5 s…20

SUPERIOR CLASS PERFORMANCE CLASS VALUE CLASS

[1] Refer to www.ledvance.com/guarantee for precise conditions | [2] 6000 lm / 5070 lm / 4185 lm @3000K | [3] 6000 lm @3000K

PANEL SURFACE SUSPENSION KIT

Suspension kit with integrated cable and terminal block

PRODUCT FEATURES

- Round metal canopy with preinstalled 5-pole terminal block
- 2- or 4-pole cable preinstalled to connect with luminaire driver
- Y-shaped metal wire suspension with carabiners
- Versions for protection class II luminaire wiring: 2-pole (standard) or 4-pole (DALI)

PRODUCT BENEFITS

- Kit for easy suspension of PANEL SURFACE luminaires
- Maximum suspension distance to ceiling 1500 mm, adjustable
- Direct electrical connection in canopy (protection class I)

AREAS OF APPLICATION

- Suitable for PANEL SURFACE

EQUIPMENT / ACCESSORIES

- Transparent wire clamps for attachment to the metal wire suspension included

LEDVANCE 2 year guarantee [1]

Product name	GTIN (EAN)	L × W × H [mm] Ø × H [mm]
PL SF SUSPENSION KIT L/E/N	4099854**732003**	151 x 50
PL SF SUSPENSION KIT L/E/N/DA+/DA-	4099854**732027**	151 x 50

SUPERIOR CLASS PERFORMANCE CLASS VALUE CLASS

[1] Refer to www.ledvance.com/guarantee for precise conditions

PANEL PRINT SKY 600 GEN 2

1

PANEL PRINT SKY 600
Panel luminaires featuring a printed realistic sky image, for 600 x 600 ceiling systems

2

PANEL PRINT SKY 600
Panel luminaires featuring a printed realistic sky image, for 600 x 600 ceiling systems

3

PANEL PRINT SKY 600
Panel luminaires featuring a printed realistic sky image, for 600 x 600 ceiling systems

4

PANEL PRINT SKY 600
Panel luminaires featuring a printed realistic sky image, for 600 x 600 ceiling systems

Product name	GTIN (EAN)	W	lm [1]	lm/W [1]	K	L80	°		IK	L × W × H [mm] Ø × H [mm]	No.
PANEL PRINT SKY 600											
PL PRINT SKY1 600 V 26W	4058075**861701**	26	3640	140		75000	110		IK02	595 x 595 x 34	1
PL PRINT SKY1 DA 600 V 26W	4058075**861961**	26	3640	140		75000	110	DALI-2, IoT	IK02	595 x 595 x 34	1
PANEL PRINT SKY 600											
PL PRINT SKY 600 V 26W SET4	4058075**861732**	104	14560	140	[1]	75000	110		IK02	595 x 595 x 34	2
PL PRINT SKY DA 600 V 26W SET4	4058075**861756**	104	14560	140	[1]	75000	110	DALI-2, IoT	IK02	595 x 595 x 34	2
PANEL PRINT SKY 600											
PL PRINT SKY 600 V 26W SET6	4058075**861770**	156	21840	140	[1]	75000	110		IK02	595 x 595 x 34	3
PL PRINT SKY DA 600 V 26W SET6	4058075**861794**	156	21840	140	[1]	75000	110	DALI-2, IoT	IK02	595 x 595 x 34	3
PANEL PRINT SKY 600											
PL PRINT SKY 600 V 26W SET9	4058075**861817**	234	32760	140	[1]	75000	110		IK02	595 x 595 x 34	4
PL PRINT SKY DA 600 V 26W SET9	4058075**861831**	234	32760	140	[1]	75000	110	DALI-2, IoT	IK02	595 x 595 x 34	4

SUPERIOR CLASS PERFORMANCE CLASS VALUE CLASS

[1] Decorative Panel: Lumen/Efficacy as well as SDCM and CRI will vary from the original Panel values based on the printed image | [2] Refer to www.ledvance.com/guarantee for precise conditions

PANEL PRINT SKY 625 GEN 2

1

PANEL PRINT SKY 625
Panel luminaires featuring a printed realistic sky image, for 625 x 625 ceiling systems

2

PANEL PRINT SKY 625
Panel luminaires featuring a printed realistic sky image, for 625 x 625 ceiling systems

3

PANEL PRINT SKY 625
Panel luminaires featuring a printed realistic sky image, for 625 x 625 ceiling systems

4

PANEL PRINT SKY 625
Panel luminaires featuring a printed realistic sky image, for 625 x 625 ceiling systems

Product name	GTIN (EAN)	W	lm [1]	lm/W [1]	K	L80			IK	L × W × H [mm] Ø × H [mm]	No.
PANEL PRINT SKY 625											
PL PRINT SKY1 625 V 26W	4058075**861848**	26	3640	140		75000	110		IK02	620 x 620 x 34	1
PL PRINT SKY1 DA 625 V 26W	4058075**861862**	26	3640	140		75000	110	DALI-2, IoT	IK02	620 x 620 x 34	1
PANEL PRINT SKY 625											
PL PRINT SKY 625 V 26W SET4	4058075**861893**	104	14560	140	[1]	75000	110		IK02	620 x 620 x 34	2
PL PRINT SKY DA 625 V 26W SET4	4058075**861916**	104	14560	140	[1]	75000	110	DALI-2, IoT	IK02	620 x 620 x 34	2
PANEL PRINT SKY 625											
PL PRINT SKY 625 V 26W SET6	4058075**861930**	156	21840	140	[1]	75000	110		IK02	620 x 620 x 34	3
PL PRINT SKY DA 625 V 26W SET6	4058075**861954**	156	21840	140	[1]	75000	110	DALI-2, IoT	IK02	620 x 620 x 34	3
PANEL PRINT SKY 625											
PL PRINT SKY 625 V 26W SET9	4058075**861978**	234	32760	140	[1]	75000	110		IK02	620 x 620 x 34	4
PL PRINT SKY DA 625 V 26W SET9	4058075**861992**	234	32760	140	[1]	75000	110	DALI-2, IoT	IK02	620 x 620 x 34	4

SUPERIOR CLASS PERFORMANCE CLASS VALUE CLASS

[1] Decorative Panel: Lumen/Efficacy as well as SDCM and CRI will vary from the original Panel values based on the printed image | [2] Refer to www.ledvance.com/guarantee for precise conditions

PANEL ACCESSORIES

PANEL LUMINAIRES

1

2

3

4

5

6

7

8

9

10

11

12

Product name	GTIN (EAN)	MATERIAL	COLOUR	L × W × H [mm] Ø × H [mm]	Ø × H [mm]	No.
SURFACE MOUNT KIT						
Reinforced surface mount frames for panel luminaires						
PANEL 600 SURFACE MOUNT KIT H75	4058075**472914**	Aluminum	White	600.5 x 600.5 x 75	75	1
PANEL 625 SURFACE MOUNT KIT H75	4058075**472938**	Aluminum	White	625.5 x 625.5 x 75	75	1
PANEL 1200 SURFACE MOUNT KIT H75 WT[1]	4099854**910616**	Aluminum	White	1200 x 300 x 76	76	1
PANEL 600 SURFACE MOUNT KIT H75 BK	4058075**834330**	Aluminum	Black	600 x 600 x 76	76	1
PANEL 625 SURFACE MOUNT KIT H75 BK	4058075**834354**	Aluminum	Black	625 x 625 x 76	76	1
PANEL 1200 SURFACE MOUNT KIT H75 BK[1]	4099854**912146**	Aluminum	Black	1200 x 300 x 76	76	1
PANEL 600 SURFACE MOUNT KIT H50	4058075**826397**	Aluminum	White	600 x 600 x 50	50	1
PANEL 625 SURFACE MOUNT KIT H50	4058075**826403**	Aluminum	White	625 x 625 x 50	50	1
SURFACE MOUNT KIT VALUE						
Surface mount frames for panel luminaires						
PANEL 600 SURFACE MOUNT KIT H70 VAL	4058075**402843**	Aluminum	White	613 x 613 x 70	70	2
PANEL 625 SURFACE MOUNT KIT H70 VAL	4058075**402867**	Aluminum	White	638 x 638 x 70	70	2
PANEL 1200 X 300 SF MOUNT KIT H70 VAL	4099854**018497**	Aluminum	White	1215 x 315 x 72	72	2
PANEL 1200 X 600 SURFACE MOUNT KIT VAL	4058075**389823**	Aluminum	White	1213 x 613 x 72	72	2
SUSPENSION KIT						
Suspension kit for panel luminaires						
PANEL SUSPENSION KIT G2[1]	4099854**910500**	Steel	Steel	1500		3
SECURITY KIT						
Security kits for panel luminaires						
PANEL SECURITY KIT 4x	4058075**472990**	Steel	Steel	1000 x 17 x 4	4	4
RECESSED ANGLED HOLDER						
Recessed angled holder for panel luminaires						
PANEL RECESSED ANGLED HOLDER 4X[1]	4099854**921216**	Steel	White	115 x 30 x 26	26	5
RECESSED MOUNT CLIPS						
Recessed mount clips for panel luminaires						
PANEL RECESSED MOUNT CLIPS VAL 4x	4058075**409859**	Steel	Steel	25 x 45 x 33	33	6
RECESSED MOUNT FRAME						
Recessed mount frames for panel luminaires						
PANEL 600 RECESSED MOUNT FRAME	4058075**402881**	Aluminum	White	625 x 625 x 76	76	7
PANEL 625 RECESSED MOUNT FRAME	4058075**402904**	Aluminum	White	650 x 650 x 76	76	7
PANEL 1200x300 RECESSED MOUNT FRAME	4058075**472976**	Aluminum	White	1231 x 331 x 76	76	7
RECESSED INVERTED FRAME						
Decorative recessed mounting frame for panel luminaires						
PANEL 600 RECESSED INVERTED FRAME H70[1]	4099854**910425**	Aluminum	White	600 x 600 x 70	70	8
PANEL 625 RECESSED INVERTED FRAME H70[1]	4099854**910449**	Aluminum	White	625 x 625 x 70	70	8
COVER CIRCULAR CUT OUT						
Decorative circular diffuser cover for panel luminaires						
PANEL 600 COVER CIRCULAR CUT OUT[1]	4099854**910463**	Aluminum	White	600 x 600 x 20	20	9
PANEL 625 COVER CIRCULAR CUT OUT[1]	4099854**910487**	Aluminum	White	625 x 625 x 20	20	9
CONNECTOR BOX						
Connector boxes for recessed luminaires						
CONNECTOR BOX 5P L/N/E 4X G2[1]	4099854**910555**	Polycarbonate (PC)	White	128.5 x 58 x 25	25	10
CONNECTOR BOX 5P L/N/E/D+/D- 4X G2[1]	4099854**910593**	Polycarbonate (PC)	White	128.5 x 58 x 25	25	10

Product name	GTIN (EAN)	MATERIAL	COLOUR	L × W × H [mm] Ø × H [mm]	Ø × H [mm]	No.
PANEL 1200 TWIST LOCK EXTENSION Twist lock cable extension for Panel Comfort 1200						5 year guarantee[2]
PANEL 1200 CABLE EXT TWIST LOCK	4099854**018510**	Polyvinylchlorid (PVC)	Transparent	2400 x 13	13	11

Product name	GTIN (EAN)	W	L × W × H [mm] Ø × H [mm]	No.
EMERGENCY KIT COMPACT Emergency kit to convert recessed luminaires to self-contained emergency luminaires with battery temperature monitoring				IP20 5 year guarantee[2]
EL KIT COMP 55V 4W LI MT AT 3H WT	4058075**860711**	4	280 x 43 x 30	12

SUPERIOR CLASS PERFORMANCE CLASS VALUE CLASS

[1] Available from September 2026 | [2] Refer to www.ledvance.com/guarantee for precise conditions

ABOUT LEDVANCE

With business activities in over 140 countries, LEDVANCE is one of the world's leading general lighting companies. Emerging from OSRAM's general lighting division, LEDVANCE's portfolio includes LED lamps and luminaires, intelligent lighting products, traditional lamps and renewable energy solutions.
#POWERTHROUGHLIGHT

LEDVANCE

LEDVANCE GmbH
Parkring 1 – 5
85748 Garching
Germany

07/26 LEDVANCE EU-W MK TRA Subject to change without notice. Errors and omission excepted.

LEDVANCE.COM