

RATED ★★★★★ BY 220+ LEADING COMPANIES

# Haven

By Office Acoustics

Innovative acoustics solutions for the modern office. Made to last.





# The future of workplace design: balancing acoustics, flexibility, and productivity

## The shift in workplace needs

The modern office is evolving as businesses adapt to hybrid work models, changing employee expectations, and the need for more efficient use of space. While open-plan layouts were initially praised for fostering collaboration, they often fail to provide the level of focus required for deep work. In fact, 85% of employees say they experience distractions in open offices (Leesman Index Workplace Study, 2023).

The challenge is no longer about choosing between open and enclosed spaces but rather about creating a workplace that allows employees to move between different environments based on their needs.

## The impact of noise on productivity

Workplace acoustics play a critical role in employee performance, yet they remain one of the most overlooked aspects of office design. Noise can reduce cognitive performance by up to 66% (Gensler Workplace Survey, 2024), leading to lost efficiency and higher stress levels.

Many businesses attempt to solve this issue with quick fixes - such as desk partitions or noise-masking systems - rather than integrating purposeful sound management solutions from the outset. The most effective workspaces take a proactive approach, incorporating sound-absorbing materials, strategically placed enclosed areas, and zoning strategies that allow for both collaboration and concentration.







## Flexible workspaces and adaptability

With 74% of companies now offering hybrid work models (CBRE Future of Work Report, 2024), offices need to be designed for adaptability. The days of static desk assignments are giving way to multi-use spaces that can be reconfigured as needed. High-performing workplaces provide a mix of settings, from enclosed pods for deep work to open areas that encourage spontaneous collaboration. The ability to transition seamlessly between different types of work not only enhances productivity but also helps employees feel more in control of their environment.

## Designing for long-term success

Investing in workplace design is not just about aesthetics - it's a strategic decision that affects both employee performance and business outcomes. Poorly designed offices contribute to inefficiency, dissatisfaction, and higher turnover rates. On the other hand, businesses that optimise their work environments see clear benefits. Studies show that companies lose an average of £1,400 per employee per year due to workplace distractions (Harvard Business Review, 2023).

However, organisations that implement thoughtful acoustic and spatial strategies report significant gains in productivity, engagement, and employee well-being. Creating balanced, adaptable workspaces ensures that businesses can evolve with changing work trends while maintaining efficiency and employee satisfaction.

Modern workplaces must balance collaboration, focus, and flexibility to meet the evolving needs of businesses and employees. By integrating sound management, adaptable layouts, and multi-use spaces, companies can reduce distractions, boost productivity, and create a future-ready work environment. Investing in workplace optimisation is not just an aesthetic choice - it's a strategic advantage.

RATED ★★★★★ BY 220+ LEADING COMPANIES

# Haven One

By Office Acoustics



A single-person phone booth crafted for private calls and uninterrupted work. Where modern design meets functionality.



## Haven One | Highlights



### Privacy you can count on

World-class soundproofing blocks a wide range of frequencies, ensuring unmatched privacy. Work with confidence in a quiet, distraction-free environment designed for focus and productivity.



### Superior ventilation for extended calls

Haven One's advanced ventilation system refreshes the air inside the booth every minute, maintaining a clean, fresh, and comfortable environment. Perfect for long work sessions or extended calls, it helps you stay focused.



### Lighting tailored to every task

Motion-activated LED lighting and LED light strips provide optimal brightness for any task. Whether focusing on detailed work or preparing for a video call, Haven One ensures the perfect lighting to support productivity.



### The comfort of natural materials

The interior is crafted from premium and sustainably sourced natural materials. The natural oak creates a cosy yet professional ambiance, ideal for focused work and private conversations, exuding calm and elegance.



Office  
Acoustics



## Haven One | Main Features

### 1. ISO-certified soundproofing


Haven One delivers guaranteed privacy with a speech level reduction of up to 30dB, backed by the industry's official ISO 23351-1:2020 certification for office phone booths and meeting pods. Triple-layered acoustic glass enhances sound isolation, making it the right choice for distraction-free work.

### 2. Sophisticated dual LED lighting system

A dedicated LED light strip on the back panel, independently adjustable by a LED light controller, creates impeccable illumination for video calls, while the main lighting ensures optimal ambiance for any task. Perfectly tailored for every use case, this lighting solution combines functionality with refined elegance.

### 3. Timeless plug-and-play simplicity

Designed for longevity, our pods focus on what truly matters - no unnecessary frills, no software to update or replace, and no subscription services. With streamlined plug-and-play functionality, they deliver hassle-free usability and enduring performance.



### 4. Seamless connectivity

Haven One is equipped with 1x electric socket, USB-A and USB-C ports, and Qi wireless charging to ensure effortless connectivity and power access for all your devices. Stay connected and fully charged without interruptions.

### 5. Custom-designed ventilation system

Haven One's advanced ventilation system ensures optimal airflow by extracting up to 240 m<sup>3</sup>/hour. The high-capacity ventilation keeps the air fresh and clean, maintaining a comfortable and healthy environment.

### 6. Fully automated

Our built-in-sensor detects when someone enters or exits the pod, automatically turning the lighting on or off to ensure convenience and energy efficiency.




A fully equipped booth with a compact design, making it the perfect addition to any workspace.



Designed with durability and sustainability in mind, it features a lightweight yet robust structure crafted from premium materials, ensuring high performance without compromise. The interior is thoughtfully made of sound-absorbing PET panels with low-maintenance hardwearing and durable carpeting, making it both practical and functional.



The booth's scratch-resistant oak veneer panels add a touch of elegance and the glass panels on both sides ensure plenty of natural light accompanies the stylish design.



Haven One also includes built-in features such as a durable oak shelf with an integrated power outlet to meet everyday office needs.



Custom-designed shelf



Ergonomic handle  
made of natural oak



Felt and carpet - highly  
durable & washable




Office  
Acoustics



# Haven One | Technical Specifications


## DIMENSIONS AND SPACE REQUIREMENTS

Dimensions	Exterior: H: 2250mm W: 1000mm D: 1000mm
	Interior: H: 2020mm W: 910mm D: 910mm
	Doorway: H: 2020mm W: 740mm
	Shelf: H: 930mm D: 280mm (with rounded corners)
Operating space requirements	H: 2350mm W: 1020mm D: 1800mm
Installation space requirements	Installation requires 1000mm of free space around the pod.  Ceiling height must be at least 2350mm to facilitate the installation.
Weight	261 kg
Door operation ratio	160°   Left handed only
Mobility	Easily move the pod without disassembling thanks to the built-in casters. To relocate, simply raise the levelling guides, then lower them again once the pod is positioned in its new location.
Shipping crate/pallet dimensions	H: 1100mm W: 2350mm D: 1000mm Weight: 310 kg



## POWER AND ELECTRICAL SETUP

Available outlets and connections inside the booth	1x power outlet (available in Type F, Type E, Type G, Type J and Type A)
	1x USB-C (10W)
	1x USB-A (5W)
	1x wireless Qi charger (10W)
External plug for powering the booth	1x plug (available in Type F, Type E, Type G, Type J and Type A)
External power cord length	3 metres
Power consumption	Standby mode: 3.4W Standby use: 57W At full brightness, including additional video call lighting: 98W  Input: 100-240 VAC, 10 A, 50-60 Hz Output: 100-240 VAC, 6.6 A, 50-60 Hz





# Haven One | Technical Specifications

## MATERIALS

**Exterior panels**                      Natural oak veneer covered MDF sheets, 26mm thickness.  
Treated with high scratch resistant coating.

**Glass**                                      Three layer sound control laminated glass (Stratophone 4.4.2) with special acoustic PVB layer.




**Handle**                                      100% natural oak.

**Interior panels**                      PET felt sheets, made with at least 60% recycled plastic.

**Table/shelf**                              Natural oak veneer-covered MDF with anti-fingerprint and scratch-resistant coating.

**Carpet**                                      Highly durable and stain resistant polyester fabric.

**Seating (optional add-on)**                      Height-adjustable ergonomic bar stool with built-in metal footrest.  
Comfortable soft velvet seat padded with high density elastic sponge.  
The maximum load capacity of up to 120 kg.  
Non-slip ring at the bottom.

**Colour options**                       natural oak     black     white



RATED ★★★★★ BY 220+ LEADING COMPANIES

# Haven Focus

By Office Acoustics



A premium one-person focus pod designed for deep work and seamless video calls.



## Haven Focus | Highlights



### Privacy you can count on

World-class soundproofing blocks a wide range of frequencies, ensuring unmatched privacy. Work with confidence in a quiet, distraction-free environment designed for focus and productivity.



### Superior ventilation for extended calls

Haven Focus's advanced ventilation system refreshes the air inside the booth every minute, maintaining a clean, fresh, and comfortable environment. Perfect for long work sessions or extended calls, it helps you stay focused.



### Lighting tailored to every task

Motion-activated LED lighting and LED light strips provide optimal brightness for any task. Whether focusing on detailed work or preparing for a video call, Haven Focus ensures the perfect lighting to support productivity.



### Ergonomic design

Designed with your comfort in mind, the booth features a height-adjustable desk for personalised use. An ergonomically designed chair is available as an add-on, providing extra support during long work sessions.

## Haven Focus | Main Features

### 1. ISO-certified soundproofing


Haven Focus delivers guaranteed privacy with a speech level reduction of up to 30dB, backed by the industry's official ISO 23351-1:2020 certification for office phone booths and meeting pods. Triple-layered acoustic glass enhances sound isolation, making it the right choice for distraction-free work.

### 2. Seamless connectivity

Haven Focus keeps you connected and powered with 2x electric sockets, USB-A and USB-C ports, an HDMI port, and a reliable Ethernet connection. Included monitor brackets support the 27" QHD conference call monitor add-on, equipped with a built-in Super HD camera.

### 3. Sophisticated dual LED lighting system

Motion-activated LED lighting, versatile LED light strips, and an advanced light controller deliver optimal brightness for any task. Whether you're concentrating on detailed work or setting up for a video call, Haven Focus ensures perfectly tailored lighting to enhance productivity and comfort.



### 4. Timeless plug-and-play simplicity

Designed for longevity, our pods focus on what truly matters - no unnecessary frills, no software to update or replace, and no subscription services. With streamlined plug-and-play functionality, they deliver hassle-free usability.

### 5. Custom-designed ventilation system

Haven Focus's advanced ventilation system ensures optimal airflow by extracting up to 240 m<sup>3</sup>/hour. The high-capacity ventilation keeps the air fresh and clean, maintaining a comfortable and healthy environment.

### 6. Fully automated built-in sensor

Our built-in sensor detects when someone enters or exits the pod, automatically turning the lighting on or off to ensure convenience and energy efficiency.



A compact and ergonomically designed booth, making it a perfect fit for any workspace.



Combining functionality with style, it offers ample space to accommodate all your gadgets. The booth's scratch-resistant panels add a touch of elegance and the glass panels on both sides ensure plenty of natural light accompanies the stylish design.



The interior is thoughtfully made of sound-absorbing PET panels with low-maintenance hardware and durable carpeting, making it both practical and functional.



Haven Focus features a thoughtfully integrated deep table, offering ample workspace to keep your devices and essentials neatly organised.



Custom-designed shelf



Ergonomic handle made of natural oak



Felt and carpet - highly durable, washable



Cable management system



Compact and modular design



Triplex glass panels




Office Acoustics

# Haven Focus | Technical Specifications


## DIMENSIONS AND SPACE REQUIREMENTS

Dimensions	Exterior:	H: 2250mm W: 1280mm D: 1000mm
	Interior:	H: 2040mm W: 1206mm D: 938mm
	Doorway:	H: 2020mm W: 740
	Shelf:	H: 870mm D: 450mm
Operating space requirements	H: 2350mm W: 1300mm D: 1800mm	
Installation space requirements	Installation requires 1000mm of free space around the pod.	
	Ceiling height must be at least 2350mm to facilitate the installation.	
Weight	298 kg	
Door operation ratio	160°   Left handed only	
Mobility	Easily move the pod without disassembling thanks to the built in casters. To relocate, simply raise the leveling guides, then lower them again once the pod is positioned in its new location.	
Shipping crate/ pallet dimensions	H: 1500mm W: 2350mm D: 1240mm	
	Weight: 478 kg	



## POWER AND ELECTRICAL SETUP

Available outlets and connections inside the booth	2x power outlets (available in Type F, Type E, Type G, Type J and Type A)
	1x USB-C (10W)
	1x USB-A (5W)
	Ethernet port
	HDMI
External plug for powering the booth	1x wireless Qi charger (10W)
	1x plug (available in Type F, Type E, Type G, Type J and Type A)
	3 metres
External power cord length	
Power consumption	Standby mode: 3.4W
	Standby use: 57W
	At full brightness, including additional video call lighting: 98W
	Input 100—240 VAC, 10 A*, 50—60 Hz Output 100—240 VAC, 6.6 A, 50—60 Hz





# Haven Focus | Technical Specifications

## MATERIALS

**Exterior panels**                      Natural oak veneer covered MDF sheets, 26mm thickness.  
Treated with high scratch resistant coating.

**Glass**                                      Three layer sound control laminated glass (Stratophone 4.4.2) with special acoustic PVB layer.




**Handle**                                      100% natural oak


**Interior panels**                      PET felt sheets, made with at least 60% recycled plastic.

**Table/shelf**                      Natural oak veneer covered MDF, with anti-fingerprint and scratch resistant coating.

**Carpet**                                      Highly durable and stain resistant polyester fabric.

**Seating (optional add-on)**                      Height-adjustable Steelcase Series 1 ergonomic chair.  
With integrated LiveBack technology, adaptive bolstering and 4D adjustable arms.  
The maximum load capacity of up to 120 kg.

**Colour options**                       natural oak     black     white



RATED ★★★★★ BY 220+ LEADING COMPANIES

# Haven Four

By Office Acoustics

**Coming soon**



A premium meeting pod for up to 4 people, designed for seamless teamwork, group meetings and collaborative video conferences.



## Haven | Sustainability

At Office Acoustics, we are dedicated to sustainability in every aspect of our business. Haven line reflects this commitment with eco-friendly materials, resource-efficient production, and impactful initiatives that support global environmental and social causes.



**4.7 million+**

Recycled plastic bottles used



**13.000+**

Solar lamps donated in Zambia



**273.000+**

Trees planted



### Sustainability at the core

Haven line is designed with a commitment to sustainability, blending eco-conscious practices with exceptional performance:

- ✓ Over 800 recycled plastic bottles are transformed into the acoustic felt used in every booth, effectively reducing plastic waste.
- ✓ The main frame is crafted entirely from natural, wood-based materials, eliminating the use of plastic or metal and prioritizing reusable resources.
- ✓ Modular construction promotes extended product lifecycles, reducing waste and resource consumption.
- ✓ Built with high-quality, durable materials to ensure longevity and minimize the need for replacements, further supporting environmental responsibility.



### Sustainable production and waste management

At Office Acoustics, we prioritise environmental efficiency in every step of our process:

- ✓ Over 800 recycled plastic bottles are transformed into the acoustic felt used in every booth, effectively reducing plastic waste.
- ✓ Renewable energy powers production where available, reducing carbon emissions.
- ✓ Advanced resource optimisation minimises waste, with leftover materials recycled or repurposed.
- ✓ Modular, fully recyclable components extend product life and reduce environmental impact.

Our commitment to eco-friendly practices is backed by globally recognised certifications, including ISO 14001:2015 for Environmental Management Systems and the prestigious EcoVadis Gold Star rating.



### Certificates and recognitions

Haven line exemplifies our commitment to sustainability through globally recognised certifications:

#### ✓ Ecovadis Gold Medal

Awarded the prestigious Ecovadis Gold Medal, we rank in the top 5% of companies worldwide for our dedication to impactful environmental initiatives and sustainable practices.

#### ✓ FSC-certified wood

The wood used in our booths is responsibly sourced from sustainably managed forests. With FSC certification, we ensure that our products actively support sustainable forestry and global conservation efforts.

#### ✓ ISO 14001:2015

for Environmental Management Systems.



Office  
Acoustics



Transportation

Our logistics are designed to minimize environmental impact at every step:

- ✓ Made-to-order production reduces waste and ensures optimal use of resources.
- ✓ Compact, modular designs enable tighter shipping loads, further cutting transport emissions.
- ✓ Packaging is entirely paper-based, ensuring easy recycling and alignment with sustainable practices.



Environmental contributions

Every Haven booth sold directly contributes to our sustainability initiatives:

- ✓ 25 trees planted to support reforestation and combat climate change worldwide.
- ✓ 2 solar lamps donated to families in Zambia, bringing clean, renewable energy to underserved communities.



Forest Stewardship Council

Certified for responsible forestry and sustainable material sourcing worldwide.



EcoVadis sustainability rating

Recognised for excellence in sustainability through rigorous global ratings.



# Office Acoustics is fully certified, ensuring sustainability, quality and safety. Driven by world-class standards.

## CERTIFICATES



All our phone booth models have been tested according to **ISO 23351-1:2020** - Acoustics - Measurement of speech level reduction of furniture ensembles and enclosures.



### FLAMMABILITY EVALUATED ACCORDING

- ✓ DIN EN 1021-1
- ✓ DIN EN 1021-2

[tuvsud.com/ps-cert](https://tuvsud.com/ps-cert)

**DIN EN 1021-1:2014** - Smouldering cigarette  
**DIN EN 1021-2:2014** - Gas flame (match flame equivalent)

## ISO COMPLIANCE

Our management systems have been certified according to:

- ISO 9001:2015** - Quality management systems
- ISO 9001:2015** - Environmental management
- ISO 9001:2015** - Information security
- ISO 9001:2015** - Occupational health and safety

Our products have been certified for electromagnetic compatibility (EMC), according to **IEC 60335-1:2020**.

# Get in touch

**Email:**

[hello@officeacoustics.com](mailto:hello@officeacoustics.com)


**Phones:**

+44 (0) 203 488 5200 [UK]

+33 (0) 1 84 60 62 10 [FR]

+49 (0) 89 201 94498 [DE]

+34 611 575 778 [ES]



[officeacoustics.com](https://officeacoustics.com)



Innovative acoustic solutions for the modern office.  
Made to last.



Office  
Acoustics