



NANAWALL OPENING GLASS WALLS

COMMERCIAL





PERFORMANCE MATTERS

The true measure of quality is how an opening glass wall performs when closed.



Watch NanaWall in Extreme Conditions:
[NanaWall.com/applications/cold-weather-climates](https://www.nanawall.com/applications/cold-weather-climates)

- **Energy Efficient**
When the NanaWall is closed, the energy efficient design keeps the cold on the outside while maintaining warmth inside—even right up against the glass and frames.
- **Seals out Wind and Rain**
Specialized seals and panel design provides superior humidity and moisture control while our sill designs resist wind-driven water from entering the home.
- **Extreme Weather Resistance**
When closed, our glass walls form a refuge against extreme weather keeping you comfortable and secure.



ENGINEERED TO LAST

Premium materials fashioned in clean, sleek lines. Hidden hardware.

Choice of all aluminum, solid wood, or solid wood aluminum clad.

For use in extreme weather climates, NanaWall offers the hurricane resistant SL73.

Florida Product Approval

Inswing: FL20108

Outswing: FL20107

See NanaWall.com for Florida product approval ratings for other systems

- **Highly Secure**

Secure tamper-resistant locks engage with the turn of a handle creating a secure multipoint connection.

- **Open and Close with Ease:**

Opening and closing a NanaWall is easy. One-handed operation quickly opens the panels as the rollers smoothly guide the panels to their open or closed position.

- **Quality Craftsmanship**

Every American-made and German engineered NanaWall system is backed by rigorous testing and high-grade materials.



NANAWALL FOLDING GLASS WALLS

NanaWall Folding Glass Walls offer clean lined aesthetics with narrow profiles and are available in aluminum, solid wood, or solid wood aluminum clad finishes. The panels can be top-hung or floor supported in inward or outward opening configurations. Numerous sill choices are available including a surface mounted and ADA compliant sill. Easy operation—no matter the size or number of panels.




- **Taller Heights, Wider Widths:** Panel heights of up to 12' (3660 mm) and widths of 4' (1220 mm) are possible.
- **Flexible Swing Door Placement:** Convenient swing entry doors, with an up to 180° swing plane, may be hinged to a side jamb or be configured within the chain of panels.
- **Control Construction Costs:** NanaWall Floor Supported folding systems offer smoother operation with stainless steel wheels on a stainless steel track and are height adjustable should building movement occur. Floor supported systems are ideal for applications where load-bearing capability of the header is a concern. The system's main weight is carried by the floor track.




NANAWALL HSW SYSTEMS

SINGLE TRACK SLIDING GLASS WALLS

NanaWall HSW systems' single track sliding glass walls offer you transformative design flexibility. With limitless spans of top-hung individual panels that ride within a single narrow head track over a single floor track—or over no floor track at all—our HSW systems help you make bolder creative statements, while producing multiple experiences in a single space. Available in aluminum and solid wood.



- **Unlimited Widths:** Extremely large openings are possible with unlimited spans of individual panels.
- **Any Shape Flexibility:** Virtually any shape is possible, including open corners and segmented curves.
- **Remote Panel Stacking:** Customizable stacking bay options allows panels to be parked remotely or hidden in closets.
- **Swing Doors that Slide Away:** HSW60 System allows swing doors to be placed anywhere in the panel span.
- **Clean Transitions:** Single floor track (or no floor track) offers cleaner lines and smoother transitions.



To request an HSW Systems brochure, please visit nanawall.com/brochure



cero[®] by NanaWall

This aluminum minimally framed large panel sliding glass wall offers the largest panes of glass offered by NanaWall. Simple in form yet engineered to perfection. Producing clean, uniform, and ultra-thin lines for maximum light filled spaces that connect the interior to the exterior.



- **Narrow Stiles and Rails—Symmetrical Picture Frame Effect:** With cero, the panel's rail and stiles are uniform with a consistent 1 5/16" (34 mm) top to bottom, achieving a symmetrical and minimal design.
- **A Floor to Ceiling Lens to the Outside:** The award-winning cero offers full floor to ceiling sliding glass panels with recessed top and bottom tracks.
- **Aesthetically Disappearing Floor Track:** cero II's non-thermally broken Flush Sill option is available for sheltered or interior environments creating aesthetically seamless transitions between spaces. Four sill options are available.
- **Multipoint Tamper-Resistant System:** With cero, security is provided with multipoint locking and a flat handle that is integrated into the 1 5/16" (34 mm) vertical profile stile to maintain the clean, minimal appearance.



To request a cero brochure, please visit nanawall.com/brochure



NANAWALL FRAMELESS GLASS WALLS

NanaWall's comprehensive frameless all glass product line consists of single track sliding, sliding pivot, folding, and center pivot systems. With all systems, the beauty of all glass is realized, allowing for maximum transparency, natural daylighting, and a clean, contemporary appearance.



- **Coordinating Systems:** HSW75, FSW75, and CSW75 can be mixed and matched to create solutions for unique design challenges.
- **No Vertical Profiles:** All glass panels with narrow top and bottom rail heights.
- **Single Track Operation, Sill or No Sill:** Product family offers solutions for sill or no sill configurations.
- **Large Panel Sizes:** Panels are available to 4' (1220 mm) wide and 10' 6" (3230 mm) in height (please contact NanaWall for larger options).
- **Shape and Configuration Flexibility:** Straight, segmented curve, T-intersections, and open corner designs available. Unlimited widths possible.

WE ARE COMMERCIAL MARKETPLACE TESTED

NanaWall opening glass walls stand up to the daily commercial grind, as well as the challenges of wind, water, extreme temperatures, forced entry, impact, and structural load.

- Independent testing results are available for air, water, forced entry and impact, thermal performance, and structural load.
- STC ratings for sound attenuation are available for select systems.
- Swing panels are tested for 500,000 cycles and meet industry operational standards (AAMA920) for the SL45, SL70, HSW60, HSW75, PrivaSEE, and ClimaCLEAR systems.






OUR SYSTEMS ARE SECURE AND DURABLE

- Multipoint locking entry doors as well as extra-long, tamper-resistant dual point locking rods between panels ensures each system meets or exceeds most forced entry testing for commercial grade door panels.
- Built-in adjustment and compensation points ensure continued ease of operation if building settling occurs.





NANAWALL INNOVATIONS & SOLUTIONS



PrivaSEE™

PrivaSEE is the only all glass single track sliding system specifically engineered for enhanced acoustical separation. PrivaSEE is independently tested and rated to an accomplished STC of 36.



To request a PrivaSEE brochure, please visit nanawall.com/brochure



▲
NW Acoustical 645

NW Acoustical 645 is the first floor supported folding glass wall able to achieve unprecedented sound control up to an impressive STC 45.



To request a NW Acoustical 645 brochure, please visit nanawall.com/brochure



To request a ClimaCLEAR brochure, please visit nanawall.com/brochure

▼
ClimaCLEAR®

Patent pending ClimaCLEAR is the only frameless all glass individual panel sliding system specifically engineered for transparent weather protection.





Offices / Interiors



Restaurants



Banks



Hotels



Retail



Sports Venues



Religious Institutions



Auto Showrooms



Hospitals



Lifestyle Shopping Centers



Educational Facilities

Performance—NFRC Tested and Labeled

See NanaWall.com for performance testing for each system.

Testing conducted at accredited and certified independent laboratories.



U-Value



Air Infiltration



Water Rating



Design Wind Load




Sound Transmission
Rated


Testing results vary per system. Please consult NanaWall or see the NanaWall Architectural Binder for actual test data for each model and configuration.

Sill Option Examples


See NanaWall.com for sill options for each system.




Low Profile Saddle Sill*




Higher Weather Performance Sill*




Hybrid Sill*



Flush Sill*



Socket**



Flush Sill***

* SL60 sill examples

** HSW system socket example

*** cero sill example

NanaWall Finishes, Glazing & Hardware Options

Standard 50 Finishes for Aluminum and Clad Systems

50 standard colors are available in powder coat and anodized finishes. *For accurate color swatch examples, please request our Powder Coating Finish Options brochure.*

STANDARD POWDER COAT OPTIONS



Custom Color Matching Available
Non-metallic colors only, with upcharge.

Wood Systems Finish Options

Standard woods include Sapeli Mahogany, Pine, Spruce, Meranti and Western Hemlock. Other specialty woods are available upon request. Please consult NanaWall for additional costs. *For accurate wood representation, please request a wood sample.*



** available with upcharge.*

Hardware Options

The standard locking hardware is compatible with a wide array of commercially available handle sets and escutcheon plates to match any design style.



Black Titanium Stainless Steel



Brushed Satin Stainless Steel

Glazing Area Options

Glazing options include insulated, low-E, argon filled triple insulated low-E, impact, and other specialty glass.



Explore our opening glass wall product families:



Folding



Sliding



Frameless



Minimal Sliding

- NanaWall opening glass walls are available factory direct through local architectural design representatives across North America. Our Certified Installation Network option ensures correct installation with speed and precision.
- From design to installation—we're here to help. Our Dedicated Design Team can answer your questions and assist with planning, ordering and optimizing your NanaWall options.

THE ONE AND ONLY NANAWALL

NanaWall has reinvented the category of opening glass wall systems. Throughout our 30-plus-year history, we have earned the trust of architects, builders, design professionals and homeowners. As a solutions provider, we reimagine the ways in which buildings, people and the elements interact.

Visit our showrooms and try a NanaWall for yourself.

NanaWall
Boundaries **Unbound**®

Nana Wall Systems, Inc.
100 Meadowcreek Drive #250
Corte Madera, CA 94925

800 873 5673
415 383 3148
Fax 415 383 0312

info@nanawall.com
NanaWall.com