




# PRODUCT CATALOGUE

April 2024

We build together.



**We build together**  
for a better living.





**Welcome to a world full of high quality,  
aesthetics and excellent service...  
in the world of THRAKON!**

The real experience of building materials and premium colors. Utilizing long-term experience and know-how, THRAKON is one of the largest research and production companies in the building materials, paints and varnishes industry. THRAKON has the ability to provide integrated services and solutions for a wide range of applications.

## **BRANDS**

THRAKON has an active presence in the market with the following leading brands.

**CLIMAPLUS**

**STATUS**

**DECOR**

**ULTRAPOR®**

**DESMOFLEX®**

**CARMYFIX®**

**REPI  
Fix**

# Why THRAKON?





### **Reliability**

THRAKON is one of the most reliable producers of mortars in Greece with guaranteed steady supply and six production facilities.



### **Quality**

We offer products, services and solutions of the highest quality which add value to our customers.



### **Responsibility**

THRAKON, since its foundation, presents in market high quality products and integrated solutions, that are innovative, environmentally friendly and economically profitable for the industry. We operate a continuous and reliable business strategy for our clients in order to justify and maintain their trust in us.



### **Technical Support**

THRAKON recognizing the importance of after sales services, is committed to provide complete solutions and advice from specialized engineers and experienced applicators. We want always be close to the customer with a high sense of responsibility.

# INDEX

## 01

### EXTERIOR THERMAL INSULATION SYSTEMS - CLIMAPLUS

Adhesives for insulation boards / Basic coat plaster	10
Insulation materials	11
Impregnating coating	14
Top coat	15
Climapaint Siloxan System	17
Reinforcement	17
Complementary products	18
Tools	19
Coloring groups table	20

9

## 02

### MICROCEMENT DECOR

Primers for preparation surfaces	23
Microcement Systems	24
Microcement Protection	24
Floor Reinforcement	26
	27

## 03

### PAINTS

Emulsion Paints / Coloring bases	29	32
Siloxan Paint	34	34
Acrylic Paints / Coloring bases	34	34
Substrates - Primers	36	36
Wood Protection / Coloring bases	38	38
Metal Protection	40	40
Stucco	43	43
Special Products	45	45
Epoxy - Polyurethane Paints	46	46
Solvents	47	47
Pigments	50	50

29

## 04

### TILE ADHESIVES - GROUTS

Gel Tile Adhesives	51	52
Tile Adhesives	52	52
Grouts	58	58
Antislip System	63	63
Primers & Cleaning Agents	63	63
Special Glues	65	65
Contact & Polyurethane Adhesives	66	66
Complementary Materials	67	67

51

# 05

## WATERPROOFING

Polyurethane	75
Bituminous PU Membrane	77
Crystalline	78
Cement Based	79
Acrylic Based	80
Complementary Products	81
Impregnating	82
Primers and Admixtures	83
Sealants	84

73

# 06

## REPAIRING MORTARS

Repairing Mortars	88
Complementary Reinforcement Products	91

87

# 07

## PLASTERS AND RENDERS

Plasters & Renders	94
THRAKON Mini Silo	97

93

# 08

## FLOORING SCREEDS

Cement based flooring screeds	100
Primers	101

99

### ICON MEMO

### CERTIFICATIONS / SYSTEMS


### INDEX

102

103

104





# 01

## EXTERIOR THERMAL INSULATION SYSTEMS - CLIMAPLUS

---

Adhesives for Insulation Boards / Basic Coat Plaster

---

Insulation materials

---

Impregnating Coating

---

Top Coat

---

Climapaint siloxan system

---

Reinforcement

---

Complementary Products

---

Tools

---

Coloring groups table

---



### CLIMABOND THC 403

#### Cement based adhesive

Cement based adhesive, polymer modified. It complies with EN 13499 and ETAG 004.



Suitable for bonding thermal insulation boards on exterior thermal insulation systems (EPS/ XPS/ Mineral Wool).



Exterior use



3,5 - 4,0 kg/m<sup>2</sup>



60 items



Code	Pkg	Shade
P11830125	25 kg	Grey



### PRO THC 404

#### Fiber reinforced, cement based adhesive - plaster

Fiber reinforced, polymer modified, cement based mortar.



Suitable for bonding and plastering thermal insulation boards on exterior thermal insulation systems.



Exterior use



3,5 - 4,0 kg/m<sup>2</sup>



60 items



Code	Pkg	Shade
P11834325	25 kg	Grey
P11834225	25 kg	White



### FIBERPLUS THC 405

#### Fiber reinforced, cement based adhesive - plaster

Fiber reinforced, polymer modified, cement based mortar. It consists of cement and quartz sand, limestone fillers and admixtures. It complies with EN 13499 and ETAG 004.



Suitable for bonding and plastering thermal insulation boards on exterior thermal insulation systems.



Exterior use



3,5 - 4,0 kg/m<sup>2</sup>



60 items



Code	Pkg	Shade
P11830325	25 kg	Grey
P11830425	25 kg	White



### CLIMAFLEX THC 410

#### Highly flexible, fiber reinforced, adhesive - plaster

Premium, highly flexible fiber-reinforced, polymer modified, cement based mortar with increased strength. It consists of cement, limestone fillers, polypropylene fibers and admixtures. It complies with EN 13499 and ETAG 004.



Suitable for bonding and plastering thermal insulation boards on exterior thermal insulation systems. Highly recommended for the implementation of CLIMAPLUS with Mineral Wool.



Exterior use



3,5 - 4,0 kg/m<sup>2</sup> (per layer)  
6,0 - 7,0 kg/m<sup>2</sup> (as coating  
for leveled surfaces)



60 items (25 kg)



4 items (5 kg)



Code	Pkg	Shade
P11830005	5 kg	Grey
P11831005	5 kg	White
P11831325	25 kg	Grey
P11831225	25 kg	White



### CLIMAFLEX THC 410 C

#### Coarse-grained, flexible, fiber reinforced, adhesive - plaster

Coarse grained, fiber reinforced, polymer modified, cement based mortar. It consists of cement, quartz sand with 1.5 mm max. grain size, limestone fillers and admixtures. It complies with EN 13499 and ETAG 004.



Suitable for bonding and plastering thermal insulation boards on exterior thermal insulation systems.



Exterior use



3,0 - 4,0 kg/m<sup>2</sup>



60 items



Code	Pkg	Shade
P11331425	25 kg	Grey
P11831125	25 kg	White



### ORGANIC BASECOAT THC 420

Organic, fiber reinforced, adhesive - plaster

Organic fiber reinforced basic coat, ready for use. Reinforced with polypropylene fibers and admixtures. It is highly flexible and complies with EN 15824.

 Suitable for bonding and plastering thermal insulation boards on exterior thermal insulation systems.



Exterior use



3,0 - 3,5 kg/m<sup>2</sup>



36 items



Code	Pkg	Shade
P21390025	25 kg	Beige



### CLIMAPLUS STICK

One component, low expansion for bonding EPS

Polyurethane foam, one-component for bonding EPS and XPS. Offers excellent quality and durability. Replaces traditional cementitious adhesives, accelerating implementation process. Saves storage space and makes application easier. Excellent traction and insulation.

 It is ideal for mounting heat insulation panels and filling voids during adhesive application. Suitable for wooden type construction materials adhered to concrete, metal, etc. Suggested for applications that need minimum expansion such as ETICS, mounting and isolating window and door frames, wall plugging etc.



Exterior use



Up to 9 m<sup>2</sup> per bottle



12 items (800 g)

Code	Pkg
T10310021	800 g



### CLIMAPLUS STICK GUN

One component polyurethane gun foam, low expansion for bonding EPS

Polyurethane foam, one-component for bonding EPS and XPS. Offers excellent quality and durability. Replaces traditional cementitious adhesives, accelerating implementation process.

 It is ideal for mounting heat insulation panels and filling voids during adhesive application. Suitable for wooden type construction materials adhered to concrete, metal, etc. Suggested for applications that need minimum expansion such as ETICS, mounting and isolating window and door frames, wall plugging etc.



Exterior use



Up to 14 m<sup>2</sup> per bottle



12 items (800 g)

Code	Pkg
T10310020	800 g

## INSULATION MATERIALS



### PU FOAM

One component, self expanding

Self-expanding polyurethane foam, one component, reacts and cures in contact with air and humidity. It has excellent adhesive properties in almost every building material.

 It is especially recommended for filling holes and gaps of thermal insulation boards, in application of the exterior thermal insulation system. It is waterproof, anti-mould and can be repainted.



Exterior use



12 Items

Code	Pkg
T10000420	750 mL



### PU FOAM GUN

One component, self expanding Self-expanding

Self-expanding polyurethane foam, one component, reacts and cures in contact with air and humidity. It has excellent adhesive properties in almost every building material.

 It is especially recommended for filling holes and gaps of thermal insulation boards, in application of the exterior thermal insulation system. It is waterproof, anti-mould and can be repainted.



Exterior use



12 Items

Code	Pkg
T10000430	750 mL



### ULTRAPOR® EPS 80

#### Expanded polystyrene boards

Expanded polystyrene (EPS) boards.

 Suitable for the complete external thermal insulation system CLIMAPLUS.

 1000 x 500  0,036 W/mK  5 days

**Indicative Density:** 15 - 17 kg/m<sup>3</sup>

(Also available in other thicknesses upon request)



Code	Thickness (mm)	m <sup>2</sup> /Pkg
P11208030	30	10,00
P11208040	40	7,50
P11208050	50	6,00
P11208060	60	5,00
P11208070	70	4,50
P11208080	80	4,00
P11208090	90	3,50
P11208010	100	3,00



### ULTRAPOR® EPS 100

#### Expanded polystyrene boards

Expanded polystyrene (EPS) boards. Increased density and improved thermal conductivity.

 Suitable for the complete external thermal insulation system CLIMAPLUS.

 1000 x 500  0,035 W/mK  5 days

**Indicative Density:** 18 - 20 kg/m<sup>3</sup>

(Also available in other thicknesses upon request)



Code	Thickness (mm)	m <sup>2</sup> /Pkg
P11201030	30	10,00
P11201040	40	7,50
P11201050	50	6,00
P11201060	60	5,00
P11201070	70	4,50
P11201080	80	4,00
P11201090	90	3,50
P11201010	100	3,00



### ULTRAPOR® EPS 150

#### Expanded polystyrene boards

Expanded polystyrene (EPS) boards. Increased density.

 Suitable for application of the CLIMAPLUS external thermal insulation system, on concrete elements, with placement on the formwork before concreting, such as columns, beams and slabs.

 1000 x 500  0,034 W/mK  5 days

**Indicative Density:** 25 - 27 kg/m<sup>3</sup>

(Also available in other thicknesses upon request)



Code	Thickness (mm)	m <sup>2</sup> /Pkg
P11201530	30	10,00
P11201540	40	7,50
P11201550	50	6,00
P11201560	60	5,00
P11201570	70	4,50
P11201580	80	4,00
P11201590	90	3,50
P11201510	100	3,00



### ULTRAPOR® EPS 200

#### Expanded polystyrene boards

Expanded polystyrene (EPS) fixed boards. Increased density.

 Suitable for application of the CLIMAPLUS external thermal insulation system, on concrete elements, with placement on the formwork before concreting, such as columns, beams and slabs. Also, it can be applied for the thermal insulation of roofs.

 1000 x 500  0,033 W/mK  5 days

**Indicative Density:** 30 - 32 kg/m<sup>3</sup>

(Also available in other thicknesses upon request)



Code	Thickness (mm)	m <sup>2</sup> /Pkg
P11202030	30	10,00
P11202040	40	7,50
P11202050	50	6,00
P11202060	60	5,00
P11202070	70	4,50
P11202080	80	4,00
P11202090	90	3,50
P11202010	100	3,00



### ULTRAPOR® GRAPHITE EPS 80

#### Self-extinguishing graphite expanded polystyrene

Boards of self-extinguishing graphite expanded polystyrene. 15%-20% better thermal insulation properties than conventional white expanded polystyrene plates.



Suitable for the complete external thermal insulation system CLIMAPLUS.



1000 x 500



0,031 W/mK



5 days



Code	Thickness (mm)	m <sup>2</sup> /Pkg
P11208130	30	10,00
P11208140	40	7,50
P11208150	50	6,00
P11208160	60	5,00
P11208170	70	4,50
P11208180	80	4,00
P11208190	90	3,50
P11208100	100	3,00



### ULTRAPOR® GRAPHITE EPS 100

#### Self-extinguishing graphite expanded polystyrene

Boards of self-extinguishing graphite expanded polystyrene. 15%-20% better thermal insulation properties than conventional white expanded polystyrene plates.



Suitable for the complete external thermal insulation system CLIMAPLUS.



1000 x 500



0,030 W/mK



5 days



Code	Thickness (mm)	m <sup>2</sup> /Pkg
P11201130	30	10,00
P11201140	40	7,50
P11201150	50	6,00
P11201160	60	5,00
P11201170	70	4,50
P11201180	80	4,00
P11201190	90	3,50
P11201110	100	3,00



### ULTRAPOR® GRAPHITE EPS 150

#### Self-extinguishing graphite expanded polystyrene

Boards of self-extinguishing graphite expanded polystyrene. 15%-20% better thermal insulation properties than conventional white expanded polystyrene plates.



Suitable for the complete external thermal insulation system CLIMAPLUS.



1000 x 500



0,030 W/mK



5 days



Code	Thickness (mm)	m <sup>2</sup> /Pkg
P11201503	30	10,00
P11201504	40	7,50
P11201505	50	6,00
P11201506	60	5,00
P11201507	70	4,50
P11201508	80	4,00
P11201509	90	3,50
P11201501	100	3,00



### ULTRAPOR® GRAPHITE EPS 200

#### Self-extinguishing graphite expanded polystyrene

Fixed boards of self-extinguishing graphite expanded polystyrene. They present 15%-20% better thermal insulation properties than conventional white expanded polystyrene plates.



Suitable for the complete external thermal insulation system CLIMAPLUS..



1000 x 500



0,030 W/mK



5 days



Code	Thickness (mm)	m <sup>2</sup> /Pkg
P11202130	30	10,00
P11202140	40	7,50
P11202150	50	6,00
P11202160	60	5,00
P11202170	70	4,50
P11202180	80	4,00
P11202190	90	3,50
P11202100	100	3,00



## ULTRAPOR® XPS

### Extruded polystyrene boards

Fixed boards of extruded polystyrene boards (XPS)

 Suitable for application in the exterior thermal insulation system CLIMAPLUS. Ideal for applications in high humidity areas, due to lack of water absorption characteristic of the extruded polystyrene.

 1000 x 600

 \* 0,033 W/mK

Thickness (cm)

3

0,034 W/mK

5

0,036 W/mK

7 - 10

 10 days

\*  $\lambda_D(\max)$ : Thermal conductivity coefficient after technical ageing. It is equivalent to the properties of the product after approximately 25 years.



Code	Thickness (mm)	m <sup>2</sup> /Pkg
T10500300	30	8,40
T10500500	50	4,80
T10510070	70	3,60
T10510080	80	3,00
T10510010	100	2,40



## ULTRAWOOL

### Thermal insulation boards

Non-combustible mineral wool insulation boards with enhanced thermal and sound insulation properties.

 Suitable for the integrated system of exterior insulation CLIMAPLUS. Highly recommended for indoor system applications, and generally in applications with high sound insulation and fire resistance requirements.

 1000 x 600

 0,037 W/mK

 20 days



Code	Thickness (mm)	m <sup>2</sup> /Pkg
C/C	100	2,88

## IMPREGNATING COATING



## CLIMA PRIMER GLX 494

### Acrylic primer - Transparent

Acrylic based primer with high penetration. Colored according to the shade chosen for final coating (organic plaster).

 Suitable for the preparation of the substrate prior to the application of acrylic based organic plasters and paints.

 Exterior & Interior use

 ~0,20 - 0,25 kg/m<sup>2</sup> per layer

 36 items (25 kg)  
60 items (5 kg)

 White and in thousands shades through the ULTRA COLOR SYSTEM of THRAKON.

**Dilution:** 15% - 20% with water

\* For group shades, see page 20.



Code	Pkg
P21470005	White 5 kg
P21800025	White 25 kg
C/C	Group A 5 kg
C/C	Group A 25 kg
C/C	Group B 5 kg
C/C	Group B 25 kg
C/C	Group C 5 kg
C/C	Group C 25 kg



### CLIMASIL PRIMER GLX 498

#### Silicone primer - Transparent

Silicone based primer with high penetration. Colored according to the shade chosen for final coating (organic plaster).

Suitable for the preparation of the substrate prior to application of organic silicone-based plasters (DEC 438).

Exterior & Interior use

36 items (25 kg)  
60 items (5 kg)

~0,20 - 0,25 kg/m<sup>2</sup> per layer

White and in thousands shades through the ULTRA COLOR SYSTEM of THRAKON.

**Dilution:** up to 5% with water.

\* For group shades, see page 20.



Code	Pkg
P21474981	White 5 kg
P21474980	White 25 kg
C/C	Group A 5 kg
C/C	Group A 25 kg
C/C	Group B 5 kg
C/C	Group B 25 kg
C/C	Group C 5 kg
C/C	Group C 25 kg

## TOP COAT

### - ACRYLIC BASED ORGANIC PLASTERS



### PRIMO TECH SILICONE

#### Acrylic base coating, modified with silicon resins

Acrylic coating reinforced with silicone. It has excellent adhesion and offers colored final surfaces in different types (RILLEN and SCRATCH), without the need for painting.

Suitable for use as a final layer plaster on the finished CLIMAPLUS external thermal insulation system and in interior and exterior masonry.

Exterior & Interior use

36 items

It can be colored in more than 600 shades, through the ULTRA COLOR SYSTEM of THRAKON.

#### RILLEN

2,0 mm: 2,7 kg/m<sup>2</sup>

#### SCRATCH

1,2 mm: 2,0 kg/m<sup>2</sup>  
1,5 mm: 2,5 kg/m<sup>2</sup>  
2,0 mm: 3,3 kg/m<sup>2</sup>



Code	Pkg
C/C	White 25 kg
C/C	Group A 25 kg
C/C	Group B 25 kg
C/C	Group C 25 kg

\* For group shades, see page 20.



### CLIMA PLASTER DEC 428

#### Decorative acrylic plaster

Acrylic based render with high elasticity and excellent adhesion, offering tinted end surfaces in different types (RILLEN or SCRATCH), without the need to paint.

Suitable for application as a final coat render for exterior thermal insulation system CLIMAPLUS and for indoor or outdoor masonry. Colored according to the new CLIMAPLUS fan deck, with more than 500 shades.

Exterior & Interior use

36 items

It can be colored in more than 600 shades, through the ULTRA COLOR SYSTEM of THRAKON.

#### RILLEN

2,0 mm: 2,7 kg/m<sup>2</sup>

#### SCRATCH

1,0 mm: 1,8 kg/m<sup>2</sup>  
1,2 mm: 2,0 kg/m<sup>2</sup>  
1,5 mm: 2,5 kg/m<sup>2</sup>  
2,0 mm: 3,3 kg/m<sup>2</sup>

#### FINE

2,0 kg/m<sup>2</sup>



Code	Pkg
C/C	White 25 kg
C/C	Group A 25 kg
C/C	Group B 25 kg
C/C	Group C 25 kg

\* For group shades, see page 20.



### MOZAIC PLASTER DEC 433

#### Mosaic decorative plaster

Decorative and practical solution, with colored marble grains, forming an impressive mosaic surface.



Use as a final coat render for exterior thermal insulation system CLIMAPLUS and for indoor or outdoor masonries.



Exterior & Interior use



36 items



2,8 - 3,2 kg/m<sup>2</sup>



5 days



Available in 16 new shades



Code	Pkg
C/C	25 kg

## - SILICONE PLASTERS



### CLIMASIL PLASTER DEC 438

#### Colored silicone plaster

Silicone render with high vapor permeability and additional antifungal activity. Offers colored end surfaces in different types (RILLEN or SCRATCH).



Use as a final coat render for exterior thermal insulation system CLIMAPLUS and for indoor or outdoor masonries. Excellent solution for constructions near or by the sea.



Exterior & Interior use



36 items



**RILLEN**

2,0 mm: 2,7 kg/m<sup>2</sup>



It can be colored in more than 600 shades, through the ULTRA COLOR SYSTEM of THRAKON.



**SCRATCH**

1,0 mm: 1,8 kg/m<sup>2</sup>  
1,2 mm: 2,0 kg/m<sup>2</sup>  
1,5 mm: 2,5 kg/m<sup>2</sup>  
2,0 mm: 3,3 kg/m<sup>2</sup>



Code	Pkg
C/C	White 25 kg
C/C	Group A 25 kg
C/C	Group B 25 kg
C/C	Group C 25 kg

\* For group shades, see page 20.

## - CEMENT BASED DRY PLASTERS



### DEC 424 SCRATCH

#### White inorganic plaster

White, cement based render of type SCRATCH, enhanced with silicone resins. Water-repellent, UV-resistant, with very strong adhesion to inorganic substrates. Suitable for substrates with high requirements in terms of flexibility and adhesion.



Use as a final coat render for exterior thermal insulation system CLIMAPLUS and for indoor or outdoor masonries.



Exterior & Interior use



60 items

Code	Pkg
C/C	25 kg



### DEC 424 FINE

#### White smooth inorganic plaster

White, cement based render with smooth finish surface. Enhanced with special resins. Water-repellent, UV-resistant (UV) and with very strong adhesion to inorganic substrates.



Use as a final coat render for exterior thermal insulation system CLIMAPLUS and for indoor or outdoor masonries.



Exterior & Interior use



60 items



1,5 - 2 kg/m<sup>2</sup> per 2 - 3 mm.

Code	Pkg
C/C	25 kg

**DEC 425 RILLEN****White inorganic plaster**

White, cement based render of type RILLEN, enhanced with special silicone resins. Water-repellent, UV-resistant, with very strong adhesion to inorganic substrates. Suitable for substrates with high requirements in terms of flexibility and adhesion.

 Use as a final coat render for exterior thermal insulation system CLIMAPLUS and for indoor or outdoor masonry.

 Exterior & Interior use

 2,0 mm: 3,0 - 3,5 kg/m<sup>2</sup>  
3,5 mm: 5,5 - 6,0 kg/m<sup>2</sup>

 60 items

Code	Pkg
C/C	25 kg

**CLIMAPAIN SILOXAN SYSTEM****CLIMAPAIN SILOXAN****High quality innovative silicone - siloxane paint**

The unique composition of CLIMAPAIN SILOXAN offers external surfaces excellent color stability, quick evaporation of moisture from the surface and an effective shield against ambient humidity.

 Suitable for all external surfaces and ideal for renewing surfaces that have been applied the external thermal insulation system.

 Exterior & Interior use

 10 - 12 m<sup>2</sup>/L

 80 items (3 L)  
36 items (10L)



Code	Pkg	Shade
P21800203	3 L	White
P21800210	10 L	

Code	Pkg	Product
P21800213	3 L	Base D
P21800220	10 L	

**CLIMAPRIMER SILOXAN****High quality colored, odorless, waterproof, silicone-based acrylic micronized water primer**

The ecological silicone-based acrylic micronized primer CLIMAPRIMER SILOXAN gives the applied surface waterproofing and excellent breathability, while at the same time shielding the substrate from rising soil moisture and the migration of salts from the substrate to the final painted surface.

 Suitable for new and existing porous external and internal surfaces, which will then be painted with CLIMAPAIN SILOXAN.

 Exterior & Interior use

 10 - 15 m<sup>2</sup>/L

 80 items (5 L)



Code	Pkg	Shade
P21800205	5 L	Translucent

**REINFORCEMENT****CLIMAPLUS MESH (160 g/m<sup>2</sup>)****Anti-alkaline fiberglass mesh, produced under ETAG 004.**

 Suitable for the reinforcement of the basic layer of the exterior thermal insulation system CLIMAPLUS.

 Exterior use

 1,1 m/m<sup>2</sup>

 33 rolls

 1m x 50m

**Grid size:** 4 x 4 mm

Code	m <sup>2</sup> / Palette
T10320020	1650



### CLIMAPLUS PROFESSIONAL (160 g/m<sup>2</sup>)

Anti-alkaline fibreglass mesh, produced under ETAG 004.

ETAG  
004

 Suitable for reinforcing the basic layer of the exterior thermal insulation system CLIMAPLUS.

 Exterior use

 1,1 m/m<sup>2</sup>

 35 rolls

 1m x 50m

**Grid size:** 4 x 4 mm

Code	m <sup>2</sup> / Palette
T10320120	1750

## COMPLEMENTARY PRODUCTS



### PLASTIC ANCHORS FOR BRICKS

CLIMAPLUS - Plastic anchor for fastening insulation boards on bricks. Applied by nailing. European Technical Approval (ETA).

 200 Items

CE CLIMA  
PLUS

Code	Dimensions
T10121070	60mm x 10mm x 70mm
T10121090	60mm x 10mm x 90mm
T10121120	60mm x 10mm x 120mm
T10121140	60mm x 10mm x 140mm
T10121160	60mm x 10mm x 160mm
T10121180	60mm x 10mm x 180mm
T10121200	60mm x 10mm x 200mm



### STEEL ANCHORS FOR BRICKS

CLIMAPLUS – Steel anchor for fastening insulation boards on bricks. Applied by nailing. European Technical Approval (ETA).

 200 Items

CE CLIMA  
PLUS

Code	Dimensions
T10122095	60mm x 10mm x 95mm
T10122115	60mm x 10mm x 115mm
T10122135	60mm x 10mm x 135mm
T10122155	60mm x 10mm x 155mm



### CLIMAPLUS BOLTED STEEL ANCHOR


CLIMAPLUS - Bolted steel anchor for AAC substrates. European Technical Approval (ETA).

 200 Items

 10 days

CE

Code	Dimensions
T010111152	60mm x 8mm x 115mm
T010111152	60mm x 8mm x 135mm
T010111152	60mm x 8mm x 155mm
T010111152	60mm x 8mm x 175mm
T010111152	60mm x 8mm x 195mm



### CORNER BEAD WITH MESH

CLIMAPLUS – PVC Corner bead profile with fiberglass mesh.



60 Items

Code	Dimensions
T010000530	2,5m x 0,08m x 0,12m




### WATERDROP PROFILE WITH MESH

CLIMAPLUS - waterdrop PVC profile with fiberglass mesh.



40 Items

Code	Dimensions
T10000671	2m x 0,10m x 0,10m



### HIDDEN WATERDROP PROFILE WITH MESH

CLIMAPLUS - Hidden waterdrop PVC profile with fiberglass mesh.



40 Items

Code	Dimensions
T10000680	2m x 0,10m x 0,10m



### CLIMAPLUS STARTER

CLIMAPLUS aluminium profile for starting application of CLIMAPLUS System.



20 Items



7 Days

Code	Dimensions
T10000450	2,5 m / 33 mm
T10000460	2,5 m / 53 mm
T10000480	2,5 m / 73 mm
T10000490	2,5 m / 83 mm

## TOOLS



### PLASTIC MILL

Plastic mill for modulating shoulder on insulation plates for boxing anchors.

Code	Diameter
T010000500	68 mm



### METAL MILL

Metal mill for modulating shoulder on insulation plates for boxing anchors.

Code	Diameter
T010000440	60 mm

# ULTRA COLOR COLORING GROUPS TABLE

Code	Group								
UC-001	A	UC-054	A	UC-103	B	UC-155	A	UC-204	B
UC-002	A	UC-055	A	UC-104	B	UC-156	B	UC-205	C
UC-003	A	UC-056	A	UC-105	B	UC-157	B	UC-206	C
UC-004	A	UC-057	A	UC-109	A	UC-158	B	UC-207	B
UC-005	A	UC-058	B	UC-110	A	UC-159	B	UC-208	B
UC-006	A	UC-059	B	UC-111	A	UC-160	B	UC-209	A
UC-007	A	UC-060	B	UC-112	A	UC-161	A	UC-210	B
UC-008	A	UC-061	B	UC-113	A	UC-162	A	UC-211	B
UC-009	A	UC-062	B	UC-114	A	UC-163	A	UC-212	B
UC-010	A	UC-063	B	UC-115	A	UC-164	A	UC-213	B
UC-011	A	UC-064	B	UC-116	B	UC-165	A	UC-214	B
UC-012	A	UC-065	B	UC-117	A	UC-166	A	UC-215	B
UC-013	B	UC-066	B	UC-118	A	UC-167	A	UC-216	A
UC-014	A	UC-067	B	UC-119	A	UC-168	B	UC-217	A
UC-015	B	UC-068	B	UC-120	A	UC-169	A	UC-218	A
UC-016	B	UC-069	B	UC-121	A	UC-170	B	UC-219	A
UC-017	B	UC-070	B	UC-122	A	UC-171	B	UC-220	A
UC-018	B	UC-071	B	UC-123	B	UC-172	B	UC-221	A
UC-019	B	UC-072	B	UC-124	B	UC-173	B	UC-222	A
UC-020	B	UC-073	B	UC-125	B	UC-174	B	UC-223	A
UC-021	B	UC-074	B	UC-126	B	UC-177	B	UC-224	A
UC-022	B	UC-077	A	UC-127	B	UC-178	B	UC-225	A
UC-023	B	UC-078	A	UC-128	B	UC-179	B	UC-226	A
UC-024	B	UC-079	A	UC-129	A	UC-180	B	UC-227	B
UC-025	B	UC-080	A	UC-130	A	UC-181	A	UC-228	B
UC-026	B	UC-081	A	UC-131	B	UC-182	A	UC-229	B
UC-027	B	UC-082	A	UC-132	B	UC-183	A	UC-230	B
UC-028	B	UC-083	A	UC-133	B	UC-184	A	UC-231	B
UC-029	B	UC-084	A	UC-134	B	UC-185	A	UC-232	B
UC-030	B	UC-085	A	UC-135	B	UC-186	A	UC-233	B
UC-031	B	UC-086	A	UC-136	B	UC-187	A	UC-234	B
UC-032	B	UC-087	A	UC-137	B	UC-188	A	UC-235	B
UC-033	B	UC-088	A	UC-138	B	UC-189	A	UC-237	B
UC-034	B	UC-089	A	UC-141	A	UC-190	A	UC-245	A
UC-037	B	UC-090	A	UC-142	A	UC-191	A	UC-246	A
UC-038	B	UC-091	A	UC-143	A	UC-192	A	UC-247	A
UC-039	B	UC-092	B	UC-144	A	UC-193	A	UC-248	B
UC-041	B	UC-093	A	UC-145	A	UC-194	A	UC-249	A
UC-045	A	UC-094	B	UC-146	A	UC-195	B	UC-250	B
UC-046	A	UC-095	B	UC-147	A	UC-196	B	UC-251	B
UC-047	A	UC-096	B	UC-148	A	UC-197	A	UC-252	B
UC-048	A	UC-097	B	UC-149	A	UC-198	A	UC-253	B
UC-049	A	UC-098	B	UC-150	A	UC-199	B	UC-254	A
UC-050	A	UC-099	B	UC-151	A	UC-200	B	UC-255	B
UC-051	A	UC-100	B	UC-152	A	UC-201	B	UC-256	A
UC-052	A	UC-101	B	UC-153	A	UC-202	B	UC-257	A
UC-053	A	UC-102	B	UC-154	A	UC-203	B	UC-258	B



GROUP A



GROUP B



GROUP C

Code	Group										
UC-259	B	UC-309	A	UC-356	B	UC-403	A	UC-450	B	UC-450	B
UC-260	B	UC-310	A	UC-357	B	UC-404	A	UC-451	B	UC-451	B
UC-261	A	UC-311	A	UC-358	B	UC-405	B	UC-452	B	UC-452	B
UC-262	B	UC-312	A	UC-359	B	UC-406	B	UC-453	B	UC-453	B
UC-263	B	UC-313	A	UC-360	B	UC-407	B	UC-454	B	UC-454	B
UC-264	B	UC-314	A	UC-361	A	UC-408	B	UC-455	B	UC-455	B
UC-265	B	UC-315	A	UC-362	A	UC-409	A	UC-456	B	UC-456	B
UC-266	B	UC-316	A	UC-363	A	UC-410	B	UC-457	B	UC-457	B
UC-267	B	UC-317	A	UC-364	A	UC-411	B	UC-458	A	UC-458	A
UC-269	A	UC-318	A	UC-365	A	UC-412	B	UC-459	A	UC-459	A
UC-270	B	UC-319	A	UC-366	A	UC-413	A	UC-460	B	UC-460	B
UC-271	B	UC-320	A	UC-367	A	UC-414	B	UC-461	B	UC-461	B
UC-272	B	UC-321	A	UC-368	A	UC-415	B	UC-462	B	UC-462	B
UC-273	B	UC-322	A	UC-369	B	UC-416	B	UC-463	B	UC-463	B
UC-274	B	UC-323	A	UC-370	B	UC-417	A	UC-464	B	UC-464	B
UC-275	B	UC-324	A	UC-371	A	UC-418	A	UC-465	B	UC-465	B
UC-276	C	UC-325	A	UC-372	A	UC-419	A	UC-466	B	UC-466	B
UC-277	A	UC-326	A	UC-373	B	UC-420	A	UC-467	B	UC-467	B
UC-278	B	UC-327	A	UC-374	B	UC-421	A	UC-468	B	UC-468	B
UC-279	B	UC-328	A	UC-375	B	UC-422	A	UC-469	A	UC-469	A
UC-280	B	UC-329	A	UC-376	A	UC-423	A	UC-470	A	UC-470	A
UC-281	B	UC-330	A	UC-377	A	UC-424	A	UC-471	A	UC-471	A
UC-282	B	UC-331	B	UC-378	A	UC-425	A	UC-472	B	UC-472	B
UC-283	B	UC-332	A	UC-379	A	UC-426	A	UC-473	A	UC-473	A
UC-285	B	UC-333	A	UC-380	A	UC-427	A	UC-474	A	UC-474	A
UC-286	B	UC-334	A	UC-381	A	UC-428	A	UC-475	A	UC-475	A
UC-287	C	UC-335	A	UC-382	A	UC-429	A	UC-476	A	UC-476	A
UC-289	A	UC-336	A	UC-383	B	UC-430	B	UC-477	B	UC-477	B
UC-290	A	UC-337	A	UC-384	A	UC-431	A	UC-478	B	UC-478	B
UC-291	A	UC-338	A	UC-385	A	UC-432	A	UC-479	B	UC-479	B
UC-292	A	UC-339	A	UC-386	A	UC-433	A	UC-480	B	UC-480	B
UC-293	A	UC-340	A	UC-387	B	UC-434	A	UC-481	B	UC-481	B
UC-294	A	UC-341	A	UC-388	B	UC-435	B	UC-482	B	UC-482	B
UC-295	A	UC-342	A	UC-389	B	UC-436	B	UC-483	B	UC-483	B
UC-296	A	UC-343	A	UC-390	B	UC-437	A	UC-484	B	UC-484	B
UC-297	A	UC-344	A	UC-391	A	UC-438	B	UC-485	B	UC-485	B
UC-298	A	UC-345	A	UC-392	A	UC-439	A	UC-486	B	UC-486	B
UC-299	A	UC-346	A	UC-393	A	UC-440	B	UC-487	B	UC-487	B
UC-300	A	UC-347	A	UC-394	A	UC-441	A	UC-488	B	UC-488	B
UC-301	A	UC-348	A	UC-395	A	UC-442	A	UC-490	B	UC-490	B
UC-302	A	UC-349	A	UC-396	A	UC-443	A	UC-493	B	UC-493	B
UC-303	A	UC-350	A	UC-397	A	UC-444	B	UC-494	B	UC-494	B
UC-304	A	UC-351	A	UC-398	A	UC-445	A	UC-497	B	UC-497	B
UC-305	A	UC-352	A	UC-399	A	UC-446	B	UC-498	B	UC-498	B
UC-306	A	UC-353	A	UC-400	A	UC-447	B	UC-499	B	UC-499	B
UC-307	A	UC-354	A	UC-401	A	UC-448	B	UC-500	B	UC-500	B
UC-308	A	UC-355	A	UC-402	A	UC-449	A				

\* The shades are displayed in numerical order while at the same time they are separated by color category.



# 02

## MICROCEMENT DECOR

Primers for surface preparation

---

Microcement Systems

---

Microcement Protection

---

Floor Reinforcement



## PRIMERS FOR SURFACE PREPARATION



### GLX 292 FLEX PRIM

#### Acrylic primer - High penetration

Ready to use micronized acrylic water-based primer with high penetration ability.



Ideal for preparing each new or old porous surface such as plaster, brick, concrete, plastered walls etc, creating an adhesion bridge for acrylic plasters, water paints, mortars, tile adhesives, acrylic and cementitious waterproofing spreads etc.



Exterior & Interior use



15-20 m<sup>2</sup>/L depending on surface porosity



240 items (1 kg)  
84 items (5 kg)  
24 items (20 kg)



16 items (1 kg)

Code	Pkg
P21472920	1 kg
P21472925	5 kg
P21472921	20 kg



### GLX 298 PREMIUM

#### Acrylic based primer for improving plaster adhesion strength

GLX 298 is ready to use acrylic based primer. Consists of synthetic resins and quartz sand.



For improving adhesion strength of cement or gypsum based plaster on smooth or nonabsorbing surfaces. After the application, a rough surface is created.



Exterior & Interior use



0,19 - 0,24 kg/m<sup>2</sup>



Pink



160 items (1 kg)

Code	Pkg	Shade
P121479800	1 kg	Pink
P121472983	5 kg	
P121472984	20 kg	

## MICROCEMENT SYSTEMS



### DECOR FINE PLUS

#### Decorative coating in paste form

Acrylic based decorative coating for microcement. One-component, ready-to-use, for indoor or outdoor application.



It is applied on horizontal or vertical surfaces from concrete, plaster, gypsum boards, cement boards, undersoil heating, existing ceramic tiles, etc. Ideal for small applications on sinks, bathtubs, stairs, etc.



Exterior & Interior use



1,5 - 1,6 kg/m<sup>2</sup>/mm layer thickness



Tinted according to the new CLIMAPLUS fan deck, in more than 500 shades. DECOR FINE PLUS can be tinted by the commercial network tinting machines.



1 - 7 days



80 items (5 kg)  
36 items (15 kg)

Code	Pkg
P21901010	5 kg
P21901000	15 kg



## DECOR

### Microcement mortar – Two components

Microcement consisting of two components for creating colored decorative surfaces on floors and walls. Creates the traditional Greek Cycladic style with water formations. Applied at a thickness 2 - 3 mm, in a single layer on a solid and properly primed substrate. Combined with the reinforcing fiberglass mesh CLIMAPLUS. Suitable for indoors and outdoors spaces. Available in packs of 30kg (25kg A and 5kg B).

 Ideal for special applications such as counters, sinks, showers, pools, planters, stairs, etc. Colors: Available in white and 9 selected shades.

 Exterior & Interior use

 1,5 kg/m<sup>2</sup>/mm layer thickness

 48 items (25 kg)  
72 items (5 kg)

Code	Pkg
T10002000	<b>A</b> Comp. 25 kg
P21901005	<b>B</b> Comp. 5 kg



## DECOR ART

### Color pigments in liquid form

Pigment in liquid form which is mixed with THRAKON DECOR. Also mixed with any type of cement such as plasters, sealants, adhesives, etc.

 Suitable for coloring microcement as well as plasters, sealants, repair, etc.

 THRAKON gives you the opportunity to choose more shades by choosing the tone you want from the color chart.

 1 - 7 days

Code	Pkg
C/C	250 mL



## DECOR SUPERIOR

### 3-component (epoxy) microcement

3-component, epoxy based, microcement for creating colored decorative surfaces on floors and walls. Creates the traditional Greek Cycladic style with various formations. Applied at a thickness 2 - 10mm, in a single layer on a solid and properly primed substrate. Combined with the reinforcing CLIMAPLUS fiberglass mesh. Suitable for indoors and outdoors applications.

 Ideal for applications in wet areas. Also ideal for areas with high movement because of the high strength.

 Exterior & Interior use

 1,5 kg/m<sup>2</sup>/mm layer thickness

 36 items (**A** 15kg + **B** 1kg + **C** 1kg)

Code	Pkg
P11901015	<b>A:</b> 15 kg
P21901131	<b>B:</b> 1 kg
P21901130	<b>C:</b> 1 kg



## DECOR ART SUPERIOR

### Color pigments in liquid form for the DECOR SUPERIOR microcement system

Pigment in liquid form which is mixed with THRAKON DECOR SUPERIOR

 Suitable for coloring microcement as well as plasters, sealants, repair, etc.

 THRAKON gives you a choice of more SHADES by choosing the desired tone from the CLIMAPLUS fan deck.

 1 - 7 days

Code	Pkg
C/C	250 mL

## MICROCEMENT PROTECTION



### DECOR PRIM

#### Impregnating primer for microcement

Micromolar primer water based high penetration, suitable for impregnating and stabilizing microcement before applying the final varnish.



Suitable for application on any cementitious surface, such as microcement, traditional type screeds, plasters etc.



Exterior & Interior use



0,1 - 0,15 kg/m<sup>2</sup> depending on the porosity of the substrate



16 Items (1 kg)

Code	Pkg
P21901001	1 kg



### DECOR PROTECT

#### Water based varnish for protecting microcement

Specially formulated varnish to protect cementitious surfaces which have been treated with DECOR PRIM.



Suitable for indoor and outdoor use on any kind of cementitious surface where there is no standing water, fats and oils.



Exterior & Interior use



0,1 - 0,2 kg/m<sup>2</sup> depending on the porosity of the substrate



16 Items (1 kg)

Code	Pkg
P21901110	1 kg



### DECOR PU VARNISH

#### Polyurethane varnish - Two components, for protecting microcement

Transparent polyurethane varnish, two components. It offers excellent waterproofing, high mechanical strength, resistance to chemical agents, protection against yellowing and UV radiation.



Suitable for sealing and protecting any kind of structural element. Highly recommended for microcement, cementitious substrates, wood, metal, natural stone, etc. The special formula contains UV filters against UV radiation providing protection of shades and styles because it does not discolor or turn yellow over time.



Exterior & Interior use



0,08 - 0,12 kg/m<sup>2</sup> depending on the porosity of the substrate



12 Items (1 kg)



Glossy or Matte

Code	Pkg
P21901121	1 kg
P21901122	4 kg



### ANTISLIP

#### Non-Slip varnish 2-component

Transparent, non-slip, 2-component varnish for indoor and outdoor use with strong adhesion, high resistance to abrasion and to chemical agents. It provides excellent waterproofing and protection to any kind of structural elements.



It provides excellent waterproofing and protection to any kind of structural elements.



Exterior & Interior use



80 - 120 gr/m<sup>2</sup>



6 items (1 kg [A+B Comp.])  
6 items (4 kg [A+B Comp.])



Transparent matte

Code	Pkg	Shade
P121901301	1 kg	Transparent/
P121901304	4 kg	Matte

## FLOOR REINFORCEMENT

**CLIMAPLUS MESH (160 g/m<sup>2</sup>)**

Anti-alkaline fiberglass mesh, produced under ETAG 004.



Suitable for the reinforcement of the basic layer of the exterior thermal insulation system CLIMAPLUS.



Exterior use



33 rolls

1,1 m/m<sup>2</sup>

1m × 50m

**Grid size:** 4 × 4 mm

Code	m <sup>2</sup> / Palette
T10320020	1650





# 03



## PAINTS

Emulsion Paints / Coloring bases

---

Siloxan Paint

---

Acrylic Paints / Coloring bases

---

Substrates - Primers

---

Wood Protection / Coloring bases

---

Metal Protection

---

Stucco

---

Special Products

---

Epoxy - Polyurethane Paints

---

Solvents

---

Pigments

---



# WORLD-CLASS COLOR SYSTEM **SUPREME & ELITE**

The most premium coloring system  
with the innovation of **THRAKON**



We build together.



# Supreme

WORLD-CLASS STAIN-BLOCKING PAINT

## ◆ **Ultimate Stain-Blocking Formula**

The formula for absolutely preventing the formation of stains is specially designed for preventing the penetration of the most persistent stains into the paint film.

## ◆ **Nano CleanGuard Technology**


Supreme has an optimized composition with elements of nanotechnology so that it can offer absolute protection of surfaces from chemical compounds and products. The applicators can recommend Supreme as a product with a paint film of amazing durability and the proprietor will enjoy absolute protection for a long time.

## ◆ **Anti-microbial Shield**

Supreme serves as a shield against microbes thanks to advanced technology ingredients that prevent the development of microorganisms on the surface of the paint film.

## ◆ **Advanced Colour-Block Technology**

The advanced Colour-Block technology is applied for the creation of extremely vivid and bright colors that will always remain new and will offer you the desired effect.



## Elite Primer 2 in 1 White Primer

## ◆ **Stain-Blocking & High Hiding Formula**

The new Stain-Blocking & High Hiding formula used in Elite has been designed to prevent the most persistent stains and the formation of colour imperfections on the surface and, as a result, the surface is perfectly prepared for applying premium paints like Supreme and covering colour imperfections.

The exceptional new-generation composition is appropriate for both interior and exterior surfaces, such as walls, ceilings, plasters, plaster boards, bricks, wooden surfaces, etc.

The ecological Elite primer is available in white hue, thus ensuring a flawless final result, while, if you want a perfect and uniform hue of the final colour, you can use one of the thousands hues of the STATUS tinting system.

# EMULSION PAINTS / COLORING BASES



## STATUS SUPREME

### Premium quality ecological emulsion paint

Premium ecological paint so special that covers the internal surfaces of the house with a sense of absolute luxury and 100% satisfaction. Supreme was designed to offer an aura of luxury, unrivaled appearance, exceptional finish and a special formula serving as a protective shield against stains and microbes spread on the surfaces of the house. The best technologies are included in the same container and you have in your hands an ecological paint like no other.



Suitable for busy homes and high traffic rooms, such as children's bedrooms, living rooms, dining rooms, kitchens, bathrooms, hallways and passages where cleaning is done often. Perfect for healthcare, hospitality and educational environments and especially for hotels, hospitals, hospital corridors, schools and public building corridors.



Interior use



10 m<sup>2</sup>/Lt



72 Items (5 Lt)

Code	Pkg	Shade
P21106102	2,5 L	White
P21106105	5 L	
Code	Pkg	Product
P21106D03	2,5 L	Base D
P21106D05	5 L	

COLOR BASES



## STATUS LUXURIOUS

### Premium ecological velvet emulsion

Premium quality ecological emulsion paint. It is odorless, easy to clean, and sustains frequent washing and little scratches. It provides a beautiful, velvet surface, offering the enjoyment of a freshly painted house for a long time. It does not allow dirt to impregnate. It has the official eco-certification by the EU.



Suitable for indoor use. Ideal for children's rooms as well as other rest areas of the house. Applied on surfaces such as walls, plasters, ceilings, plasterboards, etc.



Interior use



12 - 15 m<sup>2</sup>/Lt



48 Items (9 Lt)

Code	Pkg	Shade
P21180008	750 mL	White
P21180003	3 L	
P21180009	9 L	

COLOR BASES



## STATUS ECO

### Premium ecological mat emulsion

Premium quality ecological emulsion paint, ideal for indoor surfaces. It is odorless and environment friendly. Spreads wonderfully, has excellent hiding power and high efficiency. Sustains frequent washing. It has the official eco-certification by the EU.



Applied on surfaces such as walls, plasters, ceilings, plasterboards and troweled coats.



Interior use



~10 m<sup>2</sup>/Lt



48 Items (10 Lt)

Code	Pkg	Shade
P21112008	750 mL	White
P21112003	3 L	
P21112010	10 L	
Code	Pkg	Product
P21112P01	1 L	Base P
P21112P03	3 L	
P21112P10	10 L	Base D
P21112D01	1 L	
P21112D03	3 L	
P21112D10	10 L	
P21112T01	1 L	Base TR
P21112T03	3 L	
P21112T10	10 L	

COLOR BASES



## STATUS KITCHEN & BATH

### Antimould high quality emulsion paint

It has excellent hiding power, high performance and easy implementation. It leaves a unique, rich mat finish that withstands washing and retains its color unchanged, giving the feeling of clean and freshly painted room for a long time.



Ideal for bathrooms and kitchens



Interior use



12 - 15 m<sup>2</sup>/L



48 items (10 L)

Code	Pkg	Shade
P21157008	750 mL	White
P21157003	3 L	
P21157010	10 L	



## STATUS EMULSION PAINT

### Emulsion paint

Premium quality, mat emulsion paint, ideal for indoor use. It has excellent hiding power, high resistance to washing and high efficiency, offering a superb finish.



Applied to surfaces such as walls, plasters, ceilings, plasterboards and troweled coats. The surface must necessarily be dry, solid and free of dust, mold and grease before application.



Interior use



12 - 15 m<sup>2</sup>/L



48 items (10 L)



12 items (750 mL)

Code	Pkg	Shade
P21108008	750 mL	White
P21108003	3 L	
P21108010	10 L	
Code	Pkg	Product
P21108P01	1 L	Base P
P21108P03	3 L	
P21108P10	10 L	
P21108D01	1 L	Base D
P21108D03	3 L	
P21108D10	10 L	
P21108T01	1 L	Base TR
P21108T03	3 L	
P21108T10	10 L	

COLOR BASES



## STATUS EMULSION COLORANT

### Emulsion colorant

STATUS Emulsion Colorants are suitable for painting various surfaces as well as tinting white emulsion and acrylic paints. They have strong colorant power and can be fully and easily incorporated. The various shades that can be created have high resistance to UV radiation and to alkali and remain unchangeable through time.



Suitable for painting various surfaces and coloring white emulsion and acrylic paints, to create complex shades.



Interior use



10 - 13 m<sup>2</sup>/Lt



12 Items (180 ml / 375ml / 750 ml)



Yellow	Red	Blue	Green
Ocher	Brick Red	Brown	Black

\* Actual shades may differ from this color chart

Code	Pkg
C/C	180 mL
C/C	375 mL
C/C	750 mL

Code	Pkg	Shade
P21107008	750 mL	White
P21107003	3 L	
P21107009	9 L	
Code	Pkg	Product
P21107P01	1 L	Base P
P21107P03	3 L	
P21107P09	9 L	
P121108D01	1 L	Base D
P121108D03	3 L	
P121108D10	9 L	

COLOR BASES



## PRIMO ECO

### Ecological emulsion paints

Ecological Emulsion Paint, offering fast drying, nice workability, has big covering strength and high performance.



Suitable for interior walls, ceilings, plaster, stairs, warehouses, cements.



Interior use



10,6 m<sup>2</sup>/Lt



48 Items (9 Lt)



12 Items (750 ml)

Code	Pkg	Shade
P21104003	3 L	White
P21104009	9 L	
P21104016	16 L	



## PRIMO PROFESSIONAL

### Enhanced emulsion paint

Emulsion paint, enhanced with acrylic resins, specially designed for professional use. It is easily applied, dries quickly, has strong coverage and impressive performance. Available in white and colored, with basic emulsion colorants.



Suitable for interior and exterior walls, ceilings, plaster, stairs, warehouses, cements.



Exterior & Interior use



10 - 12 m<sup>2</sup>/Lt



48 Items (9 Lt)  
36 Items (16 Lt)



## BONUS ACRYLIC

### Budget emulsion paint

Economic emulsion paint, specially designed for professional use. It is easily applied, dries quickly, has strong coverage and impressive performance Available in white.

Suitable for interior walls, ceilings, warehouses etc. The surface must be dry and free of dust or oils before painting.

Exterior & Interior use

10 - 12 m<sup>2</sup>/L

48 items (9 L)  
36 items (15 L)

Code	Pkg	Shade
P21159003	3 L	White
P21159009	9 L	
P21159015	15 L	



## STATUS WATERCOLOR

### Excellent quality watercolor

Excellent quality paint ready to use. It allows the surfaces to breathe better preventing the accumulation of water vapor and cleaning the space. It's easy to work with, great performance and leaves a nice, all-white surface.

Suitable for any interior space, such as ceilings in kitchens, bathrooms, warehouses, stairwells and generally where a washing machine is not required sealing of surfaces. The surface must be dry and free of dust or oil before painting.

Interior use

6 - 8 m<sup>2</sup>/L

48 items (9 L)

Code	Pkg	Shade
P21362003	3 L	White
P21362009	9 L	

## SILICONE - SILOXAN PAINT



## CLIMAPAIN SILOXAN

### High quality innovative silicone - siloxane paint

The unique composition of CLIMAPAIN SILOXAN offers external surfaces excellent color stability, quick evaporation of moisture from the surface and an effective shield against ambient humidity.

Suitable for all external surfaces and ideal for renewing surfaces that have been applied the external thermal insulation system.

Exterior & Interior use

10 - 12 m<sup>2</sup>/L

80 items (3 L)  
36 items (10L)



Code	Pkg	Shade
P21800203	3 L	White
P21800210	10 L	
Code	Pkg	Product
P21800213	3 L	Base D
P21800220	10 L	

## ACRYLIC PAINTS / COLORING BASES



## STATUS 100% ACRYLIC

### Acrylic paint

Premium Quality acrylic paint specifically designed to withstand harsh weather conditions such as big temperature changes, sunlight, sea saltiness, and atmospheric pollution. The bright white and the unchanged in time shades, make spaces look freshly painted for years.

Suitable for painting exterior surfaces such as walls, plaster, plasterboard, cement, concrete. The surface must necessarily be dry, solid and free of dust, mold and grease before application.

Exterior use

12 - 15 m<sup>2</sup>/Lt

48 Items (10 Lt)

12 Items (750 ml)

Code	Pkg	Shade
P21138008	750 mL	White
P21138003	3 L	
P21138010	10 L	
Code	Pkg	Product
P21138P01	1 L	Base P
P21138P03	3 L	
P21138P10	10 L	Base D
P21138D01	1 L	
P21138D03	3 L	
P21138D10	10 L	
P21138T01	1 L	Base TR
P21138T03	3 L	
P21138T10	10 L	



## STATUS ALL WEATHER

### Elastomeric waterproof facade paint

STATUS All-Weather is a pioneering product that dyes and isolates the exterior walls at the same time, ensuring absolute protection from the humidity and exceptional endurance. Its special composition creates a flexible membrane that covers all the veins and "monitors" the constrictions and dilations of the surface. Thanks to the built-in filters against the ultraviolet radiation it remains flexible without going off or peeling.



It is the ideal solution for coating and protection of buildings, mainly in urban and mountainous areas. It has the ability to prevent the formation of mold, and has a reduced tendency for retention pollutant (UV cross-linking).



Exterior use



8 - 10 m<sup>2</sup>/Lt



48 Items (10 Lt)

	Code	Pkg	Shade
COLOR BASES	P21155003	3 L	White
	P21155010	10 L	
	Code	Pkg	Product
COLOR BASES	P21155P03	3 L	Base P
	P21155P10	10 L	
COLOR BASES	P21155D03	3 L	Base D
	P21155D10	10 L	
COLOR BASES	P21155T03	3 L	Base TR
	P21155T10	10 L	



## PRIMO 100%

### Acrylic paint for concrete surfaces

Acrylic paint for exterior use. It is easily applied, dries fast, has good coverage and good resistance to sunlight and harsh weather conditions. It is an economic and efficient solution for the professional painter.



Ideal for outdoor use on surfaces such as walls, plaster, plasterboard, cement, concrete, bricks. The surface must necessarily be dry, solid and free of dust, mold and grease before application.



Exterior use



10 - 12 m<sup>2</sup>/Lt



48 Items (9 Lt)



12 Items (750 ml)



White



Grey

Brick Red

\* Actual shades may differ from this color chart

	Code	Pkg	
COLOR BASES	C/C	750 mL	
		3 L	
		9 L	
	Code	Pkg	Product
COLOR BASES	P21137P03	3 L	Base P
	P21137P09	9 L	
COLOR BASES	P21137D03	3 L	Base D
	P21137D09	9 L	



## STATUS RELIEF

### Textured decorative paint

Textured, decorative paint, suitable for outdoor use. Offers strong adhesion and excellent durability under severe weather conditions. Creates numerous decorative relief projects providing a beautiful aesthetic result by using appropriate paint rollers.



On new and old surfaces such as plaster, concrete, wood etc. The surface must be dry, clean, free of dust, mold or grease before application.



Exterior & Interior use



2 - 3 m<sup>2</sup>/Lt



36 Items (15 kg)

	Code	Pkg	Shade
COLOR BASES	P21540005	5 kg	White
	P21540015	15 kg	

## SUBSTRATES – PRIMERS



### ELITE PRIMER

#### 2 in 1 White Primer

100% acrylic high-performance white primer offering maximum coverage and ensuring perfect preparation of the surface. Elite offers unparalleled advantages and is described by perfect adhesion to the application surface. The new Stain-Blocking & High Hiding formula used in Elite has been designed to prevent the most persistent stains and the formation of color imperfections on the surface and, as a result, the surface is perfectly prepared for applying premium paints like Supreme and covering color imperfections.

 The exceptional new-generation composition is appropriate for both interior and exterior surfaces, such as walls, ceilings, plasters, plaster boards, bricks, wooden surfaces, etc.

 Exterior & Interior use  14 - 18 m<sup>2</sup>/Lt  64 Items (3 Lt)  
36 Items (9 Lt)

 Available in white hue, thus ensuring a flawless final result, while, if you want a perfect and uniform hue of the final color, you can use one of the thousands hues of the STATUS tinting system.

Code	Pkg	Shade
P21106003	3 L	White
P21106009	9 L	



### CLIMAPRIMER SILOXAN

#### High quality colored, odorless, waterproof, silicone-based acrylic micronized water primer

The ecological silicone-based acrylic micronized primer CLIMAPRIMER SILOXAN gives the applied surface waterproofing and excellent breathability, while at the same time shielding the substrate from rising soil moisture and the migration of salts from the substrate to the final painted surface.

 Suitable for new and existing porous external and internal surfaces, which will then be painted with CLIMAPAIN SILOXAN.

 Exterior & Interior use  10 - 15 m<sup>2</sup>/L

 80 items (5 L)



Code	Pkg	Shade
P21800205	5 L	Translucent



### GLX 292 FLEX PRIM

#### Acrylic primer - High penetration

Ready to use micronized acrylic water-based primer with high penetration ability.

 Ideal for preparing each new or old porous surface such as plaster, brick, concrete, plastered walls etc, creating an adhesion bridge for acrylic plasters, water paints, mortars, tile adhesives, acrylic and cementitious waterproofing spreads etc.

 Exterior & Interior use  15-20 m<sup>2</sup>/L depending on surface porosity

 240 items (1 kg)  
84 items (5 kg)  
24 items (20 kg)

Code	Pkg
P21472920	1 kg
P21472925	5 kg
P21472921	20 kg



## STATUS GYPSUM BOARD PRIMER

### Gypsum board primer

Acrylic primer, for interior use, with excellent filling coverage, suitable for plasterboard, and also masonry surfaces made of plaster, concrete, etc. It has excellent adhesion, smoothening the unevenness of drywall surfaces. It can be repainted with any emulsion paint. Available in white and in thousands of shades, through the STATUS coloring system.

The surface must be clean and dry. Dilute 5-10% with water. Repaint after 3-4 h. Storage at a dry environment with temperatures between +5°C and +35°C.



Interior use



12 - 15 m<sup>2</sup>/Lt



48 Items (9 Lt)

Code	Pkg	Shade
P21306203	3 L	White
P21306209	9 L	



## STATUS ACRYLIC PRIMER

### Acrylic primer

Water-soluble, acrylic undercoat for emulsion paints, suitable for interior and exterior use. It has excellent adhesion and elasticity. Provides strong grip on the final color and Offers significantly great durability. It is off white when packaged. After application, it becomes transparent.



Ideal for the preparation of new surfaces, such as exposed concrete, plaster, plasterboard, stucco surfaces, brick, etc. Also suitable for stabilizing surfaces painted with water paint (glue) or lime.



Exterior & Interior use



15 - 20 m<sup>2</sup>/Lt



48 Items (10 Lt)

Code	Pkg	Shade
P21306008	750 mL	Light white
P21306003	3 L	
P21306010	10 L	



## STATUS DUR

### Waterproof primer, solvent based

Transparent, solvent based, waterproof primer for walls. Impregnates, stabilizes and waterproofs surfaces, while allowing them to breathe. It is the best preparation before using vinyl or acrylic emulsions, Relief, paints for concrete or insulation boards.



Ideal for preparing every new or old porous surface such as plaster, brick, concrete, plastered walls etc. Also a great solution for surfaces coated with glue, lime or bad quality old colors.



Exterior & Interior use



12 - 14 m<sup>2</sup>/Lt



12 Items (1 Lt)

Code	Pkg	Shade
P21307001	1 L	Transparent
P21307005	5 L	
P21307015	15 L	



## STATUS AQUADUR

### Waterproof primer, water based

Transparent, water based, waterproof, acrylic primer for walls. Impregnates, stabilizes and waterproofs surfaces, providing better grip for the final color.



Suitable for preparing any surface such as plaster, brick, concrete, plastered walls etc. prior to painting with plastic or acrylic paints. Excellent solution for walls painted with glue, lime or bad quality old colors.



Exterior & Interior use



15 - 20 m<sup>2</sup>/Lt



12 Items (1 Lt)

Code	Pkg	Shade
P21307101	1 L	Transparent
P21307105	5 L	

## WOOD PROTECTION / COLORING BASES



### STATUS POLYPRIMER

#### Ecological multipurpose primer

Ecological water soluble multipurpose undercoat for interior and exterior use. Certified with Ecolabel. Easy to apply, has excellent hiding power and ensures high adhesion and a flawless end result.



Ideal for wooden surfaces before painted with water based enamel paints. Also suitable for metal, plaster, plasterboard, hard PVC, polyester and glass. Suitable for the isolation of black spots caused from humidity in interior walls and ceilings. Odorless during application.



Exterior & Interior use



10 - 12 m<sup>2</sup>/L



12 items (750 mL)

Code	Pkg	Shade
P21332008	750 mL	White
P21332003	2,5 L	



### STATUS AQUADROP

#### Ecological water based enamel paint

Finest quality certified ecological water based enamel paint, ideal for interior and exterior use. Some of the main advantages of this product is that it is odorless and does not turn yellow after time. It spreads easily and covers wonderfully, leaving a lovely surface to withstand frequent washing and harsh weather conditions for many years.



Specially designed for painting any wooden surface such as doors, cabinets, windows and walls, metal, hard PVC or glass. Prior use of Status Polyprimer is absolutely necessary.



Exterior & Interior use



12 - 14 m<sup>2</sup>/Lt



12 Items (750 ml)

AVAILABLE IN:  
**SATIN AND GLOSS.**

Code	Pkg	Shade
C/C	750 mL	White
C/C	2,5 L	
Code	Pkg	Product
C/C	750 mL	Base P
C/C	2,25 L	
C/C	750 mL	Base D
C/C	2,25 L	
C/C	750 mL	Base TR
C/C	2,25 L	



### STATUS ENAMEL UNDERCOAT

#### Enamel undercoat

White, mat primer, specially formulated to furnish a perfect base for enamels. It provides excellent hiding and filling power, very good levelling and easy sanding, offering a uniform, excellent finish to the topcoat.



Suitable for wooden surfaces and walls, for indoor and outdoor use.



Exterior & Interior use



16 - 18 m<sup>2</sup>/Lt



12 Items (750 ml)

Code	Pkg	Shade
P21131008	750 mL	White
P21131003	2,5 L	
P21131005	5 L	



### STATUS ULTRASHIELD RIPOLIN

#### Enamel paint for wooden surfaces

Excellent quality, solvent-based paint for interior and exterior use. Featuring excellent hiding power and easy brushing, it offers a perfect finish, washable, with great resistance in hard weather conditions, providing a long-lasting protection.



Specially formulated for the painting of all wooden surfaces such as doors, trim, frames, cabinets etc. It is also suitable for walls and metals.



Exterior & Interior use



14 - 16 m<sup>2</sup>/Lt



12 Items (750 ml)

AVAILABLE IN:  
**SATIN AND GLOSS.**

Code	Pkg	Shade
C/C	375 mL	White
C/C	750 mL	
C/C	2,5 L	
P21125204	375 mL	White
P21125208	750 mL	
Code	Pkg	Product
C/C	750 mL	Base P
C/C	2,25 L	
C/C	750 mL	Base D
C/C	2,25 L	
C/C	750 mL	Base TR
C/C	2,25 L	



## STATUS TEAK OIL

### Preservation oil, enriched with wax

Increases the lifetime of wooden surfaces and substitutes natural wood oils lost over time. Seals, nourishes and revives the wood surface to be applied.



Ideal for freshening and maintenance of garden furniture and all decorative wooden constructions



Exterior & Interior use



13 - 15 m<sup>2</sup>/Lt



12 Items (750 ml)

Code	Pkg	Shade
P21020018	750 mL	Colorless



## STATUS BASEWOOD

### Wood preservative

Colorless preservative and primer suitable for the preparation of wooden surfaces before the application of varnish. Its advanced composition protects effectively the wood from mould, fungi, blue stains and dry rot.



Suitable for interior and exterior use, it can be applied on all kinds of wooden surfaces such as doors, windows, frames, cladding, beams, roofs, fences, pergolas, garden furniture etc.



Exterior & Interior use



20 m<sup>2</sup>/Lt



6 Items (750 ml)

Code	Pkg	Shade
P21333008	750 mL	Colorless
P21333003	2,5 L	



## STATUS EVERWOOD

### 3 in 1 Protective woodstain

Protective woodstain, specially formulated for the effective protection of the indoor and outdoor wood. Due to its special formulation, it offers deep penetration to the wood while allowing it to 'breathe'. The built-in filters against the ultraviolet radiation and its water repulsive characteristic protect effectively from solar radiation, rain and humidity. Thus, it ensures longlasting protection, accentuating the natural beauty of the wood.



It is appropriate for all wooden surfaces such as doors, frames, cladding, banisters, eaves, fences, pergolas, sheds and garden furniture.



Exterior & Interior use



25 m<sup>2</sup>/Lt



6 Items (750 ml)



203 Pine	206 Oak	215 Cherry	218 Chestnut
221 Walnut	224 Mahogany	212 Oregon	209 Teak
Colorless			

Code	Pkg
C/C	750 mL
C/C	2,5 L



## AQUAWOOD

### Protective water based wood varnish

Water based woodstain varnish, specially formulated for the effective protection of the indoor and outdoor wood, enhancing the natural beauty of it. It is odorless, fast drying, does not crack or peel. It offers deep penetration to the wood, while allowing it to "breathe".



For all wooden surfaces, new or old: doors, windows, ceilings, doors, pergolas, garden furniture, fences, wood paneling, etc.



Exterior & Interior use



18 - 20 m<sup>2</sup>/Lt



6 Items (750 ml)



203 Pine	206 Oak	215 Cherry	218 Chestnut
221 Walnut	224 Mahogany	212 Oregon	209 Teak
Colorless			

Code	Pkg
C/C	750 mL
C/C	2,5 L



## STATUS ECOVARN

### Water based ecological varnish

Ecological colorless water-soluble varnish. It protects and also decorates each wooden surface indoors and outdoors. It is odourless, highly efficient and easily applied. Thanks to the builtin filters against ultraviolet radiation, the surface remains fible and fully protected even under adverse weather conditions. Certified Ecolabel from European Union.



For all wooden surfaces, new or old: doors, windows, ceilings, doors, pergolas, garden furniture, fences, wood paneling, etc. Moreover highly apply on walls and metal. It is also recommended as final coating for the protection of decorative effects as it does not turn yellow. The result is a splendid, particularly durable surface that remains inalterable for a long time.



Exterior & Interior use



8 - 10 m<sup>2</sup>/Lt



12 Items (750 ml)

Code	Pkg	Shade
C/C	750 ml	Colorless - Glossy or Satin
C/C	2,5 Lt	



## STATUS NAUTICAL

### Yacht varnish

Highly durable, transparent yacht varnish that protects and decorates any wooden surface outdoors. Due to its built-in filters against solar radiation (anti-UV filters) it provides great resistance, protecting from chaps and peeling. Creates a flexible, waterproof surface providing long-lasting protection.



Specially formulated for the painting of wooden ships but also for doors, frames, windows, pergolas, handrails etc. Ideal for timbers strongly affected by humidity, salty sea breeze and bright sunshine.



Exterior & Interior use



15 - 16 m<sup>2</sup>/Lt



12 Items (750 ml)

Code	Pkg	Shade
P121125408	750 ml	Glossy Colorless
P121125403	2,5 Lt	



## STATUS WOOD CLASSIC

### Decorative wood varnish

High quality, one-component polyurethane varnish for indoor or outdoor use.



Suitable for any kind of wooden surface, new or old: doors, windows, ceilings, doors, pergolas, garden furniture, fences, wood paneling, etc.



Exterior & Interior use



8-10 m<sup>2</sup>/Lt



12 Items (180ml / 750 ml)



206 Oak	209 Teak	221 Walnut
215 Cherry	203 Pine	107 Mahogany
Colorless		

\* Actual shades may differ from this color chart

Code	Pkg	Shade
P121125002	180 ml	Glossy Colorless
P121125008	750 ml	
P121125003	2,5 Lt	
C/C	180 ml	Glossy - Shade
C/C	750 ml	
C/C	750 ml	Colorless - Matte or Satin
C/C	2,5 L	

## METAL PROTECTION



## STATUS STEEL

### Transparent varnish for metallic surfaces

Transparent varnish for metallic surfaces. For indoor and outdoor use. Resistant to extreme weather conditions. Appropriate for the protection and decoration of old and new metallic surfaces. Offers high durability in time and protects from rust, hits and thermal expansions of the metallic surfaces.



The surface must be clean, dry and free from dust and grease before application. The product can be applied between +10° C and +25° C by brush or roller. Apply two coats evenly crosswise.



Exterior & Interior use



15 - 20 m<sup>2</sup>/Lt



12 Items (750 ml)

Code	Pkg	Shade
C/C	750 ml	Transparent satin or Transparent matte
C/C	2,5 Lt	



## STATUS BUILDING PRIMER

### Building primer

Ideal undercoat for the preparation of metal surfaces. Works softly spreads wonderfully, has great coverage and does not flow. Ensures very good adhesion in the final paint, offering a uniform surface and exceptional final result.



Can be applied to all metal surfaces. It is also suitable for application on wood, plaster and the construction in general, as it is applied softly, providing excellent spreading capacity, strong hiding power and it does not tear. The surface must be necessarily dry, solid and free of dust, mould and grease before application.



Exterior & Interior use



10 - 12 m<sup>2</sup>/Lt



12 Items (750 ml)

Code	Pkg	Shade
P121306108	750 ml	White
P121306103	2,5 Lt	
P121306105	5 Lt	



## STATUS RUST PRIMER

### Anticorrosive primer

Primer with excellent anticorrosive properties and high durability. Provides effective protection against rust, even under harsh weather conditions. Its superior workability and excellent spreading capacity ensure very good covering and exceptional final result.



On metal surfaces such as rails, farming equipment, car frames etc, providing effective protection against rust even under hard weather conditions.



Exterior & Interior use



13 - 15 m<sup>2</sup>/Lt



12 Items (375 ml / 750 ml)



Grey

Brick Red

\* Actual shades may differ from this color chart

Code	Pkg
C/C	375 ml
C/C	750 ml
C/C	2,5 Lt



## STATUS MARINE PRIMER

### Red lead marine primer

Powerful red lead marine primer. Due to its thixotropic properties, performs high workability, spreads extremely well, dries quickly and provides excellent traction.



Excellent for the effective protection of metal surfaces from oxidation. It is also applicable as a primer on wooden surfaces such as windows, boats etc.



Exterior use



5 - 6 m<sup>2</sup>/kg



12 Items (500 gr / 1 kg)

Code	Pkg	Shade
P121121004	500 gr	Orange
P121121001	1 kg	
P121121005	5 kg	



## STATUS DUKO

### Gloss enamel paint

Glossy extra strong enamel paint, suitable for decoration and protection of all metallic surfaces, indoor and outdoor. Featuring excellent hiding power and easy brushing, it offers a perfect finish, with exceptional resistance in hard weather conditions, providing a longlasting protection and shades that survive unaltered for a long time.



Ideal for the decoration and protection of any metallic surface. Also suitable for application on properly primed wooden surfaces and walls.



Exterior & Interior use



13 - 15 m<sup>2</sup>/Lt



12 Items (180 ml / 375 ml / 750 ml)



44 Red	63 Forest Green	65 Dark Green
74 Myconean Blue	76 Norwegian Blue	99 Leaden
01 White	24 Black	

Code	Pkg	Shade
C/C	180 ml	White and in 39 ready shades*
C/C	375 ml	
C/C	750 ml	
C/C	2,5 Lt*	

\* Available only for 2,5 Lt  
Actual shades may differ from this color chart



## DUROMETAL HARDENER

### Hardener

Polyurethane hardener for STATUS DUROMETAL. Gives faster drying and greater hardness.



Mix in a ratio of 20% by volume with all hard enamel paints.



Exterior & Interior use



12 Items (750 ml)

Code	Pkg	Shade
P121135008	750 ml	Transparent



## STATUS DUROMETAL

### Hard enamel paint

Featuring excellent hiding power and easy brushing, provides a perfect finish, with exceptional resistance in hard weather conditions, providing a long-lasting protection and shades that remain unaltered for a long time.



On all metal constructions. Also suitable for painting trucks, tractors, machinery, etc. The surface must necessarily be dry, solid and free of dust, mold, grease before application.



Exterior & Interior use



13 - 15 m<sup>2</sup>/Lt



12 Items (750 ml)



AVAILABLE IN:  
**SATIN, GLOSS AND MATTE.**

Code	Pkg	Shade
C/C	750 ml	White, Black, Moss green
C/C	2,5 Lt	
C/C	750 ml	Matte Black, Aluminium
Code	Pkg	Product
P121120P08	750 ml	Base P
P121120P03	2,25 Lt	
P121120D08	750 ml	Base D
P121120D03	2,25 Lt	
P121120T08	750 ml	Base TR
P121120T03	2,25 Lt	

### COLORING BASES



## STATUS RUSTBLOCK

### Anticorrosive gloss enamel paint

Specially designed paint to be applied on rusty surfaces without prior use of rust primer, offering a glossy effect as a final result. Exhibits high adhesion and very good leveling and offers excellent resistance to harsh weather conditions. The result is a shiny, highly durable surface, with intact nuances for a very long time.



Its state of the art composition ensures strong protection against rust on any new or old metal surface preventing rust appearance, without prior use of anticorrosive primer.



Exterior & Interior use



6 - 8 m<sup>2</sup>/Lt



12 Items (750 ml)



406 Silver	418 Cypress	412 Red	415 Mykonian	409 Dark Blue
421 Grey	424 Dark grey	427 Brown	400 White	403 Black

Code	Pkg
C/C	750 ml
C/C	2,5 Lt

\* Actual shades may differ from this color chart



## STATUS RUSTBLOCK HAMMER FINISH

### Hammer finish anticorrosive enamel paint

Specially designed paint to be applied on rusty surfaces without prior use of rust primer, offering a hammer effect as a final result. Exhibits high adhesion and very good leveling and offers excellent resistance to harsh weather conditions. The result is a shiny, highly durable surface, with intact nuances for a very long time. Available in 5 colors.



Its state of the art composition ensures strong protection against rust on any new or old metal surface preventing rust appearance, without prior use of anticorrosive primer.



Exterior & Interior use



6 - 8 m<sup>2</sup>/Lt



12 Items (750 ml)



406 Silver 418 Cypress 430 Bronze 436 Grey 439 Aegean

Code	Pkg
C/C	750 ml
C/C	2,5 Lt



## STATUS METALLIC

### Decorative metallized water based paint

Decorative anticorrosive water based paint, ideal for exterior or interior metallic surfaces, for wall, wood, railing, handrail, doors. Its composition ensures strong protection against rust, preventing rust appearance. It offers excellent resistance, very good leveling, high adhesion as well as antirust protection. It provides a durable surface with color shades that are retained for a long time.



Ideal for any outdoor or indoor metal surface but also for wall or wood railing, handrail, door and more. It is applied directly on corroded metallic surfaces.



Exterior & Interior use



7 - 9 m<sup>2</sup>/Lt



6 Items (650 ml)



450 Silver 452 Grey 454 Graphite  
456 Gold 458 Olive Green 460 Terracotta

Code	Pkg
C/C	650 ml

## STUCCO



## STATUS ONE COVER

### Lightweight acrylic putty

White, ready to use, lightweight acrylic putty for indoor and outdoor surfaces. It is easily applied and does not crack. The surface can be painted as soon as the putty is dry.



It can be used with only one step as filling material for cracks and holes at a maximum thickness of 3cm.



Exterior & Interior use



12 - 15 m<sup>2</sup>/Lt



12 Items (1 Lt)

Code	Pkg	Shade
P121385001	1 Lt	White



## STATUS 100% ACRYLIC PUTTY

### Acrylic putty

White putty for indoor and outdoor use in construction. Can be used as filling material on surfaces made of plaster, wood, concrete e.t.c. It has easy application and when sanded it offers a smooth and durable surface without cracks.



On any surface of plaster, wood, concrete,plaster, etc.



Exterior & Interior use



400 gr/m<sup>2</sup>



12 Items (800 gr)  
24 Items (400 gr)

Code	Pkg	Shade
P121381004	400 gr	White
P121381008	800 gr	
P121381005	5 Kg	



## STUCCOPRO DEC 470

### Fine-grained spatula putty – For indoor & outdoor use

White, one component, dry mix putty. Replaces the traditional stuccos and oil stuccos. The final result gives a very smooth surface, without lumping, lines and cracks after drying.



Applied on indoor surfaces: concrete, cement based plasters.



Exterior & Interior use



1,0 kg/m<sup>2</sup>/mm for two layers



60 Items (20 kg)



4 Items (5 kg)

Code	Pkg	Shade
P111801005	5 kg	White
T010000150	20 kg	



## DEC 480

### Spatula putty – For indoor & outdoor use

White, one component dry mix putty. Replaces the traditional stuccos and oil stuccos, while covering larger areas in comparison with them. Offers a smooth surface, suitable for painting or bonding wallpaper.



Applied on indoor surfaces: concrete, cement based plasters.



Exterior & Interior use



1,2 kg/m<sup>2</sup>/mm for two layers



60 Items (20 kg)

Code	Pkg	Shade
P111801120	20 kg	White



## FINE PUTTY

### Acrylic Sealant

Acrylic single component, multi-use sealant. Suitable for filling cracks and joints indoors and outdoors. It can be painted, while it is waterproof after maturation.



Suitable for filling joints at all porous surfaces such as brick, concrete, wood etc. Not suitable for outdoor application joints that have permanent contact with water.



Exterior & Interior use



12 Items (280 ml)

Code	Pkg	Shade
T010000360	280 ml	White



## SPECIAL PRODUCTS

**STONE VARNISH****Acrylic stone varnish**

Impregnating, premium quality, transparent, decorative stone varnish, specially designed to emphasize and protect any kind of stone. Specially formulated for penetrating the pores of the surface and enhancing the natural color of the surface.



It is suitable for interior and exterior use in natural or artificial stones, ceramics, marbles, bricks, granite, etc. Can also be used in terraces, fireplaces, walls, mosaics and elsewhere. The surface must necessarily be dry, solid and free of dust, mold, grease before application.



Exterior & Interior use



10 -12 m<sup>2</sup>/Lt



12 Items (750 ml)

Code	Pkg	Shade
P121126008	750 ml	Colorless
P121126003	2,5 Lt	

**STATUS ARTISTICO****Water-based decorative glaze**

Water-based, decorative glaze, specially formulated for the creation of translucent, versatile paint effects, appropriate for interior surfaces decoration. Can be applied on all types of surfaces such us walls, ceilings, woods, metals etc. Designed and based on high quality specifications.



Status Artístico may be colored through tinting system, providing a semi-opaque finish and can stay workable for sufficient time. A combination of colors, tools and techniques allow the creation of spectacular effects, showing off the creative side and making any place truly unique.



Exterior & Interior use



12 -15 m<sup>2</sup>/Lt



12 Items (750 ml)

Code	Pkg	Shade
P121364008	750 ml	Transparent*

\* (Off white)

**CARMYPAINT RP-10****Road marking paint**

Road marking solvent-based paint, to be used as a binder of reflective glass beads. It has excellent adhesion and reflectivity. The glass beads should be dispersed in fresh painted lane striping, which must be fluid.



On asphalt surfaces, using machine road marking.



Exterior & Interior use



2 - 4 m<sup>2</sup>/kg



White

Yellow



72 items (5 kg)  
24 items (25 kg)

Code	Pkg
C/C	5 kg
C/C	25 kg



## EPOXY - POLYURETHANE PAINTS



### STATUSPOX

#### Epoxy paint

Two component epoxy paint. It has high resistance to mechanical and chemical stresses. It is also highly resistant to oils, diesel, gasoline, acids and alkalis, and exhibits excellent adhesion to concrete and metal surfaces. Available in grey color or RAL 7032 and can be produced in any color on request.



Suitable for painting floors in industrial sites, factories, warehouses, garages etc. For indoor use.



Exterior & Interior use



3 - 4 m<sup>2</sup>/kg for film thickness  
150 - 200m



36 items (**A** 12kg + **B** 2,5kg)

Code	Pkg	Shade
P129011000	<b>A</b> Comp. 12 kg	Grey *
P121118003	<b>B</b> Comp. 2,5kg	

\* Available in other shades after order.



### STATUSPOOL PRIMER

#### Primer for pool paint

Two component, epoxy primer for swimming pools and non-potable water tanks.



Priming new concrete pools or local repairs of the old substrate.



Exterior use



8 - 9 m<sup>2</sup>/Lt (for dry film 60m.)



72 items (**A** 4L + **B** 2L)

Code	Pkg	Shade
P121136004	<b>A</b> Comp. 4 Lt	White
P121136010	<b>B</b> Comp. 2 Lt	



### STATUSPOOL

#### Pool paint

Two component polyurethane top coat for swimming pools. It's highly resistant to UV radiation and in acidic or alkaline environment. It has excellent grip, absolute impermeability to water and high elasticity, protects the surface from cracking, peeling or chalking. Can be exposed in direct sunlight even when the pool is empty, without chalking.



Suitable for painting swimming pools, fountains and tanks.



Exterior use



13 - 15 m<sup>2</sup>/Lt (per layer)



White

Aqua Blue



72 items (**A** 4L + **B** 2L)

Code	Pkg
C/C	<b>A</b> Comp. 4 Lt
C/C	<b>B</b> Comp. 2 Lt



### WASH PRIMER

#### Special primer

Yellow, two-component special primer.



Suitable for the preparation of non-ferrous surfaces such as aluminum, copper, zinc and galvanized steel. Thinning with LS 702



Exterior & Interior use



14 - 15 m<sup>2</sup>/kg (for dry film 10m.)



12 Items (800 gr / 200 gr)

Code	Pkg	Shade
P121310008	<b>A</b> Comp. 800 gr	Green
P121310002	<b>B</b> Comp. 200 gr	



### STATUS REMOVER

#### Paints and varnishes

New generation powerful corrosive for paints and varnishes. Does not contain dichloromethane.



Suitable for the removal of old or new varnish, paint and primers.



Exterior & Interior use



12 Items (375 ml / 750 ml)

Code	Pkg	Shade
P121690004	375 ml	Transparent
P121690008	750 ml	
P121690003	4 Lt	



### CARMYSAIL PRIMER

#### Epoxy primer

High quality epoxy primer with antiosmotic properties.



Suitable for steel, aluminum, wood and fiberglass.



Exterior & Interior use



7 - 9 m<sup>2</sup>/Lt (for dry film 50-60 m.)



12 Items (A + B set [500 ml + 250 ml])

Code	Pkg	Shade
P121139003	A Comp. 2 Lt	Grey
P121139101	B Comp. 1 Lt	
P121139118	Packaging A + B Comp. 500 + 250 ml	



### CARMYSAIL

#### Polyurethane paint

Premium quality polyurethane paint. Highly resistant to oil, grease and cleaning agents.



Suitable for application on surfaces of fiberglass, iron, aluminum and wood. Highly recommended for dyeing vessel over the above materials.



Exterior use



13 - 15 m<sup>2</sup>/Lt (for dry film 30-40 m.)



12 Items (A + B set [500 ml + 250 ml])



White	Black	Aqua Blue
Blue	Red	Yellow

Code	Pkg
C/C	A Comp. 2 Lt
P121139001	B Comp. 1 Lt
C/C	Packaging A + B Comp. 500 + 250 ml

\* Actual shades may differ from this color chart

## SOLVENTS



### WHITE SPIRIT

#### Solvent for paint brush



15 Items (375 ml)  
28 Items (750 ml)  
8 Items (4 Lt)

Code	Pkg
P121701004	375 ml
P121701008	750 ml
P121701014	4 Lt
P121701016	15 Lt



### ACETONE

#### General use solvent

Suitable for diluting varnishes and cleaning paint equipment.



12 Items (750 ml)

Code	Pkg
P121704008	750 ml
P121704014	4 Lt
P129029900	15 Lt



### LS-702

#### Solvent for air paints, oven toluol base

Suitable for dilution: STAUSPOX, WASH PRIMER, CARMYPAINT RP-10.



12 Items (750 ml)

Code	Pkg
P121702008	750 ml
P121702003	4 Lt



### LS-703

#### Solvent for air paints, oven xylene base

Suitable for dilution: STATUSPOOL PRIMER, STATUSPOOL & CARMYSAIL.



12 Items (750 ml)

Code	Pkg
P121703008	750 ml
P121703014	4 Lt



### LS-705

#### Gun cleaning solvent



72 items (4 L)  
24 items (15 L)

Code	Pkg
P121735014	4 Lt
P121705015	15 Lt



### LS-735

#### Nitro Solvents general use.

Suitable for dilution: CARMYSAIL PRIMER.



12 Items (750 ml)

Code	Pkg
P121735008	750 ml
P121735014	4 Lt
P121735015	15 Lt

# PIGMENTS



## COLORANT

High quality pigments for color effect unchanged over time.

- All packaging are 1 Lt
- 1 Lt = 1598 units (lines) ÷ 33,3 Y (1Y = 48 lines))
- C 30, C 31, C 32, C 33, C 34 used for tinting organic plasters
- Pigments are not amenable to any discount

Code	Pkg
T023373040	C04 WHITE
T023373050	C05 BLUE
T023373060	C06 YELLOW
T023373070	C07 RED
T023373080	C08 GREEN
T023373090	C09 YELLOW CONCENTRATED
T023373100	C10 BLUE CONCENTRATED
T023373110	C11 OCHRE
T023373120	C12 ORANGE
T023373130	C13 RED CONCENTRATED
T023373140	C14 AUBREY
T023373150	C15 BRICK RED
T023373160	C16 VIOLET
T023373210	C21 BLACK CONCENTRATED
T023373220	C22 MAGENTA
T023373230	C23 WEAK BLACK
T023373240	C24 BLACK
T023373250	C25 MAGENTA
T023373260	C26 ORANGE
T023373270	C27 YELLOW
T023373280	C28 YELLOW CONCENTRATED
T023373290	C29 BLUE CONCENTRATED
T023373300	C30 BLACK CONCENTRATED
T023373310	C31 VIOLET CONCENTRATED
T023373320	C32 RED CONCENTRATED
T023373330	C33 YELLOW CONCENTRATED
T023373340	C34 ORANGE CONCENTRATED





# 04

## TILE ADHESIVES - GROUTS

---

Gel Tile Adhesives

---

Tile Adhesives

---

Grouts

---

Antislip System

---

Primers & Cleaning Agents

---

Special Glues

---

Contact & Polyurethane Adhesives

---

Complementary Materials

---



## GEL TILE ADHESIVES



### GEL

#### Gel-type cement-based tile adhesive

High-quality gel type, cement-based, tile adhesive with an extended open time application and zero vertical slip. The ACTIVE GEL TECH advanced technology, in the adhesive composition, produce a soft consistency that does not thicken for a long time while become so liquid to give effortless workability. The combination of extended open time and zero vertical slip of adhesive increase the workers' productivity, while the NEW GENERATION ELASTICITY makes it more elastic in comparison to with conventional C2TE class adhesives.

C2TE

Code	Pkg	Shade
P11421265	25 kg	White

Small or large ceramic tiles of all types, granite tiles, natural stone tiles, cotto, klinker, etc. on all standart substrates

Exterior & Interior use

2,5 - 5,0 kg/m<sup>2</sup>

48 items (25 kg)



### GEL PLUS

#### Gel-type cement-based tile adhesive

Advanced, high-quality gel type, cement-based, tile adhesive with an increased open time application and zero vertical slip. The ACTIVE GEL TECH advanced technology, in the adhesive composition, produce a soft consistency that does not thicken for a long time while become so liquid to give effortless workability.

S1

C2TE

Code	Pkg	Shade
P11421266	25 kg	White

Ideal for absorbent and non-absorbent tiles of all dimensions, types and qualities, without restrictions and all substrates.

Exterior & Interior use

2,5 - 5 kg/m<sup>2</sup>

48 items (25 kg)

## TILE ADHESIVES



### ACRYLIC SKW 112

#### Tile adhesive

SKW 112 is a thin layer, cement based tile adhesive, produced with quartz sand and used for applications on both horizontal and vertical surfaces. For indoor and outdoor use.

C1

Code	Pkg	Shade
P11411121	25 kg	Grey
P11411120	25 kg	White

Suitable for applications of ceramic tiles on common substrates such as concrete, light weight concrete, renders, traditional cement based floor screeds, self leveling floor screeds, etc.

Exterior & Interior use

2 - 4 kg/m<sup>2</sup>

60 Items (Grey 25kg)  
48 Items (White 25kg)



### EXTRA SKW 114

#### Tile adhesive with slip resistance

SKW 114 is a thin layer, cement based tile adhesive, produced with quartz sand, offering resistance to vertical sliding. Its thixotropic characteristics give the applicator the ability to apply tiles from upper side downwards, when applied on vertical surfaces. For application on indoor and outdoor surfaces.

Suitable for application of absorbent ceramic tiles on wall or floor, on common substrates such as concrete, light weight concrete, renders, traditional cement based floor screeds, self-leveling floor screeds, etc.

Exterior & Interior use 2 - 4 kg/m<sup>2</sup>

60 Items (Grey 25kg)  
48 Items (White 25kg) 4 Items (Grey/ White 5kg)

C1T

Code	Pkg	Shade
P11411143	25 kg	Grey
P11411141	5 kg	
P11411142	25 kg	White



### SPECIAL SKW 116

#### Tile adhesive with slip resistance and increased open time

SKW 116 is a thin layer, cement based tile adhesive, produced with quartz sand for applications on both horizontal and vertical surfaces. The integrated composition of the product offers high strength, resistance to vertical sliding and extended open time for application. For indoor and outdoor surfaces.

Suitable for application of ceramic tiles on common substrates such as concrete, light weight concrete, renders, traditional cement based floor screeds, self-leveling floor screeds, etc.

Exterior & Interior use 2 - 4 kg/m<sup>2</sup>

60 Items (Grey 25kg)  
48 Items (White 25kg)

C1TE

Code	Pkg	Shade
P11411161	25 kg	Grey
P11411160	25 kg	White



### STONE SKW 117

#### Thick-bed adhesive for fixing tiles and natural stone

Thick-bed, polymer modified, cement based adhesive for fixing tiles and natural stone. It provides vertical slip resistance of the tile on the tile on the wall and extended open time.

Specially suited for fixing ceramic tiles and natural stone on all common mineral substrates. It is recommended for substrate leveling before tiling.

Exterior & Interior use 2,0 - 8,0 kg/m<sup>2</sup>

60 Items (Grey 25kg)  
48 Items (White 25kg)

C1TE

Code	Pkg	Shade
P11411171	25 kg	Grey
P11411170	25 kg	White



### QUARTZ VKW 121

#### Enhanced tile adhesive for non-absorbing tiles with extended open time

Premium quality tile adhesive, cement based. Used in horizontal and vertical surfaces. Offers high strength and increased open time. For indoor and outdoor surfaces.

Suitable for bonding stone tiles, cotto, klinker, absorbent and non-absorbent wall or floor tiles, on substrates such as concrete, lightweight concrete, coatings, screeds, self-leveling floor screeds etc. Particularly high performance in applications requiring extended open time, property that ensures excellent workability.

Exterior & Interior use 2 - 4 kg/m<sup>2</sup>

60 Items (Grey 25kg)  
48 Items (White 25kg)

C2E

Code	Pkg	Shade
P11490080	25 kg	Grey
P11421210	25 kg	White



## VINYL VKW 122

### Enhanced acrylic tile adhesive

Tile adhesive for absorbent and non-absorbent tiles, cementitious base for use on horizontal and vertical surfaces.



Suitable for bonding stone, cotto, klinker tiles. It is particularly recommended for non-absorbent tiles and substrates that are subjected to intense stress. It is applied on substrates such as concrete, lightweight concrete, coatings, cement mortars, self-leveling floors, etc.



Exterior &  
Interior use



2 - 4 kg/m<sup>2</sup>



60 items (Grey 25 kg)  
48 items (White 25 kg)

C2TE

Code	Pkg	Shade
P11421233	25 kg	Grey
P11421223	25 kg	White



## SUPER ACRYLIC VKW 124

### Enhanced tile adhesive for non-absorbing tiles with slip resistance and extended open time

VKW 124 is a thin layer, cement based, tile adhesive, produced with quartz sand, for applications on both horizontal and vertical surfaces. It offers slip resistance, extended open time and excellent workability. For indoor and outdoor surfaces.



Suitable for application of stone tiles, marble tiles, granite tiles, cotto, klinker, absorbing and non absorbing tiles, on common substrates such as concrete, light weight concrete, renders, mosaics, traditional cement screeds, self-leveling floor screeds, etc. Offers high performance in applications requiring extended open time and is recommended for application of tiles, on vertical surfaces, from top to bottom.



Exterior &  
Interior use



2 - 4 kg/m<sup>2</sup>



60 Items (Grey 25kg)  
48 Items (White 25kg)

C2TE

Code	Pkg	Shade
P11421240	25 kg	Grey
P11421243	25 kg	White



## FLEX VKW 126

### Elastic tile adhesive

Premium tile adhesive, elastic, cement based, produced with quartz sand, for applications on both horizontal and vertical surfaces. It offers slip resistance, extended open time and excellent workability. For indoor and outdoor surfaces.



Suitable for application of stone tiles, marble tiles, granite tiles, cotto, klinker, gres, porcellane, absorbing and non absorbing tiles. Intended for application on difficult substrates subjected to thermal expansions and heavy traffic, as well as in areas with constant moisture conditions, such as heated floors, bathrooms, showers, car showrooms, malls, public areas, exterior tile layering, balconies, terraces, gypsum boards, etc.



Exterior &  
Interior use



2 - 4 kg/m<sup>2</sup>



60 Items (Grey 25kg)  
48 Items (White 25kg)



4 items (White 5 kg)

S1

C2TE

Code	Pkg	Shade
P11421263	25 kg	Grey
P11421262	5 kg	White
P11421261	25 kg	White



### GRANITO STABILO VKW 127

#### Coarse-grained adhesive for large dimension tiles

Coarse grained, cement based, adhesive, produced with quartz sand. The special granulometry of the product allows easy installation avoiding tile plunge due to the high weight. For indoor and outdoor surfaces.



Particularly recommended for bonding large dimension tiles (e.g. 60x60 or larger), porcellanato, klinker, cotto, on common substrates such as concrete, plaster, cement based floor screeds, heated floors, baths, showers etc. It is also suitable for the substrate levelling prior to tiling. The tile application can be done the following day to a layer thickness up to 15mm.



Exterior & Interior use



60 Items (Grey 25kg)  
48 Items (White 25kg)



4 - 8 kg/m<sup>2</sup>, depending on the smoothness of the surface and whether smoothing of the substrate is required

C2TE

Code	Pkg	Shade
P11421271	25 kg	Grey
P11421270	25 kg	White



### SUPERFLEX VKW 128

#### Highly fiberforced elastic tile adhesive

Frost flexible, fiberforced, cement-based, tile adhesive, produced with quartz sand, intended for applications on both horizontal and vertical surfaces. It offers slip resistance, extended open time, very high elasticity and excellent workability. For indoor and outdoor surfaces.



Suitable for application of absorbing and non absorbing tiles, wall or floors, for tiles type like porcellanato, stone tiles, marble tiles, granite tiles, cotto, klinker, gres, porcellane tiles, and for application on difficult substrates subjected to thermal expansions and heavy traffic, as well as in areas with constant moisture such as heated floors, bathrooms, showers, car showrooms, malls, public areas, exterior tile layering, balconies, terraces, gypsum boards, etc. Also recommended for applications in mountainous areas prevailing frost long periods of time.



Exterior & Interior use



60 Items (Grey 25kg)  
48 Items (White 25kg)



2 - 4 kg/m<sup>2</sup>

S1

C2TE

Code	Pkg	Shade
P11421280	25 kg	Grey
P11421281	25 kg	White



### ULTRAFLEX VKW 129

#### Super elastic fiberforced tile adhesive

Super Elastic tile adhesive suitable for most demanding applications.



Suitable for welding absorbent and non-absorbent small or large ceramic tiles of all types, thin stone tiles, marble tiles natural or artificial granite, klinker, gres, on exterior building facades. Also suitable for applications on substrates with high demands subject to vibrations and intense contractions such as: plasterboard, underfloor heating, terraces, balconies. On wooden surfaces like: MDF, plywood, chipboard, lofts, wooden stairs. It is ideal for bonding of ceramic tiles and glass mosaic tiles in swimming pools, WC, bathrooms, changing rooms, moisture resistant plasterboard etc. Suitable for application of large tiles dimensions and new tiles on old paving.



Exterior & Interior use



60 Items (Grey 25kg)  
48 Items (White 25kg)



2 - 4 kg/m<sup>2</sup>

S2

C2TE

Code	Pkg	Shade
P11491290	25 kg	Grey
P11890125	25 kg	White



## SUPER ELASTIC VKW 132

### 2-Component elastic tile adhesive

Highly flexible, 2-component, tile adhesive, for surfaces subjected to thermal expansions and vibrations. For indoor and outdoor surfaces.



Suitable for application of all tile types, floor and wall, wooden or vibrating surfaces, gypsum boards, swimming pools, WC, showers etc. Suitable for application of tiles on lofts, wooden stairs, roofs, balconies and heated floors as well as for application of big tile dimensions and new tiles on existing tiling.



Exterior & Interior use



2,5 - 4 kg/m<sup>2</sup>



24 Items

S2

C2TE

Code	Pkg	Shade
P11421321	10 kg	White



## EXPRESS FKW 134

### Fast setting tile adhesive

Fast-setting, thin layer, cement based tile adhesive. Ideal when there is demand for grouting and delivering the project at the same day (wall or floor). Offers resistance to slip. For indoor and outdoor surfaces.



Suitable for application of stone tiles, marble tiles, granite tiles, absorbing and non absorbing tiles on common substrates such as concrete, light weight concrete, renders, traditional cement based floor screeds, self-leveling floor screeds, etc.



Exterior & Interior use



3 - 5 kg/m<sup>2</sup>



48 Items

C2FT

Code	Pkg	Shade
P11491341	25 kg	White



## TRASS MKW 136

### Adhesive for marbles

Cement based adhesive for marble and natural granite. Suitable for applications on both horizontal and vertical surfaces and for application in big thickness. For indoor and outdoor surfaces.



Suitable for application of marbles and granite for inside and outside use. Excellent solution for decorative coatings, prevents staining of marble elements. Qualified as a slip resistant tile adhesive.



Exterior & Interior use



4 - 5 kg/m<sup>2</sup>



48 Items

C2T

Code	Pkg	Shade
P11491360	25 kg	White



## MARBLE VKW 137

### Mortar for bonding marbles, stone and pavement plates

Ready mix mortar with special additives for quick, simple and economical application of marbles, without altering the hues. For indoor and outdoor surfaces.



Coatings of marble floors, stone, and for laying - grouting of pavement plates. It can also be applied with plastering machine. Normal use, just add water.



Exterior & Interior use



15 kg/m<sup>2</sup>



48 items

Code	Pkg	Shade
P11421370	25 kg	White



### DECO KDW 138

#### White mortar for glass and decorative bricks

Cement based mortar for applying and grouting decorative building elements. It has the ability to be applied on a layer up to 1-2 cm thickness.



Suitable for applications of glass or decorative bricks, on common substrates such as concrete, light weight concrete, renders, cement based floor screeds, self-levelling floor screeds etc.



Exterior & Interior use




48 Items



#### Consumption:

For glass bricks with dimensions 19x19x8 cm and grout thickness 1cm the consumption is 17-19 kg/m<sup>2</sup>  
For decorative bricks with dimensions 19x5x1.5 cm and grout thickness 1cm the consumption is 10 kg/m<sup>2</sup>

Code	Pkg	Shade
P11491381	25 kg	White



### FIRE STONE FSW 140

#### Mortar for firebricks

Fire-resistant, cement based mortar, with high temperature resistance, up to 1000°C.



Suitable for bonding and grouting of all types of fire bricks, for repairing joints and firebricks on fireplaces, furnaces, smokestacks etc.



Exterior & Interior use



60 items



4 - 5 kg/m<sup>2</sup>



4 items (5 kg)

Code	Pkg	Shade
P11450010	5 kg	
P11450000	25 kg	Grey



### ACRYL VKW 142

#### Ready-to-use tile adhesive in paste form

Ready-to-use acrylic tile adhesive in paste form. Great flexibility, strong adhesion, quick and easy application. For indoor use.



Ideal for tiling on gypsum boards, cement boards, wood, MDF, old tiles substrates, etc. For indoor application only.



Exterior & Interior use



60 Items (5kg)  
36 Items (15kg)



1,5 - 5 kg/m<sup>2</sup>, depending on the evenness of the substrate



Code	Pkg	Shade
P21490550	5 kg	
P21490560	15 kg	White



### EPOXY VKW 145

#### Strong epoxy tile adhesive

2-component epoxy adhesive (A+B). Ideal for swimming pools, chemical industries, food industries, professional kitchens, refrigerators, refrigeration areas, slaughterhouses, chemical laboratories, clinics, laundries etc.



Suitable for application of ceramic tiles on metal surfaces, stainless steel, asbestos, MDF and glass. It is applied for bonding on wall and floor absorbing and non absorbing ceramic, small and large dimensions tiles, natural and artificial stone, pieces of glass, gres porcelanato, granite tiles for floor, cotto, Klinker.



Exterior & Interior use



60 Items (5kg A+B)



1,5 - 5 kg/m<sup>2</sup>, depending on the evenness of the substrate.



Code	Pkg
P21420000	5 kg (A+B)

**Packaging:** 4,5 kg A + 0,5 kg B (ratio A' component: B' component = 9:1)

## GROUTS



## ULTRA GROUTECH FMF 150

## Tile grout



Enhanced technical features and excellent workability. FMF 150 is a one component, polymer modified, cement based, tile grout produced with quartz sand. It is classified as type CG2 according to EN 13888. It is available in two types:

- Fine grain No. 301 - No 326: application thickness up to 5mm.
- Coarse grain No. 501 - No 525: application thickness 5-20mm.



Ideal for wall or floor tile grouting, use in interior and exterior areas.



Exterior & Interior use



120 Items (5 kg)



4 Items (5 kg)



## COARSE GRAIN

Tiles (cm x cm x mm)	Joint width mm			
	5	10	15	20
20 x 20 x 8	0,86	1,72	2,58	3,44
30 x 30 x 8	0,57	1,15	1,72	2,29
30 x 60 x 9	0,48	0,97	1,45	1,94
40 x 40 x 9	0,48	0,97	1,45	1,94

\*Consumption kg/m<sup>2</sup>

## CALCULATE

QUICKLY & EASILY  
THE CONSUMPTION  
OF GROUTS  
BY USING THE  
APPLICATION:  
[www.thrakon.gr/en/calculator/](http://www.thrakon.gr/en/calculator/)



## COLOR CHART - COARSE GRAIN

		NEW SHADES**	
Shade	Code	Shade	Code
501 White	P111505010	530 Anemone	P11505300
502 Cream	P111505020	531 Almond	P11505310
503 Beige	P111505030	532 Manhattan	P11505320
505 Ivory	P111505050	533 Pearl Grey	P11505330
507 Light Grey	P111505070	534 Cement Grey	P11505340
509 Grey	P111505090	535 Taupe Grey	P11505350
510 Dark Grey	P111505100	536 Mouse Grey	P11505360
511 Anthracite	P111505110	537 Dark Brown	P11505370
513 Brown	P111505130	538 Blue Grey	P11505380
515 Wege	P111505150	539 Black	P11505390
516 Cotto	P111505160		
519 Light Blue	P111505190		
525 Black	P111505250		

\* Actual color shades may differ from this Color chart

\*\* New shades will be available from July

**FINE GRAIN**

Tiles (cm x cm x mm)	Joint width mm				
	1	2	3	4	5
20 x 20 x 8	0,15	0,30	0,44	0,59	0,74
30 x 30 x 8	0,10	0,20	0,30	0,39	0,49
30 x 60 x 9	0,08	0,17	0,25	0,33	0,42
40 x 40 x 9	0,08	0,17	0,25	0,33	0,42

\*Consumption kg/m<sup>2</sup>**CALCULATE**

QUICKLY & EASILY  
THE CONSUMPTION  
OF GROUTS  
BY USING THE  
APPLICATION:  
[www.thrakon.gr/en/calculator/](http://www.thrakon.gr/en/calculator/)

**COLOR CHART - FINE GRAIN**

Joint Thickness 0 up to 5 mm	NEW SHADES**	
	Shade	Code
301 White	P111503010	330 Jasmine
302 Cream	P111503020	331 Manhattan
303 Beige	P111503030	332 Pearl Grey
304 Pearl Beige	P111503040	333 Cement Grey
305 Ivory	P111503050	334 Dark Grey
306 Pearl Grey	P111503060	335 Almond
307 Light Grey	P111503070	336 Pearl Beige
308 Manhattan Grey	P111503080	337 Taupe
309 Grey	P111503090	338 Taupe Grey
310 Dark Grey	P111503100	339 Olive Grey
311 Anthracite	P111503110	340 Soil
312 Mocha	P111503120	341 Mouse Grey
313 Brown	P111503130	342 Black
314 Chocolate	P111503140	343 Caramel
315 Wege	P111503150	344 Brown
316 Cotto	P111503160	345 Terracotta
317 Red	P111503170	346 Ceramic
318 Aqua Marine	P111503180	347 Chocolate
319 Light blue	P111503190	348 Dark Brown
320 Green	P111503200	349 Satin Beige
321 Ochre	P111503210	350 Fresh Rose
322 Yellow	P111503220	351 Blue
323 Pink	P111503230	352 Blue Grey
324 Blue	P111503240	353 Tea Tree
325 Black	P111503250	354 Mint
326 Veraman	P111503260	355 Green Aesthetic
		356 Anemone
		357 Vanilla
		358 Champagne
		359 Sand Brown
		360 Mocha
		361 Honey
		362 Mustard

\* Actual color shades may differ from this Color chart

\*\* New shades will be available from July



## EPOXY GROUTECH FMF 155

### Advanced high resistant 2-component epoxy grout and tile adhesive

Advanced technology without solvents, porcelain, high strength, two-component epoxy grout, suitable for filling joints 0-20 mm wide. EPOXY GROUTECH stands out for its excellent workability and easy cleaning, while maintaining its color uniformity. It is suitable for grouting indoor and outdoor spaces, in any kind of tiles, tesserae and natural stones. At the same time, it can be used as an adhesive on surfaces that require welding with chemical resistance. Shades: Available in white and 17 shades with perfect color stability.



Its unique formula gives high resistance to applications where resistance to chemical and mechanical stress is required, such as floors, tiles with normal or marine waters, liquid and urban storage solutions, homes, construction sites, food production and processing facilities, food industries, industries, hospital laboratories and clinics.



Exterior & Interior use



60 Items (3 kg)



In stock: 701, 707, 709, 711

Other codes: 5-10 working days



### EPOXY GROUTECH FMF 155

#### Joint width mm

Tiles (cm x cm x mm)	3	5	7	10
12,5 x 25 x 9	0,52	0,86	1,21	1,73
12,5 x 25 x 12	0,69	1,15	1,61	2,30
20 x 20 x 8	0,38	0,64	0,90	1,28
20 x 20 x 12	0,58	0,96	1,34	1,92
30 x 30 x 8	0,26	0,43	0,60	0,85
Inlays (cm x cm x mm)	3	5	7	10
2 x 2 x 3	1,44	2,40	3,36	4,80

\* Consumption kg/m<sup>2</sup>



### COLOR CHART EPOXY GROUTECH FMF 155

Shade	Code
701 White	P121507010
702 Cream	P121507020
703 Beige	P121507030
704 Pearl Beige	P121507040
705 Ivory	P121507050
706 Pearl Grey	P121507060
707 Light Grey	P121507070
708 Manhattan Grey	P121507080
709 Grey	P121507090
710 Dark Grey	P121507100
711 Anthracite	P121507110
712 Mocha	P121507120
713 Brown	P121507130
714 Chocolate	P121507140
715 Wege	P121507150
718 Aqua Marine	P121507180
719 Light blue	P121507190
721 Ochre	P121507210
722 Yellow	P121507220
724 Blue	P121507240

\* Actual color shades may differ from this Color chart

The elegant  
signature  
for your  
space!

THRAKON  
GROUTEC



LUX

ULTRA

EPOXY



## LUX GROUTECH FMF 160

### Porcelain grout

Grout with a characteristic chromatic homogeneity, stability and high mechanical strengths. It ensures sealing, achieving excellent water repellent properties and antifungal protection. Prevents the growth of microorganisms and the formation of fungus and salt stains on its surface. FMF 160 LUX is a fast setting grout and it is classified as type CG2 according to EN 13888.



Suitable for grouting ceramic tiles, marbles and granites on wall and floor applications. For exterior and interior use. It has excellent workability. It is applied at joint thickness from 1mm up to 8mm. It gives a smooth end result, on surfaces. Available in 17 colors.



Exterior & Interior use



120 Items (5 kg)



4 Items (5 kg)

CG2  
WA

EN  
13888



### LUX GROUTECH FMF 160

#### Joint width mm

Tiles (cm x cm x mm)	2	4	6	8
20 x 20 x 8	0,30	0,59	0,89	1,18
30 x 30 x 8	0,20	0,39	0,59	0,79
60 x 60 x 9	0,17	0,33	0,50	0,67
40 x 40 x 9	0,11	0,22	0,33	0,44
Inlays (cm x cm x mm)	2	4	6	8
2 x 2 x 3	1,11	2,22	3,33	4,44

\* Consumption kg/m<sup>2</sup>



### COLOR CHART LUX GROUTECH FMF 160

#### NEW SHADES\*\*

Shade	Code	Shade	Code	Shade	Code
601 White	P111506010	630 Jasmine	P11506300	647 Chocolate	P11506470
602 Cream	P111506020	631 Manhattan	P11506310	648 Dark Brown	P11506480
603 Beige	P111506030	632 Pearl Grey	P11506320	649 Satin Beige	P11506490
604 Pearl Beige	P111506040	633 Cement Grey	P11506330	650 Fresh Rose	P11506500
605 Ivory	P111506050	634 Dark Grey	P11506340	651 Blue	P11506510
606 Pearl Grey	P111506060	635 Almond	P11506350	652 Blue Grey	P11506520
607 Light Grey	P111506070	636 Pearl Beige	P11506360	653 Tea Tree	P11506530
609 Grey	P111506090	637 Taupe	P11506370	654 Mint	P11506540
610 Dark Grey	P111506100	638 Taupe Grey	P11506380	655 Green Aesthetic	P11506550
611 Anthracite	P111506110	639 Olive Grey	P11506390	656 Anemone	P11506560
612 Mocha	P111506120	640 Soil	P11506400	657 Vanilla	P11506570
613 Brown	P111506130	641 Mouse Grey	P11506410	658 Champagne	P11506580
614 Chocolate	P111506140	642 Black	P11506420	659 Sand Brown	P11506590
615 Wege	P111506150	643 Caramel	P11506430	660 Mocha	P11506600
616 Cotto	P111506160	644 Brown	P11506440	661 Honey	P11506610
619 Light Blue	P111506190	645 Terracotta	P11506450	662 Mustard	P11506620
625 Black	P111506250	646 Ceramic	P11506460		

\* Actual color shades may differ from this Color chart

\*\* New shades will be available from July

## ANTISLIP SYSTEM



### ANTISLIP

#### Non-Slip varnish 2-component

Transparent, non-slip, 2-component varnish for indoor and outdoor use with strong adhesion, high resistance to abrasion and to chemical agents. It provides excellent waterproofing and protection to any kind of structural elements.



Suitable for waterproofing and protection of any type of construction element. Creates a non-slip surface, even when it is wet, and at the same time it seals and protects any kind of building block.



Exterior & Interior use



80 - 120 gr/m<sup>2</sup>



6 Items (1 kg [A+B comp.])  
6 Items (4 kg [A+B comp.])

Code	Pkg	Shade
P121901301	1 kg	Transparent/ Matte
P121901304	4 kg	



### ANTISLIP PROMOTER

#### Adhesion promoter

Transparent, deep penetration enhancer one component for interior and exterior use. Turns on chemically the surface and provides strong adhesion to glass and ceramic surfaces.



It is recommended before applying AntiSlip on glass and ceramic surfaces such as: glass ceramic tiles, glass, glass blocks as it is activated chemically.



Exterior & Interior use



50 - 100 gr/m<sup>2</sup> one or two layers



12 Items (1 kg)

Code	Pkg	Shade
P121901401	1 kg	Transparent/ Matte

## PRIMERS & CLEANING AGENTS



### STATUS REMOVER

#### Color and epoxy grout remover

New generation powerful corrosive for paints and epoxy grouts. Does not contain dichloromethane.



Suitable for the removal of old or new varnish, paint and primers.



Exterior & Interior use



12 Items (375 ml / 750 ml)

Code	Pkg	Shade
P121690004	375 ml	
P121690008	750 ml	
P121690003	4 Lt	Transparent



### VLX 181

#### Non-acid general purpose cleaner for joints and ceramic tiles

Non-acid transparent general purpose cleaner for marble and tiles with lemon perfume. It cleans in depth, without causing any disaff ects, and shines perfectly at the same time.



Especially suitable for cases that require the use of mild cleaning agents (e.g. for cleaning marbles, calcium tiles, calcium carbonate tiles and sensitive tiles in general). It is ideal for tiles with silk decorative elements and special decorations, which are cleaned with a soft cloth.



Exterior & Interior use



1 Lt/ 5 m<sup>2</sup> surface



16 Items (1 Lt)

Code	Pkg
T021540100	1 Lt



## VLX 182

### Acid general purpose cleaner for joints and ceramic tiles

Acid transparent liquid cleaner and shining aid for joints and ceramic tiles. Cleans, shines and maintains the colors of grout vibrant and shiny after application.



Removes cementitious residues, salt and calcareous crust, residues from adhesives and sand mortars, stain for greases, varnishes, oils, etc. Do not use for cleaning marble, decorative stone from limestone and non acid-resistant surfaces.



Exterior & Interior use



1 Lt/ 5,5 m<sup>2</sup> surface



16 Items (1 Lt)

Code	Pkg
T021540000	1 Lt



## VLX 185 GROUT ELASTIC

### Elatic admixture for grouts

Elastifying admixture for cementitious grouts. Reduces water absorption.



Highly recommended for grouting surfaces which are off ended by contractionexpansion and moisture such as underfl oor heating, pool surroundings, tanks, bathrooms, terraces, balconies etc.



Exterior & Interior use



FMF 150 ULTRA GROUTECH: 1800 g/5 kg FMF 150  
FMF 160 LUX GROUTECH: 1200 g/5 kg FMF 160



16 Items (1 Lt)

Code	Pkg
P121540000	1 Lt



## VLX 186

### Acrylic admixture for mortars – Primer for special applications

Environmental friendly, acrylic admixture for mortars and a primer for non-absorbing substrates. It does not contain organic solvents. It is used as a primer for bonding tiles on demanding substrates (old tiles, marble, mosaic).



Suitable for improving the properties of tile adhesives and grouts. Increases bonding strength and significantly reduces water absorption.



Exterior & Interior use



16 Items (1 Lt)



#### Admixture:

40 -80g per kg

#### Primer:

- **Non absorbing substrates:**  
1 kg/15 m<sup>2</sup> surface
- **Absorbing substrates:**  
1 kg/5 m<sup>2</sup> surface

Code	Pkg
P121541000	1 kg
P121541100	5 kg
P121541200	20 kg



## GLX 190

### Acrylic primer with quartz sand grains for tile & mosaics

Adhesion primer that consists of synthetic resin, inorganic fillers and quartz sand with selected grain size. Increases the bonding strength of the tile adhesive on smooth and low absorbing surfaces.



Suitable to be used as a bonding agent on old tiles and mosaics when new tiles are going to be applied, in indoor and outdoor surfaces. It is also applied on fine renders, wood, PVC and cement boards.



Exterior & Interior use



0,24 - 0,28 kg/m<sup>2</sup>



160 Items (1 kg)  
36 Items (5 kg)  
60 Items (15 kg)

Code	Pkg	Shade
P121479000	1 kg	
P121471901	5 kg	Red
P121471901	15 kg	

## SPECIAL GLUES

**CM-121****Wood glue**

Liquid, ready to use synthetic white glue.



Bonding wood, tile, parquet soil, paper, furniture, etc. Good stirring is recommended before use.



Exterior & Interior use

Code	Pkg
P21109005	5 kg
P21109018	18 kg

**CM-141****Granulated wood glue**

Synthetic, crystalline, transparent adhesive for strong and elastic bonding. Does not leave stains on wood.



Bonding wood, tile and laminate ground.



Exterior & Interior use



24 Items (200 ml)  
12 Items (1/2 kg)  
12 Items (1 kg)

Code	Pkg
P121109104	200 ml*
P121109102	1/2 kg
P121109101	1 kg
P121109105	5 kg
C/C	18 kg

\* Bottle

**CM-PK****Parquet glue**

High quality synthetic, water-soluble glue in wood color for wooden floors.



Suitable for bonding of wooden parquets on wood, concrete and mosaic.



2 - 4 m<sup>2</sup>/kg



45 items (5 kg)  
36 items (15 kg)

Code	Pkg
P121109905	5 kg
P121109815	15 kg

**CM-AM****Acrylic based magnetic glue**

Water soluble acrylic based glue. Offers high resistance to temperature and humidity.



Ideal for synthetic (PVC or other material) floor and wall tiles.  
Spread on the flooring only.



Exterior & Interior use



2 - 4 m<sup>2</sup>/kg

Code	Pkg
P21109035	5 kg

## CONTACT & POLYURETHANIC ADHESIVES



### CARMYFIX CM-43

#### Contact adhesive – General use

High quality polychloroprene based adhesive.



Suitable for bonding leather, cork, paper, carpet, fabric, rubber, wood, metal and many other materials.



Exterior & Interior use



6 x 15 items (75 mL)  
40 items (100 mL/200 mL)  
24 items (500 mL/1L)  
4 items (5 L)

Code	Pkg
P21118975	75 mL *
P21201910	100 mL
P21118902	200 mL
P21118904	500 mL
P21201901	1 L
P21118915	5 L
P21118925	15 L

\* Tube



### CARMYFIX CM-54

#### Heat resistant contact adhesive

High quality, Heat resistant polychloroprene based adhesive.



Suitable for welding formica sheet on particle board, wood, metal and fabric. Highly recommended for use in vehicle upholstery.



Exterior & Interior use



24 items (0,5L/1L)

Code	Pkg
P21118173	0,5L
P21118172	1 L
P21118176	5 L



### CARMYFIX CM-233

#### Strong contact adhesive

High quality, strong polychloroprene based adhesive

Suitable for bonding leather, fabric, rubber, EVA, natural rubber, etc. in the shoe industry. Ideal for use in inflatable boats and diving suits made of Hypalon- Neoprene. The addition of Carmydur hardener (3-5%) increases the adhesive strength and resistance to heat.



Exterior & Interior use



24 items (1 L)

Code	Pkg
P21201086	1 L
P21201087	5 L



### CARMYFIX CM-888

#### Transparent polyurethane glue

Polyurethane based adhesive.

Suitable for bonding synthetic materials such as polyurethane, thermoplastic rubber TR or PVC on leather or other synthetic materials. Ideal for use in inflatable boats made of PVC. The addition of the hardener Carmydur (3-5%) increases the adhesive strength and resistance to heat.



Exterior & Interior use



24 items (1 L)

Code	Pkg
P21201811	1 L
P21201850	5 L
P21201815	15 L



### CARMYDUR

#### Hardener

Isocyanate hardener for various adhesives based on synthetic rubber or polyurethane. CARMYDUR Hardener can be used as a second component for adhesives CM-233 and CM-888, for making the bonding stronger and heat resistant.



Exterior & Interior use



24 Items (30 g)  
20 Items (800 g)

Code	Pkg
P21118101	30 g
P21201108	800 g

## COMPLEMENTARY MATERIALS



### CROSSES FOR TILES

Code	Description	Thickness (mm)	Packaging (Items)
T010610150	C1	1	500
T010610250	C2	2	500
T010610350	C3	3	500
T010610450	C4	4	500
T010610550	C5	5	500
T010610650	C6	6	500
T010610750	C7	7	500
T010610760	C9	9	500
T010610120	C10	10	250



### SHAPE T FOR TILES

Code	Description	Thickness (mm)	Packaging (Items)
T010600020	T2	2	500
T010600030	T3	3	500
T010600040	T4	4	500
T010600050	T5	5	500
T010600070	T7	7	500
T010600090	T9	9	500



### WEDGE FOR TILES

Code	Packaging (Items)
T010690010	500

FIELDS OF APPLICATION	C2TE	C2TE S1	C1	C1T	C1TE	C1TE	C2E	C2TE	C2TE
PRODUCT	GEL	GEL+	SKW 112	SKW 114	SKW 116	SKW 117	VKW 121	VKW 122	VKW 124
<b>TYPE OF STRUCTURAL ELEMENT</b>									
Absorbent tiles									
Large-size slabs									
Non absorbent tiles									
Glass mosaic									
Marble									
Natural stone									
Decorative bricks & Glass bricks									
Firebricks									
<b>INDOORS / FLOOR</b>									
Cementitious floors									
Light weight concrete	paint	paint	paint	paint	paint	paint	paint	paint	paint
Mosaic								bucket	bucket
Underfloor heating systems									
Old layer of ceramic tiles									
Wooden surface chipboard									
Metallic surface									
<b>WALL</b>									
Application downwards									
Cement/lime plasters									
Gypsum plasters	paint	paint	paint	paint	paint	paint	paint	paint	paint
Gypsum boards								bucket	bucket
Cement boards								bucket	bucket
Old layer of ceramic tiles									
Autoclaved Aerated Concrete	paint	paint	paint	paint	paint	paint	paint	paint	paint
<b>BATHROOM</b>									
Cementitious floor/plaster									
Gypsum board									bucket
<b>OUTDOORS (BALCONY - TERRACE)</b>									
Cementitious floors			bucket	bucket	bucket				
Light weight concrete	paint	paint	paint bucket	paint bucket	paint bucket	paint	paint	paint	paint
<b>FAÇADE</b>									
Application downwards									
Cement/lime plasters									
Gypsum board								bucket	bucket
Autoclaved Aerated Concrete	paint	paint					paint	paint	paint
<b>FLOOR</b>									
Cementitious floors									
<b>SWIMMING POOL</b>									
Cementitious surfaces									

 Recommended use

 Apply primer VLX 186 or GLX 190 or GLX 298 prior to application

 Add 1-2 kg VLX 186 per 25 kg bag

 Apply primer GLX 290 prior to application



## EN 12004-1 REQUIREMENTS FOR CEMENT BASE TILES ADHESIVES

Adhesive category	Symbol	C1	C2
	Description	With regular characteristics	With advanced characteristics
Initial tensile bond strength	EN 12004-2, 8.3	≥ 0,5 N/mm <sup>2</sup>	≥ 1 N/mm <sup>2</sup>
Tensile bond strength after thermal aging	EN 12004-2, 8.3	≥ 0,5 N/mm <sup>2</sup>	≥ 1 N/mm <sup>2</sup>
Tensile bond strength after immersion in water	EN 12004-2, 8.3	≥ 0,5 N/mm <sup>2</sup>	≥ 1 N/mm <sup>2</sup>
Tensile adhesion strength after freeze-thaw cycles	EN 12004-2, 8.3	≥ 0,5 N/mm <sup>2</sup>	≥ 1 N/mm <sup>2</sup>
Open time: Tensile bond strength	EN 12004-2, 8.1	≥ 0,5 N/mm <sup>2</sup> after at least 20 min	

## SPECIAL CHARACTERISTICS FOR TILE ADHESIVES

Technical characteristics			
Symbol	Description	Control method	Requirement
T	Vertical slip	EN 12004-2, 8.2	≤ 0,5 mm
E	Extended Open Time / Tensile Adhesion Strength	EN 12004-2, 8.1	≥ 0,5 N/mm <sup>2</sup> after at least 30 min
F	Early bond strength in tension	EN 12004-2, 8.3	≥ 0,5 N/mm <sup>2</sup> after 6 hours max
	Open time: bond strength in tension	EN 12004-2, 8.1	≥ 0,5 N/mm <sup>2</sup> after at least 10 min

Adhesive type	Control method	Dispersion adhesive		Reacting resin adhesives	
		D1: Normal	D2: Advanced	R1: Normal	R2: Advanced
Technical characteristics		Minimum requirements			
Initial shear bond strength		≥ 1,00 N/mm <sup>2</sup>	≥ 1,00 N/mm <sup>2</sup>	≥ 2,00 N/mm <sup>2</sup>	≥ 2,00 N/mm <sup>2</sup>
Adhesion strength in shear	D: EN 12004-2, 8.4 R: EN 12004-2, 8.5	≥ 1,00 N/mm <sup>2</sup>	≥ 1,00 N/mm <sup>2</sup>		
			≥ 0,50 N/mm <sup>2</sup>	≥ 2,00 N/mm <sup>2</sup>	≥ 2,00 N/mm <sup>2</sup>
			≥ 1,00 N/mm <sup>2</sup>		
				≥ 2,00 N/mm <sup>2</sup>	
					≥ 2,00 N/mm <sup>2</sup>
Open time: Tensile bond strength	EN 12004-2, 8.1	≥ 0,5 N/mm <sup>2</sup> after at least 20 min			

## EN 12004-1 REQUIREMENTS FOR ELASTIC TILES ADHESIVES

Transverse deformation		Symbol	S1	S2
		Description	2,5mm ≤ S < 5mm	S ≥ 5mm
Tile Adhesives THRAKON	Category	Description		
<b>SKW 112</b>	C1	With regular characteristics, for absorbing tiles and common substrates – Indoor and outdoor us.		
<b>SKW 114</b>	C1T	With regular characteristics, for absorbing tiles and common substrates – Slip resistance.		
<b>SKW 116/117</b>	C1TE	With regular characteristics, for absorbing tiles and common substrates. With slip resistance and increased open time.		
<b>MKW 136</b>	C2T	With advanced characteristics, for non absorbing tiles and slip resistance – Indoor and outdoor use.		
<b>VKW 121</b>	C2E	With advanced characteristics, for non absorbing tiles and increased open time – Indoor and outdoor use.		
<b>VKW 122/124/127/GEL</b>	C2TE	With advanced characteristics, for non absorbing tiles with slip resistance and increased open time – Elastic – Indoor and outdoor use.		
<b>VKW 126/128/GEL+</b>	C2TE-S1	With advanced characteristics, for non absorbing tiles with slip resistance and increased open time – Very elastic – Indoor and outdoor use.		
<b>VKW 129/132</b>	C2TE-S2	With advanced characteristics, for non absorbing tiles with slip resistance and increased open time – Super elastic – Indoor and outdoor use.		
<b>FKW 134</b>	C2FT	Fast setting with advanced characteristics for non absorbing tiles, with slip resistance – Indoor and outdoor use.		
<b>VKW 142</b>	D2TE	Dispersion adhesive with advanced characteristics for all kind of tiles, with slip resistance and increased open time. Indoor and outdoor use.		
<b>VKW 145</b>	R2T	Epoxy adhesive with advanced characteristics for all kind of tiles and with slip resistance. Indoor and outdoor use.		

## EN 13888 REQUIREMENTS FOR CEMENT BASED TILE GROUTS

Adhesive type		Symbol	CG1	CG2
		Description	With regular characteristics	With advanced characteristics
Technical Characteristics		Control method	Requirement	Requirement
Compressive strength after dry storage		EN 12808-3	≥ 15,0 N/mm <sup>2</sup>	≥ 15,0 N/mm <sup>2</sup>
Flexural strength after dry storage		EN 12808-3	≥ 2,5 N/mm <sup>2</sup>	≥ 2,5 N/mm <sup>2</sup>
Compressive strength after freeze-thaw cycles		EN 12808-3	≥ 15,0 N/mm <sup>2</sup>	≥ 15,0 N/mm <sup>2</sup>
Flexural strength after freeze-thaw cycles		EN 12808-3	≥ 2,5 N/mm <sup>2</sup>	≥ 2,5 N/mm <sup>2</sup>
Shrinkage		EN 12808-4	≤ 3 mm/m	≤ 3 mm/m
Water absorption after 30 min:		EN 12808-5	≤ 5 g	≤ 2 g
Water absorption after 240 min:		EN 12808-5	≤ 10 g	≤ 5 g
Abrasion resistance		EN 12808-2	≤ 2 000 mm <sup>3</sup>	≤ 1 000 mm <sup>3</sup>
Tile Adhesives THRAKON	Category	Description		
<b>FMF 150</b>	CG2	With advanced characteristics for demanding applications, high abrasion resistance, low water absorption and shrinkage – Indoor and outdoor application.		
<b>FMF 160 LUX</b>	CG2	With advanced characteristics for demanding applications, high abrasion resistance, low water absorption and shrinkage – Interior and exterior application.		
<b>FMF 155</b>	RG	Advanced epoxy grout with high mechanical strength, resistance to weather conditions, resistance to acids, alkalis and many organic solvents, also in water 52 and saline water.		



# 05

## WATERPROOFING

Polyurethane System

---

Bituminous PU Membranes

---

Crystalline

---

Cement Based

---

Acrylic Based

---

Complementary Products

---

Impregnating

---

Primers and Admixtures

---

Sealants

---

THRAKON innovates once again, with the launch of the DESMOFLEX series.

# DESMOFLEX®

The DESMOFLEX® range offers ultimate and long-lasting waterproofing solutions.

THRAKON's laboratories have created products that will offer excellent waterproofing and excellent mechanical, thermal and chemical resistance, with the new generation "DESMOFLEX®" technology.

The DESMOFLEX® range consists of the DESMOFLEX® PU System, a three-product waterproofing system, and DESMOFLEX® Aqua.



Learn more at  
[www.desmoflex.gr](http://www.desmoflex.gr)

## POLYURETHANE SYSTEM

### DESMOFLEX® Aqua / The Superb Aqua Formula

#### HIGH QUALITY POLYURETHANE WATER-BASED MEMBRANE

Not just a sealant: The sealant designed for great durability and duration!



DESMOFLEX® Aqua is a high quality white, aliphatic, polyurethane water-based membrane of one component, suitable for long-term waterproofing. Its unique composition is designed to create a single, elastic, hydrophobic membrane that completely covers capillaries and cracks up to 2mm. In addition, DESMOFLEX® Aqua provides excellent mechanical, thermal and chemical resistance as well as protection from frost and ultraviolet (UV resistance) for a long time. After application, the surface remains walkable and resistant to stagnating waters, maintaining high whiteness over time.

-  Suitable for long term waterproofing of roofs, terraces, balconies and asphalt felts, EPDM or PVC membrane. Waterproofing of horizontal surfaces from concrete, cement mortars etc., especially for surfaces with stagnating waters.
-  Exterior & Interior use
-  1,0 - 1,2 kg/m<sup>2</sup> for 2 layers
-  80 items (4kg)  
36 items (12 kg)

Code	Pkg	Shade
P21660403	4 kg	White
P21660412	12 kg	

\* Also available in other shades upon request.

### DESMOFLEX® PU System / The Ultimate Polyurethane System

#### INNOVATIVE POLYURETHANE SYSTEM

The polyurethane excellence of THRAKON: Holistic waterproofing solution!

New!



#### DESMOFLEX® Polyurethane Primer One component polyurethane primer

Transparent polyurethane solvent primer, one component. It is used as a primer in THRAKON's DESMOFLEX® PU waterproofing system. It has a great penetrating capacity on absorbent surfaces. It is ready to use, and dries quickly. At the same time, it polymerizes with the moisture of the subsoil and the air.

-  Exterior & Interior use
-  150 – 250 ml/m<sup>2</sup> applied in one layer
-  72 items (4 kg)

Code	Pkg	Shade
P21660804	4 kg	Transparent



#### DESMOFLEX® Epoxy Primer Pioneering technology 2-component epoxy primer, water based

A transparent, rigid, two component epoxy primer, water-based. Used as a universal primer in waterproofing, sealing and floor coating applications on absorbent and non-absorbent surfaces. DESMOFLEX® Epoxy Primer cures by reaction (cross linking) of the two components. Also provides high tensile and impact strength.

-  Exterior & Interior use
-  100 - 200 gr/m<sup>2</sup> applied in one layer

**Pkg:** 3 kg A + 1 kg B

Code	Pkg	Shade
P21660103	(A+B) 4 kg	Transparent



### DESMOFLEX® Polyurethane

#### New generation liquid-applied polyurethane waterproofing membrane (1K)

A polyurethane based, white, glossy one component used for long term waterproofing. Due to its polyurethane technology, provides solutions to problems of waterproofing where the other methods fail, like to surfaces with stagnant waters and ices. Based on pure elastomeric hydrophobic polyurethane resins, which result in excellent mechanical, chemical, thermal, UV and natural element resistance properties. DESMOFLEX® PU polymerizes with the moisture of the subsoil and air.



Exterior &  
Interior use



1,4 - 2,4 kg/m<sup>2</sup> applied in  
2 or 3 layers



36 items (25 kg)



5 items (6 kg)

Code	Pkg	Shade
P21660205	6 kg	White
P21660225	25 kg	Glossy



### DESMOFLEX® Top Coat

#### Advanced technology 2-component aliphatic polyurethane top-coat, UV-stable (2K)

2-component coating with unaffected whiteness and gloss, suitable for the long-term protection of roofs, rooms, balconies and asphalt, EPDM or PVC membranes that have been prior sealed with DESMOFLEX® PU. It provides excellent mechanical, thermal, chemical and UV resistance as well as protection against frost and chalk.



Exterior &  
Interior use



120 - 250 g/m<sup>2</sup> per layer



72 items (5 kg)

Code	Pkg	Shade
P21660305	5 kg	White Glossy



### DESMOFLEX® Fiber Fix

#### 1-component fibre-reinforced liquid polyurethane membrane for waterproofing details on roofs and terraces

DESMOFLEX® Fiber Fix is a fibre-reinforced, spreadable, one-component polyurethane-based membrane with high thixotropy and elasticity. It polymerizes with the humidity of the environment forming a single membrane without bubbles. Intended for use as a spreadable sealant for long-term insulation of roofs, terraces and floor joints, where details must be covered. Its unique composition of elastomeric, hydrophobic polyurethane resin and inorganic chemical additives makes it resistant to chemical and thermal attacks, ultraviolet (UV) radiation, to intense weather conditions while giving it excellent mechanical properties so that it can easily cope with various mechanical stresses.



Suitable for roofs details waterproofing, terraces but also joints between floors. More specifically, it is indicated for joints between wall and floor, at angles up to 90°, pipes, skylights, ventilation, chimneys, bases of air conditioning units, siphons, gutters, skylights, photovoltaic and solar systems. In addition, it is indicated for the waterproofing of details in large technical projects of high demands.



Exterior &  
Interior use



~ 1,4 - 2,4 kg/m<sup>2</sup>



5 items (6 kg)

Code	Pkg	Shade
P21660425	6kg	Grey
P21660405		White



### DESMOFLEX® Catalyst

#### Reaction accelerator

DESMOFLEX® Catalyst is a reaction accelerator suitable for use in conjunction with the DESMOFLEX® PU system. It is used when the application is to be done under low temperatures or when greater thicknesses of layers are required, as well as shorter waiting times between them. With the addition of DESMOFLEX® CATALYST, the uniform polymerization of the waterproofing membrane is accelerated, resulting in the possibility of applying the next layer within 4-5 h, even in conditions of low atmospheric humidity. At the same time, the creation of bubbles is prevented, and the mechanical strength increases.

Suitable for polyurethane system applications at low temperatures or when greater layer thicknesses are required, as well as shorter waiting times between them.

Exterior & Interior use

3% by weight DESMOFLEX® Polyurethane

12 items (750 gr)

Code	Pkg
P21660608	750 gr



### D-FLEX® Clear

#### Transparent elastic, spreadable, sealing membrane with high mechanical strength

Transparent elastic spreadable membrane of polyurethane technology for long-term waterproofing. The sophisticated D-FLEX® technology gives the application surface excellent protection against UV radiation so that it does not turn yellow over time and remains transparent and elastic. The hydrophobic film that is formed shows high tightness and elasticity, while it is also characterized by excellent mechanical and chemical resistance.

Suitable as a waterproofing material on surfaces where we do not want to change the aesthetic effect, such as external surfaces (roof/terrace/wall) covered by tiles, natural stone, wood, bamboo, decorative cement mortars (tread, slopes, etc.), glass blocks, domes, glass patios and greenhouses, polycarbonate sheets, etc. It is also used as a binding material for glueing mosaics/flakes to decorative indoor and outdoor floors.

Exterior & Interior use

3-4 m<sup>2</sup>/kg per layer

72 items (5 kg)

12 items (750 gr)

Code	Pkg
P21660618	750 gr
P21660605	5 kg

## ΑΣΦΑΛΤΙΚΑ ΠΟΛΥΟΥΡΕΘΑΝΙΚΑ



### D-FLEX® Bitu

#### 2-component bituminous polyurethane

D-FLEX® BITU bituminous polyurethane consists of a set of hydrophobic polyurethane resins (A component) and bitumen (B component). The final produced membrane, which develops from the mixing and reaction of the 2-components in markedly time (fast curing), exhibits excellent elasticity and mechanical strength while offering high resistance to any chemical attack.

Suitable for basements/foundations, planted roofs, non-potable water tanks, irrigation canals, under tiles (after applying quartz sand on the last layer) in kitchens, bathrooms, balconies, roofs, under thermal insulation roof slabs, in technical road works for the waterproofing of bridge decks, in tunnels, etc., as well as for application to elenite, sheet metal, gypsum boards, cement boards and polyurethane foam.

Exterior & Interior use

1,5- 2,0 L/m<sup>2</sup> for 2-3 coats, depending on the substrate.

**Packaging:** A 20 L + B 20 L

Code	Pkg
P21660416	(A+B) 40 L



### D-FLEX® Bitu Aqua

One-component, polyurethane-bituminous liquid waterproofing membrane

D-FLEX® BITU AQUA is a one-component thixotropic liquid membrane, asphalt-polyurethane dispersion base. The produced membrane is characterized by high elasticity and mechanical strength, while it offers excellent adhesion to many types of surfaces. It is used on horizontal and vertical surfaces, and the sophisticated D-FLEX® technology gives the application surface excellent protection against UV radiation with a long-lasting effect.



Suitable for building basements (foundations), retaining walls, wet areas, bituminous membranes, for application under tiles (after applying quartz sand on the last layer), gypsum boards, cement boards, as well as for use on roofs, terraces and balconies.



Exterior & Interior use



~ 1.0 - 1.5 kg/m<sup>2</sup>



33 items (20 kg)

Code	Pkg
P21661414	20 kg

## CRYSTALLINE

New!



### CRYSTALLINE SLURRY DSF 310

Brushable crystalline waterproofing slurry

Brushable cement-based waterproofing slurry with crystallising effect for high performance waterproofing and deep protection (not only on the surface). When applied on the concrete surface, the active chemicals create insoluble crystalline complexes. These crystals make concrete watertight while on the same time protecting small cracks from penetration of water, even under pressure.



Waterproofing of old and new surfaces of concrete, for interior or exterior surfaces, no matter where water pressure is applied. Also ideal for waterproofing cutting concrete joints, underground concrete elements, drinking water tanks made of concrete, swimming pools, water irrigation channels etc.



Exterior & Interior use



60 items (25 kg)



5 days

Code	Pkg	Shade
P121603100	25 kg	Grey

New!



### CRYSTALLINE ADMIX DSF 315

Crystalline waterproofing admixture

Concrete admixture in powder form for waterproofing and protection of concrete. It creates crystals which close porous and hair cracks on surface of concrete. It can be used at concrete production plants (before adding water) or on-site (after mixing cement with water).



Ideal for waterproofing of foundations, underground areas, water tanks, swimming pools, etc



Exterior & Interior use



50 items (20 kg)



5 days

Code	Pkg
P121603150	20 kg

## CEMENT BASED

**FLEX DSF 350****Flexible, 2-component, brushable waterproofing slurry**

DSF 350 FLEX is a flexible waterproofing mortar suitable for the waterproofing of indoor and outdoor surfaces.



Suitable for waterproofing in roofs, inverted roofs, underground tanks, balconies, showers before tiling. Offers elasticity. Suitable for surfaces that subject to contractions and expansions as well as vibrations. Crack-bridging ability.



Exterior & Interior use



1,5 kg/m<sup>2</sup> 1 mm per layer



60 items (A 25 kg + B 10 kg)

**Packaging:** A 25 kg + B 10 kg

Code	Pkg	Shade
P11603500	35 kg	Grey
P11603501	35 kg	White

**SUPER ELASTIC DSF 353****Highly flexible, 2-component, brushable waterproofing slurry**

DSF 353 SUPER ELASTIC is an elastic waterproofing mortar suitable for the waterproofing of indoor and outdoor areas



Suitable for waterproofing concrete surfaces such as foundations, tunnels, retaining walls, above ground tanks, swimming pools, terraces. Provides protection from corrosive atmosphere. Offers great elasticity. Suitable for surfaces that subject to contractions and expansions as well as vibrations. Crack-bridging ability. May be applied as a final layer on terraces.



Exterior & Interior use



1,4 - 1,6 kg/m<sup>2</sup> 1 mm per layer



60 items (A 20 kg + B 10 kg)

**Packaging:** A 20 kg + B 10 kg

Code	Pkg	Shade
P11603530	30 kg	Grey
P11603531	30 kg	White

**STRONG DSF 360****Brushable waterproofing slurry**

DSF 360 is a brushable, cement-based, waterproofing slurry, modified by polymer additives for applications under both positive and negative pressures, for indoor and outdoor applications.



Suitable for sealing concrete surfaces such as underground areas, water tanks, tunnels, foundations, ducts, elevator wells, exterior chimney areas in old and new constructions.



Exterior & Interior use



2,5 - 4 kg/m<sup>2</sup> per two layers, depending on the type of the surface



60 items (25 kg)



4 items (5 kg)

Code	Pkg	Shade
P11603611	5 kg	Grey
P11603610	25 kg	
P11603601	5 kg	White
P11603600	25 kg	

**FIBERELASTIC DSF 363****Flexible, fiber-reinforced, brushable waterproofing slurry**

Flexible, fiber reinforced, brushable one-component sealing slurry, reinforced with special polymeric components, creating an absolutely tight, elastic and flexible membrane of high strength.



Suitable for sealing surfaces like concrete foundations, tunnels, retaining walls, above ground tanks, swimming pools, terraces. Provides protection against the corrosive agents in the atmosphere. Applied to substrates that are subject to vibration and contraction. Bridges hairline cracks present in the substrate.



Exterior & Interior use



2 - 4 kg/m<sup>2</sup> per two layers, depending on the waterproofing requirements



60 items (18 kg)

Code	Pkg	Shade
P11603630	18 kg	Grey
P11603631	18 kg	White



## DSF 370

### Waterproofing plaster

DSF 370 is a waterproofing, one-component, cement based plaster that consists of high silica content for improved waterproofing properties. Provides thin layers on interior or exterior surfaces of buildings, underground spaces, canals and water tanks.



Suitable for waterproofing applications upon concrete, brick, cement, stone and other very hard surfaces and substrates located constantly under water.



Exterior & Interior use



6 kg/m<sup>2</sup> per 3 mm



35 items (40 kg)

Code	Pkg	Shade
P11603700	40 kg	Grey

## ACRYLIC BASED



## FLEX HYDROSTOP DSF 300

### Elastomeric waterproofing membrane

DSF 300 Flex Hydrostop is a flexible, brushable, one-component, waterproofing membrane for waterproofing jointless and with no connections substrates, vertical or horizontal surfaces.



Suitable for tiling on humid places (rooms, showers, toilets, washing machines) as well as waterproofing concrete elements or floors on terraces and balconies which are to be coated with tiles. Used as a system, applied after GLX 292 primer (for absorbent substrates or STATUS DUR WATER).



Exterior & Interior use



1,6 - 2 kg/m<sup>2</sup> per two layers, depending on the type of the surface



60 Items (20 kg)

Code	Pkg
P21603000	5 kg
P21603001	20 kg



## ROOF SEALER FLX 380

### Brushable, elastomeric waterproofing membrane

Highly flexible, acrylic based, one-component, brushable membrane. The white shade protects against ultraviolet radiation and heat transfer through the buildings.



Suitable for sealing terraces, roofs, balconies, corners etc. It is also used for sealing corners and filling hair cracks (up to 1 mm) and joints between concrete slabs up to 1 mm in size, on surfaces that exhibit contraction and vibration.



Exterior & Interior use



1 kg/m<sup>2</sup> per two layer application depending on the type of the surface



324 Items (1 kg)

60 Items (5 kg)

33 Items (12 kg)



12 Items (1 kg)

Code	Pkg	Shade
P21613804	1 kg	Terracotta
P21613805	5 kg	
P21613803	12 kg	
P21613801	1 kg	White
P21613802	5 kg	
P21613800	12 kg	



## HYBRID PU FLX 385

### Hybrid, brushable, elastomeric waterproofing membrane without solvents

Hybrid, waterproofing coating for roofs with UV cross linking system. New technology, roof waterproofing elastic membrane without solvents. High resistance to moisture, UV radiation and low temperatures.



Suitable for roof waterproofing on new or old construction giving the ability to withstand standing water. Appropriate for spreading bituminous membrane with or without chip. Applied on concrete, mortar, cement tiles, ceramic tiles, terrazzo and asphalt membranes. Also suitable for application to surfaces of glass, metal, galvanized steel, elenite, asphalt coated aluminum. Excellent adhesion to polyurethane waterproofing layers and insulating polyurethane or polycarbonate panels.



Exterior & Interior use



0.8 - 1,5 kg/m<sup>2</sup>,per two layer application



80 items (4 kg)

36 items (12 kg)

Code	Pkg	Shade
P21613851	4 kg	White
P21613850	12 kg	

## COMPLEMENTARY PRODUCTS

**FIBERGLASS MESH (70 g/m<sup>2</sup>)****Grid width 10cm:**

Fiberglass for strengthening universal sealant spreads (e.g. FLX 380, FLX 385, DSF 360, DSF 350, DSF 353, DSF 363) in particular tough cases of multiple cracking.



Tape 10cm x 50m

70 g/m<sup>2</sup>**Open frames:** 4 x 5 mm

Code
T10400710

**WATERPROOFING FIBERGLASS MESH (70 g/m<sup>2</sup>)****Waterproofing fiberglass mesh****Grid width 100cm:**

Fiberglass for strengthening universal sealant spreads (e.g. FLX 380, FLX 385, DSF 360, DSF 350, DSF 353) in particular tough cases of multiple cracking.



Roll 1 m x 50 m

70 g/m<sup>2</sup>

33 Rolls

**Open frames:** 1 x 2 mm

Code
T10400700

**KF 12/7 & F 12/7****Joint sealing tapes**

Elastic waterproofing tapes offered in two types:

**Joint Sealing Tape F 12/7:** Elastic, fleece-backed, sealing tapes for bridging movement joints, floor and wall intersections 10m/item.

**Joint Sealing Tape KF 12/7:** Elastic, knitted fabric-backed, sealing tapes for bridging movement joints, floor and wall intersections in horizontal and vertical angles for increased waterproofing 50m/item.



Used as a system with THRAKON waterproofing products  
(DSF 300 - DSF 350 - DSF 353 - DSF 360 - DSF 363)

**Width of mesh:** 12 cm**Width of thermoplastic elastomeric part:** 7 cm

Code	Pkg
T10000250	Roll F 12/7
T10400000	Roll KF 12/7

**THRAKON FABRIC (60 g/m<sup>2</sup>)****Waterproof reinforcement polyester fabric**

Polyester fabric weighing 60 g/m<sup>2</sup>, for reinforcing various roofs spinal layers, either on the entire surface, or in dangerous places (e.g. cracks). It is applied in combination with the roofing membranes renewal, wet application over the entire surface to be waterproofed or locally at: wall-to-floor joints (joints), wall-to-wall joints (joints), around discharge pipes and chimneys, ceiling units and air conditioners, water outlet (siphon), 90 degree corners, inside joints and over cracks, etc.



Roll 1,00m height x 100 m width  
0,20m height x 100 m width



7 days

Code	Pkg
T10000351	1,00x100m
T10000350	0,20x100m

## IMPREGNATING



### HYDRO R

#### Hydrophobic impregnation product

Ready to use, clear, water repellent, solvent-based, liquid, for permanent waterproofing of all kinds of inorganic substrates such as plaster, exposed concrete, exposed masonry, decorative bricks, tiles and tile joints, natural and artificial stones, tiles, etc. It does not create film and is vapor permeable.



The surface must be clean, dry, structurally sound and free from all dirt. Protect adjacent materials that may be destroyed of the solvents. The material is applied by spraying, roller or brush in 1-2 layers, wet on wet.



Exterior & Interior use



0,15 - 0,35 L/m<sup>2</sup> per coat, depending on the type of substrate



72 items (5 L)  
24 items (20 L)

Code	Pkg
P21610005	5 L
P21610000	20 L



### NANOSHIELD O

#### Nanomolecular product for protection of surfaces against oil

Product of nanomolecular structure that seals porous and slightly porous surfaces from oil stains, moisture infiltration, creating salts and prevents mold. At the recommended dosage it does not create film and does not cause aesthetic alteration to the application surface. Characterized by excellent penetration and has the advantage of rapid absorption on the substrate.



Apply to various surfaces such as marble, mgranite, brick, concrete, plasterboard, chipboard, plaster, tile grout etc. Suitable for indoors and outdoors.



Exterior & Interior use



50 -100 mL/m<sup>2</sup>, depending on the absorbency of the substrate.



240 items (1 L)  
72 items (5 L)



16 items (1 L)



White (transparent when dry)

Code	Pkg
P21620000	1 L
P21620100	5 L



### NANOSHIELD W

#### Nanomolecular product for protection of porous surfaces against moisture, mildew, fungus and creation of salts

Product of nanomolecular structure, which seals the absorbent surfaces from moisture and from the occurrence of salts, mold and fungi.



Suitable for indoor and outdoor, in brickwork, natural stone, concrete, plasterboard, particleboard, plaster, tile grout etc.



Exterior & Interior use



100 - 200 mL/m<sup>2</sup>, depending on the absorbency of the substrate



240 items (1 L)  
72 items (5 L)



16 items (1 L)



White (transparent when dry)

Code	Pkg
P21621000	1 L
P21621100	5 L

## PRIMERS AND ADMIXTURES



### ANTI-LIME

#### Plasticizer – Retarder for mortars

ANTI-LIME is a transparent resin liquid that replaces the use of lime. Prevents from problems caused by using lime (e.g. "blows").

Ideal for mortar, plaster, masonry, marble, stone and tile applications. Suitable when the extension of open time and the improvement of the adhesion strength of mortars on the application surface is required.

Exterior & Interior use

a) For plasters:  
0,2 - 0,5 kg / cement bag

240 Items (1 kg)

b) For masonry mortars:  
0,15 kg / cement bag

16 Items (1 kg)

Code	Pkg
P21390010	1 kg
P21390015	5 kg
P21390020	20 kg



### GLX 290

#### Acrylic primer – Transparent

GLX 290 is one component, acrylic based primer that impregnates and stabilizes cementitious mortars, creating a bonding bridge for materials to follow. It protects the surfaces from staining and prevents the absorption of water.

Suitable for coating surfaces before painting or repairs.

Exterior & Interior use

80 items (4 kg)

Undiluted:  
60-90 g/m<sup>2</sup> per coat

Dilution:

• For relatively smoothly cementitious substrates

(e.g. cementitious floor screeds, plasters, etc.):

primer: water = 1:4 - 300-350 g/m<sup>2</sup> per coat

primer: water = 1:3 - 350-400 g/m<sup>2</sup> per coat

• For absorbent surfaces like AAC:

primer: water = 1:4 - 400-450 g/m<sup>2</sup> per coat

Code	Pkg
P21472901	4 kg

\* These consumptions are indicative and depend on the type of substrate (absorption, smoothness, etc.) and the type of application.



### GLX 292 FLEX PRIM

#### Acrylic primer - High penetration

Ready to use micronized acrylic water-based primer with high penetration ability.

Ideal for preparing each new or old porous surface such as plaster, brick, concrete, plastered walls etc, creating an adhesion bridge for acrylic plasters, water paints, mortars, tile adhesives, acrylic and cementitious waterproofing spreads etc.

Exterior & Interior use

15 - 20 m<sup>2</sup>/L depending on surface porosity

240 items (1 kg)  
84 items (5 kg)  
24 items (20 kg)

16 items (1 kg)

Code	Pkg
P21472920	1 kg
P21472925	5 kg
P21472921	20 kg



### LATEX 296

#### Polymer latex for multiple type improvement of mortars

Building acrylic admixture. Suitable for improving the properties of mortars such as: mechanical strengths, shrinkage, adhesion on various surfaces, flexibility, resistance to frost, permeability, resistance to friction, resistance to acids and workability. Recommended for cement and gypsum based mortars. Without organic solvents.

Suitable for all kinds of mortars based on cement or plaster.

Exterior & Interior use

Dilute with water.  
Ratio: THRAKON LATEX 296:  
water = 1:1 to 1:5

240 Items (1 kg)

16 Items (1 kg)

Code	Pkg
P21472960	1 kg
P21472962	5 kg
P21472961	20 kg

## GLX 298 PREMIUM

### Acrylic based primer for improving plaster adhesion strength



GLX 298 is ready to use acrylic based primer. Consists of synthetic resins and quartz sand.



For improving adhesion strength of cement or gypsum based plaster on smooth or non-absorbing surfaces. After the application, a rough surface is created.



Exterior & Interior use



160 Items (1 kg)



0,19 - 0,24 kg/m<sup>2</sup>



Pink

Code	Pkg	Shade
P121479800	1 kg	Pink
P121472983	5 kg	
P121472984	20 kg	

## SEALANTS

## ANTI-MOULD

### Anti-mould silicone



One-component acetoxy cure silicone sealant for a range of general sealing and glazing applications.



Suitable for applications that require elasticity, in general sealing applications and application of glass panes. Sealing perimeter of the frames. Sanitary applications. Joints and expansions. Not paintable.



Exterior & Interior use



12 items (280 mL)



Joint 6 mm x 6 mm:  
8 m per cartridge  
Joint 12 mm x 6 mm:  
4 m per cartridge

Code	Pkg	Shade
C/C	280 mL	Transparent, White

## KITCHEN & BATH

### Silicone sealant



Specially designed silicone sealant, acetoxy based for use in wet areas such as bathrooms and kitchens. Not suitable for aquariums.



Suitable for welding of glass and cabin bathroom joints, during construction. Filling of tile joints, bathtubs and bathroom cabinets during installation. On glass surfaces without priming. Filling joints between the tub and tiles. Sealing sinks, bath compounds as well as waterproofing and welding of glass bricks.



Exterior & Interior use



12 items (280 mL)



Joint 6 mm x 6 mm:  
8 m per cartridge  
Joint 12 mm x 6 mm:  
4 m per cartridge

Code	Pkg	Shade
C/C	280 mL	Transparent, White





## ELASTO PU

### Polyurethane joint sealant, medium modulus expansion

Polyurethane, medium modulus expansion one-component polyurethane joint sealant, with medium expansion, that matures during exposure to atmospheric humidity. Offers great adhesion.



Suitable for sealing and for the construction of expansion joints in all common building materials such as cement, bricks, ceramics, glass, wood, irons galvanized and chrome plated as well as various plastic.



Exterior & Interior use



12 items (310 mL / 600 mL)



Joint 15 mm x 8 mm:

2,5 m per cartridge 310 mL

5 m per 600 mL

Joint 20 mm x 10 mm:

1,5 m per cartridge 310 mL

3 m per 600 mL

Code	Pkg	Shade
C/C	310 mL	White/ Grey*/ Brown*
C/C	600 mL	

\*Upon order



## PU FOAM

### Polyurethane foam - Hand use one component self expanding

Self-expanding polyurethane foam, one component, reacts and hardens in contact with air and humidity. It has excellent adhesive properties in almost all building materials.



Suitable for filling holes and gaps on thermal insulation plates, during application of exterior thermal insulation system.



Exterior use



12 items

Code	Pkg
T10000420	750 mL



## PU FOAM GUN

### Polyurethane gun foam one component self expanding

Self-expanding polyurethane foam, one component, reacts and hardens in contact with air and humidity. It has excellent adhesive properties in almost all building materials.



Suitable for filling holes and gaps on thermal insulation plates, during application of exterior thermal insulation system.



Exterior use



12 items

Code	Pkg
T10000430	750 mL





# 06

## REPAIRING MORTARS

---

Repairing Mortars

---

Complementary Reinforcement Products

---

## REPAIRING MORTARS



### EPOSHIELD INJECT S

Injectable, two-component epoxy resin suitable for cracks width 0.1-3.0 mm.

Injectable solvent free, two-component epoxy resin. Used to apply resin injections in concrete cracks width 0.1-3.0 mm.

Suitable for injections in concrete cracks 0.1-3 mm wide. Suitable for fixing and anchoring of reinforcing bars in concrete surfaces. It is also a valuable tool for fixing and anchoring of reinforcing bars in existing building elements. It offers excellent results even on damp substrates.

Exterior & Interior use

1,1 kg/L headspace for crack sealing

12 Items (1 kg)

Code	Pkg
P21624001	1 kg



### EPOSHIELD INJECT W

Injectable two-component epoxy resin for cracks > 3.0mm - Bonding agent

Injectable solvent free, two-component epoxy resin. Used to apply resin injections in concrete cracks larger than 3.0 mm.

It is used as a bonding key between fresh and old concrete, according to the Concrete Regulation. It is also suitable for injection application in concrete cracks wider than 3mm. Suitable for fixing and anchoring of reinforcement rods in concrete surfaces.

Exterior & Interior use

1,5 kg/L headspace for crack sealing

12 Items (1 kg)

Code	Pkg	Shade
P21623001	1 kg	Grey
P21623004	4 kg	



### REPIFIX TOP WRM 483

Extra fine cementitious putty

Extra fine cementitious putty reinforced with special resins. With excellent workability by hand or airless pistol, leaving a smooth finish, with high abrasion resistance, very good adhesion to the substrate, ready for painting.

For putting exposed concrete and stucco surfaces, cover or nesting resources. Also ideal for local repairs seals cracks etc. Suitable for indoor and outdoor use. It is classified as concrete repair mortar type PCC R2 according to EN 1504-3.

Exterior & Interior use

~ 1,3 kg/m<sup>2</sup>/mm Thickness

60 items (25 kg)

4 items (5 kg)

PCC R2 EN 1504-3

Code	Pkg	Shade
C/C	5 kg	Grey
P11704831	25 kg	
P11704834	5 kg	White
P11704832	25 kg	



### WRM 500

Fast setting repairing mortar

WRM 500 is a fast setting sealing mortar (3 minutes setting time). Cement based, non shrinkable and requires only water for its preparation.

Immediately seals cracks, leaks, holes and joints in all masonry and concrete constructions, such as dams, sewers, wastewater tanks, water tanks, underground spaces, tunnels, foundations. Suitable for anchoring of bolts, piping, sanitary ware and in general for works that require fast and strong support.

Exterior & Interior use

1 kg yields approximately 0.6 L of ready to use mortar

100 items

Code	Pkg	Shade
P11705500	4 kg	Grey



### REPIFIX PROTECT WRM 510

Anticorrosive primer for steel reinforcement

One-component, spread anticorrosive product, consisting of special specifications cement, silicon, resins and improvers additives.

Suitable for anticorrosive use on reinforcement steel, preparation of concrete, iron and other structural materials as a bonding key prior to the application of repairing materials.

Exterior & Interior use

On reinforcement: 0,06 - 0,12 kg /m

120 Items (5 kg)

As bonding agent: Approximately 2,0 kg/m<sup>2</sup> for 2 layers

4 Items (5 kg)

Code	Pkg	Shade
P11705101	1 kg	Grey
P11705100	5 kg	



### REPIFIX EXTRA WRM 512

#### Mortar for plastering and building

Mortar for plastering and building. Ideal for simple applications. Suitable for indoor and outdoor use.



Suitable for the restoration of fallen plasters and simple cracks on the masonry.



Exterior & Interior use




~15 kg/m<sup>2</sup>/mm Thickness



60 Items (25 kg)

Code	Pkg	Shade
P11705121	25 kg	Grey
P11705120	25 kg	White



### REPIFIX CLASSIC WRM 515

#### Repairing mortar R2

Repairing cement based product, one-component, type PCC R2 based on EN 1504-3.



Suitable for repairing concrete surfaces, masonry, plaster, gutters construction, manufacturing roof ridges, etc.



Exterior & Interior use



~ 15 kg/m<sup>2</sup>/cm Thickness



60 items (25 kg)



Code	Pkg	Shade
P11705150	25 kg	White
P11705154	25 kg	Grey
P11705152	25 kg	Brick red



### REPIFIX RAPID WRM 518

#### Fast setting (60min) repairing mortar R2

WRM 518 is a one-component, resinous, cement based, fast setting repairing material, type PCC R2 based on EN 1504-3.



Suitable for repairing concrete surfaces, masonry, plaster, gutters construction, manufacturing roof ridges, etc.



Exterior & Interior use



~ 15 kg/m<sup>2</sup>/cm Thickness



60 Items

**Gutter construction:** 1,8 - 2,6 kg/m



Code	Pkg	Shade
P11705180	25 kg	Grey



### REPIFIX REPAIR WRM 519

#### High-strength fibre-reinforced repair mortar R3

High-strength reinforced cementitious repair mortar for class R3 concrete. The specific composition of REPIFIX Repair protects the reinforcement from corrosion and restores the passivity of the concrete, while at the same time it is non-shrinking and shows excellent compatibility with the old concrete, resistance to frost and moisture.



Suitable for repair and rehabilitation of old and new, reinforced or unreinforced concrete.



Exterior & Interior use



~ 17-18 kg/m<sup>2</sup>/cm thickness



60 items (25 kg)



Code	Pkg	Shade
P11710000	5 kg	Grey
P11710001	25 kg	Grey



### REPIFIX RAPID+ WRM 520

#### Fast setting repairing mortar R3

WRM 520 is a top quality, one-component, cement based, fast setting (20 minutes), type CC R3, based on EN 1504-3, repairing product for concrete surfaces. Non-shrinking, shows excellent relevance with concrete. Consisting of special specifications cement, silicon resins and additives. Anticorrosion antioxidant activity.



Suitable for repairing damages on concrete constructional defects, wear, impact etc. repairing steps, parapets, pre-constructed and other concrete elements.



Exterior & Interior use



~ 19 - 20 kg/m<sup>2</sup>/cm Thickness



60 Items (25 kg)  
120 Items (5 kg)



4 Items (5 kg)



Code	Pkg	Shade
P11705201	5 kg	Grey
P11705200	25 kg	Grey



### REPIFIX POWER WRM 525

#### High strength, fiber reinforced, repairing mortar R4

Premium quality and high strength, fiber reinforced, one-component, repairing mortar for concrete, type PCC R4, based on EN 1504-3.



Suitable for demanding repairs to concrete surfaces. Applied in thicknesses up to 40 mm per layer with a trowel or launching.



Exterior & Interior use



60 Items (25 kg)  
120 Items (5 kg)



~ 17 - 18 kg/m<sup>2</sup>/cm Thickness



4 Items (5 kg)

PCC  
R4

EN  
1504-3

Code	Pkg	Shade
P11705250	5 kg	
P11705251	25 kg	Grey



New!

### REPIFIX GROUT WRM 530

#### Cementitious grouting for accurate anchoring

Ready to use, cementitious, shrinkage compensated with a controlled increase in volume product. It is waterproof, free of chlorides and high-alumina cement as well as resistant to frost and de-icing salts. It offers high strength (R4) and can be applied for accurate anchoring in big thickness (up to 100 mm).



Ideal for accurate anchoring like steam or gas turbines, electricity generators, compressors, planes, oil machines, cranes, pumpls, crashing units, machines for cutting marbles etc



Exterior & Interior use



60 items (25 kg)



Depending on the application type



5 days

PCC  
R4

Code	Pkg	Shade
P11705350	25 kg	Grey

\*Available on June



### REPIFIX FAST WRM 550

#### Fast setting repairing plaster

WRM 550 is a white, fast setting, cement based, repairing plaster/ render. It consists of cement, lime, marble and improvers admixtures. Perfect for small repairs on walls.



Suitable for plastering of old or new constructions, small repairs (patching), filling holes, repair of detached plaster pieces, wide cracks and missing endings.



Exterior & Interior use



60 Items (25 kg)  
120 Items (5 kg)



13 - 14 kg/m<sup>2</sup> for 1cm thickness



4 Items (5 kg)

Code	Pkg	Shade
P11705502	5 kg	
P11705501	25 kg	White



### CEM EXPRESS

#### Fast setting cement



Used for fast fixing, repairing, anchoring, sealing holes etc. and generally where high strength and speed work is required.



Exterior & Interior use



120 Items (4 kg)



For the preparing of 1L ready for use mix, about 1.6kg CEM EXPRESS is required



4 Items (4 kg)

Code	Pkg	Shade
P11700001	4 kg	Grey



### WHITE CEMENT

#### Portland-limestone cement CEM II/A-L 42,5N



White portland cement, strength class 42.5N, is characterized by high whiteness and excellent workability. It is an ideal solution for any project that requires the production of particularly light-colored concrete and mortars in building constructions.



Exterior & Interior use



120 items (5 kg)



4 items (5 kg)

Code	Pkg	Shade
21.11.820005	5 kg	White



### HIGH STRENGTH GENERAL USE CEMENT

Portland-composite cement CEM II /A-M (V-L) 42,5N



High strength enhanced cement for general use, strength class 42.5N. Due to its enhanced composition and rapid strength development, it is an ideal solution for concrete production.



Exterior & Interior use



120 items (5 kg)



4 items (5 kg)

Code	Pkg	Shade
21.11.820105	5 kg	Grey

## COMPLEMENTARY REINFORCEMENT PRODUCTS



### CLIMAPLUS MESH (160 g/m<sup>2</sup>)

Anti-alkaline fiberglass mesh, produced under ETAG 004.



Suitable for the reinforcement of the basic layer of the exterior thermal insulation system CLIMAPLUS.



Exterior use



1,1 m/m<sup>2</sup>



33 rolls



1m × 50m

**Grid size:** 4 × 4 mm

Code	m <sup>2</sup> / Palette
T10320020	1650



### CLIMAPLUS PROFESSIONAL (160 g/m<sup>2</sup>)

Anti-alkaline fibreglass w, produced under ETAG 004.



Suitable for reinforcing the basic layer of the exterior thermal insulation system CLIMAPLUS.



Exterior use



1,1 m/m<sup>2</sup>



35 rolls



1m × 50m

**Grid size:** 4 × 4 mm

Code	m <sup>2</sup> / Palette
T10320120	1750



### FIBERGLASS FOR WALL REINFORCEMENT (223 g/m<sup>2</sup>)



Exterior use



223 g/m<sup>2</sup>



4 rolls



0,23m height × 50m length

**Open frames:** 10 × 10 mm

Code	Pkg
T010402300	Rolls



### POLYPROPYLENE FIBERS

Synthetic polypropylene fibers that are effective even in small doses. For watertight concrete tanks, watertight grout, reinforced coatings, anti-friction floors etc. Manufactured only from virgin polypropylene without plasticizers. Due to its special surface treatment, it decomposes very easily to 300 million per kilo (at 6 mm).



Exterior & Interior use



150 g/ Packaging

Code	Pkg
T10000650	0,9 kg / 6 mm



# 07

## PLASTERS AND RENDERS

Plasters & Renders

---

THRAKON Mini Silo

---

## PLASTERS & RENDERS



### SHP 205

#### Spray plaster

Spray plaster for surface preparation, acting as a bridge to enhance adhesion for the next layers of plaster.

 Used for all kind of surfaces. Suitable for application on surfaces of concrete, masonry (brick, concrete blocks, aerated concrete, etc), ceilings as well as for surfaces covered with insulation plates.

 Exterior & Interior use

 5 kg/m<sup>2</sup> for thickness of application 0.5 cm

 60 Items (25 kg)

 Also provided in silo

**Max grain size:** 3.5 mm max

Code	Pkg	Shade
P11880025	25 kg	Grey
P11880000	Big Bag	



### GHP 210

#### Basic coat plaster

Basic plaster with very strong adhesion to all normal substrates, due to quartz sand composition. Offers excellent workability, high strength without any crack formation.

 Suitable for filling and leveling the surface before applying final coat or decorative layer. Applied over a thin coat of spray plaster THRAKON SHP 205.

 Exterior & Interior use

 14-15 kg/m<sup>2</sup> for thickness of application 1,0 cm

 60 Items (25 kg)  
35 Items (40 kg)

 Also provided in silo

**Max grain size:** 2,5 mm max

Code	Pkg	Shade
P11820325	25 kg	Grey
P11820440	40 kg	
P11820425	Big Bag	



### FHP 221 WR

#### Water repellent, final coat plaster with quartz sand

Final layer plaster with quartz sand. Ideal for coastal areas and locations with increased humidity.

 Suitable for surface finishes. Applied following the base coat plaster GHP 210. The thickness of application per layer is up to 3 mm.

 Exterior & Interior use

 3 - 4 kg/m<sup>2</sup> per 3 mm

 60 items (25 kg)  
35 items (40 kg)

 Also provided in silo

**Max grain size:** 0,5 mm max

Code	Pkg	Shade
P11810325	25 kg	White
P11810140	40 kg	
C/C	Big Bag	



### FHP 225 WR

#### Water repellent, final coat plaster with marble

Water repellent, final coat plaster. The extra white marble composition contributes to a respectively snow white result.

 Suitable for surface finishes. Applied following the base coat plaster GHP 210. The thickness of application per layer is:

- up to 3mm - FHP 225-0 WR
- up to 7mm - FHP 225-1 WR

 Exterior & Interior use

 FHP 225-0 WR: 3-4 kg/m<sup>2</sup> per 3 mm  
FHP 225-1 WR: 5-6 kg/m<sup>2</sup> per 5 mm

 60 Items (25 kg)  
35 Items (40 kg)

 Also provided in silo

**Max grain size:** • FHP 225-0 WR: 0,5 mm max  
• FHP 225-1 WR: 1,4 mm max

Code	Pkg	Shade
P11810625	25 kg	White
P11810440	40 kg	
P11500051	Big Bag	



### NHP 250 WR

#### Water repellent, one hand plaster with quartz sand

Final hand plaster with quartz sand, with additional water-repellent action. Replaces the base coat plaster and the final coat plaster. Excellent adhesion, provides leveling and smoothing with a single application. Ideal for coastal areas and in locations with increased humidity.

It is produced in 2 types:

- NHP 250-1 WR: Grey
- NHP 250-2 WR: White

It is applied as one-coat plaster over a thin coat of spray plaster THRAKON SHP 205

Exterior & Interior use

14 kg/m<sup>2</sup> per 1cm thickness

35 Items (40 kg)

Also provided in silo

**Max grain size:** 1,4 mm max

Code	Pkg	Shade
P11840040	40 kg	Grey
P11490520	Big Bag	
P11840240	40 kg	White
P11490510	Big Bag	



### NHP 255 WR

#### Water repellent, one hand plaster with marble

White, water repellent, one hand plaster that replaces the base coat plaster and the final coat plaster. Leveling and smoothing with one hand use. The extra white marble composition contributes to a snow white result. Ideal for coastal areas and general in locations with increased humidity.

It is applied as one-coat plaster over a thin coat of spray plaster THRAKON SHP 205

Exterior & Interior use

13-15 kg/m<sup>2</sup> per 1cm thickness

60 Items (25 kg)  
35 Items (40 kg)

Also provided in silo

**Max grain size:** 1,4 mm max

Code	Pkg	Shade
P11840025	25 kg	White
P11840540	40 kg	
P11840640	Big Bag	

New!



### NHP 270

#### Lightweight one hand plaster

White heat-insulating, lightweight single-layer plaster based on cement and natural minerals. It is ideal for smooth surfaces, indoors and outdoors, without the need for troweling. It is applied to surfaces made of aerated concrete, bricks, visible concrete, heat-insulating plates, etc., ensuring a final surface ready for painting.

Suitable for the final finishing of the surfaces after the plaster layer.

Exterior & Interior use

8-10 kg/m<sup>2</sup>/cm

40 items (25 kg)

Also provided in silo

**Max grain size:** 1,6 mm max

Code	Pkg	Shade
C/C	25 kg	White

\*Available on June



### NHP 260

#### Gypsum plaster for mixing machines

One coat, ready mix, gypsum plaster. The exceptional quality of the gypsum composition provides excellent adhesion to the substrate. Leveling, smoothing, and a snow white final surface with one hand use.

Suitable for indoor areas (walls and ceilings) on substrates such as brick, aerated concrete, exposed concrete, insulation boards etc.

Interior use

7-9 kg/m<sup>2</sup>/cm

40 items (30 kg)

Also provided in silo

Code	Pkg	Shade
T10002601	30 kg	White



## NHP 261 GYPSUM

### Building plasters

Fast setting gypsum plaster suitable for quick repairs as well as repairs on vertical surfaces. Gives a snow white result.



Ideal for supporting, building up, marble decorations, as protective layer (e.g. temporarily marble cover) as well as blending with other building materials.



Interior use



40 items (30 kg)

Code	Pkg	Shade
T10002610	30 kg	White



## QZS 700

### Quartz sand

Dried, filtered and graded in different granulometries quartz sand. Excellent workability and with lower water absorption. It contains no salts or foreign particles.



Suitable for a variety of construction and other uses such as industrial floors, screeds, slabs, pipes, blocks, filters for potable and nonpotable water, drainage construction, gardening, sports projects, etc.



Exterior & Interior use



5 days



54 items (25 kg)

#### Max grain size:

No 1: 0,2 - 0,5 mm

No 2: 0,5 - 0,8 mm

No 3: 0,8 - 1,4 mm

No 4: 1,4 - 2,5 mm

No 5: 2,5 - 3,5 mm

Code	Pkg	Κοκκού.
P11800010	25 kg	No.1
P11800020	25 kg	No.2
P11800030	25 kg	No.3
P11800040	25 kg	No.4
P11800050	25 kg	No.5
P11801000	Big Bag	No.1
P11802000	Big Bag	No.2
P11803000	Big Bag	No.3
P11804000	Big Bag	No.4
P11801500	Big Bag	No.5



## MIX 280

### Masonry mortar

Ready to mix mortar, cement based, reinforced with polymer additives for fast and simplified building applications.



Suitable for building of structural elements such as brickwork, cement blocks, stone, pavement slabs and other common building materials.



Exterior & Interior use



Indicative consumption for bricks of dimensions 12x9x19 cm: 23kg/m<sup>2</sup>



35 items (40 kg)



Also provided in silo

Code	Pkg	Shade
P11850250	25 kg	
P11850040	40 kg	Grey
P11850000	Big Bag	



## PAW 290

### Adhesive for Autoclaved Aerated Concrete blocks (AAC)

PAW 290 is one-component polymer modified cement based mortar.



For building of structural elements made of Autoclaved Aerated Concrete.



Exterior & Interior use



1 bag of 25 kg per 1.25 m<sup>3</sup> aerated concrete



60 items (25 kg)



Also provided in silo

Code	Pkg	Shade
P11492901	25 kg	White

## THRAKON MINI SILO

**THRAKON SILO**

THRAKON MINI SILO, is a small folding silo suitable for storing dry mix mortars in raw form. Available in volume sizes: 6m<sup>3</sup> and 11m<sup>3</sup>. The products for which a silo could be used have the silo symbol.

**Code**

T010000812







# 08

## FLOORING SCREEDS

---

Cement based flooring screeds

---

Primers

---

## CEMENT BASED FLOORING SCREEDS



### NSD 600

#### Cement-based floor screed 3 - 10 cm

NSD 600 is a ready to mix, cement-based mortar suitable for floor filling and leveling. Consists of selected quartz sand of 2.5mm maximum grain size.

Applied at thickness of 3-10 cm. Recommended for: creation of inclinations of flat roofs and outdoor places, ramps, preparation of concrete floors for the installation of any type of tile, marble, decorative materials or parquet, indoor and outdoor areas.

 Exterior & Interior use

 15 - 17 kg/m<sup>2</sup> of dry mortar for 1 cm thickness

 35 Items

Code	Pkg
P11902040	40 kg



### NSF 610

#### Self-levelling floor screed up to 10 mm

NSF 610 is a self-levelling, cement based mortar for the smoothening and levelling of floors. Consists of cement, quartz sand of 0.5 mm max. grain and admixtures.

Applied at a thickness of up to 10 mm. Suitable for construction of selflevelling floors, for preparation in order to install wall to wall carpeting, tiles, plastic or wooden floors glued or not. Final applied surface can be left completely uncovered or painted.

 Exterior & Interior use

 18 kg/m<sup>2</sup> for 1 cm thickness

 60 Items

Code	Pkg
P11903125	25 kg



### NSF 611

#### Self-levelling floor screed 1 - 4 cm

NSF 611 is a self-levelling, cement based mortar for floor smoothening and levelling. It consists of cement, quartz sand of 3.5 mm max. grain and admixtures.

Applied at a thickness of 1 - 4 cm. Suitable for construction of self-levelling floors, for preparation in order to install wall to wall carpeting, tiles, plastic or wooden floors glued or not. Final applied surface can be left completely uncovered or painted.

 Exterior & Interior use

 18 kg/m<sup>2</sup> for 1 cm thickness.

 60 Items

Code	Pkg
P11903225	25 kg



### NSH 650

#### Surface hardener

NSH 650 is a cement-based, polymer-modified, surface hardener for flooring screeds.

Suitable for floor applications that require high mechanical strengths. Consists of cement, quartz sand, pigments and additives.

 Exterior & Interior use

 3 - 5 kg/m<sup>2</sup>

 35 items

Code	Pkg	Shade
P11900040	40 kg	Grey

## PRIMERS

**FLOOR SEAL S****Curing compound with antievaporation agent for concrete floors**

1-component, solvent-based, clear acrylic resin polymer. The unique composition of the product: protects the fresh concrete from rapid evaporation of mixing water, hardens the existing brittle floors to increase their abrasion and wear resistance, enhances the maturation of concrete in order to avoid cracks and dryness, and seals the concrete to avoid dust.



Ideal for areas that are subject to moisture but with light traffic such as basements, parking lots, warehouses, and for large exposed concrete surfaces, such as industrial floors, parking spaces, concrete slabs.



Exterior & Interior use



72 items (4 L)  
24 items (20 L)

**FLOOR SEAL W****Resinous floor stabilizer**

Resinous floor stabilizer, water-based, with high penetration capacity. It is applied to cement floors to prevent the creation of dust while at the same time sealing the pores of the surface, thus minimizing its absorbency. It is also used on friable surfaces to stabilize them and improve their abrasion resistance. After its application, it becomes transparent and thus does not aesthetically alter the surface.



Suitable for stabilizing, reducing absorbency and increasing the surface hardness of cement mortar and concrete floors.



Exterior & Interior use



72 items (5 kg)  
24 items (20 kg)

Code	Pkg	Shade
P21902104	4 L	Transparent
P21902120	20 L	



Code	Pkg	Shade
C/C	5 kg	Transparent
C/C	20 kg	



## ICON MEMO



Interior and exterior use



Exterior use



Interior use



Application



Delivery time



Dimensions



Weight



Consumption



Items per pallet



Items per box



Shades



Also provided in silo



Coefficient of thermal conductivity



Where C/C appears,  
call us to provide you with  
the code of the product.



## CERTIFICATIONS / SYSTEMS

<b>C1</b>	With normal characteristics, for absorbent tiles and common substrates - Exterior & Interior use.	<b>CG2 WA</b>	With enhanced features for demanding applications, with high abrasion resistance, low water absorption and low shrinkage - Exterior & Interior use.		Fire protection class A2
<b>C1T</b>	With normal characteristics, for absorbent tiles and normal substrates - with zero vertical slip - Exterior & Interior use.	<b>D2TE</b>	Dispersion adhesive with enhanced characteristics for all types of tiles, with zero vertical slip and extended open time - Exterior & Interior use.		Certification of the external thermal insulation system.
<b>C1TE</b>	With normal characteristics for absorbent tiles and common substrates. With slip resistance and extended open time - Exterior & Interior use.	<b>R2T</b>	Epoxy-based glue with reinforced characteristics for all types of tiles and with zero vertical slip - Exterior & Interior use.		European Standard EN 13499 for the thermal insulation system.
<b>C2T</b>	With enhanced features for non-absorbent tiles and zero vertical slip - Exterior & Interior use.	<b>S1</b>	With enhanced features for non-absorbent tiles, with zero vertical slip and extended open time - Very Elastic - Exterior & Interior use.		Standard requirements for cementitious grouts.
<b>C2E</b>	With enhanced features for non-absorbent tiles and extended open time - Exterior & Interior use.	<b>S2</b>	With enhanced features for non-absorbent tiles, with zero vertical slip and extended open time - Super Elastic - Exterior & Interior use.		Standard requirements for Expanded Polystyrene (EPS) according to the performance of the material in strength.
<b>C2TE</b>	With enhanced features for non-absorbent tiles, with zero vertical slip and extended open time - Elastic - Exterior & Interior use.	<b>CE</b>	The CE marking is the mark of product quality. Its existence ensures for the consumer that the characteristics of the product he has chosen correspond to the European characteristics established for the product.		Harmonized standard for external and internal coatings.
EU Ecolabel for products that meet strict ecological criteria.			Fiber reinforced product		A product that can be used in the CLIMA PLUS external thermal insulation system.

# INDEX

<b>A</b>			
ACETONE	48	DESMOFLEX® TOP COAT	76
ANTI-LIME	83	D-FLEX® BITU	77
ANTI-MOULD	84	D-FLEX® BITU AQUA	78
ANTISLIP	26, 63	D-FLEX® CATALYST	77
ANTISLIP PROMOTER	63	D-FLEX® CLEAR	77
<b>B</b>			
BONUS ACRYLIC	34	D-FLEX® FIBER FIX	76
<b>C</b>			
CARMYDUR	67	DSF 300 FLEX HYDROSTOP	80
CARMYFIX CM-233	66	DSF 350 FLEX	79
CARMYFIX CM-43	66	DSF 353 SUPER ELASTIC	79
CARMYFIX CM-54	66	DSF 360 STRONG	79
CARMYFIX CM-888	66	DSF 363 FIBERELASTIC	79
CARMYPAINT RP-10	45	DSF 370	80
CARMSAIL	47	<b>E</b>	
CARMSAIL PRIMER	47	ELASTO PU	85
CEM EXPRESS	90	EPOSHIELD INJECT S	88
CERTIFICATIONS / SYSTEMS	103	EPOSHIELD INJECT W	88
CLIMA PLASTER DEC 428	15	<b>F</b>	
CLIMA PRIMER GLX 494	14	FHP 221 WR	94
CLIMABOND THC 403	10	FHP 225 WR	94
CLIMAFLEX THC 410	10	FIBERGLASS FOR WALL	91
CLIMAFLEX THC 410 C	10	REINFORCEMENT (223 g/m <sup>2</sup> )	
CLIMAPAIN SILOXAN	17	FIBERGLASS MESH (70 g/m <sup>2</sup> )	81
CLIMAPLUS BOLTED STEEL ANCHOR	18	FIBERPLUS THC 405	10
CLIMAPLUS COLORING GROUPS	20	FINE PUTTY	44
CLIMAPLUS MESH (160 g/m <sup>2</sup> )	17, 27, 91	FKW 134 EXPRESS	56
CLIMAPLUS PROFESSIONAL (160 g/m <sup>2</sup> )	18, 91	FLOOR SEAL S	101
CLIMAPLUS STARTER	19	FLOOR SEAL W	101
CLIMAPLUS STICK	11	FLX 380 ROOF SEALER	80
CLIMAPLUS STICK GUN	11	FLX 385 HYBRID PU	80
CLIMAPRIMER SILOXAN	17	FMF 150 ULTRA GROUTECH	58
CLIMASIL PLASTER DEC 438	16	FMF 155 EPOXY GROUTECH	60
CLIMASIL PRIMER GLX 498	15	FMF 160 LUX GROUTECH	62
CM-121	65	FSW 140 FIRE STONE	57
CM-141	65	<b>G</b>	
CM-AM	65	GEL	52
CM-PK	65	GEL +	52
COLORANT	49	GHP 210	94
CORNER BEAD WITH MESH	19	GLX 190	64
CROSSES FOR TILES	67	GLX 290	83
CRYSTALLINE ADMIX DSF 315	78	GLX 292 FLEX PRIM	24, 36, 83
CRYSTALLINE SLURRY DSF 310	78	GLX 298 PREMIUM	24, 85
<b>D</b>			
DEC 424 FINE	16	<b>H</b>	
DEC 424 SCRATCH	16	HIDDEN WATERDROP PROFILE	19
DEC 425 RILLEN	17	WITH MESH	
DEC 480	44	HIGH STRENGTH GENERAL USE	91
DECOR ART	25	CEMENT	
DECOR ART SUPERIOR	25	HYDRO R	82
DECOR FINE PLUS	24	<b>I</b>	
DECOR PRIM	26	ICON MEMO	102
DECOR PROTECT	26	<b>K</b>	
DECOR PU VARNISH	26	KDW 138 DECO	57
DECOR SUPERIOR	25	KF 12/7 & F 12/7	81
DECOR ΠΑΙΘΗ 2-ΣΥΣΤΑΤΙΚΩΝ	25	KITCHEN & BATH SILICONE	84
DESMOFLEX® Aqua	75	<b>L</b>	
DESMOFLEX® EPOXY PRIMER	75	LATEX 296	83
DESMOFLEX® POLYURETHANE	76	LS-702	48
DESMOFLEX® POLYURETHANE PRIMER	75	LS-703	48
		LS-705	48
		LS-735	48
<b>M</b>			
METAL MILL	19	<b>N</b>	
MIX 280	96	NANOSHIELD O	82
MKW 136 TRASS	56	NANOSHIELD W	82
MOZAIC PLASTER DEC 433	16	NHP 250 WR	95
		NHP 255 WR	95
		NHP 260	95
		NHP 261 GYPSUM	96
		NHP 270	95
		NSD 600	100
		NSF 610	100
		NSF 611	100
		NSH 650	100
<b>O</b>			
ORGANIC BASECOAT THC 420	11	<b>P</b>	
		PAW 290	96
		PLASTIC ANCHORS FOR BRICKS	18
		PLASTIC MILL	19
		POLYPROPYLENE FIBERS	91
		PRIMO 100%	35
		PRIMO ECO	33
		PRIMO PROFESSIONAL	33
		PRIMO TECH SILICONE	15
		PRO THC 404	10
		PU FOAM	11, 85
		PU FOAM GUN	11, 85
<b>Q</b>			
QZS 700	96	<b>R</b>	
		REPIFIX CLASSIC WRM 515	89
		REPIFIX EXTRA WRM 512	89
		REPIFIX FAST WRM 550	90
		REPIFIX POWER WRM 525	90
		REPIFIX PROTECT WRM 510	88
		REPIFIX RAPID WRM 518	89
		REPIFIX RAPID+ WRM 520	89
		REPIFIX REPAIR WRM 519	89
		REPIFIX TOP WRM 483	88
<b>S</b>			
SHAPE T FOR TILES	67	<b>T</b>	
SHP 205	94	ICON	
SKW 112 ACRYLIC	52	ICON	
SKW 114 EXTRA	53	ICON	
SKW 116 SPECIAL	53	ICON	
SKW 117 STONE	53	ICON	
STATUS 100% ACRYLIC	34	ICON	
STATUS 100% ACRYLIC PUTTY	43	ICON	
STATUS ACRYLIC PRIMER	37	ICON	
STATUS ALL WEATHER	35	ICON	
STATUS AQUADROP	38	ICON	
STATUS AQUADUR	37	ICON	
STATUS AQUAWOOD	39	ICON	
STATUS ARTISTICO	45	ICON	
STATUS BASEWOOD	39	ICON	
STATUS BUILDING PRIMER	41	ICON	

STATUS DUKO	41	VLX 181	63
STATUS DUR	37	VLX 182	64
STATUS DUROMETAL	42	VLX 185 GROUT ELASTIC	64
STATUS DUROMETAL HARDENER	42	VLX 186	64
STATUS ECO	32		
STATUS ECOVARN	40		
STATUS ELITE	36	<b>W</b>	
STATUS EMULSION COLORANT	33	WATERDROP PROFILE WITH MESH	19
STATUS EMULSION PAINT	33	WATERPROOFING FIBERGLASS MESH	81
(70 g/m <sup>2</sup> )			
STATUS ENAMEL UNDERCOAT	38	WEDGE FOR TILES	67
STATUS EVERWOOD	39	WHITE CEMENT	90
STATUS GYPSUM BOARD PRIMER	37	WHITE SPIRIT	47
STATUS KITCHEN & BATH	32	WRM 500	88
STATUS LUXURIOUS	32		
STATUS MARINE PRIMER	41		
STATUS METALLIC	43		
STATUS NAUTICAL	40		
STATUS ONE COVER	43		
STATUS POLYPRIMER	38		
STATUS RELIEF	35		
STATUS REMOVER	47, 63		
STATUS RUST PRIMER	41		
STATUS RUSTBLOCK	42		
STATUS RUSTBLOCK HAMMER FINISH	43		
STATUS STEEL	40		
STATUS STONE VARNISH	45		
STATUS SUPREME	32		
STATUS TEAK OIL	39		
STATUS ULTRASHIELD RIPOLIN	38		
STATUS WASH PRIMER	46		
STATUS WATERCOLOR	34		
STATUS WOOD CLASSIC	40		
STATUSPOOL	46		
STATUSPOOL PRIMER	46		
STATUSPOX	46		
STEEL ANCHORS FOR BRICKS	18		
STUCCOPRO DEC 470	44		

<b>T</b>	
THRAKON FABRIC (60 g/m <sup>2</sup> )	81
THRAKON SILO	97

<b>U</b>	
ULTRAPOR® EPS 80	12
ULTRAPOR® EPS 100	12
ULTRAPOR® EPS 150	12
ULTRAPOR® EPS 200	12
ULTRAPOR® GRAPHITE EPS 80	13
ULTRAPOR® GRAPHITE EPS 100	13
ULTRAPOR® GRAPHITE EPS 150	13
ULTRAPOR® GRAPHITE EPS 200	13
ULTRAPOR® XPS	14
ULTRAWOOL	14

<b>V</b>	
VKW 121 QUARTZ	53
VKW 122 VINYL	54
VKW 124 SUPER ACRYLIC	54
VKW 126 FLEX	54
VKW 127 GRANITO STABILO	55
VKW 128 SUPERFLEX	55
VKW 129 ULTRAFLEX	55
VKW 132 SUPER ELASTIC	56
VKW 137 MARBLE	56
VKW 142 ACRYL	57
VKW 145 EPOXY	57







#### Headquarters

130 Siggrou Avenue  
Athens -11745  
7<sup>th</sup> floor

#### Customer Service

📞 +30 210 36 33 512  
✉️ sales@thrakon.gr

#### Technical Support

📞 +30 210 36 33 512  
✉️ info@thrakon.gr

#### Join us at:

-  / Thrakon.Greece
-  / company/thrakon-group

-  / thrakon.greece
-  / THRAKONGreece

#### We build together.

[www.thrakon.gr](http://www.thrakon.gr)