








LARGE ELECTRIC TRANSACTION DRAWER / 00500993





MEDIUM ELECTRIC TRANSACTION DRAWER / 20000991




SMALL ELECTRIC TRANSACTION DRAWER / 30000991











PREMIUM MANUAL TRANSACTION DRAWER / 13000991




BASIC MANUAL TRANSACTION DRAWER WITH COUNTERTOP / 28000993







60X63 WINDOW-DRAWER COMBINATION UNIT / 12000989




56X48 WINDOW-DRAWER COMBINATION UNIT / 12000993






50X60 WINDOW-DRAWER COMBINATION UNIT / 12001017



32X48 WINDOW-DRAWER COMBINATION UNIT / 12000992





48


PREMIUM SECURITY WINDOWS

Premium security windows come standard with UL-listed, level-1 bullet-resistant glass and a number of configurable options and upgrades.

112X32 PREMIUM WINDOW / 12000996









OUTSIDE ELEVATION

56X32 PREMIUM WINDOW / 12000994






*HVHZ/Hurricane-rated models available.

The purpose of this drawing is to provide an indication of standard product dimensions and spatial requirements only. Contact Bavis for the official CAD file of record and product details such as UL numbers, optional upgrades and additional configurations.


32X32 PREMIUM WINDOW / 12000987



BASIC BALLISTIC WINDOWS


Basic ballistic windows come standard with UL-listed, level-1 bullet-resistant glass. Unlike their premium counterparts, these windows do not include trim around the frame.

65X36 BASIC WINDOW / 12147995




RECOMMENDED WALL OPENING: 65-3/8" WIDE X 36-1/8" TO 36-3/8" TALL

56X33 BASIC WINDOW / 12147992





43X36 BASIC WINDOW / 12147996



RECOMMENDED WALL OPENING: 42-3/4" WIDE X 36-1/8" TO 36-3/8" TALL


32X33 BASIC WINDOW / 12147991







CAPTIVE CARRIER STANDARD CONFIGURATION




HORIZONTAL TUBE SHOULD HAVE A SUPPORT EVERY 10' CAPABLE OF 150 LBS.

IF THE HORIZONTAL TUBE IS USED UNCUT IN THE HORIZONTAL, THERE ARE ENOUGH SUPPLIES TO POSITION THE TOP OF THE HORIZONTAL TUBE 12' 4" ABOVE THE DRIVEWAY SURFACE.

MINIMUM HEIGHT FROM FINISHED FLOOR TO THE TOP OF THE HORIZONTAL TUBE 9' 5-3/4", (113-3/4").

CAPTIVE CARRIER REVERSE LANE CONFIGURATION




RECOMMENDED MINIMUM - MAXIMUM HORIZONTAL LENGTH:
MIN. C-L TO C-L OF VERTICALS: 32"
MAX. C-L TO C-L OF VERTICALS: 33' 10"


HORIZONTAL TUBE SHOULD HAVE A SUPPORT EVERY 10' CAPABLE OF 150 LBS.

IF THE HORIZONTAL TUBE IS USED UNCUT IN THE HORIZONTAL, THERE ARE ENOUGH SUPPLIES TO POSITION THE TOP OF THE HORIZONTAL TUBE 12' 4" ABOVE THE DRIVEWAY SURFACE.

CAPTIVE CARRIER SPLAYED CONFIGURATION




TRANSTRAX STANDARD CONFIGURATION




HORIZONTAL TUBE SHOULD HAVE A SUPPORT EVERY 10' CAPABLE OF 150 LBS.


IF THE HORIZONTAL TUBE IS USED UNCUT IN THE HORIZONTAL, THERE ARE ENOUGH SUPPLIES TO POSITION THE TOP OF THE HORIZONTAL TUBE 12' 4° ABOVE THE DRIVEWAY SURFACE.

TRANSTRAX REVERSE LANE CONFIGURATION






BASIC PNEUMATIC TUBE SYSTEM / 23000994



ADVANCED PNEUMATIC TUBE SYSTEM / 23000992



Bavis' emphasis on product quality and their commitment to creating value for the customer make them an ideal partner, and we highly recommend Bavis to anyone looking to elevate their drive-thru experience.

Agility Recovery

READY TO HELP!

PHARMACIES / BANKS
DISPENSARIES / HOSPITALS
MFG. FACILITIES / UTILITIES
GOVERNMENT / GATE SECURITY
RETROFITS / NEW BUILDS



ABOUT BAVIS

Since 1957, Bavis Fabacraft has manufactured drive thru solutions that expand customer access, ensure employee and customer security and empower businesses to transact more, faster.



Better Drive-thru

PHARMACIES | BANKS | DISPENSARIES | GOVERNMENT SERVICES

BAVIS.COM | 513.677.0500 | info@bavis.com **LinkedIn:** company/bavisfabacraft | **Twitter:** @BavisFabacraft

201 Grandin Rd. | Maineville, OH 45039