REGENCY
FIREPLACE PRODUCTS

• ARCHITECT • DESIGNER • BUILDER •

INNOVATIVE FIREPLACE SOLUTIONS



regency-fire.com/professionals



G800P shown with birch log set, herringbone brick panels in black and clean finish install.



Why Choose Regency?

At Regency Fireplace Products, we understand that every project is unique, and every detail matters. That's why we have been the trusted choice for architects, builders, and designers for over 45 years.

Here's why you should choose Regency for your next construction or renovation project:

UNRIVALED QUALITY

Our commitment to excellence in design, craftsmanship, and functionality ensures that our products stand the test of time, providing both beauty and performance.

INNOVATIVE TECHNOLOGY

We leverage cutting-edge technology to create fireplaces that not only enhance the aesthetics of a space but also offer unmatched efficiency and environmental sustainability.

DIVERSE RANGE OF OPTIONS

Whether your design calls for a dramatic wood-burning fireplace or a sleek, modern gas fireplace, we offer a wide range of styles and configurations to suit any project's needs.

EXCEPTIONAL CUSTOMER SUPPORT

Our dedicated team is here to assist you every step of the way, from product selection to installation and beyond. We pride ourselves on providing personalized service and expert guidance to ensure your project's success.

How We Help Professionals

At Regency, we understand the challenges that architects, builders, and designers face when specifying fireplace products for their projects. That's why we go above and beyond to support professionals like you in every aspect of your work:

STREAMLINED PROCESS

Our efficient ordering and delivery process ensures that projects stay on schedule, minimizing delays and maximizing productivity. We understand the importance of meeting deadlines and strive to make the process as smooth and seamless as possible.

EDUCATIONAL RESOURCES

Earn CEU credits with our variety of educational resources through our partnership with AEC (Architecture, Engineering, and Construction) Daily and the AIA (American Institute of Architects). We help the professional community grow their knowledge and expertise through our tailored seminars both online and through lunch and learning opportunities.

TECHNICAL EXPERTISE

Our team of technical experts is available to provide support and guidance throughout the project lifecycle. Whether you need assistance with product specifications, installation instructions, or troubleshooting, we're here to help. Submit your plans for review for a quick turn-around time and helpful suggestions to ensure your project goes smoothly.

ARCHITECT AND SPECIFICATION LIBRARIES

We collaborate with leading design associations to provide seamless 3-part specifications and offer a robust library of BIM files, ensuring our products integrate effortlessly into design and construction workflows. By actively participating in trade and design shows, we stay connected with industry professionals and trends, making our product information readily accessible, accurate, and up to date.


INSIDE SALES TEAM

Our inside sales team is dedicated to helping professionals like you by reviewing plans and working closely with you to ensure that your fireplace specifications meet your project requirements. We understand the importance of getting every detail right and are committed to providing the support you need to achieve your vision.





G600C shown with coal black crushed glass and painted black steel panels installed with a clean front finish using the cool wall system and chase vent.



Our Resources

At Regency, we believe in providing architects, builders, and designers with the resources they need to succeed. Explore our dedicated resources for professionals:

FOR BUILDERS

Visit our builder's portal to access product specifications, installation guides, and project galleries. Whether you're working on a residential development or a commercial project, we have the tools and resources you need to bring your vision to life.

FOR DESIGNERS

Discover inspiration and tools tailored for designers, including design trends, case studies, and visual resources. Whether you're designing a luxury home or a boutique hotel, we have the resources you need to create breathtaking spaces. ***Contact us if you are interested in becoming a part of our Designer Showcase.***

FOR ARCHITECTS

Access comprehensive resources for architects, including CAD drawings, technical data, and design specifications. Whether you're designing a new building or renovating an existing space, our resources can help you bring your vision to life.

DIGITAL TOOLKIT

Explore our digital toolkit, featuring high-quality images, brochures, and videos to enhance your presentations and proposals. Our digital toolkit makes it easy to use Regency Products to inspire your clients.

BIM FILES

Simplify your design process with our BIM files, providing accurate 3D models and data for seamless integration into your projects. Our BIM files save you time and effort, allowing you to focus on what you do best – creating stunning spaces. Files are available on our website or directly in leading BIM libraries for your software.

EXPLORE ALL OUR RESOURCES : **REGENCY-FIRE.COM/PROFESSIONALS**



San Francisco Bay 40 shown with black reflective crystals, dri ftwood log set, black steel inner panels.

Commercial Use


Our products are ideal for commercial applications, offering unparalleled design flexibility. With advanced technologies like our patented Cool Wall System™ and Power Venting, you can unleash your creativity and craft unique, statement-making finishes. Plus, our systems accommodate long vent runs, making it easy to exhaust outside of large buildings.

City Series Gas Fireplaces and our Grandview G1200 offer the XL fireplace experience and the flexibility needed for commercial projects - particularly well suited for hotels, restaurants and condominium shared spaces.


Technologies

FLEXIBLE VENTING OPTIONS


Regency's Power Vent systems have longer vertical and horizontal vents. Due to this functionality, designers and architects are able to craft applications with freedom and unparalleled flexibility.



Inline Power Vent system shown vertical vent run



Inline Power Vent system shown horizontal vent run



End of line flush horizontal Power Vent system shown in a negative vent run

INLINE POWER VENT SYSTEM

- Allows for both vertical and horizontal termination (horizontal terminations can use Regency's AstroCap)
- Vent runs up to 72 ft. (rigid pipe approved for up to 72 ft. & flex pipe approved for up to 40 ft.)
- Use up to six 90° elbows or twelve 45° elbows
- Use flex vent or rigid pipe
- Access panel required for servicing inline Power Vent




Inline Power Vent



Horizontal Direct Vent Astro Cap
(Used on Inline power vent applications)



Horizontal Flush Power Vent Cap
(Used on End of line applications)





Cool Wall System™


Our patented Cool Wall System™ helps maintain the perfect wall surface temperature around the fireplace. The floating glass safety barrier draws in cool air which is split between the heat exchanger and the inside wall surface. Within the heat exchanger, the air is heated and then directed out the back of the fireplace.




Unlimited finishes.
No limits. No restrictions.

Designed to maintain a cool wall to accommodate custom finishes right to the edge of your fireplace. Complete your fireplace aesthetic with:

- Wood
- Marble
- Glass
- Metal
- Tile
- Fabric
- Wallpaper
- Textured Panel
- Embossed Panel
- Faux Stone



3D Wall Panel



Herringbone Wood Panel







Controllable Warmth

FLEXIBLE VENTING OPTIONS

Regency's patented Cool Wall System™ releases heat at ceiling level which helps evenly distribute the airflow throughout the living space. Through this natural convection of air, excessive radiant heat is reduced enabling users to enjoy the utmost comfort and lounge in the warmth of beautiful flames more often.


- Enjoy the flexibility to choose from 3 different chase vent solutions
- Release warmth into the room discreetly



Front



Side(s)



Top


APP CONTROL

Put the power of flame directly in your hand. Our Proflame Connect Plus App allows precise regulation of the fireplace, turning it on/off, adjusting flame height, and setting temperature directly via smartphone. An optional Wi-Fi enabled module provides the ultimate fireplace control.



Heat Distribution Kit


Increase the effectiveness of your fireplace by dispersing warm air from the fireplace to remote locations in the same room or other rooms in your home by using the Heat Wave™ power duct system.




New York View 40 shown with black reflective crystals, birch log set, black glass inner reflective panels and extended view panels.

City Series


Linear Gas Fireplaces




NEW YORK VIEW
Single Sided




SEATTLE SEE-THROUGH
See-Through



SAN FRANCISCO BAY
Three Sided



CHICAGO CORNER
Corner Left or Right



SANTA MONICA PIER
Pier Left or Right

Features


Offering clean, uninterrupted viewing areas with stunning flame pictures, City Series creates an impactful statement in any room. Take your design to the edge with the freedom to finish with any material, right up to the firebox perimeter - from wood to wallpaper and everything in between!

Safely hang a TV or artwork directly above the fire and enjoy for hours with Cool Wall System's ductless heat dispersion which allows heat to be released at the ceiling and gradually warm the room.

- Clean uninterrupted view of the fire
- Dual-glass invisible safety barrier
- Standard interior lights to accentuate the fire
- Organic & contemporary firebed options
- TV & artwork friendly
- Maximum comfort with Cool Wall System's™ heat dispersion
- No noisy fans or expensive chase ducting required



Santa Monica Pier 50 shown with black reflective crystals, volcanic stones in tan and black enamel inner reflective panels.



Crushed Glass - Black Coal



Crushed Glass - Ginger



Crushed Glass - Iceberg




Andiron Lava Embers - Black




Crystals - Black



Crystals - Copper



Crystals - Starfire



Black and Grey Shale



Choose your look

Integrated accessories with warm realistic firebed. Relaxed, natural flames rise from a richly detailed bed of logs, stones, crystals, or crushed glass media options.



Driftwood Log Set



Birch Log Set



Split Oak Log Set



Elevated Burner - Oak Log Set *(50 & 60 series only)*




Volcanic Stones - Tan or Grey




Fireballs

INTERIOR FIREBOX PANELS



Black Steel Interior Panels



Black Enamel Inner Reflective Panels



Black Glass Inner Reflective Panels



Ledgestone Panels
(50 & 60 series only)



Black Fluted Panels
(50 & 60 series only)

New York View 60 with elevated burner and ledgestone inner panels.


San Francisco Bay 60 shown with black reflective crystals, driftwood logs set and black steel inner panels.




New York View 72 shown with black reflective crystals, birch log set and black steel inner panels.

Grandview Gas Fireplaces


Traditional Gas Fireplaces



MEDIUM (G600)



LARGE (G800)



EXTRA LARGE (G1200)



G1200P shown with Birch logs and volcanic black brick panels.



G800P shown with Oak log set, rustic brown brick panels and clean finish install.

Features

Traditional fireplaces with modern technology. The Grandview series brings all the beauty and warmth of a traditional fireplace but offers all the benefits of modern technology. Finish in any material with optional Cool Wall System™ and hang TV's and artwork safely above the fireplace.

- Mix & match accessories for 100's of different looks
- Largest viewing area in its class
- Clean Front or Traditional Design
- Cool Wall System™ allows for any finishing material right to the edge of the fireplace
- TV & artwork friendly
- Rear or top vent for versatile installations

G800E shown with birch log set, black steel panels and clean finish install.


G800E shown Oak log set, rustic brown brick panels and four sided faceplate in black.

Choose your look



MULTIPLE INTERIOR PANELS


Rustic Brown Brick Panels


Herringbone - Black Brick Panels


Herringbone - Rustic Brown Brick Panels


Volcanic Black Brick Panels


Painted Black Steel Panels


Black Enamel or Black Glass Reflective Panels


MULTIPLE INTERIOR OPTIONS


Birch Log Set


Oak Log Set


Driftwood Log Set

Available for G600 & G800 Series Only


Crushed Glass – Ginger


Crushed Glass – Coal Black


Crushed Glass – Iceberg


Volcanic Stones

MULTIPLE FRONT OPTIONS (Available for G600 & G800 Series Only)


Clean Front Finishing Trim


Outside Finishing Trim


Faceplate

FACEPLATE AVAILABLE IN THREE COLORS:


Black

Brushed Nickel


Antique Copper




Avita EXA160 (64") installed as a three-sided bay fireplace.


Avita Series

Premium Electric Fireplaces


Introducing the Avita: where cutting-edge innovation meets timeless elegance. The Avita is not merely an electric fireplace – it's a statement of refined living. Crafted to encapsulate the l ife and soul of a real log fire, its immersive flame visuals and ambient lighting bring evocative realism, with or without the heat. With next-generation technology at its core, the Avita represents a new age of ultra-realistic luxury electric fire design. Premium non-reflective glass ensures a spectacular view of the highly realistic oak log-effects, brought to life with in ternal log lighting, a glimmering crystalline ember-bed, and a host of lighting options.



SINGLE-SIDED



TWO-SIDED CORNER



THREE-SIDED

Features

- Three sizes available: 48”, 64” and 75”
- 1-Sided Linear, 2-Sided Corner, or 3-Sided Bay installation options
- Option to install as a 5,000 BTU heater with 120V or 9,500 BTU heater with 240V (Hardwire Only)
- Chromalight® Plus LED System
- Internal log lighting, glowing ember bed and host of flame visua l options
- Internally lit split Oak log-effect with pulsing effects
- Crackling fireside sound-effect setting
- Remote, Touch Panel and App Control
- Premium non-reflective glass
- Optional Mood Lighting System
- Crystalline textured base
- Ecodesign Energy Saving Features
- Fan-only mode, delivering gentle air circulation
- Comes with Edge+ finishing frame for single-sided installations
- Flames can be enjoyed with or without the heat



Avita EXA120 (48”) installed as a single-sided fireplace.

Avita EXA190 (75") installed as a two-sided corner fireplace.





Avita EXA160 (64”) installed as a single-sided fireplace.

Outdoor Gas Fireplaces

Design your own outdoor fireplace

Enjoy the drama of beautiful wide-angle flames or the cozy atmosphere of a traditional fire, but outdoors. Customizable burners, see-through linear models, and traditional design options offer versatile alternatives for elegant outdoor living spaces. Create flexible living and outdoor rooms to meet the unique needs of your customers with Regency's lineup of outdoor gas fireplaces.



G800P shown with Driftwood log set, reflective glass black panels and four sided black faceplate. Installed on a covered patio using the outdoor installation kit.



HZO60 shown in single-sided application.


Features

Enjoy all the benefits of the Grandview series with an outdoor conversion kit. Create stunning fire features with our collection of burners, or build see-through outdoor fireplaces with our linear range - the possibilities are endless. Build outdoor spaces your clients will love and extend patio season with our full range of outdoor products.




BURNERS

Regency's Plateau Outdoor Burners are as limitless as they are beautiful, with many design possibilities. Install these linear burners end to end and combine with other burners to create various lengths: 30", 60", 80", or 100", for flexible outdoor design.



OUTDOOR FIREPLACES

Regency's outdoor fireplace extends living spaces and enhances patio enjoyment. Choose single-sided or see-through models, with clean-edge installation or decorative surrounds. Add a manufactured framing kit for simple installation and seamless outdoor design.




GRANDVIEW OUTDOOR

Add Grandview's flexibility and beauty to outdoor living spaces, featuring mix-and-match accessories, Cool Wall System™, and TV-friendly clearances. Elevate your patio with comfort, style, versatility, and exceptional outdoor design for year-round enjoyment.

5 Full Service Distribution Centers

1 CANADA-WEST
6988 Venture St.
Delta, BC V4G 1H4
Toll Free: (866) 946-5155

2 CANADA-EAST
425 Hanlon Creek Blvd.
Guelph, ON N1C 0A1
Toll Free: (800) 273-4362



3 NORTHWEST
20055 NE San Rafael St
Portland, OR 97230
Toll Free: (877) 503-2467

4 CENTRAL
1710 Afton Road
Sycamore, IL 60178
Toll Free: (888) 355-2501

5 EAST
2201B Lakeside Blvd.
Edgewood, MD 21040
Toll Free: (800) 569-4635

Ready when you need it! With over 2,000 dealers to serve you and 5 dedicated fulfillment centers throughout North America, we can get you the right products at the right time for your project.
For inquiries and assistance, please contact our dedicated professionals at:
PROHELP@REGENCY-FIRE.COM

Visit our website for more information: regency-fire.com/professionals

REGENCY
regency-fire.com

© 2026 FPI Fireplace Products International Ltd. Regency®, AstroCap®, Heat Wave™ and Cool Wall System™ are registered or proprietary trademarks of FPI Fireplace Products International Ltd. All rights reserved. Printed in Canada (09/26) Part No. 944-450