

Delivering the Power of  
**POSSIBILITIES**



EX SERIES  
A2 Selection






---

# WE'RE LOOKING FORWARD.

At Nichiha, we think the future is bright.

Your projects come in all shapes, styles and markets. That's why Nichiha is dedicated to helping you build the perfect structure for you, clad in our EX Series.

We combine the aesthetic of your favorite building material with the uncompromising durability of fiber cement, giving you the look you want in considerably less time and for a fraction of the cost. Our expansive collection of textures includes metal, wood, block, stone and brick options in a full range of colors and finishes. Once you've used a Nichiha product, you'll see the difference — and want to use it again and again.






14 | BRICK SERIES

16 | MASONRY SERIES

18 | ESSENTIAL FLASHING SYSTEM

20 | HARDWARE & ACCESSORIES





---

## MULTIPLE LOOKS. ONE SOURCE.

Less time managing, more time imagining.

Why settle for one look when you can get multiple textures and finishes from a single manufacturer? With Nichiha EX Series, you can mix and match cladding styles to achieve the varied look you've been searching for. Whether you're looking for metal, stone, wood, concrete or brick, we have it all. Plus, all of our panel styles operate on the same clip installation system — saying goodbye to multiple contractors. You'll be able to move from conception with ease, all while saving time and money.



**USEFUL TIP**

Add the finishing touches to your next project with our Essential Flashing System on page 18.

Sleek. Bold. Vibrant.

# THE DESIGNER SERIES



---


## Get sophistication in your color.

Modern appeal. High performance. Cost-effective. The Designer Series, featuring Memoria, is ideal for contemporary design projects. With its satin finish, ease of installation and virtually limitless color palette, Memoria provides significantly more value than traditional aluminum composite phenolic panels.

MEMORIA



EFM201 □X



EFM202 □X




EFM203 □X




EFM204 □X




EFM205 □X



ETM301 □X




EFM301 □X




EFM302 □X




EFM303 □X



EFM304 □X



EFM305 □X



EFM306 □X




EDM307 □X



EFM308 □X



EFM319 □X




EDM310 □X




EDM315 □X



EDM316 □X



EDM317 □X



EDM318 □X

MEMORIA SPECS

EX SERIES 1820

DIMENSIONS (ACTUAL MM) 455mm x 1820mm

THICKNESS (ACTUAL MM) 16mm

WEIGHT (KGS. PER PANEL) 17kg/piece

WEIGHT (KGS. PER M<sup>2</sup>) 20.5kg/m<sup>2</sup>

EXPOSED COVERAGE (M<sup>2</sup> PER PANEL) 0.828m<sup>2</sup>

PACKAGING (PIECES PER PACK) 2 [1.656m<sup>2</sup>]

← NOTE: CAN ONLY BE INSTALLED HORIZONTALLY.

# Find form and function in THE MODERN SERIES



---


## Take modern to the next level with the power of fiber cement.

The clean, modular look of the Nichiha Modern Series is a versatile choice for commercial and residential projects alike. The stylish tones and subtle seams are the perfect partner for gleaming glass and stainless steel. If you're looking for a modern contrast, the cool hues glow when paired with the warmth of wood.


ILMIO offers many of the same features as MEMORIA, but takes urban to the next level with a tough, textured finish. ILMIO is built to last with strong construction that stands up to everyday wear and tear, making it the perfect panel for high-traffic areas. You've picked one that packs a punch while saving you time and money in the long run.



ILMIO



EFM501□X



EFM502□X



EFM503□X



EDM504□X



EDM505□X

ILMIO SPECS

EX SERIES 1820

DIMENSIONS (ACTUAL MM) 455mm x 1820mm

THICKNESS (ACTUAL MM) 16mm

WEIGHT (KGS. PER PANEL) 17kg/piece

WEIGHT (KGS. PER M<sup>2</sup>) 20.5kg/m<sup>2</sup>

EXPOSED COVERAGE (M<sup>2</sup> PER PANEL) 0.828m<sup>2</sup>

PACKAGING (PIECES PER PACK) 2 [1.656m<sup>2</sup>]

 NOTE: CAN ONLY BE INSTALLED HORIZONTALLY.



Create depth and intrigue with  
**THE DIMENSION SERIES**



# Color. Texture. Depth. It's Design Complexity Made Simple.

Don't settle for a single, flat look when the Dimension series lets you add depth, texture and color to your designs. Our multi-dimensional Ribbed panels bring visual interest to smooth surfaces, like glass or metal, with recessed reveals and striking shadow lines. An additional element, like color, is the perfect way to add another layer of depth and intrigue. The Dimension series gives you the design flexibility you desire to bring walls to life.


## RIBBED



EPS231 □X



EDS2312 □X



EDS2313 □X

## RIBBED SPECS

## EX SERIES 3030

DIMENSIONS (ACTUAL MM)	455mm x 3030mm
THICKNESS (ACTUAL MM)	16mm
WEIGHT (KGS. PER PANEL)	26kg/piece
WEIGHT (KGS. PER M <sup>2</sup> )	18.8kg/m <sup>2</sup>
EXPOSED COVERAGE (M <sup>2</sup> PER PANEL)	1.378m <sup>2</sup>
PACKAGING (PIECES PER PACK)	2 [2.757m <sup>2</sup> ]



NOTE: CAN BE INSTALLED HORIZONTALLY OR VERTICALLY.  
NOTE: THERE ARE 9 RIBS PER PANEL.



# Warm up your project with THE WOOD SERIES



---

## Get the natural look of wood with the unmatched durability.

Nichiha provides the look of wood without the drawbacks of natural wood cladding. Built to last, our VintageWood and CastingWood panels offer the rich textures of wood while providing color stability and withstanding extreme weather elements. VintageWood exudes modern refinement and works well in both modern and vintage designs. With its earthy appeal, CastingWood adds rustic sophistication to all types of projects. Both products pair perfectly with glass, metal and block panels, adding a touch of warmth to the coolness of these materials.

VintageWood and CastingWood are as versatile as they are durable. Our Wood Series panels can install both vertically and horizontally and can be used in interior and exterior settings. Hidden fasteners provide a clean and beautiful look. Creating the perfect match, Nichiha gives you the beauty of wood backed by the brawn of fiber cement.

## VINTAGEWOOD




EPF282□US / EPC762□X



EPF283□US / EPC763□X



EPF284□US / EPC764□X



EPF285□US / EPC765□X



EPF286□US / EPC766□X

## CASTINGWOOD




EPC241□X



EPC2410□X



EPC243□X



EPC2411□X




EPC245□X



EPC246□X



EPC247□X



EPC248□X

## VINTAGEWOOD SPECS

### EX SERIES 1818

DIMENSIONS (ACTUAL MM)	455mm x 1818mm
THICKNESS (ACTUAL MM)	16mm
WEIGHT (KGS. PER PANEL)	16kg/piece
WEIGHT (KGS. PER M <sup>2</sup> )	19.3kg/m <sup>2</sup>
EXPOSED COVERAGE (M <sup>2</sup> PER PANEL)	0.827m <sup>2</sup>
PACKAGING (PIECES PER PACK)	2 [1.654m <sup>2</sup> ]

 NOTE: CAN ONLY BE INSTALLED HORIZONTALLY.

### EX SERIES 3030

DIMENSIONS (ACTUAL MM)	455mm x 3030mm
THICKNESS (ACTUAL MM)	16mm
WEIGHT (KGS. PER PANEL)	26kg/piece
WEIGHT (KGS. PER M <sup>2</sup> )	18.8kg/m <sup>2</sup>
EXPOSED COVERAGE (M <sup>2</sup> PER PANEL)	1.378m <sup>2</sup>
PACKAGING (PIECES PER PACK)	2 [2.757m <sup>2</sup> ]

 CAN BE INSTALLED HORIZONTALLY OR VERTICALLY.

## CASTINGWOOD SPECS

### EX SERIES 3030

DIMENSIONS (ACTUAL MM)	455mm x 3030mm
THICKNESS (ACTUAL MM)	16mm
WEIGHT (KGS. PER PANEL)	26kg/piece
WEIGHT (KGS. PER M <sup>2</sup> )	18.8kg/m <sup>2</sup>
EXPOSED COVERAGE (M <sup>2</sup> PER PANEL)	1.378m <sup>2</sup>
PACKAGING (PIECES PER PACK)	2 [2.757m <sup>2</sup> ]

 CAN BE INSTALLED HORIZONTALLY OR VERTICALLY.

Find imperfect perfection with

# THE CONCRETE SERIES



**DETROIT PISTONS**  
PERFORMANCE CENTER

---

## Put a fresh face on industrial chic with fiber cement.

Take back your time with the Nichiha Concrete Series. Designed to mimic the natural texture of concrete, our three panels offer distinct textures and styles to fit your creative vision. Plus, with the power of fiber cement, you can enjoy the look and feel of concrete without the curing times, cracking or color inconsistency.

IndustrialBlock offers a distressed design with all the irregularities and characteristics of natural concrete. It can pair seamlessly with a wide range of products, whether you are aiming for a modern or vintage vibe. EmpireBlock delivers the look and feel of precast concrete block with a modern twist. Perfect for indoor environments as well as exterior cladding, it features a unique dimple that defines the look of industrial chic.

## EMPIREBLOCK



EPC432□X

### EMPIREBLOCK SPECS

### EX SERIES 3030

DIMENSIONS (ACTUAL MM)	455mm x 3030mm
THICKNESS (ACTUAL MM)	16mm
WEIGHT (KGS. PER PANEL)	26kg/piece
WEIGHT (KGS. PER M <sup>2</sup> )	18.8kg/m <sup>2</sup>
EXPOSED COVERAGE (M <sup>2</sup> PER PANEL)	1.378m <sup>2</sup>
PACKAGING (PIECES PER PACK)	2 [2.757m <sup>2</sup> ]



CAN BE INSTALLED HORIZONTALLY OR VERTICALLY.

## INDUSTRIALBLOCK



EQS291□X / EPC601□X



Want the concrete look without the dimples?  
Check out our IndustrialBlock panel.

### INDUSTRIALBLOCK SPECS

### EX SERIES 1820

DIMENSIONS (ACTUAL MM)	455mm x 1820mm
THICKNESS (ACTUAL MM)	16mm
WEIGHT (KGS. PER PANEL)	16kg/piece
WEIGHT (KGS. PER M <sup>2</sup> )	20.5kg/m <sup>2</sup>
EXPOSED COVERAGE (M <sup>2</sup> PER PANEL)	0.828m <sup>2</sup>
PACKAGING (PIECES PER PACK)	2 [1.656m <sup>2</sup> ]



NOTE: CAN ONLY BE INSTALLED HORIZONTALLY.

### EX SERIES 3030

DIMENSIONS (ACTUAL MM)	455mm x 3030mm
THICKNESS (ACTUAL MM)	16mm
WEIGHT (KGS. PER PANEL)	26kg/piece
WEIGHT (KGS. PER M <sup>2</sup> )	18.8kg/m <sup>2</sup>
EXPOSED COVERAGE (M <sup>2</sup> PER PANEL)	1.378m <sup>2</sup>
PACKAGING (PIECES PER PACK)	2 [2.757m <sup>2</sup> ]



CAN BE INSTALLED HORIZONTALLY OR VERTICALLY.

## RCWALL16



ELG731□X

### RCWALL16 SPECS

### EX SERIES 3030

DIMENSIONS (ACTUAL MM)	455mm x 3030mm
THICKNESS (ACTUAL MM)	16mm
WEIGHT (KGS. PER PANEL)	26kg/piece
WEIGHT (KGS. PER M <sup>2</sup> )	18.8kg/m <sup>2</sup>
EXPOSED COVERAGE (M <sup>2</sup> PER PANEL)	1.378m <sup>2</sup>
PACKAGING (PIECES PER PACK)	2 [2.757m <sup>2</sup> ]



CAN BE INSTALLED HORIZONTALLY OR VERTICALLY.

# Bring the classic to the present with THE BRICK SERIES



---

## Get a timeless brick finish without the traditional hassle.

The slight variations in color, the stately good looks, the grout lines — it's all there in the Nichiha Brick Series. Thanks to a proprietary multi-layered coating process, the beauty of brick is built to last in these fiber cement panels. With various finishes and colors, you have the freedom to create the brick building of your choice without the extra cost or hassle. These panels really do have it all; however, we did leave out the tons of weight and the extra time required to see your project to completion.



## PLYMOUTHBRICK



EPF151□X



Get the classic look of kiln-fired brick with the modern strength of PlymouthBrick panels.

## MODERNBRICK



EPF791□US

### PLYMOUTHBRICK SPECS

### EX SERIES 1818

DIMENSIONS (ACTUAL MM)	455mm x 1818mm
THICKNESS (ACTUAL MM)	16mm
WEIGHT (KGS. PER PANEL)	16kg/piece
WEIGHT (KGS. PER M <sup>2</sup> )	19.3kg/m <sup>2</sup>
EXPOSED COVERAGE (M <sup>2</sup> PER PANEL)	0.827m <sup>2</sup>
PACKAGING (PIECES PER PACK)	2 [1.654m <sup>2</sup> ]

 NOTE: CAN ONLY BE INSTALLED HORIZONTALLY.

### MODERNBRICK SPECS

### EX SERIES 1818

DIMENSIONS (ACTUAL MM)	455mm x 1818mm
THICKNESS (ACTUAL MM)	16mm
WEIGHT (KGS. PER PANEL)	16kg/piece
WEIGHT (KGS. PER M <sup>2</sup> )	19.3kg/m <sup>2</sup>
EXPOSED COVERAGE (M <sup>2</sup> PER PANEL)	0.827m <sup>2</sup>
PACKAGING (PIECES PER PACK)	2 [1.654m <sup>2</sup> ]

 NOTE: CAN ONLY BE INSTALLED HORIZONTALLY.


## SHADEBRICK



EPB321□X



EPB324□X



EPB322□X

### SHADEBRICK SPECS

### EX SERIES 3030

DIMENSIONS (ACTUAL MM)	455mm x 3030mm
THICKNESS (ACTUAL MM)	16mm
WEIGHT (KGS. PER PANEL)	26kg/piece
WEIGHT (KGS. PER M <sup>2</sup> )	18.8kg/m <sup>2</sup>
EXPOSED COVERAGE (M <sup>2</sup> PER PANEL)	1.378m <sup>2</sup>
PACKAGING (PIECES PER PACK)	2 [2.757m <sup>2</sup> ]



Gain rock solid solutions with  
**THE MASONRY SERIES**

---

## Get the beauty of stone for a fraction of the price.

Nichiha's Masonry Series makes grandeur attainable for every situation. Offering a distinct finish, this series of stone panels is as elegant as it is affordable.

With its subtle color and deep texture, our Masonry Series adds a traditional design aesthetic to any commercial building. This finish goes up in a fraction of the time required by a crew of masonry contractors. Plus, with various textures and colors, you have even more possibilities for customization - all backed by the power of fiber cement.

## LEBON



EFF101□X



EFF102□X



EFF106□X



EFF104□X



EFF107□X

## MUSTERSTONE



EQG6221□X



EQG6222□X



EQG6223□X

## LEBON SPECS

## EX SERIES 1820

DIMENSIONS (ACTUAL MM)	455mm x 1820mm
THICKNESS (ACTUAL MM)	16mm
WEIGHT (KGS. PER PANEL)	16kg/piece
WEIGHT (KGS. PER M <sup>2</sup> )	20.5kg/m <sup>2</sup>
EXPOSED COVERAGE (M <sup>2</sup> PER PANEL)	0.828m <sup>2</sup>
PACKAGING (PIECES PER PACK)	2 [1.656m <sup>2</sup> ]

 NOTE: CAN ONLY BE INSTALLED HORIZONTALLY.

## MUSTERSTONE SPECS


## EX SERIES 3030











DIMENSIONS (ACTUAL MM)	455mm x 3030mm
THICKNESS (ACTUAL MM)	16mm
WEIGHT (KGS. PER PANEL)	26kg/piece
WEIGHT (KGS. PER M <sup>2</sup> )	18.8kg/m <sup>2</sup>
EXPOSED COVERAGE (M <sup>2</sup> PER PANEL)	1.378m <sup>2</sup>
PACKAGING (PIECES PER PACK)	2 [2.757m <sup>2</sup> ]

# THE DETAILS MAKE THE DESIGN.

Make your project stand out with our Essential Flashing System.


In architectural design, every detail counts. Our Essential Flashing System is designed to help you remember even the smallest part so you can easily complete your project with the highest level of precision. It includes the Nichiha accessories needed to complete the fiber cement installation system and create a clean, polished look for your building.



					<b>COMPRESSION JOINT FLASHING</b>	FTA□	
					<b>OVERHANG FLASHING</b>	JOH725□	
	<b>OVERHANG FLASHING OUTSIDE CORNER</b>	<b>OVERHANG FLASHING INSIDE CORNER</b>	<b>OVERHANG FLASHING ENDCAP</b>	<b>OVERHANG FLASHING CLIP</b>		JOH725□S	
	JOH725□B	JOH725□D	JOH725□C				
				<b>STARTER FLASHING</b>	<b>STARTER FLASHING OUTSIDE CORNER</b>	<b>STARTER FLASHING INSIDE CORNER</b>	<b>OVERHANG FLASHING ENDCAP</b>
	FTD475□B	FTD475□D	FTD475□C	FTD475□			

NOTE: EACH COMPONENT OF THE ESSENTIAL FLASHING SYSTEM IS SOLD SEPARATELY.

Nichiha takes accessory protection to the next level with a **removable film layer**. Once installed, simply peel off the film to reveal blemish-free fixtures.



**Our starter flashing serves a dual role** — ensuring your project is polished to perfection and operating as a bug screen to keep annoying pests away.

# NEVER FORGET THE LITTLE THINGS AGAIN.

Our installation hardware and accessories easily take your vision from the drawing board to reality.



**ULTIMATE CLIP II WITH JOINT TAB ATTACHMENT - JEL778**

THICKNESS	10mm
PACKAGING (PCS PER BOX)	30



**ULTIMATE HORIZONTAL STARTER TRACK - FA700**

THICKNESS	10mm
PACKAGING (PCS PER BOX)	10




**ULTIMATE VERTICAL STARTER TRACK - FA710T**

THICKNESS	10mm
PACKAGING (PCS PER BOX)	10



**SINGLE FLANGE SEALANT BACKER - FHK1015R**

THICKNESS	10mm
PACKAGING (PCS PER BOX)	10



**DOUBLE FLANGE SEALANT BACKER - FH1015R**

THICKNESS	10mm
PACKAGING (PCS PER BOX)	10



**SPACER FSP1005**

THICKNESS (FSP1005)	5mm
PACKAGING (PCS PER BOX)	50



**EAVES TRIM FTM11**

LENGTH	L=3030mm
PACKAGING (PCS PER PACK)	10



**L-FORM CAVITY VENT FSK1000**

LENGTH	L=1220mm
PACKAGING (PCS PER BOX)	10



**CORNERS**

HORIZONTAL	16 x 80 x 80x 455mm
PACKAGING (PCS PER BOX)	6
VERTICAL	16 x 80 x 80 x 3030mm
PACKAGING (PCS PER BOX)	4

# Behind our EX Series is SOME SERIOUS TECHNOLOGY.

## ✓ EASY INSTALLATION

Time-saving clip installation system that reduces construction time and minimizes mistakes.



## NO MORTAR, NO MESS

Prefinished panels eliminate the need for messy mortar or costly masonry-skilled labor.



## ANY WEATHER PRODUCT

Products can be installed year round in any climate across the country. No geographical restrictions means more possibilities.



## LOW MAINTENANCE

No-fuss products. Little ongoing cleaning or regular maintenance needed. Bring your vision to life and ensure it looks great for years to come.



## ENGINEERED FOR PERFORMANCE


Go beyond our durable panels and discover a meticulously engineered moisture management system that provides a vertical drainage point for air and moisture to exit.

### THE ULTIMATE CLIP

creates a hidden fastening system that all but eliminates face fastening. Installation is quick and easy and never requires speciality subcontractors.

### NICHIHA EX SERIES PANELS

are lightweight, easy to handle and available in a virtually endless color palette and a diverse offering of textural finishes.



### NICHIHA'S JOINT TAB ATTACHMENT

is designed to support panel lateral stability, helping vertical joints stay tightly closed. The tab fits in place easily and is fastened to the Ultimate Clip with provided screw.

### DRAINED AND BACK-VENTILATED RAINSCREEN

design allows water to escape and air to circulate, reducing the risk of mold and water damage inside the building.

### THE ULTIMATE STARTER TRACK

pulls double-duty. It ensures a fast, level installation, and its patented drainage channel directs water out and away from the base of the wall.



EX 1818/1820 in DESIGNER SERIES and MODERN SERIES can be horizontally installed not only in a stacked bond application but also in a staggered bond application.

---

# THE POWER OF POSSIBILITIES AND PARTNERSHIPS

Your creative vision is unique. That's why Nichiha offers you the power of cooperation to help your project move from conception to completion. Our ever-expanding offering of textures and finishes lifts buildings to new and unexpected places, and we want to share them with you. We place a high value on our relationships and are proud to work with our dedicated partners across the country. Join us to discover the power of possibilities and partnerships with Nichiha.



TSUKAMOTO BUILDING 1-6-5 NIHONBASHI HONCHO, CHUO-KU, TOKYO, 103-0023. JAPAN  
NOTE: Printed material may not accurately depict actual product color.



EU2109CTEB ■